



3 hours compliant bulkhead emergency light

Emergency Light LED Bulkhead

Safety is important for building owners, and therefore having proper emergency lighting in place is a major concern for them. The Emergency bulkhead EM121C offers an easy solution for stand-alone emergency lighting, with maintained/non-maintained mode which leave the choices by customers. The lithium battery (LiFePO4) has many advantages over nickel-based products, as it has a longer lifetime, better discharge behaviors, is produced in a more welfare friendly way and can be recycled.

Benefits

- Welfare friendly solution versus nickel-based products as the battery can be recycled
- Lithium based battery type provides longer lifetime
- low self-discharge and high temperature tolerance

Features

- 3 hours battery duration when full charged
- Self-test function
- LFP is designed environmental friendly
- Maintained or non-maintained mode selection

Application

- Airports
- Offices
- Retail

Specifications

Emergency Light LED Bulkhead

Mounting type	Recessed/Surface/Ceiling
Operating Temperature range	0 to +45°C
Light Source	LED
Mains Voltage	220-240V/50-60Hz
Emergency lighting	Emergency lighting Pro 3hrs
Material	Housing: ABS/Cover: PC
Main color of the luminaire	RAL 9003

Ingress protection	IP40
Light source replaceable	No
Overall height	63mm
Overall length	355mm
Overall width	111mm
Installation	surface/ceiling/recessed

Versions



Emergency Light Bulkhead

Product details




Emergency Light Bulkhead



Emergency Light Bulkhead



Emergency Light Bulkhead



Emergency Light Bulkhead

Emergency Light LED Bulkhead

