



# Philips Uni Posttop: Urban street light targets at residential areas, pathways, plazas, etc.

## Uni Posttop

The modern shaped post top attracts customers' attention with its unique, streamlined design. The fixture distributes soft and homogeneous light to pathways, residential areas thanks to the application of the reflector. Various quality test based on Philips standards offers robustness not only to its design but also functionality, delivering table and outstanding performance to customers.

### Benefits

- Modern streamlined design fits various application scenarios, i.e., residential areas, pathways, plazas.
- Robust design ensures both appearance classy and quality stability.
- Soft lighting due to the application of alumina reflector.


### Features

- Excellent thermal management
- Optimized optics for efficient and comfortable lighting levels
- Injection die-casting aluminum body
- High- quality PC diffuser

Application

- Road and Street
- Parks and Plazas
- Residential
- Main urban roads and streets, side and residential roads and streets
- City centers and historical areas
- Cycle and pedestrian paths, squares, parks and playgrounds

Dimensional drawing



General Information	
Driver included	Yes
Light Technical	
Light source color	740 neutral white
Correlated Color Temperature (Nom)	4000 K
Color rendering index (CRI)	70
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Optical cover type	Polycarbonate bowl/cover clear
Housing Color	Gray
Mech. impact protection code	IK08
Ingress protection code	IP65
Approval and Application	
CE mark	Yes

Light Technical

Order Code	Full Product Name	Luminous Flux
911401696508	BDS400 LED NW 220V 30W WB PSU 7012	4,200 lm
911401696608	BDS400 LED NW 220V 60W WB PSU 7012	8,400 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401696508	BDS400 LED NW 220V 30W WB PSU 7012	30 W

Order Code	Full Product Name	Power Consumption
911401696608	BDS400 LED NW 220V 60W WB PSU 7012	60 W

