



Your everyday LEDspot GU10

Essential LEDspot GU10

Essential LEDspots are compatible with most existing fixtures with a GU10 socket and are designed as a retrofit replacement for halogen spots. Essential LEDspots deliver significant energy savings and minimize initial investment.

Benefits

- Up to 90% energy saving compared with traditional halogen lamps
- Lower maintenance costs
- Low initial investment

Features


- Easy retrofit
- Lifetime up to 15,000 hours
- Non-dimmable
- UV- and IR-free light

Application

- Domestic applications

Essential LEDspot GU10

Dimensional drawing




Product	D	C
LEDspot50W GU10Kit_S 827 100-240V 36D PF	50 mm	54 mm
LEDspot50W GU10Kit_S 865 100-240V 36D PF	50 mm	54 mm

General Information	
Cap-Base	GU10
Switching Cycle	50,000
Nominal lifetime	15,000 hour(s)
Light Technical	
Beam Angle (Nom)	36 degree(s)
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Luminous Flux	350 lm
Luminous Intensity (Nom)	600 cd
Operating and Electrical	
Input Frequency	50 to 60 Hz
Line Frequency	50 to 60 Hz
Power Consumption	5 W
Starting Time (Nom)	0.5 s
Wattage Equivalent	50 W
Temperature	
T-Case Maximum (Nom)	75 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Shape	PAR16


Light Technical

		Correlated Color Temperature	
Order Code	Full Product Name	(Nom)	Color Code
929001971061	LEDspot50W GU10Kit_S 865 100-240V 36D PF	6500 K	865
929001971161	LEDspot50W GU10Kit_S 827 100-240V 36D PF	2700 K	827




Essential LEDspot GU10

Accent Diagrams



Accent Diagram - LEDspot50W GU10Kit_S 827
100-240V 36D PF

Beam Diagrams



Beam diagram - LEDspot50W GU10Kit_S 827
100-240V 36D PF

