



Strong performance spot light for retrofit MR16 halogen spots

MASTER LEDspot LV

Delivering intense accent beam, MASTER LEDspot LV is an ideal retrofit solution for spot lighting. MASTER LEDspot LV is designed to replace halogen or incandescent spots. It realizes natural colors, enables cozy and comfortable ambience for residential, hospitality and emphasizes the beauty of merchandise in retail. New smaller housing provides perfect fitting with majority of luminaires in a market with a MR16 GU 5.3 holder. It not only employs Philips' patented solution to guarantee the broadest possible compatibility with standard 12V halogen electronic transformers, it also delivers high beam intensity which is equivalent to halogen MR16 spots. The dimming function enables to create the desired atmosphere and it works with broad selection of dimmers. Its high SDCM ensure stricter color consistency, that is maintained over product life. MASTER LEDspot LV delivers huge energy savings and minimizes maintenance cost without any compromise on light quality and lifetime, enabling residential and business owners to achieve a return on their investment within short period time.

Benefits

- High intensity of beam for accent lighting in professional applications
- Strong brightness maintained over time
- More natural colors realised for cozy ambience for hospitality and better merchandise display in retail application

MASTER LEDspot LV


Features

- High intensity of beam equivalent to halogen spots
- Better color realisation with high CRI value, and strong color consistency over time
- Clearly defined beam spread for accent lighting
- Compatible with an extensive range of transformers and smooth dimming for dimmable products
- High lumen maintenance with long lifetime up to 40,000 hours

Application

- Home: Living room, bed room, hall way
- Hospitality: Hotel guest room, corridors, lobby, reception area, restaurant, bars, cafes
- Retail: Exhibitions, display cabinets, shops, dressing room, check out area

Dimensional drawing



Product	D	C
MASTER LED 6.5-50W 927 MR16 36D Dim	50 mm	
MASTER LED 6.5-50W 930 MR16 24D Dim	50 mm	46.5 mm
MASTER LED 6.5-50W 930 MR16 24D ND	50.5 mm	46.5 mm
MASTER LED 6.5-50W 930 MR16 36D Dim	50 mm	46.5 mm

General Information	
Cap-Base	GU5.3
Switching Cycle	50,000
Nominal lifetime	40,000 hour(s)
Light Technical	
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	- Hz
Line Frequency	- Hz
Power Consumption	6.5 W
Starting Time (Nom)	0.5 s
Wattage Equivalent	50 W
Temperature	
T-Case Maximum (Nom)	90 °C
Mechanical and Housing	
Bulb Shape	MR16

Light Technical (1/2)

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color Temperature (Nom)	Color Code	Luminous Flux
929001882008	MASTER LED 6.5-50W 930 MR16 24D ND	24 degree(s)	3000 K	930	470 lm
929003072008	MASTER LED 6.5-50W 930 MR16 24D Dim	24 degree(s)	3000 K	930	500 lm
929003072208	MASTER LED 6.5-50W 927 MR16 36D Dim	36 degree(s)	2700 K	927	500 lm
929003072308	MASTER LED 6.5-50W 930 MR16 36D Dim	36 degree(s)	3000 K	930	500 lm

Light Technical (2/2)

MASTER LEDspot LV

Order Code	Full Product Name	Luminous Intensity (Nom)
929001882008	MASTER LED 6.5-50W 930 MR16 24D ND	2,300 cd
929003072008	MASTER LED 6.5-50W 930 MR16 24D Dim	2,800 cd

Controls and Dimming


Order Code	Full Product Name	Dimmable
929001882008	MASTER LED 6.5-50W 930 MR16 24D ND	No
929003072008	MASTER LED 6.5-50W 930 MR16 24D Dim	Only with specific dimmers

Mechanical and Housing

Order Code	Full Product Name	Bulb Finish
929001882008	MASTER LED 6.5-50W 930 MR16 24D ND	Clear
929003072008	MASTER LED 6.5-50W 930 MR16 24D Dim	-

Approval and Application


Order Code	Full Product Name	Ambient temperature range
929001882008	MASTER LED 6.5-50W 930 MR16 24D ND	-20 °C to 45 °C
929003072008	MASTER LED 6.5-50W 930 MR16 24D Dim	-
929003072208	MASTER LED 6.5-50W 927 MR16 36D Dim	-
929003072308	MASTER LED 6.5-50W 930 MR16 36D Dim	-




Order Code	Full Product Name	Luminous Intensity (Nom)
929003072208	MASTER LED 6.5-50W 927 MR16 36D Dim	1,400 cd
929003072308	MASTER LED 6.5-50W 930 MR16 36D Dim	1,600 cd

Order Code	Full Product Name	Dimmable
929003072208	MASTER LED 6.5-50W 927 MR16 36D Dim	Only with specific dimmers
929003072308	MASTER LED 6.5-50W 930 MR16 36D Dim	Only with specific dimmers


Order Code	Full Product Name	Bulb Finish
929003072208	MASTER LED 6.5-50W 927 MR16 36D Dim	-
929003072308	MASTER LED 6.5-50W 930 MR16 36D Dim	-




Accent Diagrams




Accent Diagram - MASTER LED 6.5-50W 930
MR16 24D Dim



Accent Diagram - MASTER LED 6.5-50W 930
MR16 36D Dim




Accent Diagram - MASTER LED 6.5-50W 927
MR16 36D Dim




Accent Diagram - MASTER LED 6.5-50W 930
MR16 24D ND


Beam Diagrams



Beam diagram - MASTER LED 6.5-50W 930
MR16 36D Dim




Beam diagram - MASTER LED 6.5-50W 930
MR16 24D ND



Beam diagram - MASTER LED 6.5-50W 927
MR16 36D Dim

Beam Diagrams



Beam diagram - MASTER LED 6.5-50W 930
MR16 24D Dim

