



Strong performance spot light for retrofit MR16 halogen spots

MASTER LEDspot LV

Delivering intense accent beam, MASTER LEDspot LV is an ideal retrofit solution for spot lighting. MASTER LEDspot LV is designed to replace halogen or incandescent spots. It realizes natural colors, enables cozy and comfortable ambience for residential, hospitality and emphasizes the beauty of merchandise in retail. New smaller housing provides perfect fitting with majority of luminaires in a market with a MR16 GU 5.3 holder. It not only employs Philips' patented solution to guarantee the broadest possible compatibility with standard 12V halogen electronic transformers, it also delivers high beam intensity which is equivalent to halogen MR16 spots. The dimming function enables to create the desired atmosphere and it works with broad selection of dimmers. Its high SDCM ensure stricter color consistency, that is maintained over product life. MASTER LEDspot LV delivers huge energy savings and minimizes maintenance cost without any compromise on light quality and lifetime, enabling residential and business owners to achieve a return on their investment within short period time.

Benefits

- High intensity of beam for accent lighting in professional applications
- Strong brightness maintained over time
- More natural colors realised for cozy ambience for hospitality and better merchandise display in retail application

MASTER LEDspot LV


Features

- High intensity of beam equivalent to halogen spots
- Better color realisation with high CRI value, and strong color consistency over time
- Clearly defined beam spread for accent lighting
- Compatible with an extensive range of transformers and smooth dimming for dimmable products
- High lumen maintenance with long lifetime up to 40,000 hours

Application

- Home: Living room, bed room, hall way
- Hospitality: Hotel guest room, corridors, lobby, reception area, restaurant, bars, cafes
- Retail: Exhibitions, display cabinets, shops, dressing room, check out area

Dimensional drawing



Product	D	C
MASTER LED 6.5-50W 927 MR16 24D Dim	50 mm	
MASTER LED 6.5-50W 927 MR16 36D Dim	50 mm	
MASTER LED 6.5-50W 927 MR16 60D Dim	50 mm	46.5 mm
MASTER LED 6.5-50W 930 MR16 24D Dim	50 mm	46.5 mm
MASTER LED 6.5-50W 930 MR16 36D Dim	50 mm	46.5 mm
MASTER LED 6.5-50W 930 MR16 60D Dim	50 mm	46.5 mm
MASTER LED 6.5-50W 940 MR16 24D Dim	50 mm	46.5 mm
MASTER LED 6.5-50W 940 MR16 36D Dim	50 mm	46.5 mm
MASTER LED 6.5-50W 940 MR16 60D Dim	50 mm	46.5 mm
MASTER LED 7.5-50W+ 827 MR16 36D Dim	50 mm	46.5 mm
MASTER LED 7.5-50W+ 830 MR16 36D Dim	50 mm	46.5 mm

General Information

Cap-Base	GU5.3
Switching Cycle	50,000
Nominal lifetime	40,000 hour(s)

Light Technical

LLMF At End Of Nominal Lifetime (Nom)	70 %
---------------------------------------	------

Operating and Electrical

Input Frequency	- Hz
Line Frequency	- Hz
Starting Time (Nom)	0.5 s
Wattage Equivalent	50 W

Controls and Dimming

Dimmable	Only with specific dimmers
----------	----------------------------

Mechanical and Housing

Bulb Shape	MR16
------------	------

Light Technical (1/2)

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Color Code
929003071908	MASTER LED 6.5-50W 927 MR16 24D Dim	24 degree(s)	2700 K	90	927
929003072008	MASTER LED 6.5-50W 930 MR16 24D Dim	24 degree(s)	3000 K	90	930
929003072108	MASTER LED 6.5-50W 940 MR16 24D Dim	24 degree(s)	4000 K	90	940
929003072208	MASTER LED 6.5-50W 927 MR16 36D Dim	36 degree(s)	2700 K	90	927
929003072308	MASTER LED 6.5-50W 930 MR16 36D Dim	36 degree(s)	3000 K	90	930
929003072408	MASTER LED 6.5-50W 940 MR16 36D Dim	36 degree(s)	4000 K	90	940
929003072708	MASTER LED 7.5-50W+ 827 MR16 36D Dim	36 degree(s)	2700 K	80	827
929003072808	MASTER LED 7.5-50W+ 830 MR16 36D Dim	36 degree(s)	3000 K	80	830

MASTER LEDspot LV

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Color Code
929003075908	MASTER LED 6.5-50W 927 MR16 60D Dim	60 degree(s)	2700 K	90	927
929003076008	MASTER LED 6.5-50W 930 MR16 60D Dim	60 degree(s)	3000 K	90	930
929003076108	MASTER LED 6.5-50W 940 MR16 60D Dim	60 degree(s)	4000 K	90	940

Light Technical (2/2)

Order Code	Full Product Name	Luminous Flux	Luminous Intensity (Nom)
929003071908	MASTER LED 6.5-50W 927 MR16 24D Dim	500 lm	2,800 cd
929003072008	MASTER LED 6.5-50W 930 MR16 24D Dim	500 lm	2,800 cd
929003072108	MASTER LED 6.5-50W 940 MR16 24D Dim	530 lm	3,400 cd
929003072208	MASTER LED 6.5-50W 927 MR16 36D Dim	500 lm	1,400 cd
929003072308	MASTER LED 6.5-50W 930 MR16 36D Dim	500 lm	1,600 cd
929003072408	MASTER LED 6.5-50W 940 MR16 36D Dim	530 lm	1,600 cd

Order Code	Full Product Name	Luminous Flux	Luminous Intensity (Nom)
929003072708	MASTER LED 7.5-50W+ 827 MR16 36D Dim	660 lm	1,700 cd
929003072808	MASTER LED 7.5-50W+ 830 MR16 36D Dim	660 lm	1,700 cd
929003075908	MASTER LED 6.5-50W 927 MR16 60D Dim	500 lm	500 cd
929003076008	MASTER LED 6.5-50W 930 MR16 60D Dim	500 lm	500 cd
929003076108	MASTER LED 6.5-50W 940 MR16 60D Dim	530 lm	550 cd


Operating and Electrical

Order Code	Full Product Name	Power Consumption
929003071908	MASTER LED 6.5-50W 927 MR16 24D Dim	6.5 W
929003072008	MASTER LED 6.5-50W 930 MR16 24D Dim	6.5 W
929003072108	MASTER LED 6.5-50W 940 MR16 24D Dim	6.5 W
929003072208	MASTER LED 6.5-50W 927 MR16 36D Dim	6.5 W
929003072308	MASTER LED 6.5-50W 930 MR16 36D Dim	6.5 W
929003072408	MASTER LED 6.5-50W 940 MR16 36D Dim	6.5 W









Order Code	Full Product Name	Power Consumption
929003072708	MASTER LED 7.5-50W+ 827 MR16 36D Dim	7.5 W
929003072808	MASTER LED 7.5-50W+ 830 MR16 36D Dim	7.5 W
929003075908	MASTER LED 6.5-50W 927 MR16 60D Dim	6.5 W
929003076008	MASTER LED 6.5-50W 930 MR16 60D Dim	6.5 W
929003076108	MASTER LED 6.5-50W 940 MR16 60D Dim	6.5 W

Temperature


Order Code	Full Product Name	T-Case Maximum (Nom)
929003071908	MASTER LED 6.5-50W 927 MR16 24D Dim	90 °C
929003072008	MASTER LED 6.5-50W 930 MR16 24D Dim	90 °C
929003072108	MASTER LED 6.5-50W 940 MR16 24D Dim	90 °C
929003072208	MASTER LED 6.5-50W 927 MR16 36D Dim	90 °C
929003072308	MASTER LED 6.5-50W 930 MR16 36D Dim	90 °C
929003072408	MASTER LED 6.5-50W 940 MR16 36D Dim	90 °C
929003072708	MASTER LED 7.5-50W+ 827 MR16 36D Dim	93 °C
929003072808	MASTER LED 7.5-50W+ 830 MR16 36D Dim	93 °C
929003075908	MASTER LED 6.5-50W 927 MR16 60D Dim	90 °C
929003076008	MASTER LED 6.5-50W 930 MR16 60D Dim	90 °C
929003076108	MASTER LED 6.5-50W 940 MR16 60D Dim	90 °C




MASTER LEDspot LV




Accent Diagrams




Accent Diagram - MASTER LED 6.5-50W 930
MR16 24D Dim




Accent Diagram - MASTER LED 6.5-50W 930
MR16 36D Dim




Accent Diagram - MASTER LED 6.5-50W 927
MR16 24D Dim




Accent Diagram - MASTER LED 6.5-50W 940
MR16 36D Dim




Accent Diagram - MASTER LED 6.5-50W 940
MR16 24D Dim




Accent Diagram - MASTER LED 7.5-50W+ 827
MR16 36D Dim



Accent Diagram - MASTER LED 6.5-50W 927
MR16 36D Dim




Accent Diagram - MASTER LED 6.5-50W 927
MR16 60D Dim




Accent Diagram - MASTER LED 6.5-50W 940
MR16 60D Dim


Beam Diagrams




Beam diagram - MASTER LED 6.5-50W 940
MR16 36D Dim




Beam diagram - MASTER LED 6.5-50W 930
MR16 36D Dim




Beam diagram - MASTER LED 6.5-50W 927
MR16 60D Dim




Beam diagram - MASTER LED 6.5-50W 927
MR16 24D Dim




Beam diagram - MASTER LED 6.5-50W 940
MR16 24D Dim




Beam diagram - MASTER LED 7.5-50W+ 827
MR16 36D Dim



Beam diagram - MASTER LED 6.5-50W 927
MR16 36D Dim



Beam diagram - MASTER LED 6.5-50W 930
MR16 24D Dim



Beam diagram - MASTER LED 6.5-50W 940
MR16 60D Dim

MASTER LEDspot LV

