



The best LED solution for High Intensity Discharge (HID) lamp replacement

TrueForce LED Industrial and retail Mains (Highbay – HPI/SON/HPL)

Philips MASTER – LED HID HPI EM/Mains Highbay lamps give you a quick and easy payback solution to replace HID alternatives in high-bay applications. MASTER – LED HID HPI EM/Mains solutions give you the LED benefits of energy efficiency and a long lifetime with a retrofit solution. The design of MASTER – LED HID HPI EM/Mains enables the direct retrofit of HID lamps without changing the fixtures or EM ballast (see installation guide for more info). The MASTER – LED HID HPI EM/Mains lamp is compatible with both 250W and 400W EM ballast to maximize the feasibility of such retrofits.

Benefits

- Cost saving with short payback time
- Low initial investment
- Enhance lighting quality with easy adoption

Features

- High Energy efficient lamps
- Long lifetime – 50,000 hrs
- Surge protection 4KV
- Direct lamp replacement solution without changing the fixture or EM ballast
- Compatible with 250W and 400W EM gear systems
- Additional Energy saving by Direct Mains connection
- Pleasant white light with CRI 80

TrueForce LED Industrial and retail Mains (Highbay – HPI/SON/HPL)

Application


- Industrial/retail – warehouses, factories, shops, transport hubs

Versions



LEDTForce HPI Others E40

Dimensional drawing



Product	D	C
TForce HB 140W E40 865 WB GM	250 mm	290 mm



TrueForce LED Industrial and retail Mains (Highbay – HPI/SON/HPL)

