



Classic LED filament lamps for decorative lighting

Classic filament LED candles and lusters

Featuring a classic heritage design, Classic filament LED candles and lusters combine the familiar shapes of classic incandescent candle or luster with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light candles and lusters.

Benefits

- Around 90% energy saving
- Very long lifetime that reduces the need for replacement
- Easy replacement of classic conventional lamps

Features

- Heritage design with classic shape
- Designed to be seen, they look good on and off
- Perfect fit and high quality finishing
- High color rendering (CRI above 80) for vivid colors
- Environmentally friendly: contains no mercury or other hazardous substances

Application

- Perfect for decorative installations
- Domestic applications
- Hospitality: restaurants and hotels

Classic filament LED candles and lusters

Versions




LEDclassic 40W B35 E14 CL
WGD90 SRT4 1




LEDclassic 40W P45 E27 CL
WGD90 SRT4 1

Dimensional drawing



| Product | D | C |
|--------------------------------------|-------|-------|
| LEDclassic 40W B35 2700K E14 D CL AU | 35 mm | 97 mm |



| Product | D | C |
|--------------------------------------|-------|-------|
| LEDclassic 40W P45 2700K E27 D CL AU | 45 mm | 78 mm |

Classic filament LED candles and lusters

General Information

| | |
|------------------------|----------------|
| Rated Lifetime (Hours) | 15,000 hour(s) |
| Switching Cycle | 20,000 |
| Nominal lifetime | 15,000 hour(s) |

Light Technical

| | |
|---------------------------------------|--------|
| Correlated Color Temperature (Nom) | 2700 K |
| Color rendering index (CRI) | 90 |
| Color Code | 927 |
| LLMF At End Of Nominal Lifetime (Nom) | 70 % |
| Luminous Flux | 470 lm |

Operating and Electrical

| | |
|---------------------|-------------|
| Input Frequency | 50 to 60 Hz |
| Power Consumption | 3.5 W |
| Starting Time (Nom) | 0.5 s |
| Wattage Equivalent | 40 W |

Temperature

| | |
|----------------------|-------|
| T-Case Maximum (Nom) | 70 °C |
|----------------------|-------|

Controls and Dimming

| | |
|----------|----------------------------|
| Dimmable | Only with specific dimmers |
|----------|----------------------------|

Mechanical and Housing

| | |
|-------------|-------|
| Bulb Finish | Clear |
|-------------|-------|

Approval and Application

| | |
|-------------------------------|---------------|
| Ambient temperature range | -20 to +45 °C |
| Energy Consumption kWh/1000 h | 4 kWh |

General Information

| Order Code | Full Product Name | Cap-Base |
|--------------|--------------------------------------|----------|
| 929003012279 | LEDclassic 40W B35 2700K E14 D CL AU | E14 |
| 929003013279 | LEDclassic 40W P45 2700K E27 D CL AU | E27 |

Mechanical and Housing

| Order Code | Full Product Name | Bulb Shape |
|--------------|--------------------------------------|------------|
| 929003012279 | LEDclassic 40W B35 2700K E14 D CL AU | B35 |
| 929003013279 | LEDclassic 40W P45 2700K E27 D CL AU | P45 |



Classic filament LED candles and lusters

