



Great energy efficient LED Waterproof

Essential LED Waterproof

The Essential LED Waterproof is a highly efficient LED waterproof at a very competitive price.

Benefits

- Philips great quality and reliability
- Long lifetime
- Energy efficient

Features

- Robust and waterproof luminaire
- Multiple light levels and colour temperatures available
- Steel clips ensure extra product robustness

Application

- Manufacturing
- Parking Garages
- Warehouses



Essential LED Waterproof

Versions



Essential LED Waterproof

Dimensional drawing



Essential LED Waterproof

General Information	
Driver included	Yes
Lamp family code	-
Light source replaceable	No
Light Technical	
Color rendering index (CRI)	≥80
Operating and Electrical	
Protection class IEC	Safety class I
Input Voltage	100 to 277 V
Line Frequency	50 or 60 Hz
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Housing Color	Gray
Mech. impact protection code	IK08
Ingress protection code	IP65
Approval and Application	
Ambient temperature range	-20 to +40 °C
Initial Performance (IEC Compliant)	
Luminous flux tolerance	-10% / +10%

Light Technical

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	
		Temperature (Nom)	(rated) (Nom)	Luminous Flux
911401803987	WT063C LED43S/NW PSU G2	4000 K	116 lm/W	4,300 lm
911401804087	WT063C LED43S/CW PSU G2	6500 K	116 lm/W	4,300 lm
911401803787	WT063C LED20S/NW PSU G2	4000 K	118 lm/W	2,000 lm
911401803887	WT063C LED20S/CW PSU G2	6500 K	118 lm/W	2,000 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401803987	WT063C LED43S/NW PSU G2	37 W
911401804087	WT063C LED43S/CW PSU G2	37 W

Order Code	Full Product Name	Power Consumption
911401803787	WT063C LED20S/NW PSU G2	17 W
911401803887	WT063C LED20S/CW PSU G2	17 W

