



SunStay - All In One solar street light

SunStay

Integrated solar street light with Lithium Ferro Phosphate battery, solar panel and charger built into the luminaire. Pressure die cast aluminium for sturdiness and long life. Specially designed pole mounting bracket allows different tilt angles, lateral and pole top mounting.

Benefits

- Brings light to areas without access to electric grid
- Saves energy
- Preserves landscape as no trenching for cabling required
- Environment friendly
- Sturdy construction for long life


Features

- High luminous efficacy of 175 lm/Watt to maximize battery performance
- Replaceable Lithium Ferro Phosphate battery for long life and hassle free operations.
- MPPT charge controller for maximum efficiency
- Pressure die-cast aluminum housing for sturdiness and excellent heat dissipation.
- Specially designed pole mounting bracket with adjustable tilt angles of 0 to 15 degrees, which can also be used in post top & lateral mounting positions
- Factory set dimming profile along with PIR sensor for run time maximization.
- Self diagnostic feature along with battery charging, discharging & cut-off LED Indicators

Application

- Class A & B roads
- Rural areas
- Parks, pedestrian path lighting
- Industries, office, schools
- Shopping centers, corporate campuses, plazas


Versions




SunStay Hybrid

Lithium Ferro Phosphate battery

Dimensional drawing




PHILIPS




Dimensions



| Description | 12NC | Product Dimension LxWxH (cm) |
|---------------------------------------|--------------|------------------------------|
| SPARE BT LFP 12.8V 30Ah SOLAR EQUIP | 919415811056 | 30x17.5x6 |
| SPARE BT LFP 12.8V 20Ah SOLAR EQUIP | 919415811055 | 30x17.5x6 |
| SPARE BT LFP 12.8V 13.6Ah SOLAR EQUIP | 919415811054 | 22x17.5x5 |



Dimensional drawing



PHILIPS

| Operating and Electrical | |
|--|-------------------------|
| Battery charging & discharging cycles | 2000 |
| Battery type | Lithium Ferro Phosphate |
| Battery voltage | 12.8 V |
| Temperature | |
| Ambient temperature range | 0 to +35 °C |
| Application Conditions | |
| Ambient temperature range for charging | 0 °C to +45 °C |

Light Technical

| Order Code | Full Product Name | Correlated Color Temperature (Nom) | Color rendering index (CRI) |
|--------------|--|------------------------------------|-----------------------------|
| 919515812627 | BRP710 LED20 CW MR S1 12V 35MO FDIM50 So | 5700 K | >70 |
| 919515812628 | BRP710 LED20 CW MR S1 12V 35MO Solar Equ | 5700 K | >70 |
| 919515812631 | BRP710 LED20 CW MR S1 12V 35MO FDIM50 So | 5700 K | >70 |
| 919515812632 | BRP710 LED20 CW MR S1 12V 35MO Solar Equ | 5700 K | >70 |
| 919515812969 | BRP710 LED20 WW MR 12V 35MO FDIM50 Solar | 3000 K | >70 |
| 919515812981 | BRP710 LED20 NW MR 12V 35MO FDIM50 Solar | 4000 K | >70 |
| 919515813174 | BRP710 LED30 CW MR HY SOLAR IN | 5700 K | >70 |
| 919515813614 | BRP710 LED20 CW MR HY SOLAR IN | 5700 K | >70 |
| 919515813615 | BRP710 LED20 CW MR HY FDIM50 SOLAR IN | 5700 K | >70 |
| 919515813616 | BRP710 LED30 CW MR HY FDIM50 SOLAR IN | 5700 K | >70 |

| Order Code | Full Product Name | Correlated Color Temperature (Nom) | Color rendering index (CRI) |
|--------------|---------------------------------------|------------------------------------|-----------------------------|
| 919515813168 | BRP710 LED45 CW MR HY SOLAR IN | 5700 K | >70 |
| 919515813617 | BRP710 LED45 CW MR HY FDIM50 SOLAR IN | 5700 K | >70 |
| 919515813754 | BRP710 LED60 CW MR HY FDIM20 SOLAR IN | 5700 K | >70 |
| 919515813978 | BRP710 LED45 CW MR HY FDIM50 SOLAR | 5700 K | >70 |
| 919515813979 | BRP710 LED60 CW MR HY FDIM20 SOLAR | 5700 K | >70 |
| 919515813982 | BRP710 LED45 CW MR HY SOLAR | 5700 K | >70 |
| 919515813985 | BRP710 LED45 NW MR HY FDIM50 SOLAR | 4000 K | >70 |
| 919515813986 | BRP710 LED60 NW MR HY FDIM20 SOLAR | 4000 K | >70 |
| 919515813989 | BRP710 LED45 NW MR HY SOLAR | 4000 K | >70 |
| 919515813992 | BRP710 LED45 WW MR HY FDIM50 SOLAR | 3000 K | >70 |
| 919515813993 | BRP710 LED60 WW MR HY FDIM20 SOLAR | 3000 K | >70 |

| Order Code | Full Product Name | Correlated Color Temperature (Nom) | Color rendering index (CRI) |
|--------------|--|------------------------------------|-----------------------------|
| 919515813996 | BRP710 LED45 WW MR HY SOLAR | 3000 K | >70 |
| 919515812387 | BRP710 LED20 CW MR S1 12V LFP AIO Solar | 5700 K | >70 |
| 919515812388 | BRP710 LED30 CW MR S1 12V LFP AIO Solar | 5700 K | >70 |
| 919515812389 | BRP710 LED20 CW MR S1 12V LFP AIO Solar | 5700 K | >70 |
| 919515812390 | BRP710 LED30 CW MR S1 12V LFP AIO Solar | 5700 K | >70 |
| 919515812625 | BRP710 LED20 CW MR S1 12V 28PO PDIM50 So | 5700 K | >70 |
| 919515812626 | BRP710 LED20 CW MR S1 12V 35MO PDIM50 So | 5700 K | >70 |
| 919515812629 | BRP710 LED20 CW MR S1 12V 28PO PDIM50 So | 5700 K | >70 |
| 919515812630 | BRP710 LED20 CW MR S1 12V 35MO PDIM50 So | 5700 K | >70 |
| 919515812966 | BRP710 LED20 WW MR 12V LFP Solar | 3000 K | >70 |
| 919515812967 | BRP710 LED20 WW MR 12V 28PO PDIM50 Solar | 3000 K | >70 |
| 919515812968 | BRP710 LED20 WW MR 12V 35MO PDIM50 Solar | 3000 K | >70 |
| 919515812970 | BRP710 LED20 WW MR 12V 35MO Solar | 3000 K | >70 |
| 919515812971 | BRP710 LED30 WW MR 12V LFP AIO Solar | 3000 K | >70 |
| 919515812978 | BRP710 LED20 NW MR 12V LFP Solar | 4000 K | >70 |
| 919515812979 | BRP710 LED20 NW MR 12V 28PO PDIM50 Solar | 4000 K | >70 |
| 919515812980 | BRP710 LED20 NW MR 12V 35MO PDIM50 Solar | 4000 K | >70 |
| 919515812982 | BRP710 LED20 NW MR 12V 35MO Solar | 4000 K | >70 |
| 919515812983 | BRP710 LED30 NW MR 12V LFP AIO Solar | 4000 K | >70 |
| 919515814301 | BRP710 LED30 WW 35MO PDIM30 BLE Solar | 3000 K | >70 |
| 919515814303 | BRP710 LED30 2700K 60MO PDM30 BLE Solar | 2700 K | >70 |
| 919515814304 | BRP710 LED30 WW 60MO PDIM30 BLE Solar | 3000 K | >70 |
| 919515814406 | BRP710 LED20 WW 28PO PDIM50 BLE Solar | 3000 K | >70 |
| 919515898025 | BRP710 LED20 NW 28PO PDIM50 BLE SOLAR EX | 4000 K | >70 |
| 919515898026 | BRP710 LED20 CW 28PO PDIM50 BLE SOLAR EX | 5700 K | >70 |

| Order Code | Full Product Name | Correlated Color Temperature (Nom) | Color rendering index (CRI) |
|--------------|--|------------------------------------|-----------------------------|
| 919515898027 | BRP710 LED30 NW 35MO PDIM30 BLE SOLAR EX | 4000 K | >70 |
| 919515898028 | BRP710 LED30 CW 35MO PDIM30 BLE SOLAR EX | 5700 K | >70 |
| 919515898031 | BRP710 LED30 NW 60MO PDIM30 BLE SOLAR EX | 4000 K | >70 |
| 919515898032 | BRP710 LED30 CW 60MO PDIM30 BLE SOLAR EX | 5700 K | >70 |
| 919515898033 | BRP710 LED20 WW 35MO PDIM50 BLE SOLAR EX | 3000 K | >70 |
| 919515898034 | BRP710 LED20 NW 35MO PDIM50 BLE SOLAR EX | 4000 K | >70 |
| 919515898035 | BRP710 LED20 CW 35MO PDIM50 BLE SOLAR EX | 5700 K | >70 |
| 919615811178 | BRP710 LED20 CW Housing KIT Solar | 5700 K | >70 |
| 919615811179 | BRP710 LED30 CW Housing KIT Solar | 5700 K | >70 |
| 919515813976 | BRP710 LED20 CW MR HY FDIM50 SOLAR | 5700 K | >70 |
| 919515813977 | BRP710 LED30 CW MR HY FDIM50 SOLAR | 5700 K | >70 |
| 919515813980 | BRP710 LED20 CW MR HY SOLAR | 5700 K | >70 |
| 919515813981 | BRP710 LED30 CW MR HY SOLAR | 5700 K | >70 |
| 919515813983 | BRP710 LED20 NW MR HY FDIM50 SOLAR | 4000 K | >70 |
| 919515813984 | BRP710 LED30 NW MR HY FDIM50 SOLAR | 4000 K | >70 |
| 919515813987 | BRP710 LED20 NW MR HY SOLAR | 4000 K | >70 |
| 919515813988 | BRP710 LED30 NW MR HY SOLAR | 4000 K | >70 |
| 919515813990 | BRP710 LED20 WW MR HY FDIM50 SOLAR | 3000 K | >70 |
| 919515813991 | BRP710 LED30 WW MR HY FDIM50 SOLAR | 3000 K | >70 |
| 919515813994 | BRP710 LED20 WW MR HY SOLAR | 3000 K | >70 |
| 919515813995 | BRP710 LED30 WW MR HY SOLAR | 3000 K | >70 |
| 919515812830 | BRP710 LED45 CW MR S1 12V LFP Solar IN | 5700 K | >70 |
| 919515812831 | BRP710 LED45 CW MR S1 12V FD30 Solar IN | 5700 K | >70 |
| 919515813566 | BRP710 LED45 CW MR S1 12V LFP Solar | 5700 K | >70 |
| 919515813567 | BRP710 LED45 CW MR S1 12V FD30 Solar | 5700 K | >70 |
| 919515813568 | BRP710 LED45 WW MR S1 12V LFP Solar | 3000 K | >70 |
| 919515813569 | BRP710 LED45 NW MR S1 12V LFP Solar | 4000 K | >70 |
| 919515813570 | BRP710 LED45 WW MR S1 12V FD30 Solar | 3000 K | >70 |

| Order Code | Full Product Name | Correlated Color Temperature (Nom) | Color rendering index (CRI) |
|--------------|---|------------------------------------|-----------------------------|
| 919515813571 | BRP710 LED45 NW MR S1 12V FD30 Solar | 4000 K | >70 |
| 919515814302 | BRP710 LED45 WW 60MO PDIM30 BLE Solar | 3000 K | >70 |
| 919515898029 | BRP710 LED45 NW 60MO PDIM30 BLE SOLAR EX | 4000 K | >70 |
| 919515898030 | BRP710 LED45 CW 60MO PDIM30 BLE SOLAR EX | 5700 K | >70 |
| 919615811180 | BRP710 LED45 CW Housing KIT Solar | 5700 K | >70 |

| Order Code | Full Product Name | Correlated Color Temperature (Nom) | Color rendering index (CRI) |
|--------------|---|------------------------------------|-----------------------------|
| 919615811265 | BRP710 P LED45 CW MR 12V LFP Solar P4125 | 5700 K | >70 |
| 919415811054 | SPARE BT LFP 12.8V 13.6Ah SOLAR EQUIP | - | - |
| 919415811055 | SPARE BT LFP 12.8V 20Ah SOLAR EQUIP | - | - |
| 919415811056 | SPARE BT LFP 12.8V 30Ah SOLAR EQUIP | - | - |

Operating and Electrical

| Order Code | Full Product Name | Battery ampere hour | Cable connection kit | Charge controller type | Charge controller wattage | Panel peak wattage | Panel type | Panel voltage |
|--------------|---|---------------------|----------------------|------------------------|---------------------------|--------------------|------------------|------------------|
| 919515812627 | BRP710 LED20 CW MR S1 12V 35MO FDIM50 So | 13.6 Ah | - | MPPT | - | 35 W | Mono crystalline | 17 Vmp, 21 Voc V |
| 919515812628 | BRP710 LED20 CW MR S1 12V 35MO Solar Equ | 13.6 Ah | - | MPPT | - | 35 W | Mono crystalline | 17 Vmp, 21 Voc V |
| 919515812631 | BRP710 LED20 CW MR S1 12V 35MO FDIM50 So | 13.6 Ah | - | MPPT | - | 35 W | Mono crystalline | 17 Vmp, 21 Voc V |
| 919515812632 | BRP710 LED20 CW MR S1 12V 35MO Solar Equ | 13.6 Ah | - | MPPT | - | 35 W | Mono crystalline | 17 Vmp, 21 Voc V |
| 919515812969 | BRP710 LED20 WW MR 12V 35MO FDIM50 Solar | 13.6 Ah | - | MPPT | - | 35 W | Mono crystalline | 17 Vmp, 21 Voc V |
| 919515812981 | BRP710 LED20 NW MR 12V 35MO FDIM50 Solar | 13.6 Ah | - | MPPT | - | 35 W | Mono crystalline | 17 Vmp, 21 Voc V |
| 919515813174 | BRP710 LED30 CW MR HY SOLAR IN | 20 Ah | Included | MPPT | 17 W | 35 W | Mono crystalline | 17 Vmp, 21 Voc V |
| 919515813614 | BRP710 LED20 CW MR HY SOLAR IN | 13.6 Ah | Included | MPPT | 11 W | 28 W | Poly crystalline | 17 Vmp, 21 Voc V |
| 919515813615 | BRP710 LED20 CW MR HY FDIM50 SOLAR IN | 13.6 Ah | Included | MPPT | 11 W | 28 W | Poly crystalline | 17 Vmp, 21 Voc V |
| 919515813616 | BRP710 LED30 CW MR HY FDIM50 SOLAR IN | 20 Ah | Included | MPPT | 17 W | 35 W | Mono crystalline | 17 Vmp, 21 Voc V |
| 919515813168 | BRP710 LED45 CW MR HY SOLAR IN | 30 Ah | Included | MPPT | 25 W | 60 W | Mono crystalline | 17 Vmp, 21 Voc V |
| 919515813617 | BRP710 LED45 CW MR HY FDIM50 SOLAR IN | 30 Ah | Included | MPPT | 25 W | 60 W | Mono crystalline | 17 Vmp, 21 Voc V |
| 919515813754 | BRP710 LED60 CW MR HY FDIM20 SOLAR IN | 30 Ah | Included | MPPT | 35 W | 60 W | Mono crystalline | 17 Vmp, 21 Voc V |
| 919515813978 | BRP710 LED45 CW MR HY FDIM50 SOLAR | 30 Ah | Included | MPPT | 25 W | 60 W | Mono crystalline | 17 Vmp, 21 Voc V |
| 919515813979 | BRP710 LED60 CW MR HY FDIM20 SOLAR | 30 Ah | Included | MPPT | 35 W | 60 W | Mono crystalline | 17 Vmp, 21 Voc V |
| 919515813982 | BRP710 LED45 CW MR HY SOLAR | 30 Ah | Included | MPPT | 25 W | 60 W | Mono crystalline | 17 Vmp, 21 Voc V |
| 919515813985 | BRP710 LED45 NW MR HY FDIM50 SOLAR | 30 Ah | Included | MPPT | 25 W | 60 W | Mono crystalline | 17 Vmp, 21 Voc V |
| 919515813986 | BRP710 LED60 NW MR HY FDIM20 SOLAR | 30 Ah | Included | MPPT | 35 W | 60 W | Mono crystalline | 17 Vmp, 21 Voc V |
| 919515813989 | BRP710 LED45 NW MR HY SOLAR | 30 Ah | Included | MPPT | 25 W | 60 W | Mono crystalline | 17 Vmp, 21 Voc V |
| 919515813992 | BRP710 LED45 WW MR HY FDIM50 SOLAR | 30 Ah | Included | MPPT | 25 W | 60 W | Mono crystalline | 17 Vmp, 21 Voc V |

| Order Code | Full Product Name | Battery ampere hour | Cable connection kit | Charge controller type | Charge controller wattage | Panel peak wattage | Panel type | Panel voltage |
|--------------|--|---------------------|----------------------|------------------------|---------------------------|--------------------|------------------|------------------|
| 919515813993 | BRP710 LED60 WW MR HY FDIM20 SOLAR | 30 Ah | Included | MPPT | 35 W | 60 W | Mono crystalline | 17 Vmp, 21 Voc V |
| 919515813996 | BRP710 LED45 WW MR HY SOLAR | 30 Ah | Included | MPPT | 25 W | 60 W | Mono crystalline | 17 Vmp, 21 Voc V |
| 919515812387 | BRP710 LED20 CW MR S1 12V LFP AIO Solar | 13.6 Ah | - | MPPT | - | 28 W | Poly crystalline | 17 Vmp, 21 Voc V |
| 919515812388 | BRP710 LED30 CW MR S1 12V LFP AIO Solar | 20 Ah | - | MPPT | - | 35 W | Mono crystalline | 17 Vmp, 21 Voc V |
| 919515812389 | BRP710 LED20 CW MR S1 12V LFP AIO Solar | 13.6 Ah | - | MPPT | - | 28 W | Poly crystalline | 17 Vmp, 21 Voc V |
| 919515812390 | BRP710 LED30 CW MR S1 12V LFP AIO Solar | 20 Ah | - | MPPT | - | 35 W | Mono crystalline | 17 Vmp, 21 Voc V |
| 919515812625 | BRP710 LED20 CW MR S1 12V 28PO PDIM50 So | 13.6 Ah | - | MPPT | - | 28 W | Poly crystalline | 17 Vmp, 21 Voc V |
| 919515812626 | BRP710 LED20 CW MR S1 12V 35MO PDIM50 So | 13.6 Ah | - | MPPT | - | 35 W | Mono crystalline | 17 Vmp, 21 Voc V |
| 919515812629 | BRP710 LED20 CW MR S1 12V 28PO PDIM50 So | 13.6 Ah | - | MPPT | - | 28 W | Poly crystalline | 17 Vmp, 21 Voc V |
| 919515812630 | BRP710 LED20 CW MR S1 12V 35MO PDIM50 So | 13.6 Ah | - | MPPT | - | 35 W | Mono crystalline | 17 Vmp, 21 Voc V |
| 919515812966 | BRP710 LED20 WW MR 12V LFP Solar | 13.6 Ah | - | MPPT | - | 28 W | Poly crystalline | 17 Vmp, 21 Voc V |
| 919515812967 | BRP710 LED20 WW MR 12V 28PO PDIM50 Solar | 13.6 Ah | - | MPPT | - | 28 W | Poly crystalline | 17 Vmp, 21 Voc V |
| 919515812968 | BRP710 LED20 WW MR 12V 35MO PDIM50 Solar | 13.6 Ah | - | MPPT | - | 35 W | Mono crystalline | 17 Vmp, 21 Voc V |
| 919515812970 | BRP710 LED20 WW MR 12V 35MO Solar | 20 Ah | - | MPPT | - | 35 W | Mono crystalline | 17 Vmp, 21 Voc V |
| 919515812971 | BRP710 LED30 WW MR 12V LFP AIO Solar | 20 Ah | - | MPPT | - | 35 W | Mono crystalline | 17 Vmp, 21 Voc V |
| 919515812978 | BRP710 LED20 NW MR 12V LFP Solar | 13.6 Ah | - | MPPT | - | 28 W | Poly crystalline | 17 Vmp, 21 Voc V |
| 919515812979 | BRP710 LED20 NW MR 12V 28PO PDIM50 Solar | 13.6 Ah | - | MPPT | - | 28 W | Poly crystalline | 17 Vmp, 21 Voc V |
| 919515812980 | BRP710 LED20 NW MR 12V 35MO PDIM50 Solar | 13.6 Ah | - | MPPT | - | 35 W | Mono crystalline | 17 Vmp, 21 Voc V |
| 919515812982 | BRP710 LED20 NW MR 12V 35MO Solar | 20 Ah | - | MPPT | - | 35 W | Mono crystalline | 17 Vmp, 21 Voc V |
| 919515812983 | BRP710 LED30 NW MR 12V LFP AIO Solar | 20 Ah | - | MPPT | - | 35 W | Mono crystalline | 17 Vmp, 21 Voc V |
| 919515814301 | BRP710 LED30 WW 35MO PDIM30 BLE Solar | 20 Ah | - | MPPT | - | 35 W | Mono crystalline | 17 V |
| 919515814303 | BRP710 LED30 2700K 60MO PDM30 BLE Solar | 30 Ah | - | MPPT | - | 60 W | Mono crystalline | 17 V |
| 919515814304 | BRP710 LED30 WW 60MO PDIM30 BLE Solar | 30 Ah | - | MPPT | - | 60 W | Mono crystalline | 17 V |
| 919515814406 | BRP710 LED20 WW 28PO PDIM50 BLE Solar | 13.6 Ah | - | MPPT | - | 28 W | Poly crystalline | 17 V |
| 919515898025 | BRP710 LED20 NW 28PO PDIM50 BLE SOLAR EX | 13.6 Ah | - | MPPT | - | 28 W | Poly crystalline | 17 V |
| 919515898026 | BRP710 LED20 CW 28PO PDIM50 BLE SOLAR EX | 13.6 Ah | - | MPPT | - | 28 W | Poly crystalline | 17 V |
| 919515898027 | BRP710 LED30 NW 35MO PDIM30 BLE SOLAR EX | 20 Ah | - | MPPT | - | 35 W | Mono crystalline | 17 V |
| 919515898028 | BRP710 LED30 CW 35MO PDIM30 BLE SOLAR EX | 20 Ah | - | MPPT | - | 35 W | Mono crystalline | 17 V |

| Order Code | Full Product Name | Battery ampere hour | Cable connection kit | Charge controller type | Charge controller wattage | Panel peak wattage | Panel type | Panel voltage |
|--------------|--|---------------------|----------------------|------------------------|---------------------------|--------------------|------------------|------------------|
| 919515898031 | BRP710 LED30 NW 60MO PDIM30 BLE SOLAR EX | 30 Ah | - | MPPT | - | 60 W | Mono crystalline | 17 V |
| 919515898032 | BRP710 LED30 CW 60MO PDIM30 BLE SOLAR EX | 30 Ah | - | MPPT | - | 60 W | Mono crystalline | 17 V |
| 919515898033 | BRP710 LED20 WW 35MO PDIM50 BLE SOLAR EX | 20 Ah | - | MPPT | - | 35 W | Mono crystalline | 17 V |
| 919515898034 | BRP710 LED20 NW 35MO PDIM50 BLE SOLAR EX | 20 Ah | - | MPPT | - | 35 W | Mono crystalline | 17 V |
| 919515898035 | BRP710 LED20 CW 35MO PDIM50 BLE SOLAR EX | 20 Ah | - | MPPT | - | 35 W | Mono crystalline | 17 V |
| 919615811178 | BRP710 LED20 CW Housing KIT Solar | 13.6 Ah | - | MPPT | - | 28 W | Poly crystalline | 17 Vmp, 21 Voc V |
| 919615811179 | BRP710 LED30 CW Housing KIT Solar | 20 Ah | - | MPPT | - | 35 W | Mono crystalline | 17 Vmp, 21 Voc V |
| 919515813976 | BRP710 LED20 CW MR HY FDIM50 SOLAR | 13.6 Ah | Included | MPPT | 11 W | 28 W | Poly crystalline | 17 Vmp, 21 Voc V |
| 919515813977 | BRP710 LED30 CW MR HY FDIM50 SOLAR | 20 Ah | Included | MPPT | 17 W | 35 W | Mono crystalline | 17 Vmp, 21 Voc V |
| 919515813980 | BRP710 LED20 CW MR HY SOLAR | 13.6 Ah | Included | MPPT | 11 W | 28 W | Poly crystalline | 17 Vmp, 21 Voc V |
| 919515813981 | BRP710 LED30 CW MR HY SOLAR | 20 Ah | Included | MPPT | 17 W | 35 W | Mono crystalline | 17 Vmp, 21 Voc V |
| 919515813983 | BRP710 LED20 NW MR HY FDIM50 SOLAR | 13.6 Ah | Included | MPPT | 11 W | 28 W | Poly crystalline | 17 Vmp, 21 Voc V |
| 919515813984 | BRP710 LED30 NW MR HY FDIM50 SOLAR | 20 Ah | Included | MPPT | 17 W | 35 W | Mono crystalline | 17 Vmp, 21 Voc V |
| 919515813987 | BRP710 LED20 NW MR HY SOLAR | 13.6 Ah | Included | MPPT | 11 W | 28 W | Poly crystalline | 17 Vmp, 21 Voc V |
| 919515813988 | BRP710 LED30 NW MR HY SOLAR | 20 Ah | Included | MPPT | 17 W | 35 W | Mono crystalline | 17 Vmp, 21 Voc V |
| 919515813990 | BRP710 LED20 WW MR HY FDIM50 SOLAR | 13.6 Ah | Included | MPPT | 11 W | 28 W | Poly crystalline | 17 Vmp, 21 Voc V |
| 919515813991 | BRP710 LED30 WW MR HY FDIM50 SOLAR | 20 Ah | Included | MPPT | 17 W | 35 W | Mono crystalline | 17 Vmp, 21 Voc V |
| 919515813994 | BRP710 LED20 WW MR HY SOLAR | 13.6 Ah | Included | MPPT | 11 W | 28 W | Poly crystalline | 17 Vmp, 21 Voc V |
| 919515813995 | BRP710 LED30 WW MR HY SOLAR | 20 Ah | Included | MPPT | 17 W | 35 W | Mono crystalline | 17 Vmp, 21 Voc V |
| 919515812830 | BRP710 LED45 CW MR S1 12V LFP Solar IN | 30 Ah | - | MPPT | - | 60 W | Mono crystalline | 17 Vmp, 21 Voc V |
| 919515812831 | BRP710 LED45 CW MR S1 12V FD30 Solar IN | 30 Ah | - | MPPT | - | 60 W | Mono crystalline | 17 Vmp, 21 Voc V |
| 919515813566 | BRP710 LED45 CW MR S1 12V LFP Solar | 30 Ah | - | MPPT | - | 60 W | Mono crystalline | 17 Vmp, 21 Voc V |
| 919515813567 | BRP710 LED45 CW MR S1 12V FD30 Solar | 30 Ah | - | MPPT | - | 60 W | Mono crystalline | 17 Vmp, 21 Voc V |
| 919515813568 | BRP710 LED45 WW MR S1 12V LFP Solar | 30 Ah | - | MPPT | - | 60 W | Mono crystalline | 17 Vmp, 21 Voc V |
| 919515813569 | BRP710 LED45 NW MR S1 12V LFP Solar | 30 Ah | - | MPPT | - | 60 W | Mono crystalline | 17 Vmp, 21 Voc V |
| 919515813570 | BRP710 LED45 WW MR S1 12V FD30 Solar | 30 Ah | - | MPPT | - | 60 W | Mono crystalline | 17 Vmp, 21 Voc V |
| 919515813571 | BRP710 LED45 NW MR S1 12V FD30 Solar | 30 Ah | - | MPPT | - | 60 W | Mono crystalline | 17 Vmp, 21 Voc V |
| 919515814302 | BRP710 LED45 WW 60MO PDIM30 BLE Solar | 30 Ah | - | MPPT | - | 60 W | Mono crystalline | 17 V |
| 919515898029 | BRP710 LED45 NW 60MO PDIM30 BLE SOLAR EX | 30 Ah | - | MPPT | - | 60 W | Mono crystalline | 17 V |
| 919515898030 | BRP710 LED45 CW 60MO PDIM30 BLE SOLAR EX | 30 Ah | - | MPPT | - | 60 W | Mono crystalline | 17 V |
| 919615811180 | BRP710 LED45 CW Housing KIT Solar | 30 Ah | - | MPPT | - | 60 W | Mono crystalline | 17 Vmp, 21 Voc V |
| 919615811265 | BRP710 P LED45 CW MR 12V LFP Solar P4125 | 30 Ah | - | MPPT | - | 60 W | Mono crystalline | 17 Vmp, 21 Voc V |
| 919415811054 | SPARE BT LFP 12.8V 13.6Ah SOLAR EQUIP | 13.6 Ah | - | - | - | - | - | - |
| 919415811055 | SPARE BT LFP 12.8V 20Ah SOLAR EQUIP | 20 Ah | - | - | - | - | - | - |

| Order Code | Full Product Name | Battery ampere hour | Cable connection kit | Charge controller type | Charge controller wattage | Panel peak wattage | Panel type | Panel voltage |
|--------------|-------------------------------------|---------------------|----------------------|------------------------|---------------------------|--------------------|------------|---------------|
| 919415811056 | SPARE BT LFP 12.8V 30Ah SOLAR EQUIP | 30 Ah | - | - | - | - | - | - |

Controls and Dimming

| Order Code | Full Product Name | Dimmable | Configurability |
|--------------|--|----------|----------------------|
| 919515812627 | BRP710 LED20 CW MR S1 12V 35MO FDIM50 So | Yes | Factory Configurable |
| 919515812628 | BRP710 LED20 CW MR S1 12V 35MO Solar Equ | Yes | Factory Configurable |
| 919515812631 | BRP710 LED20 CW MR S1 12V 35MO FDIM50 So | Yes | Factory Configurable |
| 919515812632 | BRP710 LED20 CW MR S1 12V 35MO Solar Equ | Yes | Factory Configurable |
| 919515812969 | BRP710 LED20 WW MR 12V 35MO FDIM50 Solar | Yes | Factory Configurable |
| 919515812981 | BRP710 LED20 NW MR 12V 35MO FDIM50 Solar | Yes | Factory Configurable |
| 919515813174 | BRP710 LED30 CW MR HY SOLAR IN | Yes | Factory Configurable |
| 919515813614 | BRP710 LED20 CW MR HY SOLAR IN | Yes | Factory Configurable |
| 919515813615 | BRP710 LED20 CW MR HY FDIM50 SOLAR IN | Yes | Factory Configurable |
| 919515813616 | BRP710 LED30 CW MR HY FDIM50 SOLAR IN | Yes | Factory Configurable |
| 919515813168 | BRP710 LED45 CW MR HY SOLAR IN | Yes | Factory Configurable |
| 919515813617 | BRP710 LED45 CW MR HY FDIM50 SOLAR IN | Yes | Factory Configurable |
| 919515813754 | BRP710 LED60 CW MR HY FDIM20 SOLAR IN | Yes | Factory Configurable |
| 919515813978 | BRP710 LED45 CW MR HY FDIM50 SOLAR | Yes | Factory Configurable |
| 919515813979 | BRP710 LED60 CW MR HY FDIM20 SOLAR | Yes | Factory Configurable |
| 919515813982 | BRP710 LED45 CW MR HY SOLAR | Yes | Factory Configurable |
| 919515813985 | BRP710 LED45 NW MR HY FDIM50 SOLAR | Yes | Factory Configurable |
| 919515813986 | BRP710 LED60 NW MR HY FDIM20 SOLAR | Yes | Factory Configurable |
| 919515813989 | BRP710 LED45 NW MR HY SOLAR | Yes | Factory Configurable |
| 919515813992 | BRP710 LED45 WW MR HY FDIM50 SOLAR | Yes | Factory Configurable |
| 919515813993 | BRP710 LED60 WW MR HY FDIM20 SOLAR | Yes | Factory Configurable |
| 919515813996 | BRP710 LED45 WW MR HY SOLAR | Yes | Factory Configurable |
| 919515812387 | BRP710 LED20 CW MR S1 12V LFP AIO Solar | Yes | Factory Configurable |
| 919515812388 | BRP710 LED30 CW MR S1 12V LFP AIO Solar | Yes | Factory Configurable |
| 919515812389 | BRP710 LED20 CW MR S1 12V LFP AIO Solar | Yes | Factory Configurable |

| Order Code | Full Product Name | Dimmable | Configurability |
|--------------|--|----------|----------------------|
| 919515812390 | BRP710 LED30 CW MR S1 12V LFP AIO Solar | Yes | Factory Configurable |
| 919515812625 | BRP710 LED20 CW MR S1 12V 28PO PDIM50 So | Yes | Factory Configurable |
| 919515812626 | BRP710 LED20 CW MR S1 12V 35MO PDIM50 So | Yes | Factory Configurable |
| 919515812629 | BRP710 LED20 CW MR S1 12V 28PO PDIM50 So | Yes | Factory Configurable |
| 919515812630 | BRP710 LED20 CW MR S1 12V 35MO PDIM50 So | Yes | Factory Configurable |
| 919515812966 | BRP710 LED20 WW MR 12V LFP Solar | Yes | Factory Configurable |
| 919515812967 | BRP710 LED20 WW MR 12V 28PO PDIM50 Solar | Yes | Factory Configurable |
| 919515812968 | BRP710 LED20 WW MR 12V 35MO PDIM50 Solar | Yes | Factory Configurable |
| 919515812970 | BRP710 LED20 WW MR 12V 35MO Solar | Yes | Factory Configurable |
| 919515812971 | BRP710 LED30 WW MR 12V LFP AIO Solar | Yes | Factory Configurable |
| 919515812978 | BRP710 LED20 NW MR 12V LFP Solar | Yes | Factory Configurable |
| 919515812979 | BRP710 LED20 NW MR 12V 28PO PDIM50 Solar | Yes | Factory Configurable |
| 919515812980 | BRP710 LED20 NW MR 12V 35MO PDIM50 Solar | Yes | Factory Configurable |
| 919515812982 | BRP710 LED20 NW MR 12V 35MO Solar | Yes | Factory Configurable |
| 919515812983 | BRP710 LED30 NW MR 12V LFP AIO Solar | Yes | Factory Configurable |
| 919515814301 | BRP710 LED30 WW 35MO PDIM30 BLE Solar | Yes | Configurable |
| 919515814303 | BRP710 LED30 2700K 60MO PDM30 BLE Solar | Yes | Configurable |
| 919515814304 | BRP710 LED30 WW 60MO PDIM30 BLE Solar | Yes | Configurable |
| 919515814406 | BRP710 LED20 WW 28PO PDIM50 BLE Solar | Yes | Configurable |
| 919515898025 | BRP710 LED20 NW 28PO PDIM50 BLE SOLAR EX | Yes | Configurable |
| 919515898026 | BRP710 LED20 CW 28PO PDIM50 BLE SOLAR EX | Yes | Configurable |
| 919515898027 | BRP710 LED30 NW 35MO PDIM30 BLE SOLAR EX | Yes | Configurable |
| 919515898028 | BRP710 LED30 CW 35MO PDIM30 BLE SOLAR EX | Yes | Configurable |

| Order Code | Full Product Name | Dimmable | Configurability |
|--------------|--|----------|----------------------|
| 919515898031 | BRP710 LED30 NW 60MO PDIM30 BLE SOLAR EX | Yes | Configurable |
| 919515898032 | BRP710 LED30 CW 60MO PDIM30 BLE SOLAR EX | Yes | Configurable |
| 919515898033 | BRP710 LED20 WW 35MO PDIM50 BLE SOLAR EX | Yes | Configurable |
| 919515898034 | BRP710 LED20 NW 35MO PDIM50 BLE SOLAR EX | Yes | Configurable |
| 919515898035 | BRP710 LED20 CW 35MO PDIM50 BLE SOLAR EX | Yes | Configurable |
| 919615811178 | BRP710 LED20 CW Housing KIT Solar | Yes | Factory Configurable |
| 919615811179 | BRP710 LED30 CW Housing KIT Solar | Yes | Factory Configurable |
| 919515813976 | BRP710 LED20 CW MR HY FDIM50 SOLAR | Yes | Factory Configurable |
| 919515813977 | BRP710 LED30 CW MR HY FDIM50 SOLAR | Yes | Factory Configurable |
| 919515813980 | BRP710 LED20 CW MR HY SOLAR | Yes | Factory Configurable |
| 919515813981 | BRP710 LED30 CW MR HY SOLAR | Yes | Factory Configurable |
| 919515813983 | BRP710 LED20 NW MR HY FDIM50 SOLAR | Yes | Factory Configurable |
| 919515813984 | BRP710 LED30 NW MR HY FDIM50 SOLAR | Yes | Factory Configurable |
| 919515813987 | BRP710 LED20 NW MR HY SOLAR | Yes | Factory Configurable |
| 919515813988 | BRP710 LED30 NW MR HY SOLAR | Yes | Factory Configurable |
| 919515813990 | BRP710 LED20 WW MR HY FDIM50 SOLAR | Yes | Factory Configurable |
| 919515813991 | BRP710 LED30 WW MR HY FDIM50 SOLAR | Yes | Factory Configurable |
| 919515813994 | BRP710 LED20 WW MR HY SOLAR | Yes | Factory Configurable |
| 919515813995 | BRP710 LED30 WW MR HY SOLAR | Yes | Factory Configurable |
| 919515812830 | BRP710 LED45 CW MR S1 12V LFP Solar IN | Yes | Factory Configurable |

| Order Code | Full Product Name | Dimmable | Configurability |
|--------------|--|----------|----------------------|
| 919515812831 | BRP710 LED45 CW MR S1 12V FD30 Solar IN | Yes | Factory Configurable |
| 919515813566 | BRP710 LED45 CW MR S1 12V LFP Solar | Yes | Factory Configurable |
| 919515813567 | BRP710 LED45 CW MR S1 12V FD30 Solar | Yes | Factory Configurable |
| 919515813568 | BRP710 LED45 WW MR S1 12V LFP Solar | Yes | Factory Configurable |
| 919515813569 | BRP710 LED45 NW MR S1 12V LFP Solar | Yes | Factory Configurable |
| 919515813570 | BRP710 LED45 WW MR S1 12V FD30 Solar | Yes | Factory Configurable |
| 919515813571 | BRP710 LED45 NW MR S1 12V FD30 Solar | Yes | Factory Configurable |
| 919515814302 | BRP710 LED45 WW 60MO PDIM30 BLE Solar | Yes | Configurable |
| 919515898029 | BRP710 LED45 NW 60MO PDIM30 BLE SOLAR EX | Yes | Configurable |
| 919515898030 | BRP710 LED45 CW 60MO PDIM30 BLE SOLAR EX | Yes | Configurable |
| 919615811180 | BRP710 LED45 CW Housing KIT Solar | Yes | Factory Configurable |
| 919615811265 | BRP710 P LED45 CW MR 12V LFP Solar P4125 | Yes | Factory Configurable |
| 919415811054 | SPARE BT LFP 12.8V 13.6Ah SOLAR EQUIP | - | - |
| 919415811055 | SPARE BT LFP 12.8V 20Ah SOLAR EQUIP | - | - |
| 919415811056 | SPARE BT LFP 12.8V 30Ah SOLAR EQUIP | - | - |

Mechanical and Housing

| Order Code | Full Product Name | Housing Color | Overall height | Overall length | Overall width |
|--------------|--|---------------|----------------|----------------|---------------|
| 919515812627 | BRP710 LED20 CW MR S1 12V 35MO FDIM50 So | Gray | 156 mm | 684 mm | 369 mm |
| 919515812628 | BRP710 LED20 CW MR S1 12V 35MO Solar Equ | Gray | 156 mm | 684 mm | 369 mm |
| 919515812631 | BRP710 LED20 CW MR S1 12V 35MO FDIM50 So | Gray | 156 mm | 684 mm | 369 mm |
| 919515812632 | BRP710 LED20 CW MR S1 12V 35MO Solar Equ | Gray | 156 mm | 684 mm | 369 mm |
| 919515812969 | BRP710 LED20 WW MR 12V 35MO FDIM50 Solar | Gray | 156 mm | 684 mm | 369 mm |

| Order Code | Full Product Name | Housing Color | Overall height | Overall length | Overall width |
|--------------|--|---------------|----------------|----------------|---------------|
| 919515812981 | BRP710 LED20 NW MR 12V 35MO FDIM50 Solar | Gray | 156 mm | 684 mm | 369 mm |
| 919515813174 | BRP710 LED30 CW MR HY SOLAR IN | RAL 7011 | 156 mm | 684 mm | 369 mm |
| 919515813614 | BRP710 LED20 CW MR HY SOLAR IN | RAL 7011 | 156 mm | 684 mm | 369 mm |
| 919515813615 | BRP710 LED20 CW MR HY FDIM50 SOLAR IN | RAL 7011 | 156 mm | 684 mm | 369 mm |
| 919515813616 | BRP710 LED30 CW MR HY FDIM50 SOLAR IN | RAL 7011 | 156 mm | 684 mm | 369 mm |
| 919515813168 | BRP710 LED45 CW MR HY SOLAR IN | RAL 7011 | 188 mm | 757 mm | 511 mm |

| Order Code | Full Product Name | Housing Color | Overall height | Overall length | Overall width |
|--------------|--|---------------|----------------|----------------|---------------|
| 919515813617 | BRP710 LED45 CW MR HY FDIM50 SOLAR IN | RAL 7011 | 188 mm | 757 mm | 511 mm |
| 919515813754 | BRP710 LED60 CW MR HY FDIM20 SOLAR IN | RAL 7011 | 188 mm | 757 mm | 511 mm |
| 919515813978 | BRP710 LED45 CW MR HY FDIM50 SOLAR | RAL 7011 | 188 mm | 757 mm | 511 mm |
| 919515813979 | BRP710 LED60 CW MR HY FDIM20 SOLAR | RAL 7011 | 188 mm | 757 mm | 511 mm |
| 919515813982 | BRP710 LED45 CW MR HY SOLAR | RAL 7011 | 188 mm | 757 mm | 511 mm |
| 919515813985 | BRP710 LED45 NW MR HY FDIM50 SOLAR | RAL 7011 | 188 mm | 757 mm | 511 mm |
| 919515813986 | BRP710 LED60 NW MR HY FDIM20 SOLAR | RAL 7011 | 188 mm | 757 mm | 511 mm |
| 919515813989 | BRP710 LED45 NW MR HY SOLAR | RAL 7011 | 188 mm | 757 mm | 511 mm |
| 919515813992 | BRP710 LED45 WW MR HY FDIM50 SOLAR | RAL 7011 | 188 mm | 757 mm | 511 mm |
| 919515813993 | BRP710 LED60 WW MR HY FDIM20 SOLAR | RAL 7011 | 188 mm | 757 mm | 511 mm |
| 919515813996 | BRP710 LED45 WW MR HY SOLAR | RAL 7011 | 188 mm | 757 mm | 511 mm |
| 919515812387 | BRP710 LED20 CW MR S1 12V LFP AIO Solar | Gray | 156 mm | 684 mm | 369 mm |
| 919515812388 | BRP710 LED30 CW MR S1 12V LFP AIO Solar | Gray | 156 mm | 684 mm | 369 mm |
| 919515812389 | BRP710 LED20 CW MR S1 12V LFP AIO Solar | Gray | 156 mm | 684 mm | 369 mm |
| 919515812390 | BRP710 LED30 CW MR S1 12V LFP AIO Solar | Gray | 156 mm | 684 mm | 369 mm |
| 919515812625 | BRP710 LED20 CW MR S1 12V 28PO PDIM50 So | Gray | 156 mm | 684 mm | 369 mm |
| 919515812626 | BRP710 LED20 CW MR S1 12V 35MO PDIM50 So | Gray | 156 mm | 684 mm | 369 mm |
| 919515812629 | BRP710 LED20 CW MR S1 12V 28PO PDIM50 So | Gray | 156 mm | 684 mm | 369 mm |

| Order Code | Full Product Name | Housing Color | Overall height | Overall length | Overall width |
|--------------|--|---------------|----------------|----------------|---------------|
| 919515812630 | BRP710 LED20 CW MR S1 12V 35MO PDIM50 So | Gray | 156 mm | 684 mm | 369 mm |
| 919515812966 | BRP710 LED20 WW MR 12V LFP Solar | Gray | 156 mm | 684 mm | 369 mm |
| 919515812967 | BRP710 LED20 WW MR 12V 28PO PDIM50 Solar | Gray | 156 mm | 684 mm | 369 mm |
| 919515812968 | BRP710 LED20 WW MR 12V 35MO PDIM50 Solar | Gray | 156 mm | 684 mm | 369 mm |
| 919515812970 | BRP710 LED20 WW MR 12V 35MO Solar | Gray | 156 mm | 684 mm | 369 mm |
| 919515812971 | BRP710 LED30 WW MR 12V LFP AIO Solar | Gray | 156 mm | 684 mm | 369 mm |
| 919515812978 | BRP710 LED20 NW MR 12V LFP Solar | Gray | 156 mm | 684 mm | 369 mm |
| 919515812979 | BRP710 LED20 NW MR 12V 28PO PDIM50 Solar | Gray | 156 mm | 684 mm | 369 mm |
| 919515812980 | BRP710 LED20 NW MR 12V 35MO PDIM50 Solar | Gray | 156 mm | 684 mm | 369 mm |
| 919515812982 | BRP710 LED20 NW MR 12V 35MO Solar | Gray | 156 mm | 684 mm | 369 mm |
| 919515812983 | BRP710 LED30 NW MR 12V LFP AIO Solar | Gray | 156 mm | 684 mm | 369 mm |
| 919515814301 | BRP710 LED30 WW 35MO PDIM30 BLE Solar | RAL 7011 | 156 mm | 684 mm | 369 mm |
| 919515814303 | BRP710 LED30 2700K 60MO PDM30 BLE Solar | RAL 7011 | 156 mm | 684 mm | 369 mm |
| 919515814304 | BRP710 LED30 WW 60MO PDIM30 BLE Solar | RAL 7011 | 156 mm | 684 mm | 369 mm |
| 919515814406 | BRP710 LED20 WW 28PO PDIM50 BLE Solar | RAL 7011 | 156 mm | 684 mm | 369 mm |
| 919515898025 | BRP710 LED20 NW 28PO PDIM50 BLE SOLAR EX | RAL 7011 | 156 mm | 684 mm | 369 mm |
| 919515898026 | BRP710 LED20 CW 28PO PDIM50 BLE SOLAR EX | RAL 7011 | 156 mm | 684 mm | 369 mm |
| 919515898027 | BRP710 LED30 NW 35MO PDIM30 BLE SOLAR EX | RAL 7011 | 156 mm | 684 mm | 369 mm |
| 919515898028 | BRP710 LED30 CW 35MO PDIM30 BLE SOLAR EX | RAL 7011 | 156 mm | 684 mm | 369 mm |

| Order Code | Full Product Name | Housing Color | Overall height | Overall length | Overall width |
|--------------|--|---------------|----------------|----------------|---------------|
| 919515898031 | BRP710 LED30 NW 60MO PDIM30 BLE SOLAR EX | RAL 7011 | 156 mm | 684 mm | 369 mm |
| 919515898032 | BRP710 LED30 CW 60MO PDIM30 BLE SOLAR EX | RAL 7011 | 156 mm | 684 mm | 369 mm |
| 919515898033 | BRP710 LED20 WW 35MO PDIM50 BLE SOLAR EX | RAL 7011 | 156 mm | 684 mm | 369 mm |
| 919515898034 | BRP710 LED20 NW 35MO PDIM50 BLE SOLAR EX | RAL 7011 | 156 mm | 684 mm | 369 mm |
| 919515898035 | BRP710 LED20 CW 35MO PDIM50 BLE SOLAR EX | RAL 7011 | 156 mm | 684 mm | 369 mm |
| 919615811178 | BRP710 LED20 CW Housing KIT Solar | Gray | 156 mm | 684 mm | 369 mm |
| 919615811179 | BRP710 LED30 CW Housing KIT Solar | Gray | 156 mm | 684 mm | 369 mm |
| 919515813976 | BRP710 LED20 CW MR HY FDIM50 SOLAR | RAL 7011 | 156 mm | 684 mm | 369 mm |
| 919515813977 | BRP710 LED30 CW MR HY FDIM50 SOLAR | RAL 7011 | 156 mm | 684 mm | 369 mm |
| 919515813980 | BRP710 LED20 CW MR HY SOLAR | RAL 7011 | 156 mm | 684 mm | 369 mm |
| 919515813981 | BRP710 LED30 CW MR HY SOLAR | RAL 7011 | 156 mm | 684 mm | 369 mm |
| 919515813983 | BRP710 LED20 NW MR HY FDIM50 SOLAR | RAL 7011 | 156 mm | 684 mm | 369 mm |
| 919515813984 | BRP710 LED30 NW MR HY FDIM50 SOLAR | RAL 7011 | 156 mm | 684 mm | 369 mm |
| 919515813987 | BRP710 LED20 NW MR HY SOLAR | RAL 7011 | 156 mm | 684 mm | 369 mm |
| 919515813988 | BRP710 LED30 NW MR HY SOLAR | RAL 7011 | 156 mm | 684 mm | 369 mm |
| 919515813990 | BRP710 LED20 WW MR HY FDIM50 SOLAR | RAL 7011 | 156 mm | 684 mm | 369 mm |
| 919515813991 | BRP710 LED30 WW MR HY FDIM50 SOLAR | RAL 7011 | 156 mm | 684 mm | 369 mm |

| Order Code | Full Product Name | Housing Color | Overall height | Overall length | Overall width |
|--------------|--|---------------|----------------|----------------|---------------|
| 919515813994 | BRP710 LED20 WW MR HY SOLAR | RAL 7011 | 156 mm | 684 mm | 369 mm |
| 919515813995 | BRP710 LED30 WW MR HY SOLAR | RAL 7011 | 156 mm | 684 mm | 369 mm |
| 919515812830 | BRP710 LED45 CW MR S1 12V LFP Solar IN | Gray | 188 mm | 757 mm | 511 mm |
| 919515812831 | BRP710 LED45 CW MR S1 12V FD30 Solar IN | Gray | 188 mm | 757 mm | 511 mm |
| 919515813566 | BRP710 LED45 CW MR S1 12V LFP Solar | Gray | 188 mm | 757 mm | 511 mm |
| 919515813567 | BRP710 LED45 CW MR S1 12V FD30 Solar | Gray | 188 mm | 757 mm | 511 mm |
| 919515813568 | BRP710 LED45 WW MR S1 12V LFP Solar | Gray | 188 mm | 757 mm | 511 mm |
| 919515813569 | BRP710 LED45 NW MR S1 12V LFP Solar | Gray | 188 mm | 757 mm | 511 mm |
| 919515813570 | BRP710 LED45 WW MR S1 12V FD30 Solar | Gray | 188 mm | 757 mm | 511 mm |
| 919515813571 | BRP710 LED45 NW MR S1 12V FD30 Solar | Gray | 188 mm | 757 mm | 511 mm |
| 919515814302 | BRP710 LED45 WW 60MO PDIM30 BLE Solar | RAL 7011 | 188 mm | 757 mm | 511 mm |
| 919515898029 | BRP710 LED45 NW 60MO PDIM30 BLE SOLAR EX | RAL 7011 | 188 mm | 757 mm | 511 mm |
| 919515898030 | BRP710 LED45 CW 60MO PDIM30 BLE SOLAR EX | RAL 7011 | 188 mm | 757 mm | 511 mm |
| 919615811180 | BRP710 LED45 CW Housing KIT Solar | Gray | 188 mm | 757 mm | 511 mm |
| 919615811265 | BRP710 P LED45 CW MR 12V LFP Solar P4125 | Gray | 188 mm | 757 mm | 511 mm |
| 919415811054 | SPARE BT LFP 12.8V 13.6Ah SOLAR EQUIP | - | 220 mm | 175 mm | 50 mm |
| 919415811055 | SPARE BT LFP 12.8V 20Ah SOLAR EQUIP | - | 300 mm | 175 mm | 60 mm |
| 919415811056 | SPARE BT LFP 12.8V 30Ah SOLAR EQUIP | - | 300 mm | 175 mm | 60 mm |

Approval and Application

| Order Code | Full Product Name | Ingress protection code |
|--------------|--|-------------------------|
| 919515812627 | BRP710 LED20 CW MR S1 12V 35MO FDIM50 So | IP65 |

| Order Code | Full Product Name | Ingress protection code |
|--------------|--|-------------------------|
| 919515812628 | BRP710 LED20 CW MR S1 12V 35MO Solar Equ | IP65 |

| Order Code | Full Product Name | Ingress protection code |
|--------------|--|-------------------------|
| 919515812631 | BRP710 LED20 CW MR S1 12V 35MO FDIM50 So | IP65 |
| 919515812632 | BRP710 LED20 CW MR S1 12V 35MO Solar Equ | IP65 |
| 919515812969 | BRP710 LED20 WW MR 12V 35MO FDIM50 Solar | IP65 |
| 919515812981 | BRP710 LED20 NW MR 12V 35MO FDIM50 Solar | IP65 |
| 919515813174 | BRP710 LED30 CW MR HY SOLAR IN | IP65 |
| 919515813614 | BRP710 LED20 CW MR HY SOLAR IN | IP65 |
| 919515813615 | BRP710 LED20 CW MR HY FDIM50 SOLAR IN | IP65 |
| 919515813616 | BRP710 LED30 CW MR HY FDIM50 SOLAR IN | IP65 |
| 919515813618 | BRP710 LED45 CW MR HY SOLAR IN | IP65 |
| 919515813617 | BRP710 LED45 CW MR HY FDIM50 SOLAR IN | IP65 |
| 919515813754 | BRP710 LED60 CW MR HY FDIM20 SOLAR IN | IP65 |
| 919515813978 | BRP710 LED45 CW MR HY FDIM50 SOLAR | IP65 |
| 919515813979 | BRP710 LED60 CW MR HY FDIM20 SOLAR | IP65 |
| 919515813982 | BRP710 LED45 CW MR HY SOLAR | IP65 |
| 919515813985 | BRP710 LED45 NW MR HY FDIM50 SOLAR | IP65 |
| 919515813986 | BRP710 LED60 NW MR HY FDIM20 SOLAR | IP65 |
| 919515813989 | BRP710 LED45 NW MR HY SOLAR | IP65 |
| 919515813992 | BRP710 LED45 WW MR HY FDIM50 SOLAR | IP65 |
| 919515813993 | BRP710 LED60 WW MR HY FDIM20 SOLAR | IP65 |
| 919515813996 | BRP710 LED45 WW MR HY SOLAR | IP65 |
| 919515812387 | BRP710 LED20 CW MR S1 12V LFP AIO Solar | IP65 |
| 919515812388 | BRP710 LED30 CW MR S1 12V LFP AIO Solar | IP65 |
| 919515812389 | BRP710 LED20 CW MR S1 12V LFP AIO Solar | IP65 |
| 919515812390 | BRP710 LED30 CW MR S1 12V LFP AIO Solar | IP65 |
| 919515812625 | BRP710 LED20 CW MR S1 12V 28PO PDIM50 So | IP65 |
| 919515812626 | BRP710 LED20 CW MR S1 12V 35MO PDIM50 So | IP65 |
| 919515812629 | BRP710 LED20 CW MR S1 12V 28PO PDIM50 So | IP65 |
| 919515812630 | BRP710 LED20 CW MR S1 12V 35MO PDIM50 So | IP65 |
| 919515812966 | BRP710 LED20 WW MR 12V LFP Solar | IP65 |
| 919515812967 | BRP710 LED20 WW MR 12V 28PO PDIM50 Solar | IP65 |
| 919515812968 | BRP710 LED20 WW MR 12V 35MO PDIM50 Solar | IP65 |
| 919515812970 | BRP710 LED20 WW MR 12V 35MO Solar | IP65 |
| 919515812971 | BRP710 LED30 WW MR 12V LFP AIO Solar | IP65 |
| 919515812978 | BRP710 LED20 NW MR 12V LFP Solar | IP65 |
| 919515812979 | BRP710 LED20 NW MR 12V 28PO PDIM50 Solar | IP65 |
| 919515812980 | BRP710 LED20 NW MR 12V 35MO PDIM50 Solar | IP65 |
| 919515812982 | BRP710 LED20 NW MR 12V 35MO Solar | IP65 |
| 919515812983 | BRP710 LED30 NW MR 12V LFP AIO Solar | IP65 |
| 919515814301 | BRP710 LED30 WW 35MO PDIM30 BLE Solar | IP65 |
| 919515814303 | BRP710 LED30 2700K 60MO PDM30 BLE Solar | IP65 |
| 919515814304 | BRP710 LED30 WW 60MO PDIM30 BLE Solar | IP65 |

| Order Code | Full Product Name | Ingress protection code |
|--------------|--|-------------------------|
| 919515814406 | BRP710 LED20 WW 28PO PDIM50 BLE Solar | IP65 |
| 919515898025 | BRP710 LED20 NW 28PO PDIM50 BLE SOLAR EX | IP65 |
| 919515898026 | BRP710 LED20 CW 28PO PDIM50 BLE SOLAR EX | IP65 |
| 919515898027 | BRP710 LED30 NW 35MO PDIM30 BLE SOLAR EX | IP65 |
| 919515898028 | BRP710 LED30 CW 35MO PDIM30 BLE SOLAR EX | IP65 |
| 919515898031 | BRP710 LED30 NW 60MO PDIM30 BLE SOLAR EX | IP65 |
| 919515898032 | BRP710 LED30 CW 60MO PDIM30 BLE SOLAR EX | IP65 |
| 919515898033 | BRP710 LED20 WW 35MO PDIM50 BLE SOLAR EX | IP65 |
| 919515898034 | BRP710 LED20 NW 35MO PDIM50 BLE SOLAR EX | IP65 |
| 919515898035 | BRP710 LED20 CW 35MO PDIM50 BLE SOLAR EX | IP65 |
| 919615811178 | BRP710 LED20 CW Housing KIT Solar | IP65 |
| 919615811179 | BRP710 LED30 CW Housing KIT Solar | IP65 |
| 919515813976 | BRP710 LED20 CW MR HY FDIM50 SOLAR | IP65 |
| 919515813977 | BRP710 LED30 CW MR HY FDIM50 SOLAR | IP65 |
| 919515813980 | BRP710 LED20 CW MR HY SOLAR | IP65 |
| 919515813981 | BRP710 LED30 CW MR HY SOLAR | IP65 |
| 919515813983 | BRP710 LED20 NW MR HY FDIM50 SOLAR | IP65 |
| 919515813984 | BRP710 LED30 NW MR HY FDIM50 SOLAR | IP65 |
| 919515813987 | BRP710 LED20 NW MR HY SOLAR | IP65 |
| 919515813988 | BRP710 LED30 NW MR HY SOLAR | IP65 |
| 919515813990 | BRP710 LED20 WW MR HY FDIM50 SOLAR | IP65 |
| 919515813991 | BRP710 LED30 WW MR HY FDIM50 SOLAR | IP65 |
| 919515813994 | BRP710 LED20 WW MR HY SOLAR | IP65 |
| 919515813995 | BRP710 LED30 WW MR HY SOLAR | IP65 |
| 919515812830 | BRP710 LED45 CW MR S1 12V LFP Solar IN | IP65 |
| 919515812831 | BRP710 LED45 CW MR S1 12V FD30 Solar IN | IP65 |
| 919515813566 | BRP710 LED45 CW MR S1 12V LFP Solar | IP65 |
| 919515813567 | BRP710 LED45 CW MR S1 12V FD30 Solar | IP65 |
| 919515813568 | BRP710 LED45 WW MR S1 12V LFP Solar | IP65 |
| 919515813569 | BRP710 LED45 NW MR S1 12V LFP Solar | IP65 |
| 919515813570 | BRP710 LED45 WW MR S1 12V FD30 Solar | IP65 |
| 919515813571 | BRP710 LED45 NW MR S1 12V FD30 Solar | IP65 |
| 919515814302 | BRP710 LED45 WW 60MO PDIM30 BLE Solar | IP65 |
| 919515898029 | BRP710 LED45 NW 60MO PDIM30 BLE SOLAR EX | IP65 |
| 919515898030 | BRP710 LED45 CW 60MO PDIM30 BLE SOLAR EX | IP65 |
| 919615811180 | BRP710 LED45 CW Housing KIT Solar | IP65 |
| 919615811265 | BRP710 P LED45 CW MR 12V LFP Solar P4125 | IP65 |
| 919415811054 | SPARE BT LFP 12.8V 13.6Ah SOLAR EQUIP | - |
| 919415811055 | SPARE BT LFP 12.8V 20Ah SOLAR EQUIP | - |
| 919415811056 | SPARE BT LFP 12.8V 30Ah SOLAR EQUIP | - |

Application Conditions

| Order Code | Full Product Name | Ambient temperature range for discharging (when light is on) | Battery location | Grid connection type | Solar dimming profile |
|--------------|---|--|------------------|----------------------|-----------------------|
| 919515812627 | BRP710 LED20 CW MR S1 12V 35MO FDIM50 So | -20 °C to +35 °C | Inside Luminaire | Off grid | 5hrs 100% + 7 hrs 50% |
| 919515812628 | BRP710 LED20 CW MR S1 12V 35MO Solar Equ | -20 °C to +35 °C | Inside Luminaire | Off grid | No Dimming |
| 919515812631 | BRP710 LED20 CW MR S1 12V 35MO FDIM50 So | -20 °C to +35 °C | Inside Luminaire | Off grid | 5hrs 100% + 7 hrs 50% |
| 919515812632 | BRP710 LED20 CW MR S1 12V 35MO Solar Equ | -20 °C to +35 °C | Inside Luminaire | Off grid | No Dimming |
| 919515812699 | BRP710 LED20 WW MR 12V 35MO FDIM50 Solar | -20 °C to +35 °C | Inside Luminaire | Off grid | 5hrs 100% + 7 hrs 50% |
| 919515812981 | BRP710 LED20 NW MR 12V 35MO FDIM50 Solar | -20 °C to +35 °C | Inside Luminaire | Off grid | 5hrs 100% + 7 hrs 50% |
| 919515813174 | BRP710 LED30 CW MR HY SOLAR IN | -20 °C to +35 °C | Integrated | Hybrid | 100% Dusk to dawn |
| 919515813614 | BRP710 LED20 CW MR HY SOLAR IN | -20 °C to +35 °C | Integrated | Hybrid | 100% Dusk to dawn |
| 919515813615 | BRP710 LED20 CW MR HY FDIM50 SOLAR IN | -20 °C to +35 °C | Integrated | Hybrid | 5hrs 100% + 7 hrs 50% |
| 919515813616 | BRP710 LED30 CW | -20 °C to +35 °C | Integrated | Hybrid | 5hrs 100% + 7 hrs 50% |

| Order Code | Full Product Name | Ambient temperature range for discharging (when light is on) | Battery location | Grid connection type | Solar dimming profile |
|--------------|---|--|------------------|----------------------|-----------------------|
| | MR HY FDIM50 SOLAR IN | | | | |
| 919515813168 | BRP710 LED45 CW MR HY SOLAR IN | -20 °C to +35 °C | Integrated | Hybrid | 100% Dusk to dawn |
| 919515813617 | BRP710 LED45 CW MR HY FDIM50 SOLAR IN | -20 °C to +35 °C | Integrated | Hybrid | 5hrs 100% + 7 hrs 50% |
| 919515813754 | BRP710 LED60 CW MR HY FDIM20 SOLAR IN | -20 °C to +35 °C | Integrated | Hybrid | 4hrs 100% + 8 hrs 20% |
| 919515813978 | BRP710 LED45 CW MR HY FDIM50 SOLAR | -20 °C to +35 °C | Inside Luminaire | Hybrid | 5hrs 100% + 7 hrs 50% |
| 919515813979 | BRP710 LED60 CW MR HY FDIM20 SOLAR | -20 °C to +35 °C | Inside Luminaire | Hybrid | 4hrs 100% + 8 hrs 20% |
| 919515813982 | BRP710 LED45 CW MR HY SOLAR | -20 °C to +35 °C | Inside Luminaire | Hybrid | 100% Dusk to dawn |
| 919515813985 | BRP710 LED45 NW MR HY FDIM50 SOLAR | -20 °C to +35 °C | Inside Luminaire | Hybrid | 5hrs 100% + 7 hrs 50% |
| 919515813986 | BRP710 LED60 NW MR HY FDIM20 SOLAR | -20 °C to +35 °C | Inside Luminaire | Hybrid | 4hrs 100% + 8 hrs 20% |
| 919515813989 | BRP710 LED45 NW MR HY SOLAR | -20 °C to +35 °C | Inside Luminaire | Hybrid | 100% Dusk to dawn |
| 919515813992 | BRP710 LED45 WW | -20 °C to +35 °C | Inside Luminaire | Hybrid | 5hrs 100% + 7 hrs 50% |

| Order Code | Full Product Name | Ambient temperature range for discharging (when light is on) | | Battery location | Grid connection type | Solar dimming profile |
|--------------|--|--|--|------------------|----------------------|--|
| | | | | | | |
| | MR HY FDIM50 SOLAR | | | | | |
| 919515813993 | BRP710 LED60 WW MR HY FDIM20 SOLAR | -20 °C to +35 °C | | Inside Luminaire | Hybrid | 4hrs 100% + 8 hrs 20% |
| 919515813996 | BRP710 LED45 WW MR HY SOLAR | -20 °C to +35 °C | | Inside Luminaire | Hybrid | 100% Dusk to dawn |
| 919515812387 | BRP710 LED20 CW MR S1 12V LFP AIO Solar | -20 °C to +35 °C | | Inside Luminaire | Off grid | 30% Dusk to dawn, 100% on motion. (Sensor disabled for 5 Hrs, after 5 Hrs) |
| 919515812388 | BRP710 LED30 CW MR S1 12V LFP AIO Solar | -20 °C to +35 °C | | Inside Luminaire | Off grid | 30% Dusk to dawn, 100% on motion. (Sensor disabled for 5 Hrs, after 5 Hrs) |
| 919515812389 | BRP710 LED20 CW MR S1 12V LFP AIO Solar | -20 °C to +35 °C | | Inside Luminaire | Off grid | 30% Dusk to dawn, 100% on motion. (Sensor disabled for 5 Hrs, after 5 Hrs) |
| 919515812390 | BRP710 LED30 CW MR S1 12V LFP AIO Solar | -20 °C to +35 °C | | Inside Luminaire | Off grid | 30% Dusk to dawn, 100% on motion. (Sensor disabled for 5 Hrs, after 5 Hrs) |
| 919515812625 | BRP710 LED20 CW MR S1 12V 28PO PDIM50 So | -20 °C to +35 °C | | Inside Luminaire | Off grid | 50% Dusk to dawn, 100% on Motion. (Sensor disabled for 5 Hrs, after 5 Hrs) |

| Order Code | Full Product Name | Ambient temperature range for discharging (when light is on) | | Battery location | Grid connection type | Solar dimming profile |
|--------------|---|--|--|------------------|----------------------|--|
| | | | | | | |
| 919515812626 | BRP710 LED20 CW MR S1 12V 35MO PDIM50 So | -20 °C to +35 °C | | Inside Luminaire | Off grid | 50% Dusk to dawn, 100% on Motion. (Sensor disabled for 5 Hrs, after 5 Hrs) |
| 919515812629 | BRP710 LED20 CW MR S1 12V 28PO PDIM50 So | -20 °C to +35 °C | | Inside Luminaire | Off grid | 50% Dusk to dawn, 100% on Motion. (Sensor disabled for 5 Hrs, after 5 Hrs) |
| 919515812630 | BRP710 LED20 CW MR S1 12V 35MO PDIM50 So | -20 °C to +35 °C | | Inside Luminaire | Off grid | 50% Dusk to dawn, 100% on Motion. (Sensor disabled for 5 Hrs, after 5 Hrs) |
| 919515812966 | BRP710 LED20 WW MR 12V LFP Solar | -20 °C to +35 °C | | Inside Luminaire | Off grid | 30% Dusk to dawn, 100% on motion. (Sensor disabled for 5 Hrs, after 5 Hrs) |
| 919515812967 | BRP710 LED20 WW MR 12V 28PO PDIM50 Solar | -20 °C to +35 °C | | Inside Luminaire | Off grid | 50% Dusk to dawn, 100% on Motion. (Sensor disabled for 5 Hrs, after 5 Hrs) |
| 919515812968 | BRP710 LED20 WW MR 12V 35MO PDIM50 Solar | -20 °C to +35 °C | | Inside Luminaire | Off grid | 50% Dusk to dawn, 100% on Motion. (Sensor disabled for 5 Hrs, after 5 Hrs) |
| 919515812970 | BRP710 LED20 WW MR 12V 35MO Solar | -20 °C to +35 °C | | Inside Luminaire | Off grid | No dimming |

| Order Code | Full Product Name | Ambient temperature range for discharging | Battery location | Grid connection type | Solar dimming profile |
|--------------|---|---|---------------------|----------------------|--|
| | | (when light is on) | | | |
| 919515812971 | BRP710 LED30 WW MR 12V LFP AIO Solar | -20 °C to +35 °C | Inside Luminaire | Off grid | 30% Dusk to dawn, 100% on motion. (Sensor disabled for 5 Hrs, after 5 Hrs) |
| 919515812978 | BRP710 LED20 NW MR 12V LFP Solar | -20 °C to +35 °C | Inside Luminaire | Off grid | 30% Dusk to dawn, 100% on motion. (Sensor disabled for 5 Hrs, after 5 Hrs) |
| 919515812979 | BRP710 LED20 NW MR 12V 28PO PDIM50 Solar | -20 °C to +35 °C | Inside Luminaire | Off grid | 50% Dusk to dawn, 100% on Motion. (Sensor disabled for 5 Hrs, after 5 Hrs) |
| 919515812980 | BRP710 LED20 NW MR 12V 35MO PDIM50 Solar | -20 °C to +35 °C | Inside Luminaire | Off grid | 50% Dusk to dawn, 100% on Motion. (Sensor disabled for 5 Hrs, after 5 Hrs) |
| 919515812982 | BRP710 LED20 NW MR 12V 35MO Solar | -20 °C to +35 °C | Inside Luminaire | Off grid | No dimming |
| 919515812983 | BRP710 LED30 NW MR 12V LFP AIO Solar | -20 °C to +35 °C | Inside Luminaire | Off grid | 30% Dusk to dawn, 100% on motion. (Sensor disabled for 5 Hrs, after 5 Hrs) |
| 919515814301 | BRP710 LED30 WW 35MO PDIM30 BLE Solar | -20 °C to +35 °C | Inside Luminaire | Off grid | 30% Dusk to dawn, 100% on motion. (Sensor disabled for 5 Hrs, after 5 Hrs) |

| Order Code | Full Product Name | Ambient temperature range for discharging | Battery location | Grid connection type | Solar dimming profile |
|--------------|---|---|---------------------|----------------------|--|
| | | (when light is on) | | | |
| 919515814303 | BRP710 LED30 2700K 60MO PDM30 BLE Solar | -20 °C to +35 °C | Inside Luminaire | Off grid | 30% Dusk to dawn, 100% on motion. (Sensor disabled for 5 Hrs, after 5 Hrs) |
| 919515814304 | BRP710 LED30 WW 60MO PDIM30 BLE Solar | -20 °C to +35 °C | Inside Luminaire | Off grid | 30% Dusk to dawn, 100% on motion. (Sensor disabled for 5 Hrs, after 5 Hrs) |
| 919515814406 | BRP710 LED20 WW 28PO PDIM50 BLE Solar | -20 °C to +35 °C | Inside Luminaire | Off grid | 50% Dusk to dawn, 100% on motion. (Sensor disabled for 5 Hrs, after 5 Hrs) |
| 919515898025 | BRP710 LED20 NW 28PO PDIM50 BLE SOLAR EX | -20 °C to +35 °C | Inside Luminaire | Off grid | 50% Dusk to dawn, 100% on motion. (Sensor disabled for 5 Hrs, after 5 Hrs) |
| 919515898026 | BRP710 LED20 CW 28PO PDIM50 BLE SOLAR EX | -20 °C to +35 °C | Inside Luminaire | Off grid | 50% Dusk to dawn, 100% on motion. (Sensor disabled for 5 Hrs, after 5 Hrs) |
| 919515898027 | BRP710 LED30 NW 35MO PDIM30 BLE SOLAR EX | -20 °C to +35 °C | Inside Luminaire | Off grid | 30% Dusk to dawn, 100% on motion. (Sensor disabled for 5 Hrs, after 5 Hrs) |
| 919515898028 | BRP710 LED30 CW 35MO PDIM30 | -20 °C to +35 °C | Inside Luminaire | Off grid | 30% Dusk to dawn, 100% on motion. (Sensor disabled for 5 Hrs, after 5 Hrs) |

| Order Code | Full Product Name | Ambient temperature range for discharging (when light is on) | Battery location | Grid connection type | Solar dimming profile |
|--------------|--|--|------------------|----------------------|---|
| | BLE SOLAR EX | | | | Hrs, after 5 Hrs) |
| 919515898031 | BRP710 LED30 NW 60MO PDIM30 BLE SOLAR EX | -20 °C to +35 °C | Inside Luminaire | Off grid | 30% Dusk to dawn, 100% on motion. (Sensor disabled for 5 Hrs, after 5 Hrs) |
| 919515898032 | BRP710 LED30 CW 60MO PDIM30 BLE SOLAR EX | -20 °C to +35 °C | Inside Luminaire | Off grid | 30% Dusk to dawn, 100% on motion. (Sensor disabled for 5 Hrs, after 5 Hrs) |
| 919515898033 | BRP710 LED20 WW 35MO PDIM50 BLE SOLAR EX | -20 °C to +35 °C | Inside Luminaire | Off grid | 50% Dusk to dawn, 100% on motion. (Sensor disabled for 5 Hrs, after 5 Hrs) |
| 919515898034 | BRP710 LED20 NW 35MO PDIM50 BLE SOLAR EX | -20 °C to +35 °C | Inside Luminaire | Off grid | 50% Dusk to dawn, 100% on motion. (Sensor disabled for 5 Hrs, after 5 Hrs) |
| 919515898035 | BRP710 LED20 CW 35MO PDIM50 BLE SOLAR EX | -20 °C to +35 °C | Inside Luminaire | Off grid | 50% Dusk to dawn, 100% on motion. (Sensor disabled for 5 Hrs, after 5 Hrs) |
| 919615811178 | BRP710 LED20 CW Housing KIT Solar | -20 °C to +35 °C | Inside Luminaire | Off grid | 30% Dusk to dawn, 100% on motion. (Sensor disabled for 5 Hrs, after 5 Hrs) |
| 919615811179 | BRP710 LED30 CW | -20 °C to +35 °C | Inside Luminaire | Off grid | 30% Dusk to dawn, 100% on motion. |

| Order Code | Full Product Name | Ambient temperature range for discharging (when light is on) | Battery location | Grid connection type | Solar dimming profile |
|--------------|------------------------------------|--|------------------|----------------------|---|
| | Housing KIT Solar | | | | (Sensor disabled for 5 Hrs, after 5 Hrs) |
| 919515813976 | BRP710 LED20 CW MR HY FDIM50 SOLAR | -20 °C to +35 °C | Inside Luminaire | Hybrid | 5hrs 100% + 7 hrs 50% |
| 919515813977 | BRP710 LED30 CW MR HY FDIM50 SOLAR | -20 °C to +35 °C | Inside Luminaire | Hybrid | 5hrs 100% + 7 hrs 50% |
| 919515813980 | BRP710 LED20 CW MR HY SOLAR | -20 °C to +35 °C | Inside Luminaire | Hybrid | 100% Dusk to dawn |
| 919515813981 | BRP710 LED30 CW MR HY SOLAR | -20 °C to +35 °C | Inside Luminaire | Hybrid | 100% Dusk to dawn |
| 919515813983 | BRP710 LED20 NW MR HY FDIM50 SOLAR | -20 °C to +35 °C | Inside Luminaire | Hybrid | 5hrs 100% + 7 hrs 50% |
| 919515813984 | BRP710 LED30 NW MR HY FDIM50 SOLAR | -20 °C to +35 °C | Inside Luminaire | Hybrid | 5hrs 100% + 7 hrs 50% |
| 919515813987 | BRP710 LED20 NW MR HY SOLAR | -20 °C to +35 °C | Inside Luminaire | Hybrid | 100% Dusk to dawn |
| 919515813988 | BRP710 LED30 NW MR HY SOLAR | -20 °C to +35 °C | Inside Luminaire | Hybrid | 100% Dusk to dawn |
| 919515813990 | BRP710 LED20 WW MR HY FDIM50 SOLAR | -20 °C to +35 °C | Inside Luminaire | Hybrid | 5hrs 100% + 7 hrs 50% |
| 919515813991 | BRP710 LED30 WW | -20 °C to +35 °C | Inside Luminaire | Hybrid | 5hrs 100% + 7 hrs 50% |

| Order Code | Full Product Name | Ambient temperature range for discharging (when light is on) | Battery location | Grid connection type | Solar dimming profile |
|--------------|--|--|------------------|----------------------|--|
| | MR HY FDIM50 SOLAR | | | | |
| 919515813994 | BRP710 LED20 WW MR HY SOLAR | -20 °C to +35 °C | Inside Luminaire | Hybrid | 100% Dusk to dawn |
| 919515813995 | BRP710 LED30 WW MR HY SOLAR | -20 °C to +35 °C | Inside Luminaire | Hybrid | 100% Dusk to dawn |
| 919515812830 | BRP710 LED45 CW MR S1 12V LFP Solar IN | -20 °C to +35 °C | Inside Luminaire | Off grid | 30% Dusk to dawn, 100% on motion. (Sensor disabled for 5 Hrs, after 5 Hrs) |
| 919515812831 | BRP710 LED45 CW MR S1 12V FD30 Solar IN | -20 °C to +35 °C | Inside Luminaire | Off grid | 5hrs 100% + 7 hrs 30% |
| 919515813566 | BRP710 LED45 CW MR S1 12V LFP Solar | -20 °C to +35 °C | Inside Luminaire | Off grid | 30% Dusk to dawn, 100% on motion. (Sensor disabled for 5 Hrs, after 5 Hrs) |
| 919515813567 | BRP710 LED45 CW MR S1 12V FD30 Solar | -20 °C to +35 °C | Inside Luminaire | Off grid | 5hrs 100% + 7 hrs 30% |
| 919515813568 | BRP710 LED45 WW MR S1 12V LFP Solar | -20 °C to +35 °C | Inside Luminaire | Off grid | 30% Dusk to dawn, 100% on motion. (Sensor disabled for 5 Hrs, after 5 Hrs) |
| 919515813569 | BRP710 LED45 NW MR S1 12V LFP Solar | -20 °C to +35 °C | Inside Luminaire | Off grid | 30% Dusk to dawn, 100% on motion. (Sensor disabled for 5 Hrs, after 5 Hrs) |

| Order Code | Full Product Name | Ambient temperature range for discharging (when light is on) | Battery location | Grid connection type | Solar dimming profile |
|--------------|---|--|------------------|----------------------|--|
| | | | | | Hrs, after 5 Hrs) |
| 919515813570 | BRP710 LED45 WW MR S1 12V FD30 Solar | -20 °C to +35 °C | Inside Luminaire | Off grid | 5hrs 100% + 7 hrs 30% |
| 919515813571 | BRP710 LED45 NW MR S1 12V FD30 Solar | -20 °C to +35 °C | Inside Luminaire | Off grid | 5hrs 100% + 7 hrs 30% |
| 919515814302 | BRP710 LED45 WW 60MO PDIM30 BLE Solar | -20 °C to +35 °C | Inside Luminaire | Off grid | 30% Dusk to dawn, 100% on motion. (Sensor disabled for 5 Hrs, after 5 Hrs) |
| 919515898029 | BRP710 LED45 NW 60MO PDIM30 BLE SOLAR EX | -20 °C to +35 °C | Inside Luminaire | Off grid | 30% Dusk to dawn, 100% on motion. (Sensor disabled for 5 Hrs, after 5 Hrs) |
| 919515898030 | BRP710 LED45 CW 60MO PDIM30 BLE SOLAR EX | -20 °C to +35 °C | Inside Luminaire | Off grid | 30% Dusk to dawn, 100% on motion. (Sensor disabled for 5 Hrs, after 5 Hrs) |
| 919615811180 | BRP710 LED45 CW Housing KIT Solar | -20 °C to +35 °C | Inside Luminaire | Off grid | 30% Dusk to dawn, 100% on motion. (Sensor disabled for 5 Hrs, after 5 Hrs) |
| 919615811265 | BRP710 P LED45 CW MR 12V LFP Solar P4125 | -20 °C to +35 °C | Inside Luminaire | Off grid | 30% Dusk to dawn, 100% on motion. (Sensor disabled for 5 Hrs, after 5 Hrs) |
| 919415811054 | SPARE BT LFP 12.8V | -20 °C to +60 °C | - | - | - |

| Order Code | Full Product Name | Ambient temperature range for discharging (when light is on) | | | |
|--------------|-------------------------------|--|----------------------|-----------------------|---|
| | | Battery location | Grid connection type | Solar dimming profile | |
| | 13.6Ah SOLAR EQUIP | | | | |
| 919415811055 | SPARE BT LFP 12.8V 20Ah | -20 °C to +60 °C | - | - | - |

| Order Code | Full Product Name | Ambient temperature range for discharging (when light is on) | | | |
|--------------|---|--|----------------------|-----------------------|---|
| | | Battery location | Grid connection type | Solar dimming profile | |
| | SOLAR EQUIP | | | | |
| 919415811056 | SPARE BT LFP 12.8V 30Ah SOLAR EQUIP | -20 °C to +60 °C | - | - | - |

