



# Urban style that last. All-purpose lighting solution.

## **VistaGlow**

VistaGlow bulkhead is an IP65, all-purpose lighting solution meant for indoor and semi outdoor application. This luminaire is designed to offer general lighting for applications such as staircases, circulation areas in the buildings and lift wells etc. VistaGlow bulkhead has robust all-weather design with a pressure die casting housing and polycarbonate cover which are sealed for life to offer a dustproof and waterproof solution. The product is available in three color temperatures to meet the requirements of different applications.

#### **Benefits**

- $\cdot$  Aesthetical design that combines well with the interiors
- $\boldsymbol{\cdot}$  Suitable for use on dusty and semi outdoor environment
- $\cdot \ \mathsf{Best\text{-}in\text{-}class} \ \mathsf{efficacy}, \ \mathsf{low} \ \mathsf{connected} \ \mathsf{load}$
- $\boldsymbol{\cdot}$  Creates a diffused natural light, ensuring visual comfort
- · Long useful life with low maintenance
- · Multiple options in CCT make it suitable for different applications in indoor
- Easy to install

#### **Features**

- · High ingress protection-IP65
- · Impact resitant-IK08
- · Compact integral design
- · Light color: 4000K, 6500K
- · Pressure diecast housing and polycarbonate cover
- External mounting through simple tools

#### **VistaGlow**

## **Application**

- · Lift wells
- Staircases
- · Indoor circulation areas
- · Wall mounted application in semi outdoor area
- Balconies and terraces
- Government buildings

# Warnings and Safety

 $\cdot$  Meant for use in Indoor Industrial environment only

#### Versions



#### WT140W LED7S

## Dimensional drawing





#### **Product details**



#### WT140W LED7S



#### WT140W LED7S

# **VistaGlow**

## **Product details**



#### WT140W LED7S

General Information	
Driver included	Yes
Light Technical	
Beam angle of light source	120 degree(s)
Optical cover type	Polycarbonate
Color rendering index (CRI)	>80
Luminous Efficacy (rated) (Nom)	107 lm/W
Luminous Flux	700 lm
Optic type	Beam angle 120°
Operating and Electrical	
Input Voltage	140-270 V
Power Consumption	6.5 W
Temperature	
Ambient temperature range	0 to +45 ℃
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Housing Color	Gray
Approval and Application	
Protection class IEC	Safety class I
Flammability mark	For mounting on
	normally
	flammable
	surfaces
Mech. impact protection code	IK08
Ingress protection code	IP65
Initial Performance (IEC Compl	iant)
Initial chromaticity	<5

# Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)
919515812243	WT140W LED7S CW PSU S1 PC	6500 K
919515812244	WT140W LED7S NW PSU S1 PC	4000 K

## **VistaGlow**



© 2024 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.