



# **Robust Design, superior performance, Unparallel strength and Durability with Superior aesthetics suitable for versatile road applications**

## **Skyline BRP340**

Skyline is sleek and elegant design innovative streetlight with best in class energy efficiency. Ease of maintenance with integrated optics makes it unique and differentiated from others. Skyline uses High efficacy driver and LED platform to ensure higher energy saving and reliable operation over committed lifetime. Skyline LED Luminaire is a solid LM 6 alloy Pressure die-cast IK 09 rated housing, ensuring high strength and safety on the pole. The solid die-cast aluminum also has excellent heat dissipation, extending the life of the components inside. The multiple lumen packs with dedicated street optics makes it optimum for the A1 and A2 category of Roads.

### **Benefits**

- Maximize the Energy savings
- Unparallel Strength and Durability with excellent thermal management leads to longer life class for luminaire
- Option of multiple optics and lumen packages providing application flexibility
- Easy serviceability with simple tools

# Skyline BRP340

## Features

- Ingress Protection -IP66
- Impact Resistance IK08
- Inbuilt encapsulated Potted Driver
- Designed for operations under diverse environment from -10°C to 35°C
- Life class is 50000 hours (L70B50 @ Ta35°C)
- Pressure die-cast housing offers excellent corrosion-resistance and robustness
- System efficiency >110 lm/W
- System lumen 14000lm, 16000lm, & 18000lm options
- High Voltage Cutoff @ 325 ± 15V with Auto Restart feature
- 440V Protection for 8 Hrs. (Phase to Phase)
- Internal Surge Protection 4KV
- Mounting Pole Diameter: 48mm to 60mm
- Class B Serviceability with Top openable cover


## Application

- Road and Street
- Highways and Express ways
- City main traffic roads
- City shopping & commercial roads
- Residential streets
- Industrial roads

## Warnings and Safety

- Meant for use in Outdoor Environment only

## Dimensional drawing



Skyline BRP340

General Information	
Driver included	Yes
Light Technical	
Luminaire light beam spread	60°
Light source color	857 daylight
Correlated Color Temperature (Nom)	5700 K
Color rendering index (CRI)	>70
Optic type outdoor	Asymmetrical axis angle 60° wide beam
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Optical cover type	Polycarbonate
Housing Color	Gray
Mech. impact protection code	IK08
Ingress protection code	IP65
Approval and Application	
Ambient temperature range	0 to +35 °C
Flammability mark	For mounting on normally flammable surfaces

Light Technical

Order Code	Full Product Name	Luminous Efficacy (rated) (Nom)	Luminous Flux
919515812407	BRP 340 LED 184 CW HO SLC S1 PSU GR	113 lm/W	18,000 lm
919515812537	BRP 340 LED 161 CW HO SLC S1 PSU GR	114 lm/W	16,000 lm
919515812539	BRP 340 LED 138 CW HO SLC S1 PSU GR SPD	117 lm/W	14,000 lm
919515812541	BRP 340 LED 161 CW HO SLC S1 PSU GR SPD	122 lm/W	16,000 lm
919515812543	BRP 340 LED 184 CW HO SLC S1 PSU GR SPD	122 lm/W	18,000 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
919515812407	BRP 340 LED 184 CW HO SLC S1 PSU GR	160 W	Surge protection level until 4 kV
919515812537	BRP 340 LED 161 CW HO SLC S1 PSU GR	140 W	Surge protection level until 4 kV
919515812539	BRP 340 LED 138 CW HO SLC S1 PSU GR SPD	120 W	Surge protection level until 10 kV differential mode

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
919515812541	BRP 340 LED 161 CW HO SLC S1 PSU GR SPD	140 W	Surge protection level until 10 kV differential mode
919515812543	BRP 340 LED 184 CW HO SLC S1 PSU GR SPD	160 W	Surge protection level until 10 kV differential mode

