



Ahead in flexibility and connectivity

Xitanium LED linear drivers – non-isolated

Xitanium linear non-isolated drivers are ideal for high voltage (HV) professional general lighting applications. The range includes DALI dimmable and programmable, 1-10V dimmable, non-dimmable and single current versions. They offer high efficiency, good quality of light and full flexibility. The new generation of 16mm DALI drivers offer ultimate performance. They comply with the latest DiiA standards, including implementation of the new DALI parts related to data. Configuring the drivers can be done quickly and wirelessly with SimpleSet. The new 21mm DALI drivers offer the best value for money.

Benefits

- Non-isolated drivers to support HV and LV linear office systems
- Flexible operating windows to simplify dynamic generation and complexity management
- Complete range of Sensor Ready (SR) drivers for connected systems

Features

- Non-isolated DALI and Fixed Output drivers with 11 mm and 16 mm height
- Flexible programming of DALI drivers via MultiOne software or wireless via SimpleSet
- Low ripple output current for camera- and scanner-friendly performance
- Unique AM dimming in DALI drivers for flicker and noise-free dimming
- Five-year system warranty and 100,000 hour lifetime

Application

- Office
- Retail
- Industry

Xitanium LED linear drivers – non-isolated

Versions



Xitanium LED linear drivers - Non - Isolated family



Xitanium 100W FO 16



CertaDrive 60W 350mA




CertaDrive 30W 0.35A 85V 230V
EL Image



Xitanium non-iso TD21

Dimensional drawing



Product	A1	A2	B1	C1	D1
Xitanium 100W 0.15-0.5A 300V iXt 230V	360 mm	350 mm	30 mm	21 mm	4.1 mm

Xtanium LED linear drivers – non-isolated

