



# TownTune Conical Comfort Bowl - Extending the home feel onto the street

## TownTune CCB

Designed to enhance existing and scalable urban spaces, the TownTune family offers all the latest lighting innovations in terms of performance, quality of light and connectivity. The family consists of four solutions: a Central Post Top (CPT), an Asymmetric Spigot Post Top / Side Entry version (ASY), a version with an extending Lyre post top bracket (Lyre), and a Central Post Top with a Conical Comfort Bowl (CCB). Each TownTune luminaire can be customized with a choice of different shapes on top of the housing, plus there's the option to add a decorative ring, which comes in two colors (excluding CCB). Design options that enable you to create your very own lighting signature and bring a distinctive identity to districts and cities. In addition, every luminaire in the TownTune family is uniquely identifiable, thanks to the Signify Service tag app. By simply scanning a QR code, placed inside the door of the mast or directly on the luminaire, you can instantly access the configuration of the luminaire. This makes maintenance and programming operations faster and easier and enables you to create your digital library of lighting assets and spare parts. TownTune also uses the LEDGINE-O lighting platform, ensuring you always have the right amount and direction of light on your street. Furthermore, thanks to being system ready (SR), TownTune is also future proof. A solution that's ready to be paired with both standalone and advanced control and lighting software applications such as Interact City.

## TownTune CCB

### Benefits

- LEDGINE-O platform for great performance, choice color temperatures and light distributions
- Optimized Total Cost of Ownership (L-Tune for flux tuning, standalone controls e.g., LumiStep, Dynadimmer, CLO (Constant Light output), LineSwitch)
- Ready to pair with advanced systems and software applications e.g., Interact City
- Long lifetime: 100,000 hours @L85 and higher
- Easy access to gear, vandal resistant (IK10), high ingress protection (IP66)

### Features

- Simple design for easy integration into urban spaces, wide range of accessories for customization
- Suitable for new and retrofit installations
- Range of lumen packages (1200 to 12000 lm) and CCTs (2200K, 2700K, 3000K, 4000K)
- Dedicated bowl for visual comfort and comfortable lighting experiences
- Service tag for easy installation and maintenance.

### Application

- Urban and residential areas
- Cycle paths, footpaths, and pedestrian crossings
- City centers and squares
- Car parks

### Versions







TownTune CCB, BDP277 with dome





TownTune CCB, BDP278 with dome

### Dimensional drawing



Dimensional drawing



General Information	
Driver included	Yes
Light source replaceable	Yes
Number of gear units	1 unit
Service tag	Yes
Light Technical	
Color rendering index (CRI)	70
Controls and Dimming	
Maximum dim level	10%
Mechanical and Housing	
Housing Color	Anthracite
Ingress protection code	IP66
Standard tilt angle side entry	-
Standard tilt angle posttop	0°
Approval and Application	
CE mark	Yes
Flammability mark	For mounting on normally flammable surfaces

Order Code	Full Product Name	Lamp family code
912300060078	BDP276 LED20-4S-740 DX52 CLO-DDF1 62P	LED20
912300060079	BDP276 LED35-4S-730 II DS50 D9 76P	LED35
912300060080	BDP276 LED39-4S/740 II DW10 DDF1 SDM10 6	LED39
912300060132	BDP276 LED24-4S/730 DX52 DGR D9 62P	LED24
912300060081	BDP277 LED35-4S-730 II DW50 DGR D9 62P	LED35
912300060076	BDP275 LED14-4S-730 DX52 CLO SRT 62P	LED14
912300060077	BDP275 LED39-4S-727 II DM50 CLOD9 MSP62P	LED39
912300060131	BDP275 LED22-4S/730 DW50 DGR D9 62P	LED22
912300060252	BDP275 LED14-4S/730 PSD DM12 PCC DGR D9	LED14
912300060253	BDP275 LED14-4S/730 PSD DX52 PCC DGR D9	LED14
912300060254	BDP275 LED18-4S/730 PSD DX52 PCC DGR D9	LED18
912300060276	BDP275 LED14-4S/730 DM11 PCC DGR D9 62P	LED14
912300060082	BDP278 LED35-4S-740- DM10 DGR D9 62P	LED35

Light Technical (1/2)

Order Code	Full Product Name	Luminaire		Correlated	
		light beam spread	Light source color	Color Temperature (Nom)	Luminous Flux
912300060078	BDP276	-	740	4000 K	1,560 lm
	LED20-4S-740		neutral		
	DX52 CLO-DDF1		white		
	62P				
912300060079	BDP276	152° x 155°	730	3000 K	2,730 lm
	LED35-4S-730 II		warm		
	DS50 D9 76P		white		

Order Code	Full Product Name	Luminaire		Correlated	
		light beam spread	Light source color	Color Temperature (Nom)	Luminous Flux
912300060080	BDP276	7° - 52° x	740	4000 K	3,120 lm
	LED39-4S/740 II	150°	neutral		
	DW10 DDF1 SDM10		white		
	6				
912300060132	BDP276	-	730	3000 K	1,920 lm
	LED24-4S/730		warm		
	DX52 DGR D9 62P		white		

Order Code	Full Product Name	Luminaire	Light	Correlated	Luminous
		light beam	source	Color	
		spread	color	Temperature	Flux
(Nom)				(Nom)	
912300060081	BDP277	12° - 29° x	730	3000 K	2,730 lm
	LED35-4S-730 II	152°	warm		
	DW50 DGR D9 62P		white		
912300060076	BDP275	-	730	3000 K	1,120 lm
	LED14-4S-730		warm		
	DX52 CLO SRT 62P		white		
912300060077	BDP275	30° - 5° x	727	2700 K	2,926 lm
	LED39-4S-727 II	153°	warm		
	DM50 CLOD9		white		
	MSP62P				
912300060131	BDP275	12° - 29° x	730	3000 K	1,760 lm
	LED22-4S/730	152°	warm		
	DW50 DGR D9 62P		white		
912300060252	BDP275	88° x 157°	730	3000 K	1,162 lm
	LED14-4S/730 PSD		warm		
	DM12 PCC DGR D9		white		

Light Technical (2/2)

Order Code	Full Product Name	Optic type outdoor	Upward
			light
			output
			ratio
912300060078	BDP276 LED20-4S-740 DX52	Distribution Extra	0.035
	CLO-DDF1 62P	Wide DX52	
912300060079	BDP276 LED35-4S-730 II DS50 D9	Distribution	0.0337
	76P	symmetrical 50	
912300060080	BDP276 LED39-4S/740 II DW10	Distribution wide 10	0.0374
	DDF1 SDM10 6		
912300060132	BDP276 LED24-4S/730 DX52 DGR	Distribution Extra	0.035
	D9 62P	Wide DX52	
912300060081	BDP277 LED35-4S-730 II DW50	Distribution wide 50	0.0313
	DGR D9 62P		
912300060076	BDP275 LED14-4S-730 DX52 CLO	Distribution Extra	0.035
	SRT 62P	Wide DX52	
912300060077	BDP275 LED39-4S-727 II DM50	Distribution medium	0.0312
	CLOD9 MSP62P	50	

Operating and Electrical

Order Code	Full Product Name	Power	Surge Protection
		Consumption	(Common/Differential)
912300060078	BDP276 LED20-4S-740	12.6 W	Surge protection level until
	DX52 CLO-DDF1 62P		6 kV differential mode and
			6 kV common mode
912300060079	BDP276 LED35-4S-730	24 W	Surge protection level until
	II DS50 D9 76P		6 kV differential mode and
			6 kV common mode

Order Code	Full Product Name	Luminaire	Light	Correlated	Luminous
		light beam	source	Color	
		spread	color	Temperature	Flux
(Nom)				(Nom)	
912300060253	BDP275	-	730	3000 K	1,162 lm
	LED14-4S/730 PSD		warm		
	DX52 PCC DGR D9		white		
912300060254	BDP275	-	730	3000 K	1,494 lm
	LED18-4S/730 PSD		warm		
	DX52 PCC DGR D9		white		
912300060276	BDP275	76° x 74°	730	3000 K	1,148 lm
	LED14-4S/730		warm		
	DM11 PCC DGR D9		white		
	62P				
912300060082	BDP278	77° - 11° x	740	4000 K	2,835 lm
	LED35-4S-740-	156°	neutral		
	DM10 DGR D9 62P		white		

Order Code	Full Product Name	Optic type outdoor	Upward
			light
			output
			ratio
912300060131	BDP275 LED22-4S/730 DW50	Distribution wide 50	0.0313
	DGR D9 62P		
912300060252	BDP275 LED14-4S/730 PSD DM12	Distribution medium	0.0358
	PCC DGR D9	12	
912300060253	BDP275 LED14-4S/730 PSD DX52	Distribution Extra	0.035
	PCC DGR D9	Wide DX52	
912300060254	BDP275 LED18-4S/730 PSD DX52	Distribution Extra	0.035
	PCC DGR D9	Wide DX52	
912300060276	BDP275 LED14-4S/730 DM11 PCC	Distribution medium	0.0369
	DGR D9 62P	11	
912300060082	BDP278 LED35-4S-740- DM10	Distribution medium	0.0374
	DGR D9 62P	10	

Order Code	Full Product Name	Power	Surge Protection
		Consumption	(Common/Differential)
912300060080	BDP276 LED39-4S/740	24 W	Surge protection level until
	II DW10 DDF1 SDM10 6		6 kV differential mode and
			10 kV common mode
912300060132	BDP276 LED24-4S/730	16.2 W	Surge protection level until
	DX52 DGR D9 62P		6 kV differential mode and
			6 kV common mode

Order Code	Full Product Name	Power	Surge Protection
		Consumption	(Common/Differential)
912300060081	BDP277 LED35-4S-730 II DW50 DGR D9 62P	24 W	Surge protection level until 6 kV differential mode and 6 kV common mode
912300060076	BDP275 LED14-4S-730 DX52 CLO SRT 62P	9.7 W	Surge protection level until 6 kV differential mode and 6 kV common mode
912300060077	BDP275 LED39-4S-727 II DM50 CLOD9 MSP62P	27.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
912300060131	BDP275 LED22-4S/730 DW50 DGR D9 62P	14.8 W	Surge protection level until 6 kV differential mode and 6 kV common mode
912300060252	BDP275 LED14-4S/730 PSD DM12 PCC DGR D9	9.8 W	Surge protection level until 6 kV differential mode and 6 kV common mode

Controls and Dimming

Order Code	Full Product Name	Dimmable
912300060078	BDP276 LED20-4S-740 DX52 CLO-DDF1 62P	Yes
912300060079	BDP276 LED35-4S-730 II DS50 D9 76P	No
912300060080	BDP276 LED39-4S/740 II DW10 DDF1 SDM10 6	Yes
912300060132	BDP276 LED24-4S/730 DX52 DGR D9 62P	No
912300060081	BDP277 LED35-4S-730 II DW50 DGR D9 62P	No
912300060076	BDP275 LED14-4S-730 DX52 CLO SRT 62P	Yes
912300060077	BDP275 LED39-4S-727 II DM50 CLOD9 MSP62P	Yes

Mechanical and Housing

Order Code	Full Product Name	Optical cover type	Mech. impact protection
			code
912300060078	BDP276 LED20-4S-740 DX52 CLO-DDF1 62P	Polycarbonate bowl/cover structured	IK10
912300060079	BDP276 LED35-4S-730 II DS50 D9 76P	Polycarbonate bowl/cover structured	IK10
912300060080	BDP276 LED39-4S/740 II DW10 DDF1 SDM10 6	Polycarbonate bowl/cover structured	IK10
912300060132	BDP276 LED24-4S/730 DX52 DGR D9 62P	Polycarbonate bowl/cover structured	IK10
912300060081	BDP277 LED35-4S-730 II DW50 DGR D9 62P	Polycarbonate bowl/cover structured	IK10
912300060076	BDP275 LED14-4S-730 DX52 CLO SRT 62P	Polycarbonate bowl/cover structured	IK09
912300060077	BDP275 LED39-4S-727 II DM50 CLOD9 MSP62P	Polycarbonate bowl/cover structured	IK10

Product Data

Order Code	Full Product Name	Power	Surge Protection
		Consumption	(Common/Differential)
912300060253	BDP275 LED14-4S/730 PSD DX52 PCC DGR D9	9.8 W	Surge protection level until 6 kV differential mode and 6 kV common mode
912300060254	BDP275 LED18-4S/730 PSD DX52 PCC DGR D9	12.4 W	Surge protection level until 6 kV differential mode and 6 kV common mode
912300060276	BDP275 LED14-4S/730 DM11 PCC DGR D9 62P	9.8 W	Surge protection level until 6 kV differential mode and 6 kV common mode
912300060082	BDP278 LED35-4S-740- DM10 DGR D9 62P	22.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode


Order Code	Full Product Name	Dimmable
912300060131	BDP275 LED22-4S/730 DW50 DGR D9 62P	No
912300060252	BDP275 LED14-4S/730 PSD DM12 PCC DGR D9	Yes
912300060253	BDP275 LED14-4S/730 PSD DX52 PCC DGR D9	Yes
912300060254	BDP275 LED18-4S/730 PSD DX52 PCC DGR D9	Yes
912300060276	BDP275 LED14-4S/730 DM11 PCC DGR D9 62P	Yes
912300060082	BDP278 LED35-4S-740- DM10 DGR D9 62P	No

Order Code	Full Product Name	Optical cover type	Mech. impact protection
			code
912300060131	BDP275 LED22-4S/730 DW50 DGR D9 62P	Polycarbonate bowl/cover structured	IK10
912300060252	BDP275 LED14-4S/730 PSD DM12 PCC DGR D9	Polycarbonate bowl/cover structured	IK10
912300060253	BDP275 LED14-4S/730 PSD DX52 PCC DGR D9	Polycarbonate bowl/cover structured	IK10
912300060254	BDP275 LED18-4S/730 PSD DX52 PCC DGR D9	Polycarbonate bowl/cover structured	IK10
912300060276	BDP275 LED14-4S/730 DM11 PCC DGR D9 62P	Polycarbonate bowl/cover clear	IK10
912300060082	BDP278 LED35-4S-740- DM10 DGR D9 62P	Polycarbonate bowl/cover structured	IK10


Order Code	Full Product Name	Product family code
912300060078	BDP276 LED20-4S-740 DX52 CLO-DDF1 62P	BDP276
912300060079	BDP276 LED35-4S-730 II DS50 D9 76P	BDP276
912300060080	BDP276 LED39-4S/740 II DW10 DDF1 SDM10 6	BDP276
912300060132	BDP276 LED24-4S/730 DX52 DGR D9 62P	BDP276
912300060081	BDP277 LED35-4S-730 II DW50 DGR D9 62P	BDP277
912300060076	BDP275 LED14-4S-730 DX52 CLO SRT 62P	BDP275
912300060077	BDP275 LED39-4S-727 II DM50 CLOD9 MSP62P	BDP275

Order Code	Full Product Name	Product family code
912300060131	BDP275 LED22-4S/730 DW50 DGR D9 62P	BDP275
912300060252	BDP275 LED14-4S/730 PSD DM12 PCC DGR D9	BDP275
912300060253	BDP275 LED14-4S/730 PSD DX52 PCC DGR D9	BDP275
912300060254	BDP275 LED18-4S/730 PSD DX52 PCC DGR D9	BDP275
912300060276	BDP275 LED14-4S/730 DM11 PCC DGR D9 62P	BDP275
912300060082	BDP278 LED35-4S-740- DM10 DGR D9 62P	BDP278


## Polar Wide Diagrams




Polar Normal (separate) - BDP275I -  
912300060079




Polar Normal (separate) - BDP275I -  
912300060080




Polar Normal (separate) - BDP275I -  
912300060082




Polar Normal (separate) - BDP275I -  
912300060081




Polar Normal (separate) - BDP275I -  
912300060132




Polar Normal (separate) - BDP275I -  
912300060131



Polar Normal (separate) - BDP275I -  
912300060254




Polar Normal (separate) - BDP275I -  
912300060253



Polar Normal (separate) - BDP275I -  
912300060252

### Polar Wide Diagrams



Polar Normal (separate) - BDP275I -  
912300060276

