



# For top performance and sustainability

## MASTER Glass LED bulbs

Featuring a classic heritage design, these filament MASTER glass bulbs combine the familiar shapes of incandescent glass LED bulbs with the benefits of long-lasting LED technology. Ideal for creating a cozy atmosphere for customers, these glass LED bulbs provide excellent quality of light. MASTER glass bulbs can be dimmed for different lumen levels and color temperatures (dimmable glass led bulbs). They also deliver significant energy savings, using 30% less energy compared to normal LED bulbs. By offering a lifetime of 25,000 hours, these dimmable glass LED bulbs also reduce maintenance costs.

### Benefits

- Saves 30% energy compared with standard Philips LED bulbs
- Very long lifetime that reduces the need for replacements
- Easy retrofit replacement for conventional lamps

### Features


- heritage design with classic shapes
- perfect fit and high-quality finish
- Very good light quality with excellent color rendering (CRI>95)
- Designed to be seen, they look good switched on or off
- Environmentally friendly: contains no mercury or other hazardous substances

### Application

- Home
- Hospitality

# MASTER Glass LED bulbs

## Dimensional drawing



Product	D	C
MAS LEDBulbDT5.9-60W E27 927A60CL G	60 mm	104 mm
MAS LEDBulbDT5.9-60W E27 CRI95A60CL G	60 mm	108 mm

General Information	
Cap-Base	E27
Switching Cycle	20,000
Nominal lifetime	25,000 hour(s)
Light Technical	
Correlated Color Temperature (Nom)	2200 K
Color Code	922-927
LLMF At End Of Nominal Lifetime (Nom)	70 %
Luminous Flux	806 lm
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power Consumption	5.9 W
Starting Time (Nom)	0.5 s
Wattage Equivalent	60 W
Temperature	
T-Case Maximum (Nom)	70 °C
Controls and Dimming	
Dimmable	Only with specific dimmers
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	A60
Approval and Application	
Energy Consumption kWh/1000 h	6 kWh

## Light Technical

		Color rendering index	
Order Code	Full Product Name	Beam Angle (Nom)	(CRI)
929003010382	MAS LEDBulbDT5.9-60W E27 927A60CL G	-	90
929003798682	MAS LEDBulbDT5.9-60W E27 CRI95A60CL G	300 degree(s)	95

## Operating and Electrical

Order Code	Full Product Name	Line Frequency	Order Code	Full Product Name	Line Frequency
929003010382	MAS LEDBulbDT5.9-60W E27 927A60CL G	50 to 60 Hz	929003798682	MAS LEDBulbDT5.9-60W E27 CRI95A60CL G	-

## Approval and Application

## MASTER Glass LED bulbs

Order Code	Full Product Name	Ambient temperature range
929003010382	MAS LEDBulbDT5.9-60W E27 927A60CL G	-20 °C to 45 °C
929003798682	MAS LEDBulbDT5.9-60W E27 CRI95A60CL G	-20 to +45 °C

