



# For an optimal combination of value and performance

## MASTER Value Glass LED bulbs

Featuring a classic heritage design, these filament LED bulbs combine the familiar shapes of incandescent bulbs with the benefits of long-lasting LED technology. These MASTER Value Glass LED bulbs offer more energy savings than normal glass LED bulbs. At the same time, they also provide customers with good light experience, enhanced by excellent dimming performance (dimmable glass LED bulbs). MASTER Value Glass LED Bulbs deliver significant energy savings, using 30% less energy compared to normal LED bulbs and provide excellent quality of light. By offering a lifetime of 15,000 hours, these dimmable LED bulbs also reduce maintenance costs.

### Benefits

- Saves 30% energy compared with standard Philips LED bulbs
- Very long lifetime that reduces the need for replacements
- Easy retrofit replacement for conventional lamps

### Features

- heritage design with classic shapes
- perfect fit and high-quality finish
- Very good light quality with excellent color rendering (CRI>90)
- Designed to be seen, they look good switched on or off
- Environmentally friendly: contains no mercury or other hazardous substances

### Application

- Home
- Hospitality

# MASTER Value Glass LED bulbs

## Versions



LEDclassic 60W A60 E27 CL  
WGD90 SRT4 1





LEDclassic 60W G93 E27 CL  
WGD90 1PF 4 1



LEDBulb MAS A60 E27 CL 1

## Dimensional drawing



Product	D	C
MAS VLE LEDBulb D5.9-60W E27 927 A60CLG	60 mm	104 mm
MAS VLE LEDBulb D5.9-60W E27 927 A60 FRG	60 mm	104 mm
MAS VLE LEDBulb D7.8-75W E27 927 A60 FRG	60 mm	104 mm
MAS VLE LEDBulbD11.2-100W E27 927 A60FRG	60 mm	108 mm
MAS VLE LEDBulbD3.4-40W E27 927 A60 FR G	60 mm	104 mm
MAS VLE LEDBulbDT5.9-60W E27 927A60CL G	60 mm	104 mm

Product	D	C
MAS VLE LEDBulb DT5.9-60W E27 927G93CL G	95 mm	137 mm

MASTER Value Glass LED bulbs

General Information	
Cap-Base	E27
Switching Cycle	20,000
Nominal lifetime	15,000 hour(s)
Light Technical	
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Line Frequency	50 to 60 Hz
Starting Time (Nom)	0.5 s
Controls and Dimming	
Dimmable	Only with specific dimmers

Light Technical

		Correlated Color			
Order Code	Full Product Name	Beam Angle (Nom)	Temperature	Color	Luminous
			(Nom)	Code	Flux
929003010302	MAS VLE LEDBulbDT5.9-60W E27 927A60CL G	-	2200 K	922-927	806 lm
929003057702	MAS VLE LEDBulb D5.9-60W E27 927 A60 FRG	300 degree(s)	2700 K	927	806 lm
929003058102	MAS VLE LEDBulb D7.8-75W E27 927 A60 FRG	300 degree(s)	2700 K	927	1,055 lm
929003058502	MAS VLE LEDBulbD11.2-100W E27 927 927 A60FRG	300 degree(s)	2700 K	927	1,521 lm
929003070702	MAS VLE LEDBulbD3.4-40W E27 927 A60 FR G	300 degree(s)	2700 K	927	470 lm
929003057502	MAS VLE LEDBulb D5.9-60W E27 927 927 A60CLG	300 degree(s)	2700 K	927	806 lm
929003010902	MAS VLE LEDBulb DT5.9-60W E27 927G93CL G	300 degree(s)	2200 K	922-927	806 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Wattage Equivalent
929003010302	MAS VLE LEDBulbDT5.9-60W E27 927A60CL G	5.9 W	60 W
929003057702	MAS VLE LEDBulb D5.9-60W E27 927 A60 FRG	5.9 W	60 W
929003058102	MAS VLE LEDBulb D7.8-75W E27 927 A60 FRG	7.8 W	75 W
929003058502	MAS VLE LEDBulbD11.2-100W E27 927 A60FRG	11.2 W	100 W

Order Code	Full Product Name	Power Consumption	Wattage Equivalent
929003070702	MAS VLE LEDBulbD3.4-40W E27 927 A60 FR G	3.4 W	40 W
929003057502	MAS VLE LEDBulb D5.9-60W E27 927 A60CLG	5.9 W	60 W
929003010902	MAS VLE LEDBulb DT5.9-60W E27 927G93CL G	5.9 W	60 W

Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
929003010302	MAS VLE LEDBulbDT5.9-60W E27 927A60CL G	70 °C
929003057702	MAS VLE LEDBulb D5.9-60W E27 927 A60 FRG	80 °C
929003058102	MAS VLE LEDBulb D7.8-75W E27 927 A60 FRG	80 °C
929003058502	MAS VLE LEDBulbD11.2-100W E27 927 A60FRG	80 °C

Order Code	Full Product Name	T-Case Maximum (Nom)
929003070702	MAS VLE LEDBulbD3.4-40W E27 927 A60 FR G	80 °C
929003057502	MAS VLE LEDBulb D5.9-60W E27 927 A60CLG	80 °C
929003010902	MAS VLE LEDBulb DT5.9-60W E27 927G93CL G	70 °C

Mechanical and Housing



Order Code	Full Product Name	Bulb Finish	Bulb Shape
929003010302	MAS VLE LEDBulbDT5.9-60W E27 927A60CL G	Clear	A60
929003057702	MAS VLE LEDBulb D5.9-60W E27 927 A60 FRG	Frosted	A60
929003058102	MAS VLE LEDBulb D7.8-75W E27 927 A60 FRG	Frosted	A60
929003058502	MAS VLE LEDBulbD11.2-100W E27 927 A60FRG	Frosted	A60

Order Code	Full Product Name	Bulb Finish	Bulb Shape
929003070702	MAS VLE LEDBulbD3.4-40W E27 927 A60 FR G	Frosted	A60
929003057502	MAS VLE LEDBulb D5.9-60W E27 927 A60CLG	Clear	A60
929003010902	MAS VLE LEDBulb DT5.9-60W E27 927G93CL G	Clear	G93

MASTER Value Glass LED bulbs

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
929003010302	MAS VLE LEDBulbDT5.9-60W E27 927A60CL G	6 kWh
929003057702	MAS VLE LEDBulb D5.9-60W E27 927 A60 FRG	6 kWh
929003058102	MAS VLE LEDBulb D7.8-75W E27 927 A60 FRG	8 kWh
929003058502	MAS VLE LEDBulbD11.2-100W E27 927 A60FRG	12 kWh
929003070702	MAS VLE LEDBulbD3.4-40W E27 927 A60 FR G	4 kWh
929003057502	MAS VLE LEDBulb D5.9-60W E27 927 A60CLG	6 kWh
929003010902	MAS VLE LEDBulb DT5.9-60W E27 927G93CL G	6 kWh



## MASTER Value Glass LED bulbs

