



For your everyday lighting jobs, CorePro LED combines the familiar shapes of classic incandescent bulbs with the benefits of long-lasting LED technology

CorePro Glass LED bulbs

Featuring a classic heritage design, these filament LED lamps combine the familiar shapes of classic incandescent bulbs with the benefits of long-lasting LED technology. A very easy choice for people who are looking for a retrofit LED replacement, these CorePro LED bulbs provide 90% energy savings compared with conventional lamps. CorePro Glass LED bulbs provide excellent quality of light in a vintage style. CorePro LED lighting that offers a lifetime of 15,000 hours to reduce maintenance costs.

CorePro Glass LED bulbs

Benefits

- Saves 30% energy compared with standard Philips LED bulbs
- Very long lifetime that reduces the need for replacements
- Easy retrofit replacement for conventional lamps

Features

- heritage design with classic shapes
- perfect fit and high-quality finish
- Very good light quality with good colour rendering (CRI>80)
- Designed to be seen, they look good switched on or off
- Enviromentally friendly: contains no mercury or other hazardous sustances

Application

- Home
- Hospitality

Versions



CLA LEDbulb 60W E27 827 CL ST64




LED Bulb A67 E27 ND Clear



MZD LEDCLA 60W A60 E27



Dimensional drawing



Product	D	C
CorePro LEDBulbND 7-60W E27 WW A60 CL G	60 mm	104 mm

CorePro Glass LED bulbs

Dimensional drawing



Product	D	C
CorePro LEDBulbND 7-60W E27 ST64 827CL G	64 mm	140 mm

Product	D	C
CorePro LEDBulbND10.5-100W E27A60 827CLG	60 mm	104 mm

General Information	
Cap base	E27
Switching Cycle	20,000
Nominal lifetime	15,000 h
Light Technical	
Beam angle (nom.)	300 degree(s)
Correlated Colour Temperature (Nom)	2700 K
Colour rendering index (CRI)	80
Colour Code	827
LLMF at end of nominal lifetime (nom.)	70 %
Operating and Electrical	
Input frequency	50 to 60 Hz
Line Frequency	50 to 60 Hz
Starting time (nom.)	0.5 s
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Lamp Finish	Clear

Light Technical

Order Code	Full Product Name	Luminous Flux
929001387692	CorePro LEDBulbND 7-60W E27 ST64 827CL G	806 lm
929002026192	CorePro LEDBulbND10.5-100W E27A60 827CLG	1,521 lm
929001387362	CorePro LEDBulbND 7-60W E27 WW A60 CL G	806 lm

Operating and Electrical

CorePro Glass LED bulbs

Order Code	Full Product Name	Power	Wattage
		Consumption	equivalent
929001387692	CorePro LEDBulbND 7-60W E27 ST64 827CL G	7 W	60 W
929002026192	CorePro LEDBulbND10.5-100W E27A60 827CLG	10.5 W	100 W

Order Code	Full Product Name	Power	Wattage
		Consumption	equivalent
929001387362	CorePro LEDBulbND 7-60W E27 WW A60 CL G	7 W	60 W

Temperature

Order Code	Full Product Name	T-Case maximum
		(nom.)
929001387692	CorePro LEDBulbND 7-60W E27 ST64 827CL G	45 °C
929002026192	CorePro LEDBulbND10.5-100W E27A60 827CLG	55 °C

Order Code	Full Product Name	T-Case maximum
		(nom.)
929001387362	CorePro LEDBulbND 7-60W E27 WW A60 CL G	45 °C

Mechanical and Housing

Order Code	Full Product Name	Bulb shape
929001387692	CorePro LEDBulbND 7-60W E27 ST64 827CL G	ST64
929002026192	CorePro LEDBulbND10.5-100W E27A60 827CLG	A60

Order Code	Full Product Name	Bulb shape
929001387362	CorePro LEDBulbND 7-60W E27 WW A60 CL G	A60

Approval and Application

Order Code	Full Product Name	Energy consumption
		kWh/1,000 hours
929001387692	CorePro LEDBulbND 7-60W E27 ST64 827CL G	7 kWh
929002026192	CorePro LEDBulbND10.5-100W E27A60 827CLG	11 kWh
929001387362	CorePro LEDBulbND 7-60W E27 WW A60 CL G	7 kWh

