



The cost-effective LED replacement for HID and SON Road lamps with MASTER – LED HID SON-T

Trueforce Core LED SON-T

Philips CorePro LED HID SON-T lamps offer you an easy, short-payback LED solution to replace High Intensity Discharge (HID) lamps. This new generation of products brings all the energy-efficiency and long-lifetime benefits of LED to HID replacement, while providing instant savings with a low initial investment. Furthermore, they're designed to have the same lamp size and light distribution as other HID lamps, so you will never know the difference. All thanks to our HighPower LED filament technology. Plus, its unique IP65 design means that it can be used for outdoor applications

Benefits

- Cost-saving lamps with short payback time
- Low initial investment
- Easy way to enhance lighting quality

Trueforce Core LED SON-T

Features

- High Energy efficient lamps
- Long lifetime – 25,000 hrs
- Surge protection 2KV
- Pleasant white light with CRI 70
- Omnidirectional light around lamp
- Additional energy saving by direct mains connection
- IP65 product (IP rated sockets required for outdoor application)

Application

- Road and Street
- Tunnel
- Car parks

Warnings and Safety

- Please refer to the installation guide or consult a Philips Lighting representative for the wiring diagram and instructions.

Versions



LEDTForce Core road Tshape E27




LEDTForce Core road Tshape E40



LEDTForce MAS SONT EU1




Dimensional drawing



Product	D	C
TForce Core LED road 45W 730 E40 MV	53.5 mm	232 mm

Trueforce Core LED SON-T

Dimensional drawing



Product	D	C
TForce Core LED road 40W 730 E40 MV	46 mm	225 mm
TForce Core LED road 40W 740 E40 MV	46 mm	225 mm

Product	D	C
TForce Core LED road 26W 730 E27 MV	38.5 mm	213 mm
TForce Core LED road 26W 740 E27 MV	38.5 mm	213 mm

Product	D	C
TForce Core LED road 17W 740 E27 MV	38.5 mm	168 mm

Trueforce Core LED SON-T

General Information	
Nominal lifetime	25,000 h
Light Technical	
Colour rendering index (CRI)	70
LLMF at end of nominal lifetime (nom.)	70 %
Operating and Electrical	
Input frequency	50 to 60 Hz
Starting time (nom.)	0.5 s
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Lamp Finish	Clear
Approval and Application	
Ambient temperature range	-30 to +45 °C

General Information

Order Code	Full Product Name	Cap base	Switching Cycle
929002484902	TForce Core LED road 17W 740 E27 MV	E27	15,000
929002485002	TForce Core LED road 26W 730 E27 MV	E27	15,000
929002485102	TForce Core LED road 26W 740 E27 MV	E27	15,000
929002485202	TForce Core LED road 40W 730 E40 MV	E40	50,000
929002485302	TForce Core LED road 40W 740 E40 MV	E40	50,000
929003778802	TForce Core LED road 45W 730 E40 MV	E40	50,000

Light Technical

Order Code	Full Product Name	Beam angle (nom.)	Correlated Colour		
			Temperature (Nom)	Colour Code	Luminous Flux
929002484902	TForce Core LED road 17W 740 E27 MV	-	4000 K	740	3,000 lm
929002485002	TForce Core LED road 26W 730 E27 MV	-	3000 K	730	4,200 lm
929002485102	TForce Core LED road 26W 740 E27 MV	-	4000 K	740	4,500 lm

Order Code	Full Product Name	Beam angle (nom.)	Correlated Colour		
			Temperature (Nom)	Colour Code	Luminous Flux
929002485202	TForce Core LED road 40W 730 E40 MV	330 degree(s)	3000 K	730	7,200 lm
929002485302	TForce Core LED road 40W 740 E40 MV	330 degree(s)	4000 K	740	7,500 lm
929003778802	TForce Core LED road 45W 730 E40 MV	300 degree(s)	3000 K	730	8,800 lm

Operating and Electrical

Order Code	Full Product Name	Line Frequency	Power	
			Consumption	
929002484902	TForce Core LED road 17W 740 E27 MV	50 to 60 Hz	17 W	
929002485002	TForce Core LED road 26W 730 E27 MV	50 to 60 Hz	26 W	
929002485102	TForce Core LED road 26W 740 E27 MV	50 to 60 Hz	26 W	

Order Code	Full Product Name	Line Frequency	Power	
			Consumption	
929002485202	TForce Core LED road 40W 730 E40 MV	50 to 60 Hz	40 W	
929002485302	TForce Core LED road 40W 740 E40 MV	50 to 60 Hz	40 W	
929003778802	TForce Core LED road 45W 730 E40 MV	-	45 W	

Temperature

Order Code	Full Product Name	T-Case maximum (nom.)
929002484902	TForce Core LED road 17W 740 E27 MV	39.8 °C
929002485002	TForce Core LED road 26W 730 E27 MV	44.55 °C

Order Code	Full Product Name	T-Case maximum (nom.)
929002485102	TForce Core LED road 26W 740 E27 MV	44.55 °C
929002485202	TForce Core LED road 40W 730 E40 MV	49 °C

Trueforce Core LED SON-T

Order Code	Full Product Name	T-Case maximum (nom.)
929002485302	TForce Core LED road 40W 740 E40 MV	49 °C

Order Code	Full Product Name	T-Case maximum (nom.)
929003778802	TForce Core LED road 45W 730 E40 MV	41 °C

Mechanical and Housing

Order Code	Full Product Name	Bulb shape
929002484902	TForce Core LED road 17W 740 E27 MV	T-shape
929002485002	TForce Core LED road 26W 730 E27 MV	T-shape
929002485102	TForce Core LED road 26W 740 E27 MV	T-shape

Order Code	Full Product Name	Bulb shape
929002485202	TForce Core LED road 40W 730 E40 MV	T-shape
929002485302	TForce Core LED road 40W 740 E40 MV	T-shape
929003778802	TForce Core LED road 45W 730 E40 MV	T52

Approval and Application

Order Code	Full Product Name	Energy consumption kWh/ 1,000 hours
929002484902	TForce Core LED road 17W 740 E27 MV	17 kWh
929002485002	TForce Core LED road 26W 730 E27 MV	26 kWh
929002485102	TForce Core LED road 26W 740 E27 MV	26 kWh
929002485202	TForce Core LED road 40W 730 E40 MV	40 kWh
929002485302	TForce Core LED road 40W 740 E40 MV	40 kWh
929003778802	TForce Core LED road 45W 730 E40 MV	45 kWh

