



Philips Deep Recessed Spotlight with the Tri-layer optics design allows to achieve the anti-glare feature, which is an icon Tech in the market currently.

Deep Recessed Spotlight

Deep Recessed offers excellent experience for the consumer, which includes eye comfort, reliable quality and outstanding performance, especially the anti glare feature.

Benefits

- Comfortable LED light that's easy on eyes
- Long lifetime
- Reliable & Outstanding Performance

Deep Recessed Spotlight

Features

- Tri-layer Optic Thec
- EyeComfort
- Outstanding performance
- Safe to use & Reliable Quality

Application


- Retail
- Offices
- Hospitality

Versions




RS350 G2 RC Rd D55 1H GC

Dimensional drawing



Deep Recessed Spotlight

Dimensional drawing



Product details



RS350 G2 RD back

Deep Recessed Spotlight

General Information	
Light source replaceable	No
Light Technical	
Color rendering index (CRI)	90
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Ingress protection code	IP20
Approval and Application	
Ambient temperature range	-20 to +40 °C
Flammability mark	For mounting on normally flammable surfaces

General Information

Order Code	Full Product Name	Driver included	Number of gear units
929003222610	RS350 G2 RC Sq L55 2*7W 30K 24D 2H	Yes	1 unit
929003222710	RS350 G2 RC Sq L55 2*7W 30K 36D 2H	Yes	1 unit
929003222810	RS350 G2 RC Sq L55 2*7W 40K 24D 2H	Yes	1 unit
929003222910	RS350 G2 RC Sq L55 2*7W 40K 36D 2H	Yes	1 unit
929003223410	RS350 G2 RC Sq L75 2*11W 30K 24D 2H	Yes	1 unit
929003223510	RS350 G2 RC Sq L75 2*11W 30K 36D 2H	Yes	1 unit
929003223610	RS350 G2 RC Sq L75 2*11W 40K 24D 2H	Yes	1 unit
929003223710	RS350 G2 RC Sq L75 2*11W 40K 36D 2H	Yes	1 unit
929003216210	RS350 G2 RC Rd D75 7W 30K 24D 1H	Yes	1 unit
929003216310	RS350 G2 RC Rd D75 7W 30K 36D 1H	Yes	1 unit
929003216410	RS350 G2 RC Rd D75 7W 30K 50D 1H	Yes	1 unit
929003216510	RS350 G2 RC Rd D75 7W 40K 24D 1H	Yes	1 unit
929003216610	RS350 G2 RC Rd D75 7W 40K 36D 1H	Yes	1 unit
929003216710	RS350 G2 RC Rd D75 7W 40K 50D 1H	Yes	1 unit
929003216810	RS350 G2 RC Rd D75 9W 30K 24D 1H	Yes	1 unit
929003216910	RS350 G2 RC Rd D75 9W 30K 36D 1H	Yes	1 unit
929003217010	RS350 G2 RC Rd D75 9W 30K 50D 1H	Yes	1 unit
929003217110	RS350 G2 RC Rd D75 9W 40K 24D 1H	Yes	1 unit
929003217210	RS350 G2 RC Rd D75 9W 40K 36D 1H	Yes	1 unit
929003217310	RS350 G2 RC Rd D75 9W 40K 50D 1H	Yes	1 unit
929003217410	RS350 G2 RC Rd D75 11W 30K 24D 1H	Yes	1 unit
929003217510	RS350 G2 RC Rd D75 11W 30K 36D 1H	Yes	1 unit
929003217610	RS350 G2 RC Rd D75 11W 30K 50D 1H	Yes	1 unit
929003217710	RS350 G2 RC Rd D75 11W 40K 24D 1H	Yes	1 unit
929003217810	RS350 G2 RC Rd D75 11W 40K 36D 1H	Yes	1 unit
929003217910	RS350 G2 RC Rd D75 11W 40K 50D 1H	Yes	1 unit
929004098710	RS350 G2 RC Rd D75 11W 27K 15D 1H	Yes	1 unit
929004098810	RS350 G2 RC Rd D75 11W 30K 15D 1H	Yes	1 unit
929004098910	RS350 G2 RC Rd D75 11W 35K 15D 1H	Yes	1 unit
929004099010	RS350 G2 RC Rd D75 11W 40K 15D 1H	Yes	1 unit

Order Code	Full Product Name	Driver included	Number of gear units
929003220010	RS350 G2 SF Rd D100 11W 30K 24D 1H	Yes	10 units
929003220210	RS350 G2 SF Rd D100 11W 40K 24D 1H	Yes	12 units
929003220410	RS350 G2 SF Rd D100 9W 30K 24D 1H	Yes	14 units
929003220610	RS350 G2 SF Rd D100 9W 40K 24D 1H	Yes	18 units
929003224210	RS350 G2 SF Rd D80 7W 30K 24D 1H	Yes	62 units
929003224410	RS350 G2 SF Rd D80 7W 40K 24D 1H	Yes	64 units
929004129910	RS350 G2 RC Sq L100 2*15W 30K 24D 2H	Yes	2 units
929004130010	RS350 G2 RC Sq L100 2*15W 30K 36D 2H	Yes	2 units
929004130110	RS350 G2 RC Sq L100 2*15W 40K 24D 2H	Yes	2 units
929004130210	RS350 G2 RC Sq L100 2*15W 40K 36D 2H	Yes	2 units
929004130310	RS350 G2 RC Sq L100 2*23W 30K 24D 2H	Yes	2 units
929004130410	RS350 G2 RC Sq L100 2*23W 30K 36D 2H	Yes	2 units
929004130510	RS350 G2 RC Sq L100 2*23W 40K 24D 2H	Yes	2 units
929004130610	RS350 G2 RC Sq L100 2*23W 40K 36D 2H	Yes	2 units
929003214410	RS350 G2 RC Rd D55 4W 30K 24D 1H	Yes	1 unit
929003214510	RS350 G2 RC Rd D55 4W 30K 36D 1H	Yes	1 unit
929003214710	RS350 G2 RC Rd D55 4W 40K 24D 1H	Yes	1 unit
929003214810	RS350 G2 RC Rd D55 4W 40K 36D 1H	Yes	1 unit
929003215010	RS350 G2 RC Rd D55 7W 30K 24D 1H	Yes	1 unit
929003215110	RS350 G2 RC Rd D55 7W 30K 36D 1H	Yes	1 unit
929003215310	RS350 G2 RC Rd D55 7W 40K 24D 1H	Yes	1 unit
929003215410	RS350 G2 RC Rd D55 7W 40K 36D 1H	Yes	1 unit

Deep Recessed Spotlight

Order Code	Full Product Name	Driver included	Number of gear units
929003219110	RS350 G2 RC Rd D100 23W 40K 50D 1H	Yes	1 unit
929004099110	RS350 G2 RC Rd D100 15W 30K 24D 1H	Yes	1 unit
929004099210	RS350 G2 RC Rd D100 15W 30K 36D 1H	Yes	1 unit
929004099410	RS350 G2 RC Rd D100 15W 40K 24D 1H	Yes	1 unit
929004099510	RS350 G2 RC Rd D100 15W 40K 36D 1H	Yes	1 unit
929003219210	RS350 G2 RC Sq L100 *2 30K 24D 2H	No	-
929003219310	RS350 G2 RC Sq L100 *2 30K 36D 2H	No	-
929003219410	RS350 G2 RC Sq L100 *2 40K 24D 2H	No	-
929003219510	RS350 G2 RC Sq L100 *2 40K 36D 2H	No	-
929003220810	RS350 G2 SF Sq L100 11W 30K 24D 1H	Yes	20 units
929003221010	RS350 G2 SF Sq L100 11W 40K 24D 1H	Yes	22 units
929003221210	RS350 G2 SF Sq L100 9W 30K 24D 1H	Yes	24 units
929003221410	RS350 G2 SF Sq L100 9W 40K 24D 1H	Yes	26 units
929003225010	RS350 G2 SF Sq L80 7W 30K 24D 1H	Yes	70 units
929003225210	RS350 G2 SF Sq L80 7W 40K 24D 1H	Yes	72 units

Order Code	Full Product Name	Driver included	Number of gear units
929003340210	RS350 G2 RC Rd D75 7W 27K 24D 1H	-	-
929003340410	RS350 G2 RC Rd D75 7W 35K 24D 1H	-	-
929003340510	RS350 G2 RC Rd D75 7W 35K 50D 1H	-	-
929003340610	RS350 G2 RC Rd D75 9W 27K 24D 1H	-	-
929003340810	RS350 G2 RC Rd D75 9W 35K 24D 1H	-	-
929003340910	RS350 G2 RC Rd D75 9W 35K 50D 1H	-	-
929003341010	RS350 G2 RC Rd D75 11W 27K 24D 1H	-	-
929003341210	RS350 G2 RC Rd D75 11W 35K 24D 1H	-	-
929003341310	RS350 G2 RC Rd D75 11W 35K 50D 1H	-	-
929003343410	RS350 G2 RC Rd D75 7W 27K 36D 1H	-	-
929003343510	RS350 G2 RC Rd D75 7W 35K 36D 1H	-	-
929003343610	RS350 G2 RC Rd D75 9W 27K 36D 1H	-	-
929003343710	RS350 G2 RC Rd D75 9W 35K 36D 1H	-	-
929003343810	RS350 G2 RC Rd D75 11W 27K 36D 1H	-	-
929003343910	RS350 G2 RC Rd D75 11W 35K 36D 1H	-	-

Light Technical

Order Code	Full Product Name	Correlated Color Temperature		Number of light		
		(Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	sources	Optic type
929003222610	RS350 G2 RC Sq L55 2*7W 30K 24D 2H	3000 K	77 lm/W	1,080 lm	2	Beam angle 24°
929003222710	RS350 G2 RC Sq L55 2*7W 30K 36D 2H	3000 K	77 lm/W	1,080 lm	2	Beam angle 36°
929003222810	RS350 G2 RC Sq L55 2*7W 40K 24D 2H	4000 K	82 lm/W	1,160 lm	2	Beam angle 24°
929003222910	RS350 G2 RC Sq L55 2*7W 40K 36D 2H	4000 K	82 lm/W	1,160 lm	2	Beam angle 36°
929003223410	RS350 G2 RC Sq L75 2*11W 30K 24D 2H	3000 K	90 lm/W	2,000 lm	2	Beam angle 24°
929003223510	RS350 G2 RC Sq L75 2*11W 30K 36D 2H	3000 K	90 lm/W	2,000 lm	2	Beam angle 36°
929003223610	RS350 G2 RC Sq L75 2*11W 40K 24D 2H	4000 K	98 lm/W	2,160 lm	2	Beam angle 24°
929003223710	RS350 G2 RC Sq L75 2*11W 40K 36D 2H	4000 K	98 lm/W	2,160 lm	2	Beam angle 36°
929003216210	RS350 G2 RC Rd D75 7W 30K 24D 1H	3000 K	80.00 lm/W	560 lm	-	Beam angle 36°
929003216310	RS350 G2 RC Rd D75 7W 30K 36D 1H	3000 K	80.00 lm/W	560 lm	-	Beam angle 36°
929003216410	RS350 G2 RC Rd D75 7W 30K 50D 1H	3000 K	80.00 lm/W	560 lm	-	Beam angle 50°
929003216510	RS350 G2 RC Rd D75 7W 40K 24D 1H	4000 K	85.71 lm/W	600 lm	-	Beam angle 24°
929003216610	RS350 G2 RC Rd D75 7W 40K 36D 1H	4000 K	85.71 lm/W	600 lm	-	Beam angle 36°
929003216710	RS350 G2 RC Rd D75 7W 40K 50D 1H	4000 K	85.00 lm/W	600 lm	-	Beam angle 50°
929003216810	RS350 G2 RC Rd D75 9W 30K 24D 1H	3000 K	81.11 lm/W	730 lm	-	Beam angle 24°
929003216910	RS350 G2 RC Rd D75 9W 30K 36D 1H	3000 K	81.11 lm/W	730 lm	-	Beam angle 36°
929003217010	RS350 G2 RC Rd D75 9W 30K 50D 1H	3000 K	81.11 lm/W	730 lm	-	Beam angle 36°
929003217110	RS350 G2 RC Rd D75 9W 40K 24D 1H	4000 K	88.89 lm/W	800 lm	-	Beam angle 24°
929003217210	RS350 G2 RC Rd D75 9W 40K 36D 1H	4000 K	88.89 lm/W	800 lm	-	Beam angle 36°
929003217310	RS350 G2 RC Rd D75 9W 40K 50D 1H	4000 K	88.00 lm/W	800 lm	-	Beam angle 36°
929003217410	RS350 G2 RC Rd D75 11W 30K 24D 1H	3000 K	90.91 lm/W	1,000 lm	-	Beam angle 36°
929003217510	RS350 G2 RC Rd D75 11W 30K 36D 1H	3000 K	90.91 lm/W	1,000 lm	-	Beam angle 36°
929003217610	RS350 G2 RC Rd D75 11W 30K 50D 1H	3000 K	90.91 lm/W	1,000 lm	-	Beam angle 36°
929003217710	RS350 G2 RC Rd D75 11W 40K 24D 1H	4000 K	98.18 lm/W	1,080 lm	-	Beam angle 36°
929003217810	RS350 G2 RC Rd D75 11W 40K 36D 1H	4000 K	98.18 lm/W	1,080 lm	-	Beam angle 36°
929003217910	RS350 G2 RC Rd D75 11W 40K 50D 1H	4000 K	98.18 lm/W	1,080 lm	-	Beam angle 36°
929004098710	RS350 G2 RC Rd D75 11W 27K 15D 1H	2700 K	81 lm/W	900 lm	1	High-gloss mirror
929004098810	RS350 G2 RC Rd D75 11W 30K 15D 1H	3000 K	86 lm/W	950 lm	1	High-gloss mirror
929004098910	RS350 G2 RC Rd D75 11W 35K 15D 1H	3500 K	90 lm/W	1,000 lm	1	High-gloss mirror
929004099010	RS350 G2 RC Rd D75 11W 40K 15D 1H	4000 K	95 lm/W	1,050 lm	1	High-gloss mirror
929003220010	RS350 G2 SF Rd D100 11W 30K 24D 1H	3000 K	90 lm/W	1,000 lm	-	Beam angle 24°

Deep Recessed Spotlight

Order Code	Full Product Name	Correlated Color Temperature		Luminous Efficacy (rated) (Nom)	Luminous Flux	Number of light		Optic type
		(Nom)				sources		
929003220210	RS350 G2 SF Rd D100 11W 40K 24D 1H	4000 K		98 lm/W	1,080 lm	-		Beam angle 24°
929003220410	RS350 G2 SF Rd D100 9W 30K 24D 1H	3000 K		81 lm/W	730 lm	-		Beam angle 24°
929003220610	RS350 G2 SF Rd D100 9W 40K 24D 1H	4000 K		88 lm/W	800 lm	-		Beam angle 24°
929003224210	RS350 G2 SF Rd D80 7W 30K 24D 1H	3000 K		77 lm/W	540 lm	-		Beam angle 24°
929003224410	RS350 G2 SF Rd D80 7W 40K 24D 1H	4000 K		82 lm/W	580 lm	-		Beam angle 24°
929004129910	RS350 G2 RC Sq L100 2*15W 30K 24D 2H	3000 K		100 lm/W	3,000 lm	2		High-gloss mirror
929004130010	RS350 G2 RC Sq L100 2*15W 30K 36D 2H	3000 K		100 lm/W	3,000 lm	2		High-gloss mirror
929004130110	RS350 G2 RC Sq L100 2*15W 40K 24D 2H	4000 K		106 lm/W	3,200 lm	2		High-gloss mirror
929004130210	RS350 G2 RC Sq L100 2*15W 40K 36D 2H	4000 K		106 lm/W	3,200 lm	2		High-gloss mirror
929004130310	RS350 G2 RC Sq L100 2*23W 30K 24D 2H	3000 K		87 lm/W	4,000 lm	2		High-gloss mirror
929004130410	RS350 G2 RC Sq L100 2*23W 30K 36D 2H	3000 K		87 lm/W	4,000 lm	2		High-gloss mirror
929004130510	RS350 G2 RC Sq L100 2*23W 40K 24D 2H	4000 K		93 lm/W	4,300 lm	2		High-gloss mirror
929004130610	RS350 G2 RC Sq L100 2*23W 40K 36D 2H	4000 K		93 lm/W	4,300 lm	2		High-gloss mirror
929003214410	RS350 G2 RC Rd D55 4W 30K 24D 1H	3000 K		87.50 lm/W	350 lm	-		Beam angle 24°
929003214510	RS350 G2 RC Rd D55 4W 30K 36D 1H	3000 K		87.50 lm/W	350 lm	-		Beam angle 36°
929003214710	RS350 G2 RC Rd D55 4W 40K 24D 1H	4000 K		92.50 lm/W	370 lm	-		Beam angle 24°
929003214810	RS350 G2 RC Rd D55 4W 40K 36D 1H	4000 K		92.50 lm/W	370 lm	-		Beam angle 36°
929003215010	RS350 G2 RC Rd D55 7W 30K 24D 1H	3000 K		77.14 lm/W	540 lm	-		Beam angle 36°
929003215110	RS350 G2 RC Rd D55 7W 30K 36D 1H	3000 K		77.14 lm/W	540 lm	-		Beam angle 36°
929003215310	RS350 G2 RC Rd D55 7W 40K 24D 1H	4000 K		82.86 lm/W	580 lm	-		Beam angle 36°
929003215410	RS350 G2 RC Rd D55 7W 40K 36D 1H	4000 K		82.86 lm/W	580 lm	-		Beam angle 36°
929003219110	RS350 G2 RC Rd D100 23W 40K 50D 1H	4000 K		89.13 lm/W	2,050 lm	-		Beam angle 36°
929004099110	RS350 G2 RC Rd D100 15W 30K 24D 1H	3000 K		100 lm/W	1,500 lm	1		High-gloss mirror
929004099210	RS350 G2 RC Rd D100 15W 30K 36D 1H	3000 K		100 lm/W	1,500 lm	1		High-gloss mirror
929004099410	RS350 G2 RC Rd D100 15W 40K 24D 1H	4000 K		106 lm/W	1,600 lm	1		High-gloss mirror
929004099510	RS350 G2 RC Rd D100 15W 40K 36D 1H	4000 K		106 lm/W	1,600 lm	1		High-gloss mirror
929003219210	RS350 G2 RC Sq L100 *2 30K 24D 2H	3000 K		105 lm/W	4,000 lm	2		Beam angle 24°
929003219310	RS350 G2 RC Sq L100 *2 30K 36D 2H	3000 K		105 lm/W	4,000 lm	2		Beam angle 36°
929003219410	RS350 G2 RC Sq L100 *2 40K 24D 2H	4000 K		113 lm/W	4,300 lm	2		Beam angle 24°
929003219510	RS350 G2 RC Sq L100 *2 40K 36D 2H	4000 K		113 lm/W	4,300 lm	2		Beam angle 36°
929003220810	RS350 G2 SF Sq L100 11W 30K 24D 1H	3000 K		90 lm/W	1,000 lm	-		Beam angle 24°
929003221010	RS350 G2 SF Sq L100 11W 40K 24D 1H	4000 K		98 lm/W	1,080 lm	-		Beam angle 24°
929003221210	RS350 G2 SF Sq L100 9W 30K 24D 1H	3000 K		81 lm/W	730 lm	-		Beam angle 24°
929003221410	RS350 G2 SF Sq L100 9W 40K 24D 1H	4000 K		88 lm/W	800 lm	-		Beam angle 24°
929003225010	RS350 G2 SF Sq L80 7W 30K 24D 1H	3000 K		77 lm/W	540 lm	-		Beam angle 24°
929003225210	RS350 G2 SF Sq L80 7W 40K 24D 1H	4000 K		82 lm/W	580 lm	-		Beam angle 24°
929003340210	RS350 G2 RC Rd D75 7W 27K 24D 1H	2700 K		75 lm/W	530 lm	-		-
929003340410	RS350 G2 RC Rd D75 7W 35K 24D 1H	3500 K		82 lm/W	580 lm	-		-
929003340510	RS350 G2 RC Rd D75 7W 35K 50D 1H	3500 K		82 lm/W	580 lm	-		-
929003340610	RS350 G2 RC Rd D75 9W 27K 24D 1H	2700 K		77 lm/W	700 lm	-		-
929003340810	RS350 G2 RC Rd D75 9W 35K 24D 1H	3500 K		85 lm/W	770 lm	-		-
929003340910	RS350 G2 RC Rd D75 9W 35K 50D 1H	3500 K		85 lm/W	770 lm	-		-
929003341010	RS350 G2 RC Rd D75 11W 27K 24D 1H	2700 K		86 lm/W	950 lm	-		-
929003341210	RS350 G2 RC Rd D75 11W 35K 24D 1H	3500 K		96 lm/W	1,060 lm	-		-
929003341310	RS350 G2 RC Rd D75 11W 35K 50D 1H	3500 K		96 lm/W	1,060 lm	-		-
929003343410	RS350 G2 RC Rd D75 7W 27K 36D 1H	2700 K		75 lm/W	530 lm	-		-
929003343510	RS350 G2 RC Rd D75 7W 35K 36D 1H	3500 K		82 lm/W	580 lm	-		-
929003343610	RS350 G2 RC Rd D75 9W 27K 36D 1H	2700 K		77 lm/W	700 lm	-		-
929003343710	RS350 G2 RC Rd D75 9W 35K 36D 1H	3500 K		85 lm/W	770 lm	-		-
929003343810	RS350 G2 RC Rd D75 11W 27K 36D 1H	2700 K		86 lm/W	950 lm	-		-
929003343910	RS350 G2 RC Rd D75 11W 35K 36D 1H	3500 K		96 lm/W	1,060 lm	-		-

Deep Recessed Spotlight

Operating and Electrical

Order Code	Full Product Name	Protection class IEC	Input Voltage	Line Frequency	Power Consumption	Suitable for random switching
929003222610	RS350 G2 RC Sq L55 2*7W 30K 24D 2H	Safety class II	220 to 240 V	50 or 60 Hz	-	No
929003222710	RS350 G2 RC Sq L55 2*7W 30K 36D 2H	Safety class II	220 to 240 V	50 or 60 Hz	-	No
929003222810	RS350 G2 RC Sq L55 2*7W 40K 24D 2H	Safety class II	220 to 240 V	50 or 60 Hz	-	No
929003222910	RS350 G2 RC Sq L55 2*7W 40K 36D 2H	Safety class II	220 to 240 V	50 or 60 Hz	-	No
929003223410	RS350 G2 RC Sq L75 2*11W 30K 24D 2H	Safety class II	220 to 240 V	50 or 60 Hz	-	No
929003223510	RS350 G2 RC Sq L75 2*11W 30K 36D 2H	Safety class II	220 to 240 V	50 or 60 Hz	-	No
929003223610	RS350 G2 RC Sq L75 2*11W 40K 24D 2H	Safety class II	220 to 240 V	50 or 60 Hz	-	No
929003223710	RS350 G2 RC Sq L75 2*11W 40K 36D 2H	Safety class II	220 to 240 V	50 or 60 Hz	-	No
929003216210	RS350 G2 RC Rd D75 7W 30K 24D 1H	Safety class II	220 to 240 V	50 or 60 Hz	7 W	No
929003216310	RS350 G2 RC Rd D75 7W 30K 36D 1H	Safety class II	220 to 240 V	50 or 60 Hz	7 W	No
929003216410	RS350 G2 RC Rd D75 7W 30K 50D 1H	Safety class II	220 to 240 V	50 or 60 Hz	7 W	No
929003216510	RS350 G2 RC Rd D75 7W 40K 24D 1H	Safety class II	220 to 240 V	50 or 60 Hz	7 W	No
929003216610	RS350 G2 RC Rd D75 7W 40K 36D 1H	Safety class II	220 to 240 V	50 or 60 Hz	7 W	No
929003216710	RS350 G2 RC Rd D75 7W 40K 50D 1H	Safety class II	220 to 240 V	50 or 60 Hz	7 W	No
929003216810	RS350 G2 RC Rd D75 9W 30K 24D 1H	Safety class II	220 to 240 V	50 or 60 Hz	9 W	No
929003216910	RS350 G2 RC Rd D75 9W 30K 36D 1H	Safety class II	220 to 240 V	50 or 60 Hz	9 W	No
929003217010	RS350 G2 RC Rd D75 9W 30K 50D 1H	Safety class II	220 to 240 V	50 or 60 Hz	9 W	No
929003217110	RS350 G2 RC Rd D75 9W 40K 24D 1H	Safety class II	220 to 240 V	50 or 60 Hz	9 W	No
929003217210	RS350 G2 RC Rd D75 9W 40K 36D 1H	Safety class II	220 to 240 V	50 or 60 Hz	9 W	No
929003217310	RS350 G2 RC Rd D75 9W 40K 50D 1H	Safety class II	220 to 240 V	50 or 60 Hz	9 W	No
929003217410	RS350 G2 RC Rd D75 11W 30K 24D 1H	Safety class II	220 to 240 V	50 or 60 Hz	11 W	No
929003217510	RS350 G2 RC Rd D75 11W 30K 36D 1H	Safety class II	220 to 240 V	50 or 60 Hz	11 W	No
929003217610	RS350 G2 RC Rd D75 11W 30K 50D 1H	Safety class II	220 to 240 V	50 or 60 Hz	11 W	No
929003217710	RS350 G2 RC Rd D75 11W 40K 24D 1H	Safety class II	220 to 240 V	50 or 60 Hz	11 W	No
929003217810	RS350 G2 RC Rd D75 11W 40K 36D 1H	Safety class II	220 to 240 V	50 or 60 Hz	11 W	No
929003217910	RS350 G2 RC Rd D75 11W 40K 50D 1H	Safety class II	220 to 240 V	50 or 60 Hz	11 W	No
929004098710	RS350 G2 RC Rd D75 11W 27K 15D 1H	Safety class II	220 to 240 V	-	11 W	Not applicable
929004098810	RS350 G2 RC Rd D75 11W 30K 15D 1H	Safety class II	220 to 240 V	-	11 W	Not applicable
929004098910	RS350 G2 RC Rd D75 11W 35K 15D 1H	Safety class II	220 to 240 V	-	11 W	Not applicable
929004099010	RS350 G2 RC Rd D75 11W 40K 15D 1H	Safety class II	220 to 240 V	-	11 W	Not applicable
929003220010	RS350 G2 SF Rd D100 11W 30K 24D 1H	Safety class II	220 to 240 V	50 or 60 Hz	11 W	No
929003220210	RS350 G2 SF Rd D100 11W 40K 24D 1H	Safety class II	220 to 240 V	50 or 60 Hz	11 W	No
929003220410	RS350 G2 SF Rd D100 9W 30K 24D 1H	Safety class II	220 to 240 V	50 or 60 Hz	9 W	No
929003220610	RS350 G2 SF Rd D100 9W 40K 24D 1H	Safety class II	220 to 240 V	50 or 60 Hz	9 W	No
929003224210	RS350 G2 SF Rd D80 7W 30K 24D 1H	Safety class II	220 to 240 V	50 or 60 Hz	7 W	No
929003224410	RS350 G2 SF Rd D80 7W 40K 24D 1H	Safety class II	220 to 240 V	50 or 60 Hz	7 W	No
929004129910	RS350 G2 RC Sq L100 2*15W 30K 24D 2H	Safety class II	220 to 240 V	-	30 W	Not applicable
929004130010	RS350 G2 RC Sq L100 2*15W 30K 36D 2H	Safety class II	220 to 240 V	-	30 W	Not applicable
929004130110	RS350 G2 RC Sq L100 2*15W 40K 24D 2H	Safety class II	220 to 240 V	-	30 W	Not applicable
929004130210	RS350 G2 RC Sq L100 2*15W 40K 36D 2H	Safety class II	220 to 240 V	-	30 W	Not applicable
929004130310	RS350 G2 RC Sq L100 2*23W 30K 24D 2H	Safety class II	220 to 240 V	-	46 W	Not applicable
929004130410	RS350 G2 RC Sq L100 2*23W 30K 36D 2H	Safety class II	220 to 240 V	-	46 W	Not applicable
929004130510	RS350 G2 RC Sq L100 2*23W 40K 24D 2H	Safety class II	220 to 240 V	-	46 W	Not applicable
929004130610	RS350 G2 RC Sq L100 2*23W 40K 36D 2H	Safety class II	220 to 240 V	-	46 W	Not applicable
929003214410	RS350 G2 RC Rd D55 4W 30K 24D 1H	Safety class II	220 to 240 V	50 or 60 Hz	4 W	No
929003214510	RS350 G2 RC Rd D55 4W 30K 36D 1H	Safety class II	220 to 240 V	50 or 60 Hz	4 W	No
929003214710	RS350 G2 RC Rd D55 4W 40K 24D 1H	Safety class II	220 to 240 V	50 or 60 Hz	4 W	No
929003214810	RS350 G2 RC Rd D55 4W 40K 36D 1H	Safety class II	220 to 240 V	50 or 60 Hz	4 W	No
929003215010	RS350 G2 RC Rd D55 7W 30K 24D 1H	Safety class II	220 to 240 V	50 or 60 Hz	7 W	No
929003215110	RS350 G2 RC Rd D55 7W 30K 36D 1H	Safety class II	220 to 240 V	50 or 60 Hz	7 W	No
929003215310	RS350 G2 RC Rd D55 7W 40K 24D 1H	Safety class II	220 to 240 V	50 or 60 Hz	7 W	No

Deep Recessed Spotlight

Order Code	Full Product Name	Protection class IEC	Input Voltage	Line Frequency	Power Consumption	Suitable for random switching
929003215410	RS350 G2 RC Rd D55 7W 40K 36D 1H	Safety class II	220 to 240 V	50 or 60 Hz	7 W	No
929003219110	RS350 G2 RC Rd D100 23W 40K 50D 1H	Safety class II	220 to 240 V	50 or 60 Hz	23 W	No
929004099110	RS350 G2 RC Rd D100 15W 30K 24D 1H	Safety class II	220 to 240 V	-	15 W	Not applicable
929004099210	RS350 G2 RC Rd D100 15W 30K 36D 1H	Safety class II	220 to 240 V	-	15 W	Not applicable
929004099410	RS350 G2 RC Rd D100 15W 40K 24D 1H	Safety class II	220 to 240 V	-	15 W	Not applicable
929004099510	RS350 G2 RC Rd D100 15W 40K 36D 1H	Safety class II	220 to 240 V	-	15 W	Not applicable
929003219210	RS350 G2 RC Sq L100 *2 30K 24D 2H	Safety class III	Max 33-40 V	- Hz	-	No
929003219310	RS350 G2 RC Sq L100 *2 30K 36D 2H	Safety class III	Max 33-40 V	- Hz	-	No
929003219410	RS350 G2 RC Sq L100 *2 40K 24D 2H	Safety class III	Max 33-40 V	- Hz	-	No
929003219510	RS350 G2 RC Sq L100 *2 40K 36D 2H	Safety class III	Max 33-40 V	- Hz	-	No
929003220810	RS350 G2 SF Sq L100 11W 30K 24D 1H	Safety class II	220 to 240 V	50 or 60 Hz	11 W	No
929003221010	RS350 G2 SF Sq L100 11W 40K 24D 1H	Safety class II	220 to 240 V	50 or 60 Hz	11 W	No
929003221210	RS350 G2 SF Sq L100 9W 30K 24D 1H	Safety class II	220 to 240 V	50 or 60 Hz	9 W	No
929003221410	RS350 G2 SF Sq L100 9W 40K 24D 1H	Safety class II	220 to 240 V	50 or 60 Hz	9 W	No
929003225010	RS350 G2 SF Sq L80 7W 30K 24D 1H	Safety class II	220 to 240 V	50 or 60 Hz	7 W	No
929003225210	RS350 G2 SF Sq L80 7W 40K 24D 1H	Safety class II	220 to 240 V	50 or 60 Hz	7 W	No
929003340210	RS350 G2 RC Rd D75 7W 27K 24D 1H	Safety class II	220 V	50 or 60 Hz	7 W	-
929003340410	RS350 G2 RC Rd D75 7W 35K 24D 1H	Safety class II	220 V	50 or 60 Hz	7 W	-
929003340510	RS350 G2 RC Rd D75 7W 35K 50D 1H	Safety class II	220 V	50 or 60 Hz	7 W	-
929003340610	RS350 G2 RC Rd D75 9W 27K 24D 1H	Safety class II	220 V	50 or 60 Hz	9 W	-
929003340810	RS350 G2 RC Rd D75 9W 35K 24D 1H	Safety class II	220 V	50 or 60 Hz	9 W	-
929003340910	RS350 G2 RC Rd D75 9W 35K 50D 1H	Safety class II	220 V	50 or 60 Hz	9 W	-
929003341010	RS350 G2 RC Rd D75 11W 27K 24D 1H	Safety class II	220 V	50 or 60 Hz	11 W	-
929003341210	RS350 G2 RC Rd D75 11W 35K 24D 1H	Safety class II	220 V	50 or 60 Hz	11 W	-
929003341310	RS350 G2 RC Rd D75 11W 35K 50D 1H	Safety class II	220 V	50 or 60 Hz	11 W	-
929003343410	RS350 G2 RC Rd D75 7W 27K 36D 1H	Safety class II	220 V	50 or 60 Hz	7 W	-
929003343510	RS350 G2 RC Rd D75 7W 35K 36D 1H	Safety class II	220 V	50 or 60 Hz	7 W	-
929003343610	RS350 G2 RC Rd D75 9W 27K 36D 1H	Safety class II	220 V	50 or 60 Hz	9 W	-
929003343710	RS350 G2 RC Rd D75 9W 35K 36D 1H	Safety class II	220 V	50 or 60 Hz	9 W	-
929003343810	RS350 G2 RC Rd D75 11W 27K 36D 1H	Safety class II	220 V	50 or 60 Hz	11 W	-
929003343910	RS350 G2 RC Rd D75 11W 35K 36D 1H	Safety class II	220 V	50 or 60 Hz	11 W	-

Mechanical and Housing

		Housing	Mech. impact			Housing	Mech. impact
Order Code	Full Product Name	Color	code	Order Code	Full Product Name	Color	code
929003222610	RS350 G2 RC Sq L55 2*7W 30K 24D 2H	White	IK03	929003216910	RS350 G2 RC Rd D75 9W 30K 36D 1H	Gray	IK03
929003222710	RS350 G2 RC Sq L55 2*7W 30K 36D 2H	White	IK03	929003217010	RS350 G2 RC Rd D75 9W 30K 50D 1H	Gray	IK03
929003222810	RS350 G2 RC Sq L55 2*7W 40K 24D 2H	White	IK03	929003217110	RS350 G2 RC Rd D75 9W 40K 24D 1H	Gray	IK03
929003222910	RS350 G2 RC Sq L55 2*7W 40K 36D 2H	White	IK03	929003217210	RS350 G2 RC Rd D75 9W 40K 36D 1H	Gray	IK03
929003223410	RS350 G2 RC Sq L75 2*11W 30K 24D 2H	Gray	IK03	929003217310	RS350 G2 RC Rd D75 9W 40K 50D 1H	Gray	IK03
929003223510	RS350 G2 RC Sq L75 2*11W 30K 36D 2H	Gray	IK03	929003217410	RS350 G2 RC Rd D75 11W 30K 24D 1H	Gray	IK03
929003223610	RS350 G2 RC Sq L75 2*11W 40K 24D 2H	Gray	IK03	929003217510	RS350 G2 RC Rd D75 11W 30K 36D 1H	Gray	IK03
929003223710	RS350 G2 RC Sq L75 2*11W 40K 36D 2H	Gray	IK03	929003217610	RS350 G2 RC Rd D75 11W 30K 50D 1H	Gray	IK03
929003216210	RS350 G2 RC Rd D75 7W 30K 24D 1H	Gray	IK03	929003217710	RS350 G2 RC Rd D75 11W 40K 24D 1H	Gray	IK03
929003216310	RS350 G2 RC Rd D75 7W 30K 36D 1H	Gray	IK03	929003217810	RS350 G2 RC Rd D75 11W 40K 36D 1H	Gray	IK03
929003216410	RS350 G2 RC Rd D75 7W 30K 50D 1H	Gray	IK03	929003217910	RS350 G2 RC Rd D75 11W 40K 50D 1H	Gray	IK03
929003216510	RS350 G2 RC Rd D75 7W 40K 24D 1H	Gray	IK03	929004098710	RS350 G2 RC Rd D75 11W 27K 15D 1H	Dark gray	IK03
929003216610	RS350 G2 RC Rd D75 7W 40K 36D 1H	Gray	IK03	929004098810	RS350 G2 RC Rd D75 11W 30K 15D 1H	Dark gray	IK03
929003216710	RS350 G2 RC Rd D75 7W 40K 50D 1H	Gray	IK03	929004098910	RS350 G2 RC Rd D75 11W 35K 15D 1H	Dark gray	IK03
929003216810	RS350 G2 RC Rd D75 9W 30K 24D 1H	Gray	IK03	929004099010	RS350 G2 RC Rd D75 11W 40K 15D 1H	Dark gray	IK03

Deep Recessed Spotlight

Order Code	Full Product Name	Housing Color	Mech. impact protection code
929003220010	RS350 G2 SF Rd D100 11W 30K 24D 1H	White	IK03
929003220210	RS350 G2 SF Rd D100 11W 40K 24D 1H	White	IK03
929003220410	RS350 G2 SF Rd D100 9W 30K 24D 1H	White	IK03
929003220610	RS350 G2 SF Rd D100 9W 40K 24D 1H	White	IK03
929003224210	RS350 G2 SF Rd D80 7W 30K 24D 1H	White	IK03
929003224410	RS350 G2 SF Rd D80 7W 40K 24D 1H	White	IK03
929004129910	RS350 G2 RC Sq L100 2*15W 30K 24D 2H	Dark gray	IK03
929004130010	RS350 G2 RC Sq L100 2*15W 30K 36D 2H	Dark gray	IK03
929004130110	RS350 G2 RC Sq L100 2*15W 40K 24D 2H	Dark gray	IK03
929004130210	RS350 G2 RC Sq L100 2*15W 40K 36D 2H	Dark gray	IK03
929004130310	RS350 G2 RC Sq L100 2*23W 30K 24D 2H	Dark gray	IK03
929004130410	RS350 G2 RC Sq L100 2*23W 30K 36D 2H	Dark gray	IK03
929004130510	RS350 G2 RC Sq L100 2*23W 40K 24D 2H	Dark gray	IK03
929004130610	RS350 G2 RC Sq L100 2*23W 40K 36D 2H	Dark gray	IK03
929003214410	RS350 G2 RC Rd D55 4W 30K 24D 1H	Gray	IK03
929003214510	RS350 G2 RC Rd D55 4W 30K 36D 1H	Gray	IK03
929003214710	RS350 G2 RC Rd D55 4W 40K 24D 1H	Gray	IK03
929003214810	RS350 G2 RC Rd D55 4W 40K 36D 1H	Gray	IK03
929003215010	RS350 G2 RC Rd D55 7W 30K 24D 1H	Gray	IK03
929003215110	RS350 G2 RC Rd D55 7W 30K 36D 1H	Gray	IK03
929003215310	RS350 G2 RC Rd D55 7W 40K 24D 1H	Gray	IK03
929003215410	RS350 G2 RC Rd D55 7W 40K 36D 1H	Gray	IK03

Approval and Application

Order Code	Full Product Name	Glow-wire test
929003222610	RS350 G2 RC Sq L55 2*7W 30K 24D 2H	Temperature 650 °C, duration 30 s
929003222710	RS350 G2 RC Sq L55 2*7W 30K 36D 2H	Temperature 650 °C, duration 30 s
929003222810	RS350 G2 RC Sq L55 2*7W 40K 24D 2H	Temperature 650 °C, duration 30 s
929003222910	RS350 G2 RC Sq L55 2*7W 40K 36D 2H	Temperature 650 °C, duration 30 s
929003223410	RS350 G2 RC Sq L75 2*11W 30K 24D 2H	Temperature 650 °C, duration 30 s
929003223510	RS350 G2 RC Sq L75 2*11W 30K 36D 2H	Temperature 650 °C, duration 30 s
929003223610	RS350 G2 RC Sq L75 2*11W 40K 24D 2H	Temperature 650 °C, duration 30 s
929003223710	RS350 G2 RC Sq L75 2*11W 40K 36D 2H	Temperature 650 °C, duration 30 s

Order Code	Full Product Name	Housing Color	Mech. impact protection code
929003219110	RS350 G2 RC Rd D100 23W 40K 50D 1H	Gray	IK03
929004099110	RS350 G2 RC Rd D100 15W 30K 24D 1H	Dark gray	IK03
929004099210	RS350 G2 RC Rd D100 15W 30K 36D 1H	Dark gray	IK03
929004099410	RS350 G2 RC Rd D100 15W 40K 24D 1H	Dark gray	IK03
929004099510	RS350 G2 RC Rd D100 15W 40K 36D 1H	Dark gray	IK03
929003219210	RS350 G2 RC Sq L100 *2 30K 24D 2H	Grey	IK03
929003219310	RS350 G2 RC Sq L100 *2 30K 36D 2H	Grey	IK03
929003219410	RS350 G2 RC Sq L100 *2 40K 24D 2H	Grey	IK03
929003219510	RS350 G2 RC Sq L100 *2 40K 36D 2H	Grey	IK03
929003220810	RS350 G2 SF Sq L100 11W 30K 24D 1H	White	IK03
929003221010	RS350 G2 SF Sq L100 11W 40K 24D 1H	White	IK03
929003221210	RS350 G2 SF Sq L100 9W 30K 24D 1H	White	IK03
929003221410	RS350 G2 SF Sq L100 9W 40K 24D 1H	White	IK03
929003225010	RS350 G2 SF Sq L80 7W 30K 24D 1H	White	IK03
929003225210	RS350 G2 SF Sq L80 7W 40K 24D 1H	White	IK03
929003340210	RS350 G2 RC Rd D75 7W 27K 24D 1H	Dark gray	-
929003340410	RS350 G2 RC Rd D75 7W 35K 24D 1H	Dark gray	-
929003340510	RS350 G2 RC Rd D75 7W 35K 50D 1H	Dark gray	-
929003340610	RS350 G2 RC Rd D75 9W 27K 24D 1H	Dark gray	-
929003340810	RS350 G2 RC Rd D75 9W 35K 24D 1H	Dark gray	-
929003340910	RS350 G2 RC Rd D75 9W 35K 50D 1H	Dark gray	-
929003341010	RS350 G2 RC Rd D75 11W 27K 24D 1H	Dark gray	-
929003341210	RS350 G2 RC Rd D75 11W 35K 24D 1H	Dark gray	-
929003341310	RS350 G2 RC Rd D75 11W 35K 50D 1H	Dark gray	-
929003343410	RS350 G2 RC Rd D75 7W 27K 36D 1H	Dark gray	-
929003343510	RS350 G2 RC Rd D75 7W 35K 36D 1H	Dark gray	-
929003343610	RS350 G2 RC Rd D75 9W 27K 36D 1H	Dark gray	-
929003343710	RS350 G2 RC Rd D75 9W 35K 36D 1H	Dark gray	-
929003343810	RS350 G2 RC Rd D75 11W 27K 36D 1H	Dark gray	-
929003343910	RS350 G2 RC Rd D75 11W 35K 36D 1H	Dark gray	-

Order Code	Full Product Name	Glow-wire test
929003216210	RS350 G2 RC Rd D75 7W 30K 24D 1H	Temperature 650 °C, duration 30 s
929003216310	RS350 G2 RC Rd D75 7W 30K 36D 1H	Temperature 650 °C, duration 30 s
929003216410	RS350 G2 RC Rd D75 7W 30K 50D 1H	Temperature 650 °C, duration 30 s
929003216510	RS350 G2 RC Rd D75 7W 40K 24D 1H	Temperature 650 °C, duration 30 s
929003216610	RS350 G2 RC Rd D75 7W 40K 36D 1H	Temperature 650 °C, duration 30 s
929003216710	RS350 G2 RC Rd D75 7W 40K 50D 1H	Temperature 650 °C, duration 30 s
929003216810	RS350 G2 RC Rd D75 9W 30K 24D 1H	Temperature 650 °C, duration 30 s
929003216910	RS350 G2 RC Rd D75 9W 30K 36D 1H	Temperature 650 °C, duration 30 s

Deep Recessed Spotlight

Order Code	Full Product Name	Glow-wire test
929003217010	RS350 G2 RC Rd D75 9W 30K 50D 1H	Temperature 650 °C, duration 30 s
929003217110	RS350 G2 RC Rd D75 9W 40K 24D 1H	Temperature 650 °C, duration 30 s
929003217210	RS350 G2 RC Rd D75 9W 40K 36D 1H	Temperature 650 °C, duration 30 s
929003217310	RS350 G2 RC Rd D75 9W 40K 50D 1H	Temperature 650 °C, duration 30 s
929003217410	RS350 G2 RC Rd D75 11W 30K 24D 1H	Temperature 650 °C, duration 30 s
929003217510	RS350 G2 RC Rd D75 11W 30K 36D 1H	Temperature 650 °C, duration 30 s
929003217610	RS350 G2 RC Rd D75 11W 30K 50D 1H	Temperature 650 °C, duration 30 s
929003217710	RS350 G2 RC Rd D75 11W 40K 24D 1H	Temperature 650 °C, duration 30 s
929003217810	RS350 G2 RC Rd D75 11W 40K 36D 1H	Temperature 650 °C, duration 30 s
929003217910	RS350 G2 RC Rd D75 11W 40K 50D 1H	Temperature 650 °C, duration 30 s
929004098710	RS350 G2 RC Rd D75 11W 27K 15D 1H	Temperature 650 °C, duration 30 s
929004098810	RS350 G2 RC Rd D75 11W 30K 15D 1H	Temperature 650 °C, duration 30 s
929004098910	RS350 G2 RC Rd D75 11W 35K 15D 1H	Temperature 650 °C, duration 30 s
929004099010	RS350 G2 RC Rd D75 11W 40K 15D 1H	Temperature 650 °C, duration 30 s
929003220010	RS350 G2 SF Rd D100 11W 30K 24D 1H	Temperature 650 °C, duration 30 s
929003220210	RS350 G2 SF Rd D100 11W 40K 24D 1H	Temperature 650 °C, duration 30 s
929003220410	RS350 G2 SF Rd D100 9W 30K 24D 1H	Temperature 650 °C, duration 30 s
929003220610	RS350 G2 SF Rd D100 9W 40K 24D 1H	Temperature 650 °C, duration 30 s
929003224210	RS350 G2 SF Rd D80 7W 30K 24D 1H	Temperature 650 °C, duration 30 s
929003224410	RS350 G2 SF Rd D80 7W 40K 24D 1H	Temperature 650 °C, duration 30 s
929004129910	RS350 G2 RC Sq L100 2*15W 30K 24D 2H	Temperature 650 °C, duration 30 s
929004130010	RS350 G2 RC Sq L100 2*15W 30K 36D 2H	Temperature 650 °C, duration 30 s
929004130110	RS350 G2 RC Sq L100 2*15W 40K 24D 2H	Temperature 650 °C, duration 30 s
929004130210	RS350 G2 RC Sq L100 2*15W 40K 36D 2H	Temperature 650 °C, duration 30 s
929004130310	RS350 G2 RC Sq L100 2*23W 30K 24D 2H	Temperature 650 °C, duration 30 s
929004130410	RS350 G2 RC Sq L100 2*23W 30K 36D 2H	Temperature 650 °C, duration 30 s

Order Code	Full Product Name	Glow-wire test
929004130510	RS350 G2 RC Sq L100 2*23W 40K 24D 2H	Temperature 650 °C, duration 30 s
929004130610	RS350 G2 RC Sq L100 2*23W 40K 36D 2H	Temperature 650 °C, duration 30 s
929003214410	RS350 G2 RC Rd D55 4W 30K 24D 1H	Temperature 650 °C, duration 30 s
929003214510	RS350 G2 RC Rd D55 4W 30K 36D 1H	Temperature 650 °C, duration 30 s
929003214710	RS350 G2 RC Rd D55 4W 40K 24D 1H	Temperature 650 °C, duration 30 s
929003214810	RS350 G2 RC Rd D55 4W 40K 36D 1H	Temperature 650 °C, duration 30 s
929003215010	RS350 G2 RC Rd D55 7W 30K 24D 1H	Temperature 650 °C, duration 30 s
929003215110	RS350 G2 RC Rd D55 7W 30K 36D 1H	Temperature 650 °C, duration 30 s
929003215310	RS350 G2 RC Rd D55 7W 40K 24D 1H	Temperature 650 °C, duration 30 s
929003215410	RS350 G2 RC Rd D55 7W 40K 36D 1H	Temperature 650 °C, duration 30 s
929003219110	RS350 G2 RC Rd D100 23W 40K 50D 1H	Temperature 650 °C, duration 30 s
929004099110	RS350 G2 RC Rd D100 15W 30K 24D 1H	Temperature 650 °C, duration 30 s
929004099210	RS350 G2 RC Rd D100 15W 30K 36D 1H	Temperature 650 °C, duration 30 s
929004099410	RS350 G2 RC Rd D100 15W 40K 24D 1H	Temperature 650 °C, duration 30 s
929004099510	RS350 G2 RC Rd D100 15W 40K 36D 1H	Temperature 650 °C, duration 30 s
929003219210	RS350 G2 RC Sq L100 *2 30K 24D 2H	Temperature 650 °C, duration 30 s
929003219310	RS350 G2 RC Sq L100 *2 30K 36D 2H	Temperature 650 °C, duration 30 s
929003219410	RS350 G2 RC Sq L100 *2 40K 24D 2H	Temperature 650 °C, duration 30 s
929003219510	RS350 G2 RC Sq L100 *2 40K 36D 2H	Temperature 650 °C, duration 30 s
929003220810	RS350 G2 SF Sq L100 11W 30K 24D 1H	Temperature 650 °C, duration 30 s
929003221010	RS350 G2 SF Sq L100 11W 40K 24D 1H	Temperature 650 °C, duration 30 s
929003221210	RS350 G2 SF Sq L100 9W 30K 24D 1H	Temperature 650 °C, duration 30 s
929003221410	RS350 G2 SF Sq L100 9W 40K 24D 1H	Temperature 650 °C, duration 30 s
929003225010	RS350 G2 SF Sq L80 7W 30K 24D 1H	Temperature 650 °C, duration 30 s
929003225210	RS350 G2 SF Sq L80 7W 40K 24D 1H	Temperature 650 °C, duration 30 s
929003340210	RS350 G2 RC Rd D75 7W 27K 24D 1H	-
929003340410	RS350 G2 RC Rd D75 7W 35K 24D 1H	-

Deep Recessed Spotlight

Order Code	Full Product Name	Glow-wire test
929003340510	RS350 G2 RC Rd D75 7W 35K 50D 1H	-
929003340610	RS350 G2 RC Rd D75 9W 27K 24D 1H	-
929003340810	RS350 G2 RC Rd D75 9W 35K 24D 1H	-
929003340910	RS350 G2 RC Rd D75 9W 35K 50D 1H	-
929003341010	RS350 G2 RC Rd D75 11W 27K 24D 1H	-
929003341210	RS350 G2 RC Rd D75 11W 35K 24D 1H	-
929003341310	RS350 G2 RC Rd D75 11W 35K 50D 1H	-

Order Code	Full Product Name	Glow-wire test
929003343410	RS350 G2 RC Rd D75 7W 27K 36D 1H	-
929003343510	RS350 G2 RC Rd D75 7W 35K 36D 1H	-
929003343610	RS350 G2 RC Rd D75 9W 27K 36D 1H	-
929003343710	RS350 G2 RC Rd D75 9W 35K 36D 1H	-
929003343810	RS350 G2 RC Rd D75 11W 27K 36D 1H	-
929003343910	RS350 G2 RC Rd D75 11W 35K 36D 1H	-

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
929003222610	RS350 G2 RC Sq L55 2*7W 30K 24D 2H	((, 0.4369 , , 0.404)) 5SDCM	+/-10%
929003222710	RS350 G2 RC Sq L55 2*7W 30K 36D 2H	((, 0.4369 , , 0.404)) 5SDCM	+/-10%
929003222810	RS350 G2 RC Sq L55 2*7W 40K 24D 2H	((, 0.3804 , , 0.3767)) 5SDCM	+/-10%
929003222910	RS350 G2 RC Sq L55 2*7W 40K 36D 2H	((, 0.3804 , , 0.3767)) 5SDCM	+/-10%
929003223410	RS350 G2 RC Sq L75 2*11W 30K 24D 2H	((, 0.4341 , , 0.3993)) 5SDCM	+/-10%
929003223510	RS350 G2 RC Sq L75 2*11W 30K 36D 2H	((, 0.4341 , , 0.3993)) 5SDCM	+/-10%
929003223610	RS350 G2 RC Sq L75 2*11W 40K 24D 2H	((, 0.3732 , , 0.3641)) 5SDCM	+/-10%
929003223710	RS350 G2 RC Sq L75 2*11W 40K 36D 2H	((, 0.3732 , , 0.3641)) 5SDCM	+/-10%
929003216210	RS350 G2 RC Rd D75 7W 30K 24D 1H	(0.4369, 0.404) 5SDCM	+/-10%
929003216310	RS350 G2 RC Rd D75 7W 30K 36D 1H	(0.4369, 0.404) 5SDCM	+/-10%
929003216410	RS350 G2 RC Rd D75 7W 30K 50D 1H	(0.4369, 0.404) 5SDCM	+/-10%
929003216510	RS350 G2 RC Rd D75 7W 40K 24D 1H	(0.3804, 0.3767) 5SDCM	+/-10%
929003216610	RS350 G2 RC Rd D75 7W 40K 36D 1H	(0.3804, 0.3767) 5SDCM	+/-10%
929003216710	RS350 G2 RC Rd D75 7W 40K 50D 1H	(0.3804, 0.3767) 5SDCM	+/-10%
929003216810	RS350 G2 RC Rd D75 9W 30K 24D 1H	(0.4369, 0.404) 5SDCM	+/-10%
929003216910	RS350 G2 RC Rd D75 9W 30K 36D 1H	(0.4369, 0.404) 5SDCM	+/-10%
929003217010	RS350 G2 RC Rd D75 9W 30K 50D 1H	(0.4369, 0.404) 5SDCM	+/-10%
929003217110	RS350 G2 RC Rd D75 9W 40K 24D 1H	(0.3804, 0.3767) 5SDCM	+/-10%
929003217210	RS350 G2 RC Rd D75 9W 40K 36D 1H	(0.3804, 0.3767) 5SDCM	+/-10%

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
929003217310	RS350 G2 RC Rd D75 9W 40K 50D 1H	(0.3804, 0.3767) 5SDCM	+/-10%
929003217410	RS350 G2 RC Rd D75 11W 30K 24D 1H	(0.4341, 0.3993) 5SDCM	+/-10%
929003217510	RS350 G2 RC Rd D75 11W 30K 36D 1H	(0.4341, 0.3993) 5SDCM	+/-10%
929003217610	RS350 G2 RC Rd D75 11W 30K 50D 1H	(0.4341, 0.3993) 5SDCM	+/-10%
929003217710	RS350 G2 RC Rd D75 11W 40K 24D 1H	(0.3732, 0.3641) 5SDCM	+/-10%
929003217810	RS350 G2 RC Rd D75 11W 40K 36D 1H	(0.3732, 0.3641) 5SDCM	+/-10%
929003217910	RS350 G2 RC Rd D75 11W 40K 50D 1H	(0.3732, 0.3641) 5SDCM	+/-10%
929004098710	RS350 G2 RC Rd D75 11W 27K 15D 1H	(0.4620, 0.4074) <5SDCM	+/-10%
929004098810	RS350 G2 RC Rd D75 11W 30K 15D 1H	(0.4373, 0.4006) <5SDCM	+/-10%
929004098910	RS350 G2 RC Rd D75 11W 35K 15D 1H	(0.4033, 0.3800) <5SDCM	+/-10%
929004099010	RS350 G2 RC Rd D75 11W 40K 15D 1H	(0.3777, 0.3659) <5SDCM	+/-10%
929003220010	RS350 G2 SF Rd D100 11W 30K 24D 1H	((, 0.4341 , , 0.3993)) 5SDCM	+/-10%
929003220210	RS350 G2 SF Rd D100 11W 40K 24D 1H	((, 0.3732 , , 0.3641)) 5SDCM	+/-10%
929003220410	RS350 G2 SF Rd D100 9W 30K 24D 1H	((, 0.4369 , , 0.404)) 5SDCM	+/-10%
929003220610	RS350 G2 SF Rd D100 9W 40K 24D 1H	((, 0.3804 , , 0.3767)) 5SDCM	+/-10%
929003224210	RS350 G2 SF Rd D80 7W 30K 24D 1H	((, 0.4369 , , 0.404)) 5SDCM	+/-10%
929003224410	RS350 G2 SF Rd D80 7W 40K 24D 1H	((, 0.3804 , , 0.3767)) 5SDCM	+/-10%
929004129910	RS350 G2 RC Sq L100 2*15W 30K 24D 2H	(0.4357, 0.4017) <5SDCM	+/-10%
929004130010	RS350 G2 RC Sq L100 2*15W 30K 36D 2H	(0.4357, 0.4017) <5SDCM	+/-10%

Deep Recessed Spotlight

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
929004130110	RS350 G2 RC Sq L100 2*15W 40K 24D 2H	(0.3779, 0.3683) <5SDCM	+/-10%
929004130210	RS350 G2 RC Sq L100 2*15W 40K 36D 2H	(0.3779, 0.3683) <5SDCM	+/-10%
929004130310	RS350 G2 RC Sq L100 2*23W 30K 24D 2H	(0.4357, 0.4017) <5SDCM	+/-10%
929004130410	RS350 G2 RC Sq L100 2*23W 30K 36D 2H	(0.4357, 0.4017) <5SDCM	+/-10%
929004130510	RS350 G2 RC Sq L100 2*23W 40K 24D 2H	(0.3779, 0.3683) <5SDCM	+/-10%
929004130610	RS350 G2 RC Sq L100 2*23W 40K 36D 2H	(0.3779, 0.3683) <5SDCM	+/-10%
929003214410	RS350 G2 RC Rd D55 4W 30K 24D 1H	(0.4369, 0.404) 5SDCM	+/-10%
929003214510	RS350 G2 RC Rd D55 4W 30K 36D 1H	(0.4369, 0.404) 5SDCM	+/-10%
929003214710	RS350 G2 RC Rd D55 4W 40K 24D 1H	(0.3804, 0.3767) 5SDCM	+/-10%
929003214810	RS350 G2 RC Rd D55 4W 40K 36D 1H	(0.3804, 0.3767) 5SDCM	+/-10%
929003215010	RS350 G2 RC Rd D55 7W 30K 24D 1H	(0.4369, 0.404) 5SDCM	+/-10%
929003215110	RS350 G2 RC Rd D55 7W 30K 36D 1H	(0.4369, 0.404) 5SDCM	+/-10%
929003215310	RS350 G2 RC Rd D55 7W 40K 24D 1H	(0.3804, 0.3767) 5SDCM	+/-10%
929003215410	RS350 G2 RC Rd D55 7W 40K 36D 1H	(0.3804, 0.3767) 5SDCM	+/-10%
929003219110	RS350 G2 RC Rd D100 23W 40K 50D 1H	(0.3732, 0.3641) 5SDCM	+/-10%
929004099110	RS350 G2 RC Rd D100 15W 30K 24D 1H	(0.4357, 0.4017) <5SDCM	+/-10%
929004099210	RS350 G2 RC Rd D100 15W 30K 36D 1H	(0.4357, 0.4017) <5SDCM	+/-10%
929004099410	RS350 G2 RC Rd D100 15W 40K 24D 1H	(0.3779, 0.3683) <5SDCM	+/-10%
929004099510	RS350 G2 RC Rd D100 15W 40K 36D 1H	(0.3779, 0.3683) <5SDCM	+/-10%
929003219210	RS350 G2 RC Sq L100 *2 30K 24D 2H	((, 0.4341 , , 0.3993)) - 5SDCM	-
929003219310	RS350 G2 RC Sq L100 *2 30K 36D 2H	((, 0.4341 , , 0.3993)) - 5SDCM	-
929003219410	RS350 G2 RC Sq L100 *2 40K 24D 2H	((, 0.3732 , , 0.3641)) - 5SDCM	-

Over Time Performance (IEC Compliant)


Order Code	Full Product Name	Driver failure rate at 5000 h
929003222610	RS350 G2 RC Sq L55 2*7W 30K 24D 2H	0.015 %

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
929003219510	RS350 G2 RC Sq L100 *2 40K 36D 2H	((, 0.3732 , , 0.3641)) 5SDCM	-
929003220810	RS350 G2 SF Sq L100 11W 30K 24D 1H	((, 0.4341 , , 0.3993)) 5SDCM	+/-10%
929003221010	RS350 G2 SF Sq L100 11W 40K 24D 1H	((, 0.3732 , , 0.3641)) 5SDCM	+/-10%
929003221210	RS350 G2 SF Sq L100 9W 30K 24D 1H	((, 0.4369 , , 0.404)) 5SDCM	+/-10%
929003221410	RS350 G2 SF Sq L100 9W 40K 24D 1H	((, 0.3804 , , 0.3767)) 5SDCM	+/-10%
929003225010	RS350 G2 SF Sq L80 7W 30K 24D 1H	((, 0.4369 , , 0.404)) 5SDCM	+/-10%
929003225210	RS350 G2 SF Sq L80 7W 40K 24D 1H	((, 0.3804 , , 0.3767)) 5SDCM	+/-10%
929003340210	RS350 G2 RC Rd D75 7W 27K 24D 1H	-	+/-10%
929003340410	RS350 G2 RC Rd D75 7W 35K 24D 1H	-	+/-10%
929003340510	RS350 G2 RC Rd D75 7W 35K 50D 1H	-	+15%/-5%
929003340610	RS350 G2 RC Rd D75 9W 27K 24D 1H	-	+/-10%
929003340810	RS350 G2 RC Rd D75 9W 35K 24D 1H	-	+/-10%
929003340910	RS350 G2 RC Rd D75 9W 35K 50D 1H	-	+15%/-5%
929003341010	RS350 G2 RC Rd D75 11W 27K 24D 1H	-	+/-10%
929003341210	RS350 G2 RC Rd D75 11W 35K 24D 1H	-	+/-10%
929003341310	RS350 G2 RC Rd D75 11W 35K 50D 1H	-	+15%/-5%
929003343410	RS350 G2 RC Rd D75 7W 27K 36D 1H	-	+/-10%
929003343510	RS350 G2 RC Rd D75 7W 35K 36D 1H	-	+/-10%
929003343610	RS350 G2 RC Rd D75 9W 27K 36D 1H	-	+/-10%
929003343710	RS350 G2 RC Rd D75 9W 35K 36D 1H	-	+/-10%
929003343810	RS350 G2 RC Rd D75 11W 27K 36D 1H	-	+/-10%
929003343910	RS350 G2 RC Rd D75 11W 35K 36D 1H	-	+/-10%



Deep Recessed Spotlight

Order Code	Full Product Name	Driver failure rate at 5000
		h
929003222810	RS350 G2 RC Sq L55 2*7W 40K 24D 2H	0.015 %
929003222910	RS350 G2 RC Sq L55 2*7W 40K 36D 2H	0.015 %
929003223410	RS350 G2 RC Sq L75 2*11W 30K 24D 2H	0.015 %
929003223510	RS350 G2 RC Sq L75 2*11W 30K 36D 2H	0.015 %
929003223610	RS350 G2 RC Sq L75 2*11W 40K 24D 2H	0.015 %
929003223710	RS350 G2 RC Sq L75 2*11W 40K 36D 2H	0.015 %
929003216210	RS350 G2 RC Rd D75 7W 30K 24D 1H	0.015 %
929003216310	RS350 G2 RC Rd D75 7W 30K 36D 1H	0.015 %
929003216410	RS350 G2 RC Rd D75 7W 30K 50D 1H	0.015 %
929003216510	RS350 G2 RC Rd D75 7W 40K 24D 1H	0.015 %
929003216610	RS350 G2 RC Rd D75 7W 40K 36D 1H	0.015 %
929003216710	RS350 G2 RC Rd D75 7W 40K 50D 1H	0.015 %
929003216810	RS350 G2 RC Rd D75 9W 30K 24D 1H	0.015 %
929003216910	RS350 G2 RC Rd D75 9W 30K 36D 1H	0.015 %
929003217010	RS350 G2 RC Rd D75 9W 30K 50D 1H	0.015 %
929003217110	RS350 G2 RC Rd D75 9W 40K 24D 1H	0.015 %
929003217210	RS350 G2 RC Rd D75 9W 40K 36D 1H	0.015 %
929003217310	RS350 G2 RC Rd D75 9W 40K 50D 1H	0.015 %
929003217410	RS350 G2 RC Rd D75 11W 30K 24D 1H	0.015 %
929003217510	RS350 G2 RC Rd D75 11W 30K 36D 1H	0.015 %
929003217610	RS350 G2 RC Rd D75 11W 30K 50D 1H	0.015 %
929003217710	RS350 G2 RC Rd D75 11W 40K 24D 1H	0.015 %
929003217810	RS350 G2 RC Rd D75 11W 40K 36D 1H	0.015 %
929003217910	RS350 G2 RC Rd D75 11W 40K 50D 1H	0.015 %
929004098710	RS350 G2 RC Rd D75 11W 27K 15D 1H	-
929004098810	RS350 G2 RC Rd D75 11W 30K 15D 1H	-
929004098910	RS350 G2 RC Rd D75 11W 35K 15D 1H	-
929004099010	RS350 G2 RC Rd D75 11W 40K 15D 1H	-
929003220010	RS350 G2 SF Rd D100 11W 30K 24D 1H	0.015 %
929003220210	RS350 G2 SF Rd D100 11W 40K 24D 1H	0.015 %
929003220410	RS350 G2 SF Rd D100 9W 30K 24D 1H	0.015 %
929003220610	RS350 G2 SF Rd D100 9W 40K 24D 1H	0.015 %
929003224210	RS350 G2 SF Rd D80 7W 30K 24D 1H	0.015 %
929003224410	RS350 G2 SF Rd D80 7W 40K 24D 1H	0.015 %
929004129910	RS350 G2 RC Sq L100 2*15W 30K 24D 2H	-
929004130010	RS350 G2 RC Sq L100 2*15W 30K 36D 2H	-
929004130110	RS350 G2 RC Sq L100 2*15W 40K 24D 2H	-
929004130210	RS350 G2 RC Sq L100 2*15W 40K 36D 2H	-
929004130310	RS350 G2 RC Sq L100 2*23W 30K 24D 2H	-
929004130410	RS350 G2 RC Sq L100 2*23W 30K 36D 2H	-
929004130510	RS350 G2 RC Sq L100 2*23W 40K 24D 2H	-
929004130610	RS350 G2 RC Sq L100 2*23W 40K 36D 2H	-
929003214410	RS350 G2 RC Rd D55 4W 30K 24D 1H	0.015 %
929003214510	RS350 G2 RC Rd D55 4W 30K 36D 1H	0.015 %
929003214710	RS350 G2 RC Rd D55 4W 40K 24D 1H	0.015 %
929003214810	RS350 G2 RC Rd D55 4W 40K 36D 1H	0.015 %
929003215010	RS350 G2 RC Rd D55 7W 30K 24D 1H	0.015 %
929003215110	RS350 G2 RC Rd D55 7W 30K 36D 1H	0.015 %
929003215310	RS350 G2 RC Rd D55 7W 40K 24D 1H	0.015 %
929003215410	RS350 G2 RC Rd D55 7W 40K 36D 1H	0.015 %
929003219110	RS350 G2 RC Rd D100 23W 40K 50D 1H	0.015 %











Order Code	Full Product Name	Driver failure rate at 5000
		h
929004099110	RS350 G2 RC Rd D100 15W 30K 24D 1H	-
929004099210	RS350 G2 RC Rd D100 15W 30K 36D 1H	-
929004099410	RS350 G2 RC Rd D100 15W 40K 24D 1H	-
929004099510	RS350 G2 RC Rd D100 15W 40K 36D 1H	-
929003219210	RS350 G2 RC Sq L100 *2 30K 24D 2H	-
929003219310	RS350 G2 RC Sq L100 *2 30K 36D 2H	-
929003219410	RS350 G2 RC Sq L100 *2 40K 24D 2H	-
929003219510	RS350 G2 RC Sq L100 *2 40K 36D 2H	-
929003220810	RS350 G2 SF Sq L100 11W 30K 24D 1H	0.015 %
929003221010	RS350 G2 SF Sq L100 11W 40K 24D 1H	0.015 %
929003221210	RS350 G2 SF Sq L100 9W 30K 24D 1H	0.015 %
929003221410	RS350 G2 SF Sq L100 9W 40K 24D 1H	0.015 %
929003225010	RS350 G2 SF Sq L80 7W 30K 24D 1H	0.015 %
929003225210	RS350 G2 SF Sq L80 7W 40K 24D 1H	0.015 %
929003340210	RS350 G2 RC Rd D75 7W 27K 24D 1H	-
929003340410	RS350 G2 RC Rd D75 7W 35K 24D 1H	-
929003340510	RS350 G2 RC Rd D75 7W 35K 50D 1H	-
929003340610	RS350 G2 RC Rd D75 9W 27K 24D 1H	-
929003340810	RS350 G2 RC Rd D75 9W 35K 24D 1H	-
929003340910	RS350 G2 RC Rd D75 9W 35K 50D 1H	-
929003341010	RS350 G2 RC Rd D75 11W 27K 24D 1H	-
929003341210	RS350 G2 RC Rd D75 11W 35K 24D 1H	-
929003341310	RS350 G2 RC Rd D75 11W 35K 50D 1H	-
929003343410	RS350 G2 RC Rd D75 7W 27K 36D 1H	-
929003343510	RS350 G2 RC Rd D75 7W 35K 36D 1H	-
929003343610	RS350 G2 RC Rd D75 9W 27K 36D 1H	-
929003343710	RS350 G2 RC Rd D75 9W 35K 36D 1H	-
929003343810	RS350 G2 RC Rd D75 11W 27K 36D 1H	-
929003343910	RS350 G2 RC Rd D75 11W 35K 36D 1H	-













Deep Recessed Spotlight













Deep Recessed Spotlight













Deep Recessed Spotlight













Deep Recessed Spotlight













Deep Recessed Spotlight





Deep Recessed Spotlight



Deep Recessed Spotlight



Deep Recessed Spotlight



Deep Recessed Spotlight

