



The ideal solution for spot-lighting

MASTER VALUE LEDspot PAR

With its robust design and warm-white beam of light, these new-generation PAR lamps are ideal for general lighting and spot lighting in the hospitality industry. It's a dimmable solution. They are especially suitable for public areas such as lobbies, corridors, stairwells, where the light is always on. The product offers more energy saving comparing with normal LED spots.

Benefits

- Up to 80% energy saving compared to halogen lamps
- Lower maintenance costs
- Retrofittable and compatible with the existing fixtures of the E27 holder

Features

- Dimmable range
- UV- and IR-free light for less heat and protection for heat-sensitive objects
- Free of mercury and hazardous materials – RoHS compliant
- Lifetime of 25,000 hours
- Free of mercury and hazardous materials – RoHS Compliant

Application

- Hospitality: hotel guest rooms, corridors, lobbies, reception areas, restaurants, bars, cafes
- Home: living room, bedrooms, hallway
- Retail: exhibitions, display cabinets, shops, dressing rooms




MASTER VALUE LEDspot PAR

Versions



LED Classic 100W PAR38 WW 25D
D 1PF 4 S

Dimensional drawing



Product	D	C
MAS LEDspot VLE D 13-100W 927 PAR38 25D	122 mm	134 mm

Product	D	C
MAS LEDspot VLE D 6-50W 927 PAR20 25D	65 mm	85 mm
MAS LEDspot VLE D 6-50W 927 PAR20 40D	65 mm	85 mm
MAS LEDspot VLE D 6-50W 930 PAR20 25D	65 mm	85 mm
MAS LEDspot VLE D 6-50W 930 PAR20 40D	65 mm	85 mm
MAS LEDspot VLE D 6-50W 940 PAR20 40D	65 mm	85 mm

Product	D	C
MAS LEDspot VLE D 9.5-75W 927 PAR30S 25D	95 mm	86 mm
MAS LEDspot VLE D 9.5-75W 930 PAR30S 25D	95 mm	86 mm
MAS LEDspot VLE D 9.5-75W 940 PAR30S 25D	95 mm	86 mm

MASTER VALUE LEDspot PAR

General Information	
Cap base	E27
Switching Cycle	50,000
Nominal lifetime	25,000 h
Light Technical	
Colour rendering index (CRI)	90
LLMF at end of nominal lifetime (nom.)	70 %
Operating and Electrical	
Input frequency	50 to 60 Hz
Line Frequency	50 to 60 Hz
Starting time (nom.)	0.5 s
Controls and Dimming	
Dimmable	Only with specific dimmers
Mechanical and Housing	
Lamp Finish	Clear

Light Technical (1/2)

		Correlated Colour			
		Beam angle	Temperature	Colour	
Order Code	Full Product Name	(nom.)	(Nom)	Code	Luminous Flux
44304400	MAS LEDspot VLE D 6-50W 927 PAR20 25D	25 degree(s)	2700 K	927	500 lm
44306800	MAS LEDspot VLE D 6-50W 930 PAR20 25D	25 degree(s)	3000 K	930	515 lm
44310500	MAS LEDspot VLE D 6-50W 927 PAR20 40D	40 degree(s)	2700 K	927	500 lm
44312900	MAS LEDspot VLE D 6-50W 930 PAR20 40D	40 degree(s)	3000 K	930	515 lm
44314300	MAS LEDspot VLE D 6-50W 940 PAR20 40D	40 degree(s)	4000 K	940	540 lm
44330300	MAS LEDspot VLE D 13-100W 927 PAR38 25D	25 degree(s)	2700 K	927	1,000 lm
44320400	MAS LEDspot VLE D 9.5-75W 927 PAR30S 25D	25 degree(s)	2700 K	927	740 lm
44322800	MAS LEDspot VLE D 9.5-75W 930 PAR30S 25D	25 degree(s)	3000 K	930	760 lm
44324200	MAS LEDspot VLE D 9.5-75W 940 PAR30S 25D	25 degree(s)	4000 K	940	820 lm

Light Technical (2/2)

Order Code	Full Product Name	Luminous intensity (nom.)	Order Code	Full Product Name	Luminous intensity (nom.)
44304400	MAS LEDspot VLE D 6-50W 927 PAR20 25D	1,500 cd	44330300	MAS LEDspot VLE D 13-100W 927 PAR38 25D	4,800 cd
44306800	MAS LEDspot VLE D 6-50W 930 PAR20 25D	1,600 cd	44320400	MAS LEDspot VLE D 9.5-75W 927 PAR30S 25D	3,000 cd
44310500	MAS LEDspot VLE D 6-50W 927 PAR20 40D	1,000 cd	44322800	MAS LEDspot VLE D 9.5-75W 930 PAR30S 25D	3,000 cd
44312900	MAS LEDspot VLE D 6-50W 930 PAR20 40D	1,000 cd	44324200	MAS LEDspot VLE D 9.5-75W 940 PAR30S 25D	3,000 cd
44314300	MAS LEDspot VLE D 6-50W 940 PAR20 40D	1,100 cd			

Operating and Electrical

		Power	Wattage
Order Code	Full Product Name	Consumption	equivalent
44304400	MAS LEDspot VLE D 6-50W 927 PAR20 25D	6 W	50 W
44306800	MAS LEDspot VLE D 6-50W 930 PAR20 25D	6 W	50 W
44310500	MAS LEDspot VLE D 6-50W 927 PAR20 40D	6 W	50 W
44312900	MAS LEDspot VLE D 6-50W 930 PAR20 40D	6 W	50 W
44314300	MAS LEDspot VLE D 6-50W 940 PAR20 40D	6 W	50 W
		Power	Wattage
Order Code	Full Product Name	Consumption	equivalent
44330300	MAS LEDspot VLE D 13-100W 927 PAR38 25D	13 W	100 W
44320400	MAS LEDspot VLE D 9.5-75W 927 PAR30S 25D	9.5 W	75 W
44322800	MAS LEDspot VLE D 9.5-75W 930 PAR30S 25D	9.5 W	75 W
44324200	MAS LEDspot VLE D 9.5-75W 940 PAR30S 25D	9.5 W	75 W

Temperature

Order Code	Full Product Name	T-Case maximum (nom.)	Order Code	Full Product Name	T-Case maximum (nom.)
44304400	MAS LEDspot VLE D 6-50W 927 PAR20 25D	80 °C	44310500	MAS LEDspot VLE D 6-50W 927 PAR20 40D	80 °C
44306800	MAS LEDspot VLE D 6-50W 930 PAR20 25D	80 °C	44312900	MAS LEDspot VLE D 6-50W 930 PAR20 40D	80 °C

MASTER VALUE LEDspot PAR


Order Code	Full Product Name	T-Case maximum (nom.)
44314300	MAS LEDspot VLE D 6-50W 940 PAR20 40D	80 °C
44330300	MAS LEDspot VLE D 13-100W 927 PAR38 25D	85 °C
44320400	MAS LEDspot VLE D 9.5-75W 927 PAR30S 25D	80 °C

Mechanical and Housing

Order Code	Full Product Name	Bulb shape
44304400	MAS LEDspot VLE D 6-50W 927 PAR20 25D	PAR20
44306800	MAS LEDspot VLE D 6-50W 930 PAR20 25D	PAR20
44310500	MAS LEDspot VLE D 6-50W 927 PAR20 40D	PAR20
44312900	MAS LEDspot VLE D 6-50W 930 PAR20 40D	PAR20
44314300	MAS LEDspot VLE D 6-50W 940 PAR20 40D	PAR20


Approval and Application

Order Code	Full Product Name	Energy consumption kWh/1,000 hours
44304400	MAS LEDspot VLE D 6-50W 927 PAR20 25D	6 kWh
44306800	MAS LEDspot VLE D 6-50W 930 PAR20 25D	6 kWh
44310500	MAS LEDspot VLE D 6-50W 927 PAR20 40D	6 kWh
44312900	MAS LEDspot VLE D 6-50W 930 PAR20 40D	6 kWh
44314300	MAS LEDspot VLE D 6-50W 940 PAR20 40D	6 kWh
44330300	MAS LEDspot VLE D 13-100W 927 PAR38 25D	13 kWh
44320400	MAS LEDspot VLE D 9.5-75W 927 PAR30S 25D	10 kWh
44322800	MAS LEDspot VLE D 9.5-75W 930 PAR30S 25D	10 kWh
44324200	MAS LEDspot VLE D 9.5-75W 940 PAR30S 25D	10 kWh





Order Code	Full Product Name	T-Case maximum (nom.)
44322800	MAS LEDspot VLE D 9.5-75W 930 PAR30S 25D	80 °C
44324200	MAS LEDspot VLE D 9.5-75W 940 PAR30S 25D	80 °C


Order Code	Full Product Name	Bulb shape
44330300	MAS LEDspot VLE D 13-100W 927 PAR38 25D	PAR38
44320400	MAS LEDspot VLE D 9.5-75W 927 PAR30S 25D	PAR30S
44322800	MAS LEDspot VLE D 9.5-75W 930 PAR30S 25D	PAR30S
44324200	MAS LEDspot VLE D 9.5-75W 940 PAR30S 25D	PAR30S




MASTER VALUE LEDspot PAR




Accent Diagrams




Accent Diagram - MAS LEDspot VLE D 6-50W
927 PAR20 40D




Accent Diagram - MAS LEDspot VLE D 6-50W
927 PAR20 25D




Accent Diagram - MAS LEDspot VLE D 9.5-75W
927 PAR30S 25D



Accent Diagram - MAS LEDspot VLE D 6-50W
930 PAR20 25D




Accent Diagram - MAS LEDspot VLE D 6-50W
940 PAR20 40D




Accent Diagram - MAS LEDspot VLE D 9.5-75W
940 PAR30S 25D

MASTER VALUE LEDspot PAR


Accent Diagrams



Accent Diagram - MAS LEDspot VLE D 9.5-75W
930 PAR30S 25D




Accent Diagram - MAS LEDspot VLE D 13-100W
927 PAR38 25D




Accent Diagram - MAS LEDspot VLE D 6-50W
930 PAR20 40D


Beam Diagrams




Beam diagram - MAS LEDspot VLE D 9.5-75W
927 PAR30S 25D




Beam diagram - MAS LEDspot VLE D 6-50W
927 PAR20 25D




Beam diagram - MAS LEDspot VLE D 6-50W
940 PAR20 40D



Beam diagram - MAS LEDspot VLE D 6-50W
930 PAR20 25D




Beam diagram - MAS LEDspot VLE D 13-100W
927 PAR38 25D




Beam diagram - MAS LEDspot VLE D 6-50W
927 PAR20 40D

MASTER VALUE LEDspot PAR


Beam Diagrams



Beam diagram - MAS LEDspot VLE D 9.5-75W
930 PAR30S 25D



Beam diagram - MAS LEDspot VLE D 6-50W
930 PAR20 40D



Beam diagram - MAS LEDspot VLE D 9.5-75W
940 PAR30S 25D

