



Trusted Performance, everyday.

Smartbright Dual select Batten BN131C

New Philips Dual Select batten offers exceptional value. It is Perfect for your everyday lighting installations. Available in 2 standard sizes, it has option of 3 CCT selection and 2 Lumen output selection to provide flexibility to customer and reduce customer stocking requirements.

Benefits

- Tri-CCT, Dual wattage selectable
- 50K hours life
- 5 Years warranty

Features


- Selectable dual power output to suit multiple application environments.
- 3 selectable colour temperatures to suit specific customer need
- Energy efficient with long service life. (50 000 hours - L70)
- 5 year warranty.
- Available in 600mm/1200mm/1500 mm size

Application

- Offices
- Parking Garages
- Residential

Smartbright Dual select Batten BN131C


Versions



BN131 L1200

BN131 L600

Dimensional drawing



Smartbright Dual select Batten BN131C

Light Technical	
Correlated Color Temperature (Nom)	4000 K
Color rendering index (CRI)	>80
Luminous Efficacy (rated) (Nom)	110 lm/W
Operating and Electrical	
Protection class IEC	Safety class I
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Optical cover type	-
Housing Color	White RAL9016
Mech. impact protection code	IK04
Ingress protection code	IP20
Approval and Application	
Ambient temperature range	-20 to +40 °C
CE mark	No
Flammability mark	For mounting on normally flammable surfaces
Initial Performance (IEC Compliant)	
Initial chromaticity	4000K (0.3825 , 0.3798), 6500K (0.3130 Y 0.3290),SDCM≤5
Luminous flux tolerance	+/-10%

Light Technical

Order Code	Full Product Name	Luminous Flux
911401801484	BN131C LED SWT/SCCT L1200 PSU Slim	4,100 lm
911401801384	BN131C LED SWT/SCCT L600 PSU Slim	2,000 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401801484	BN131C LED SWT/SCCT L1200 PSU Slim	17 W

Order Code	Full Product Name	Power Consumption
911401801384	BN131C LED SWT/SCCT L600 PSU Slim	9 W

