



For top performance and sustainability

MASTER LED tube T8 UltraEfficient with Recycled Plastic

With energy prices rising and the EU's Green Deal continuing to fund energy efficient building renovations, many are looking into make their company's lighting more sustainable. The new Philips MASTER LEDtube UltraEfficient T8 is a true breakthrough on the way to more sustainable lighting. It replaces your current fluorescent tube or LED tube directly and offers immediately great energy cost reduction as well as a much longer lifetime!

Benefits

- Absolute performance in energy saving: up to 44% compared with standard LED tube
- Reliable performance of up to 100,000 hours
- Energy cost and CO2 savings from the start

Features


- Ultra efficiency achieves an incredible class A energy efficiency rating
- Made with on average 40% post-consumer-recycled plastic
- Up to 100,000 hours lifetime
- Rotatable end-cap that gives light where needed
- Shatterproof, passing drop test horizontally from a height of 4m on to a flat concrete according to IEC 61549
- Enable easy implementation of HACCP without need for additional guard, supported by product level NSF certificate

Application

- Industry & warehouse
- Office, education & retail

MASTER LED tube T8 UltraEfficient with Recycled Plastic

Dimensional drawing



Product	D1	D2	A1	A2	A3
MAS LEDtube 1200mm UE 11.9W 840 T8 EELA	25.8 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
MAS LEDtube 1200mm UE 11.9W 840 T8 EELA	25.8 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
MAS LEDtube 1200mm UE 11.9W 865 T8 EELA	25.8 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm

General Information	
Cap-Base	G13 ROT
Switching Cycle	200,000
Nominal lifetime	100,000 hour(s)
Light Technical	
Beam Angle (Nom)	160 degree(s)
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Luminous Flux	2,500 lm
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power Consumption	11.9 W
Starting Time (Nom)	0.5 s
Temperature	
T-Case Maximum (Nom)	40 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	T8
Approval and Application	
Ambient temperature range	-20 to +45 °C

Light Technical

Order Code	Full Product Name	Correlated Color Temperature	
		(Nom)	Color Code
929003482202	MAS LEDtube 1200mm UE 11.9W 840 T8 EELA	4000 K	840
929003482208	MAS LEDtube 1200mm UE 11.9W 840 T8 EELA	4000 K	840
929003731808	MAS LEDtube 1200mm UE 11.9W 865 T8 EELA	6500 K	865

Operating and Electrical

Order Code	Full Product Name	Line Frequency	Wattage
			Equivalent
929003482202	MAS LEDtube 1200mm UE 11.9W 840 T8 EELA	50 to 60 Hz	-
929003482208	MAS LEDtube 1200mm UE 11.9W 840 T8 EELA	-	36 W

Order Code	Full Product Name	Line Frequency	Wattage
			Equivalent
929003731808	MAS LEDtube 1200mm UE 11.9W 865 T8 EELA	-	36 W

MASTER LED tube T8 UltraEfficient with Recycled Plastic

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
929003482202	MAS LEDtube 1200mm UE 11.9W 840 T8 EELA	12 kWh
929003482208	MAS LEDtube 1200mm UE 11.9W 840 T8 EELA	-
929003731808	MAS LEDtube 1200mm UE 11.9W 865 T8 EELA	-

