



The fourth generation InteGrade LED modules for canopy, door and shelf lighting

Integrade G4

With InteGrade, you can build unique lighting solutions into refrigerated cabinets and shelves. The LED engines and fixtures come in a range of color temperatures – including specially formulated colors like the sensational premium white (PW) for superb rendering of whites and colors. Revolutionary integrated optics direct the light exactly where it's needed.

Benefits

- Diverse options of high output 'vision' and cost-conscious 'value' types.
- Enhance product visibility and contribute to the shopping experience.
- Reduce maintenance costs thanks to longer life, fewer lamp changes.
- Shrink carbon footprint to as LEDs contain no mercury or lead.
- Complying with eco-design.
- Free plastic packaging.

Features

- CCTs: 3000 (PW), 4000 (PW), 5600, 6500, Meat and WWR.
- CRI up to 93
- Efficacy up to 137 lm/w
- Dimmable
- Shelf Lengths (mm): 140, 575, 760, 855, 1150.
- Canopy Lengths (mm): 140, 575, 760, 855, 1150.
- Door Lengths (mm): 140, 575, 760, 855, 1150, 1180, 1430, 1460, 1570, 1600, 1660.

Integrade G4

Application

- Shelf, Canopy and Door lighting

Versions



InteGrade Engine

