



The fourth generation InteGrade LED modules for canopy, door and shelf lighting

InteGrade G4

The fourth-generation InteGrade LED modules for canopy, door and shelf lighting offer you a choice of: Standard colours for maximum energy saving 3,000, 3,500, 4,000, 5,600, 6,500 K and WarmWhiteRed (WWR). Premium white for ultimate product attractiveness (3,000 and 4,000 K). High flux for extreme product visibility, InteGrade modules are available as high-output 'vision' and cost-conscious 'value' products.

Benefits

- Diverse options of high output 'vision' and cost-conscious 'value' types.
- Enhance product visibility and contribute to the shopping experience.
- Reduce maintenance costs thanks to longer life, fewer lamp changes.
- Shrink carbon footprint to as LEDs contain no mercury or lead.
- Complying with eco-design.
- Free plastic packaging.

Features

- CCTs: 3000 (PW), 4000 (PW), 5600, 6500, Meat and WWR.
- CRI up to 93
- Efficacy up to 137 lm/w
- Dimmable
- Shelf Lengths (mm): 140, 575, 760, 855, 1150.
- Canopy Lengths (mm): 140, 575, 760, 855, 1150.
- Door Lengths (mm): 140, 575, 760, 855, 1150, 1180, 1430, 1460, 1570, 1600, 1660.

Integrade G4

Application

- Shelf, Canopy and Door lighting

Versions



InteGrade Engine

