



# Compact Design..... Sleek yet Powerful

## Pureline Slim EX

The PureLine Slim family of luminaires gives you compromise-free office illumination. It is a perfect solution for office application and general indoor area lighting with Sleek profile which helps Declutter the ceilings. The range brings together high-flux lighting with a homogeneous optical system without making any concessions on energy efficiency design.

### Benefits

- Optimized lighting for office space: smooth and comfortable
- Dimmable and fixed output drivers
- Suitable for working and non-working areas
- Compliant with office lighting norms
- Sleek with minimal bezel
- Sustainability coupled with comfortable ambience
- Enhance Interiors

# Pureline Slim EX

## Features

- Superior efficacy >110 lm/W
- Suitable for Standalone & Continuous Mounting
- Up-Down lighting distribution
- Uniform & volumetric light distribution
- Comfortable Light - CRI of 80 to ensure better color rendering.
- Minimum Bezel
- Lifetime: 50,000 Hrs. @ Ta45°C, Safe and Reliable performance
- Higher power factor, lower peak currents, and higher efficiency.
- Flicker Free Lighting Effects - New light platform and optical design with ripple < 5%
- Lighting solution with high uniformity provides comfort in office lighting experience.
- Connected ready(Dali/interact) versions available for Smart offices/workspaces
- Multiple Lumen Packs & CCT - For different office applications and mounting heights


## Application

- Modern Workspaces
- Meeting and Conference room
- Institutions
- Community Centers

## Warnings and Safety

- Meant for Indoor Application Only. Should not be used in outdoor environment.

## Versions



Recessed Pureline Slim 4ft





Suspended Pureline Slim 4ft



Suspended up/down Pureline Slim 4ft

## Pureline Slim EX

## Dimensional drawing



## General Information

Driver included	Yes
-----------------	-----

## Light Technical

Beam angle of light source	- degree(s)
Color rendering index (CRI)	>80
Optic type	-

## Operating and Electrical

Protection class IEC	Safety class I
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz

## Mechanical and Housing

<b>Housing Color</b>	Aluminum and gray
<b>Mech. impact protection code</b>	IK02
<b>Ingress protection code</b>	IP20

## Approval and Application

Ambient temperature range	0 to +45 °C
Flammability mark	For mounting on normally flammable surfaces

### Initial Performance (IEC Compliant)

Initial chromaticity	<5
----------------------	----

## Operating and Electrical

Order Code	Full Product Name	Power Consumption
919515898129	RC780B LED26S-6500 PSU W7L120 OD SI EX	23 W
919515898181	SP780 X LED22S-4000 PSU W6L112 OD SI EX	19 W
919515898229	SP780P LED26S-4000 PSD W6L112 OD SI EX	23 W

Order Code	Full Product Name	Power Consumption
919515898179	SP781 X LED27S-4000 PSU W6L112 OD SI EX	22 W
919515898314	SP781P LED27S-4000 PSU W6L112 OC OD SI E	23 W

## Controls and Dimming

Pureline Slim EX

Order Code	Full Product Name	Dimmable
919515898129	RC780B LED26S-6500 PSU W7L120 OD SI EX	No
919515898181	SP780 X LED22S-4000 PSU W6L112 OD SI EX	No
919515898229	SP780P LED26S-4000 PSD W6L112 OD SI EX	Yes

Order Code	Full Product Name	Dimmable
919515898179	SP781 X LED27S-4000 PSU W6L112 OD SI EX	No
919515898314	SP781P LED27S-4000 PSU W6L112 OC OD SI E	No

Mechanical and Housing

Order Code	Full Product Name	Optical cover type
919515898129	RC780B LED26S-6500 PSU W7L120 OD SI EX	Polycarbonate Diffuser
919515898181	SP780 X LED22S-4000 PSU W6L112 OD SI EX	Polycarbonate Diffuser
919515898229	SP780P LED26S-4000 PSD W6L112 OD SI EX	Polycarbonate Diffuser

Order Code	Full Product Name	Optical cover type
919515898179	SP781 X LED27S-4000 PSU W6L112 OD SI EX	Polycarbonate Diffuser
919515898314	SP781P LED27S-4000 PSU W6L112 OC OD SI E	Polycarbonate bowl/ cover prismatic

