



Enhancing your petrol station with smart lighting

Mini 300 LED gen3

Mini 300 LED gen3 luminaires, perfect product design and latest LED technology combination for highly efficient light outputs can turn your petrol station into a branded landmark and help visitors to approach safely in visual comfort. Mini 300 LED gen3, the state-of-the-art LED luminaires with light on demand intelligent motion sensing control system takes energy saving to new levels with dimming, but at the same time, ensuring sufficient lighting for orientation and safety. The light scenarios can be tailored to your preference at the first installation or during the lifespan of the products. The optional Master-Slave combination with a built-in presence and light sensor there's no need for an external sensor and one Master Mini 300 LED gen3 can control up to 6 basic luminaires. Not only will this have a positive impact on your investment, it can also lead to additional energy saving. Mini 300 LED gen3 luminaire is so light that it can be installed effortlessly by one person. Luminaire settings can even be changed from ground level using a smart phone or tablet as a remote control, eliminating the need to work at height. With the free Mini 300 LED App, even the status of the luminaire can be read while standing on the floor. The Mini 300 LED gen3 luminaires in recessed mounted, surface mounted and floodlight versions, which are suitable for undercanopy lighting, is a breakthrough, retrofit solution reduces installation costs.

Benefits

- Perfect quality of lighting with choice of dedicated optical beams comply all demands of different petrol station configurations
- Minimized energy consumption with customizable built-in controls and scheduler
- Easy commissioning and wireless control set-up possibilities with smartphones and tablets
- Extremely simple and light weight for easy and rapid mounting, also fully retrofit into existing installations

Mini 300 LED gen3


Features

- Highly efficient long-life LED platform for maximum energy saving and reduced maintenance costs
- SMART control system with integral motion sensor module and scheduler for programable auto dimming of light at different levels
- BASIC+ control system only with factory pre-set motion sensor for auto dimming of light at limited level
- Dedicated App with easy user interface for smartphones and tablets

Application

- Petrol stations

Dimensional drawing



Product details



Mini300_gen3-
BBP333_360_360-DPP.TIF



Mini300_gen3-BBP333_470_470-
DPP.TIF



Mini300_gen3-BBP333_560_410-
DPP.TIF



Mini300_gen3-
BBP333_RM_with_accessory_kit-
DPP.TIF

Mini 300 LED gen3

Product details



Mini300_gen3-BBP333-DPP.TIF



Mini300_gen3-BBP333-
with_accessory_kit-DPP.TIF



Mini300_gen3-BCP333-DPP.TIF

Mini 300 LED gen3

General Information	
Driver included	Yes
Light source replaceable	Yes
Number of gear units	1 unit
Service tag	Yes
Light Technical	
Luminaire light beam spread	113°
Color rendering index (CRI)	70
Optic type outdoor	Petrol rotational symmetric medium
Upward light output ratio	0
Operating and Electrical	
Surge Protection (Common/ Differential)	Standard surge protection level
Controls and Dimming	
Maximum dim level	10%
Mechanical and Housing	
Optical cover type	Polycarbonate bowl/cover flat
Housing Color	White
Mech. impact protection code	IK08
Ingress protection code	IP66
Standard tilt angle side entry	-
Standard tilt angle posttop	-
Approval and Application	
CE mark	Yes
Flammability mark	For mounting on normally flammable surfaces

General Information

Order Code	Full Product Name	Lamp family code
910925865265	BBP333 LED159/757 I PRM MDUW	LED159
910925865266	BBP333 LED128/757 I PRM MDUW	LED128
910925865267	BBP333 LED81/757 I PRM MDUW	LED81
910925865268	BBP333 LED159/757 I PRM	LED159
910925865269	BBP333 LED128/757 I PRM	LED128
910925865270	BBP333 LED81/757 I PRM	LED81
910925865271	BBP333 LED159/740 I PRM MDUW	LED159
910925865272	BBP333 LED128/740 I PRM MDUW	LED128
910925865273	BBP333 LED81/740 I PRM MDUW	LED81
910925865274	BBP333 LED159/740 I PRM	LED159
910925865275	BBP333 LED128/740 I PRM	LED128
910925865276	BBP333 LED81/740 I PRM	LED81
910925865307	BBP333 LED159/757 I PRM D9 SNS	LED159
910925865278	BCP333 LED128/757 I PRM MDUW	LED128
910925865279	BCP333 LED81/757 I PRM MDUW	LED81
910925865280	BCP333 LED159/757 I PRM	LED159
910925865281	BCP333 LED128/757 I PRM	LED128
910925865282	BCP333 LED81/757 I PRM	LED81
910925865283	BCP333 LED159/740 I PRM MDUW	LED159
910925865284	BCP333 LED128/740 I PRM MDUW	LED128
910925865285	BCP333 LED81/740 I PRM MDUW	LED81
910925865286	BCP333 LED159/740 I PRM	LED159
910925865287	BCP333 LED128/740 I PRM	LED128
910925865288	BCP333 LED81/740 I PRM	LED81

Light Technical

		Correlated Color		
Order Code	Full Product Name	Light source color	Temperature (Nom)	Luminous Flux
910925865265	BBP333 LED159/757 I PRM MDUW	757 cool white	5700 K	15,900 lm
910925865266	BBP333 LED128/757 I PRM MDUW	757 cool white	5700 K	12,800 lm
910925865267	BBP333 LED81/757 I PRM MDUW	757 cool white	5700 K	8,100 lm
910925865268	BBP333 LED159/757 I PRM	757 cool white	5700 K	14,240 lm
910925865269	BBP333 LED128/757 I PRM	757 cool white	5700 K	11,570 lm

		Correlated Color		
Order Code	Full Product Name	Light source color	Temperature (Nom)	Luminous Flux
910925865270	BBP333 LED81/757 I PRM	757 cool white	5700 K	7,380 lm
910925865271	BBP333 LED159/740 I PRM MDUW	740 neutral white	4000 K	15,900 lm
910925865272	BBP333 LED128/740 I PRM MDUW	740 neutral white	4000 K	12,800 lm
910925865273	BBP333 LED81/740 I PRM MDUW	740 neutral white	4000 K	8,100 lm
910925865274	BBP333 LED159/740 I PRM	740 neutral white	4000 K	14,240 lm

Mini 300 LED gen3

Order Code	Full Product Name	Correlated Color		
		Light source	Temperature	Luminous
		color	(Nom)	Flux
910925865275	BBP333 LED128/740 I PRM	740 neutral white	4000 K	11,570 lm
910925865276	BBP333 LED81/740 I PRM	740 neutral white	4000 K	7,380 lm
910925865307	BBP333 LED159/757 I PRM D9 SNS	757 cool white	5700 K	14,240 lm
910925865278	BCP333 LED128/757 I PRM MDUW	757 cool white	5700 K	12,800 lm
910925865279	BCP333 LED81/757 I PRM MDUW	757 cool white	5700 K	8,100 lm
910925865280	BCP333 LED159/757 I PRM	757 cool white	5700 K	14,400 lm
910925865281	BCP333 LED128/757 I PRM	757 cool white	5700 K	11,700 lm

Order Code	Full Product Name	Correlated Color		
		Light source	Temperature	Luminous
		color	(Nom)	Flux
910925865282	BCP333 LED81/757 I PRM	757 cool white	5700 K	7,462 lm
910925865283	BCP333 LED159/740 I PRM MDUW	740 neutral white	4000 K	15,900 lm
910925865284	BCP333 LED128/740 I PRM MDUW	740 neutral white	4000 K	12,800 lm
910925865285	BCP333 LED81/740 I PRM MDUW	740 neutral white	4000 K	8,100 lm
910925865286	BCP333 LED159/740 I PRM	740 neutral white	4000 K	14,400 lm
910925865287	BCP333 LED128/740 I PRM	740 neutral white	4000 K	11,700 lm
910925865288	BCP333 LED81/740 I PRM	740 neutral white	4000 K	7,462 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
910925865265	BBP333 LED159/757 I PRM MDUW	92 W
910925865266	BBP333 LED128/757 I PRM MDUW	75 W
910925865267	BBP333 LED81/757 I PRM MDUW	48 W
910925865268	BBP333 LED159/757 I PRM	90 W
910925865269	BBP333 LED128/757 I PRM	74 W
910925865270	BBP333 LED81/757 I PRM	48 W
910925865271	BBP333 LED159/740 I PRM MDUW	92 W
910925865272	BBP333 LED128/740 I PRM MDUW	75 W
910925865273	BBP333 LED81/740 I PRM MDUW	48 W
910925865274	BBP333 LED159/740 I PRM	90 W
910925865275	BBP333 LED128/740 I PRM	74 W
910925865276	BBP333 LED81/740 I PRM	48 W

Order Code	Full Product Name	Power Consumption
910925865307	BBP333 LED159/757 I PRM D9 SNS	90 W
910925865278	BCP333 LED128/757 I PRM MDUW	75 W
910925865279	BCP333 LED81/757 I PRM MDUW	48.5 W
910925865280	BCP333 LED159/757 I PRM	91 W
910925865281	BCP333 LED128/757 I PRM	74 W
910925865282	BCP333 LED81/757 I PRM	48 W
910925865283	BCP333 LED159/740 I PRM MDUW	92 W
910925865284	BCP333 LED128/740 I PRM MDUW	75 W
910925865285	BCP333 LED81/740 I PRM MDUW	48.5 W
910925865286	BCP333 LED159/740 I PRM	91 W
910925865287	BCP333 LED128/740 I PRM	74 W
910925865288	BCP333 LED81/740 I PRM	48 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
910925865265	BBP333 LED159/757 I PRM MDUW	Yes
910925865266	BBP333 LED128/757 I PRM MDUW	Yes
910925865267	BBP333 LED81/757 I PRM MDUW	Yes
910925865268	BBP333 LED159/757 I PRM	No
910925865269	BBP333 LED128/757 I PRM	No
910925865270	BBP333 LED81/757 I PRM	No
910925865271	BBP333 LED159/740 I PRM MDUW	Yes
910925865272	BBP333 LED128/740 I PRM MDUW	Yes
910925865273	BBP333 LED81/740 I PRM MDUW	Yes
910925865274	BBP333 LED159/740 I PRM	No
910925865275	BBP333 LED128/740 I PRM	No
910925865276	BBP333 LED81/740 I PRM	No

Order Code	Full Product Name	Dimmable
910925865307	BBP333 LED159/757 I PRM D9 SNS	Yes
910925865278	BCP333 LED128/757 I PRM MDUW	Yes
910925865279	BCP333 LED81/757 I PRM MDUW	Yes
910925865280	BCP333 LED159/757 I PRM	No
910925865281	BCP333 LED128/757 I PRM	No
910925865282	BCP333 LED81/757 I PRM	No
910925865283	BCP333 LED159/740 I PRM MDUW	Yes
910925865284	BCP333 LED128/740 I PRM MDUW	Yes
910925865285	BCP333 LED81/740 I PRM MDUW	Yes
910925865286	BCP333 LED159/740 I PRM	No
910925865287	BCP333 LED128/740 I PRM	No
910925865288	BCP333 LED81/740 I PRM	No




Product Data

Mini 300 LED gen3

Order Code	Full Product Name	Product family code
910925865265	BBP333 LED159/757 I PRM MDUW	BBP333
910925865266	BBP333 LED128/757 I PRM MDUW	BBP333
910925865267	BBP333 LED81/757 I PRM MDUW	BBP333
910925865268	BBP333 LED159/757 I PRM	BBP333
910925865269	BBP333 LED128/757 I PRM	BBP333
910925865270	BBP333 LED81/757 I PRM	BBP333
910925865271	BBP333 LED159/740 I PRM MDUW	BBP333
910925865272	BBP333 LED128/740 I PRM MDUW	BBP333
910925865273	BBP333 LED81/740 I PRM MDUW	BBP333
910925865274	BBP333 LED159/740 I PRM	BBP333
910925865275	BBP333 LED128/740 I PRM	BBP333
910925865276	BBP333 LED81/740 I PRM	BBP333

Order Code	Full Product Name	Product family code
910925865307	BBP333 LED159/757 I PRM D9 SNS	BBP333
910925865278	BGP333 LED128/757 I PRM MDUW	BGP333
910925865279	BGP333 LED81/757 I PRM MDUW	BGP333
910925865280	BGP333 LED159/757 I PRM	BGP333
910925865281	BGP333 LED128/757 I PRM	BGP333
910925865282	BGP333 LED81/757 I PRM	BGP333
910925865283	BGP333 LED159/740 I PRM MDUW	BGP333
910925865284	BGP333 LED128/740 I PRM MDUW	BGP333
910925865285	BGP333 LED81/740 I PRM MDUW	BGP333
910925865286	BGP333 LED159/740 I PRM	BGP333
910925865287	BGP333 LED128/740 I PRM	BGP333
910925865288	BGP333 LED81/740 I PRM	BGP333




Polar Wide Diagrams



Polar Normal (separate) - BBP333I - 910925865283

Polar Normal (separate) - BBP333I - 910925865275

Polar Normal (separate) - BBP333I - 910925865287






Polar Normal (separate) - BBP333I - 910925865274

Polar Normal (separate) - BBP333I - 910925865272

Polar Normal (separate) - BBP333I - 910925865286

Mini 300 LED gen3




Polar Wide Diagrams



Polar Normal (separate) - BBP333I - 910925865278

Polar Normal (separate) - BBP333I - 910925865282




Polar Normal (separate) - BBP333I - 910925865265



Polar Normal (separate) - BBP333I - 910925865271

Polar Normal (separate) - BBP333I - 910925865269

Polar Normal (separate) - BBP333I - 910925865273




Polar Normal (separate) - BBP333I - 910925865307

Polar Normal (separate) - BBP333I - 910925865267


Polar Normal (separate) - BBP333I - 910925865266

Mini 300 LED gen3


Polar Wide Diagrams




Polar Normal (separate) - BBP333I - 910925865270




Polar Normal (separate) - BBP333I - 910925865268




Polar Normal (separate) - BBP333I - 910925865276




Polar Normal (separate) - BBP333I - 910925865281




Polar Normal (separate) - BBP333I - 910925865285




Polar Normal (separate) - BBP333I - 910925865280



Polar Normal (separate) - BBP333I - 910925865284



Polar Normal (separate) - BBP333I - 910925865288



Polar Normal (separate) - BBP333I - 910925865279

Mini 300 LED gen3

