



UniStrip G4 – Best in Class Linear LED Surface Mounted Luminaire for Exterior Fixed and Dynamic Architectural Lighting Applications

UniStrip G4

UniStrip G4 is a surface mounted, exterior-rated LED luminaire that is designed for façade and outdoor architectural lighting applications. One family that fits all your needs, wall washing, grazing and also linear flood lighting. The robust mechanical and unique optical designs make it ideal for illuminating buildings facades, bridges, overpasses and any application that requires a linear lighting solution. Available in white, monochromatic colors, RGB, RGBW and tunable white and DMX control option available with up to 8 pixels (8IDs) to give architects and designers the freedom to explore a wide range of concepts and design with no limitations.

Benefits

- High and Low Power LEDs versions available
- Various spread lenses that fit all applications
- Adjustable brackets and through wiring for end-to-end connection

UniStrip G4

Features

- Six sub-families with power ranges from 3W to 120W
- DC and AC powered versions
- Narrow, medium, wide and asymmetric beams available
- Optional glare shields for more visual comfort


Application

- Bridges, Monuments, Facades
- Landscape
- Parks and Plazas

Warnings and Safety



- For outdoor use only

Versions






BCP381

Dimensional drawing



UniStrip G4

Dimensional drawing



Product details


UniStrip G4 Detail Photo



UniStrip G4 Detail Photo



UniStrip G4 Detail Photo



UniStrip G4 Detail Photo



Product details


UniStrip G4 Detail Photo



159A3710 Detail Photo



UniStrip G4 Detail Photo



159A3691 Detail Photo



UniStrip G4 Detail Photo



UniStrip G4 Detail Photo



UniStrip G4 Detail Photo



UniStrip G4 Detail Photo



159A3731 Detail Photo



General Information	
Driver included	No
Mechanical and Housing	
Housing Color	Dark gray
Mech. impact protection code	IK06
Ingress protection code	IP66
Approval and Application	
CE mark	Yes

General Information

Order Code	Full Product Name	Light source replaceable	Order Code	Full Product Name	Light source replaceable
51417199	BCP386 60LED 40K 24V 60 L100	-	51982499	BCP381 24LED 30K 24V A2 L100	No
51426399	BCP386 60LED RGBWW 24V A11 L100 DMX	-	72536299	BCP381 6LED 30K 24V A2 L30	No
51427099	BCP386 60LED RGBNW 24V A11 L100 DMX	-	72675899	BCP381 24LED 40K 24V 40 L100	No
51977099	BCP381 24LED 27K 24V 40 L100	No	72598099	BCP382 18LED 40K 24V 17 L50	No
51987999	BCP382 36LED 27K 24V 40 L100	No	72539399	BCP382 36LED 40K 24V A2 L100	No
72626099	BCP382 36LED 27K 24V A2 L100	No	72740399	BCP382 36LED 40K 24V 17 L100	No
72739799	BCP382 36LED 30K 24V A2 L100	No			

Light Technical

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Flux
51417199	BCP386 60LED 40K 24V 60 L100	-	Neutral white	4000 K	80	1,045 lm
51426399	BCP386 60LED RGBWW 24V A11 L100 DMX	-	Red, green, blue and white	-	-	695 lm
51427099	BCP386 60LED RGBNW 24V A11 L100 DMX	-	Red, green, blue and white	-	-	730 lm
51977099	BCP381 24LED 27K 24V 40 L100	40° x 40°	Warm white	2700 K	80	1,651 lm
51987999	BCP382 36LED 27K 24V 40 L100	40° x 40°	Warm white	2700 K	80	2,367 lm
72626099	BCP382 36LED 27K 24V A2 L100	16° x 35°	Warm white	2700 K	80	2,393 lm
72739799	BCP382 36LED 30K 24V A2 L100	16° x 35°	Warm white	3000 K	80	2,393 lm
51982499	BCP381 24LED 30K 24V A2 L100	16° x 35°	Warm white	3000 K	80	1,663 lm
72536299	BCP381 6LED 30K 24V A2 L30	16° x 35°	Warm white	3000 K	80	432 lm
72675899	BCP381 24LED 40K 24V 40 L100	40° x 40°	Neutral white	4000 K	80	1,783 lm
72598099	BCP382 18LED 40K 24V 17 L50	17° x 17°	Neutral white	4000 K	80	1,292 lm
72539399	BCP382 36LED 40K 24V A2 L100	16° x 35°	Neutral white	4000 K	80	2,584 lm
72740399	BCP382 36LED 40K 24V 17 L100	17° x 17°	Neutral white	4000 K	80	2,533 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
51417199	BCP386 60LED 40K 24V 60 L100	15 W	51982499	BCP381 24LED 30K 24V A2 L100	24 W
51426399	BCP386 60LED RGBWW 24V A11 L100 DMX	15 W	72536299	BCP381 6LED 30K 24V A2 L30	6 W
51427099	BCP386 60LED RGBNW 24V A11 L100 DMX	15 W	72675899	BCP381 24LED 40K 24V 40 L100	24 W
51977099	BCP381 24LED 27K 24V 40 L100	24 W	72598099	BCP382 18LED 40K 24V 17 L50	18 W
51987999	BCP382 36LED 27K 24V 40 L100	36 W	72539399	BCP382 36LED 40K 24V A2 L100	36 W
72626099	BCP382 36LED 27K 24V A2 L100	36 W	72740399	BCP382 36LED 40K 24V 17 L100	36 W
72739799	BCP382 36LED 30K 24V A2 L100	36 W			

Controls and Dimming

Order Code	Full Product Name	Dimmable
51417199	BCP386 60LED 40K 24V 60 L100	No
51426399	BCP386 60LED RGBWW 24V A11 L100 DMX	Yes
51427099	BCP386 60LED RGBNW 24V A11 L100 DMX	Yes
51977099	BCP381 24LED 27K 24V 40 L100	No
51987999	BCP382 36LED 27K 24V 40 L100	No
72626099	BCP382 36LED 27K 24V A2 L100	No
72739799	BCP382 36LED 30K 24V A2 L100	No

Order Code	Full Product Name	Dimmable
51982499	BCP381 24LED 30K 24V A2 L100	No
72536299	BCP381 6LED 30K 24V A2 L30	No
72675899	BCP381 24LED 40K 24V 40 L100	No
72598099	BCP382 18LED 40K 24V 17 L50	No
72539399	BCP382 36LED 40K 24V A2 L100	No
72740399	BCP382 36LED 40K 24V 17 L100	No

Mechanical and Housing

Order Code	Full Product Name	Optical cover type
51417199	BCP386 60LED 40K 24V 60 L100	Clear glass
51426399	BCP386 60LED RGBWW 24V A11 L100 DMX	Clear glass
51427099	BCP386 60LED RGBNW 24V A11 L100 DMX	Clear glass
51977099	BCP381 24LED 27K 24V 40 L100	Clear flat
51987999	BCP382 36LED 27K 24V 40 L100	Clear flat
72626099	BCP382 36LED 27K 24V A2 L100	Clear flat
72739799	BCP382 36LED 30K 24V A2 L100	Clear flat

Order Code	Full Product Name	Optical cover type
51982499	BCP381 24LED 30K 24V A2 L100	Clear flat
72536299	BCP381 6LED 30K 24V A2 L30	Clear flat
72675899	BCP381 24LED 40K 24V 40 L100	Clear flat
72598099	BCP382 18LED 40K 24V 17 L50	Clear flat
72539399	BCP382 36LED 40K 24V A2 L100	Clear flat
72740399	BCP382 36LED 40K 24V 17 L100	Clear flat

Approval and Application

Order Code	Full Product Name	Flammability mark
51417199	BCP386 60LED 40K 24V 60 L100	-
51426399	BCP386 60LED RGBWW 24V A11 L100 DMX	-
51427099	BCP386 60LED RGBNW 24V A11 L100 DMX	-
51977099	BCP381 24LED 27K 24V 40 L100	For mounting on normally flammable surfaces
51987999	BCP382 36LED 27K 24V 40 L100	For mounting on normally flammable surfaces
72626099	BCP382 36LED 27K 24V A2 L100	For mounting on normally flammable surfaces
72739799	BCP382 36LED 30K 24V A2 L100	For mounting on normally flammable surfaces

Order Code	Full Product Name	Flammability mark
51982499	BCP381 24LED 30K 24V A2 L100	For mounting on normally flammable surfaces
72536299	BCP381 6LED 30K 24V A2 L30	For mounting on normally flammable surfaces
72675899	BCP381 24LED 40K 24V 40 L100	For mounting on normally flammable surfaces
72598099	BCP382 18LED 40K 24V 17 L50	For mounting on normally flammable surfaces
72539399	BCP382 36LED 40K 24V A2 L100	For mounting on normally flammable surfaces
72740399	BCP382 36LED 40K 24V 17 L100	For mounting on normally flammable surfaces

