



The most cost-effective outdoor spot light with better efficient and performance

UniPoint

Our UniPoint is designed to produce both general and accent lighting while concealing the body of the device, allowing only the light to be exposed. This design can be used to change the surroundings by adding subtle or dramatic contrasting effects. It also includes exclusive features such as energy efficiency, chromatic quality and miniaturization. We guarantee extreme reliability and high level of resistance to adverse weather conditions and vandalism

Benefits

- In stylish and very compact design
- Price point versus PHILIPS standards
- Effortless and flexible installation
- Customizing for you

Features

- High quality LED
- Different choice of light source and beam angles
- Die-cast aluminum housing + dark grey sand coating to ensure anticorrosion
- Structural waterproof technology
- IP66
- IK06
- Quality and reliability in line with all regulations

Application

- Buildings
- Statues
- Columns
- Pillars
- Eaves

Versions



UniPoint BGP312 1LED






UniPoint BGP312 3LED



UniPoint BGP312 5LED

Dimensional drawing



General Information	
Driver included	No
Light source replaceable	No
Light Technical	
Light source color	830 warm white
Correlated Color Temperature (Nom)	3000 K
Color rendering index (CRI)	>75
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Optical cover type	Glass bowl/cover
Housing Color	Dark gray
Mech. impact protection code	IK06
Ingress protection code	IP66
Standard tilt angle side entry	-
Standard tilt angle posttop	-
Approval and Application	
CE mark	No

Light Technical

Order Code	Full Product Name	Luminaire light beam		Luminous Flux	Optic type outdoor
		spread			
911401710682	BGP312 1LED 3000K MB	25°		120 lm	Medium beam angle 25°
911401710762	BGP312 3LED 3000K NB	10°		330 lm	Narrow beam angle 10°
911401710862	BGP312 5LED 3000K MB	25°		595 lm	Medium beam angle 25°

Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401710682	BGP312 1LED 3000K MB	3 W
911401710762	BGP312 3LED 3000K NB	6 W

Order Code	Full Product Name	Power Consumption
911401710862	BGP312 5LED 3000K MB	10 W

