



Get your city ready for the future with DigiStreet

DigiStreet

Developed with the aim to become your long term partner, the system ready architecture of DigiStreet enables you to enjoy the benefits of connected lighting systems today and also gets the city ready for the innovations to come!. Its two sockets enable you to connect directly to the CityTouch system and is also prepared to connect you to the future innovations of IoT. Next to this, each individual luminaire is uniquely identifiable, thanks to the Service tag application. With a simple scan of a QR code, placed on the inside of the mast door, you gain instant access to the luminaire configuration, making maintenance and programming operations faster and easier, no matter what stage of the luminaire's lifetime. DigiStreet is also equipped with dedicated light recipes that: 1) maintain an optimal ecosystem for bats or 2) preserve a dark night sky.

Benefits

- Prepared for the future, it is easy to upgrade directly after installation or later with future CMS nodes and sensors to enable new functionalities
- Large availability of lens optics to match international road and street geometries
- Equipped with Service tag, a QR-based identification system that makes each luminaire uniquely identifiable and provides maintenance, installation and spare part information


Features

- Easy luminaire identification due to the Service tag
- High efficacy up to 161 lm/W
- Choice of 30+ different beams and different internal louvers
- Surge protection, 10 kV
- L-tune tool available
- Lifetime 100Khrs up to L96 at Tq +25 °C
- Internal louver (optional)

Application

- Traffic routes and main access road
- Urban and residential area
- City centers and main streets
- Cycle paths, footpaths and pedestrian crossings

Dimensional drawing



Product details

Digistreet-BGP760-DP06.tif



Digistreet-BGP760-DP09.tif



Digistreet-BGP760-DP10.tif



Digistreet-BGP760-DP11.tif




Digistreet-BGP761-DP17.tif



Digistreet-BGP761-DP18.tif



Digistreet-BGP761-DP19.tif



Digistreet-BGP761-DP20.tif



Product details



Digistreet-BGP761-DP21.tif



Digistreet-BGP761-DP22.tif



Digistreet-BGP761-DP23.tif



Digistreet-BGP761-DP24.tif



Digistreet-BGP761-DP25.tif



Digistreet-BGP761-DP26.tif

General Information	
Driver included	Yes
Light source replaceable	Yes
Service tag	Yes
Light Technical	
Upward light output ratio	0
Mechanical and Housing	
Optical cover type	Flat glass
Housing Color	Dark gray
Mech. impact protection code	IK09
Ingress protection code	IP66
Standard tilt angle side entry	0°
Standard tilt angle posttop	0°
Approval and Application	
CE mark	Yes
Flammability mark	-

General Information

Order Code	Full Product Name	Lamp family		
		Gear	code	Number of gear units
910925866220	BGP762 LED120-/830 II DN11 DGR D11 76	-	LED120	1 unit
910925866221	BGP762 LED159-/830 II DM70 DGR DDF27 D18	-	LED159	1 unit
910925866222	BGP762 LED129-/740 I DM11 DGR 32-48	-	LED129	1 unit
910925866224	BGP762 LED110-/740 I DN10 DGR 32-48	-	LED110	1 unit
910925866225	BGP762 LED149-/740 I DM50 DGR 32-48	-	LED149	1 unit
910925866226	BGP762 LED180-/740 I DX10 DGR 32-48	-	LED180	1 unit
910925866227	BGP762 LED100-/830 II DM11 DGR D9 62	-	LED100	1 unit
910925866228	BGP762 LED139-/830 II DM11 DGR D9 62	-	LED139	1 unit
910925866229	BGP762 LED170-/830 II DW10 DGR 76	-	LED170	1 unit
910925866245	BGP762 LED200-/740 I DW50 DGR 62	-	LED200	1 unit
910925866246	BGP762 LED210-/740 II DX70 DGR 76	-	LED210	1 unit
910925866252	BGP762 LED220-/740 II DW10 DGR SRG10 62	-	LED220	1 unit
910925866492	BGP762 LED120/740 I DM10 DGR 62 S	-	LED120	1 unit
910925863554	BGP760 LED10-/740 I DM10 DGR 32-48	EB	LED10	1 unit
910925863555	BGP760 LED12-/830 II DM11 DGR D9 62	EB	LED12	1 unit
910925863556	BGP760 LED14-/740 I DN10 DGR 32-48	EB	LED14	1 unit
910925863557	BGP760 LED16-/830 II DN11 DGR D11 62	EB	LED16	1 unit
910925863560	BGP760 LED22-/740 I DM50 DGR 32-48	EB	LED22	1 unit
910925863561	BGP760 LED24-/830 II DM70 DGR DDF27 D18	EB	LED24	1 unit
910925863562	BGP760 LED27-/740 I DS50 DGR 32-48	EB	LED27	1 unit
910925863563	BGP760 LED30-/830 II DW10 DGR 62	EB	LED30	1 unit
910925863564	BGP760 LED34-/740 I DX10 DGR 32-48	EB	LED34	1 unit
910925863566	BGP760 LED44-/740 I DW50 DGR 32-48	EB	LED44	1 unit
910925863567	BGP760 LED49-/740 II DX70 DGR 62	EB	LED49	1 unit
910925866249	BGP763 LED300-/740 I DW50 DGR 62	-	LED300	2 units
910925866250	BGP763 LED260-/740 I DX10 DGR 32-48	-	LED260	2 units
910925866251	BGP763 LED340-/740 II DW10 DGR SRG10 62	-	LED340	2 units
910925866253	BGP763 LED320-/740 II DX70 DGR 76	-	LED320	2 units
910925866230	BGP761 LED45-/740 I DM10 DGR 32-48	-	LED45	1 unit
910925866231	BGP761 LED74-/740 I DM50 DGR 32-48	-	LED74	1 unit
910925866232	BGP761 LED94-/740 I DX10 DGR 32-48	-	LED94	1 unit
910925866234	BGP761 LED55-/740 I DN10 DGR 32-48	-	LED55	1 unit
910925866235	BGP761 LED84-/740 I DS50 DGR 32-48	-	LED84	1 unit
910925866238	BGP761 LED50-/830 II DM11 DGR D9 62	-	LED50	1 unit
910925866239	BGP761 LED79-/830 II DM70 DGR DDF27 D18	-	LED79	1 unit
910925866240	BGP761 LED59-/830 II DN11 DGR D11 62	-	LED59	1 unit
910925866241	BGP761 LED90-/740 II DW10 DGR 62	-	LED90	1 unit
910925866497	BGP761 LED119/740 I DM10 DGR 62 S	-	LED119	1 unit

Light Technical (1/2)

Order Code	Full Product Name	Luminaire	Light	Correlated	Color
		light beam	source	Color	rendering
		spread	color	Temperature (Nom)	index (CRI)
910925866220	BGP762	53° x 71°	830	3000 K	80
	LED120-/830 II		warm		
	DN11 DGR D11 76		white		

Order Code	Full Product Name	Luminaire	Light	Correlated	Color
		light beam	source	Color	rendering
		spread	color	Temperature (Nom)	index (CRI)
910925866221	BGP762	-	830	3000 K	80
	LED159-/830 II		warm		
	DM70 DGR		white		
	DDF27 D18				

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
910925866222	BGP762 LED129-/740 I DM11 DGR 32-48	160° - 42° x 54°	740 neutral white	4000 K	70
910925866224	BGP762 LED110-/740 I DN10 DGR 32-48	68° x 158°	740 neutral white	4000 K	70
910925866225	BGP762 LED149-/740 I DM50 DGR 32-48	154° - 31° x 54°	740 neutral white	4000 K	70
910925866226	BGP762 LED180-/740 I DX10 DGR 32-48	150° - 43° x 67°	740 neutral white	4000 K	70
910925866227	BGP762 LED100-/830 II DM11 DGR D9 62	160° - 42° x 54°	830 warm white	3000 K	80
910925866228	BGP762 LED139-/830 II DM11 DGR D9 62	160° - 42° x 54°	830 warm white	3000 K	80
910925866229	BGP762 LED170-/830 II DW10 DGR 76	61° x 150°	830 warm white	3000 K	80
910925866245	BGP762 LED200-/740 I DW50 DGR 62	152° - 24° x 66°	740 neutral white	4000 K	70
910925866246	BGP762 LED210-/740 II DX70 DGR 76	106° x 86°	740 neutral white	4000 K	70
910925866252	BGP762 LED220-/740 II DW10 DGR SRG10 62	61° x 150°	740 neutral white	4000 K	70
910925866492	BGP762 LED120/740 I DM10 DGR 62 S	157° - 33° x 55°	740 neutral white	4000 K	70
910925863554	BGP760 LED10-/740 I DM10 DGR 32-48	157° - 33° x 55°	740 neutral white	4000 K	70
910925863555	BGP760 LED12-/830 II DM11 DGR D9 62	160° - 42° x 54°	830 warm white	3000 K	80
910925863556	BGP760 LED14-/740 I DN10 DGR 32-48	68° x 157°	740 neutral white	4000 K	70
910925863557	BGP760 LED16-/830 II DN11 DGR D11 62	53° x 71°	830 warm white	3000 K	80
910925863560	BGP760 LED22-/740 I DM50 DGR 32-48	154° - 31° x 54°	740 neutral white	4000 K	70

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
910925863561	BGP760 LED24-/830 II DM70 DGR DDF27 D18	-	830 warm white	3000 K	80
910925863562	BGP760 LED27-/740 I DS50 DGR 32-48	32° x 29°	740 neutral white	4000 K	70
910925863563	BGP760 LED30-/830 II DW10 DGR 62	61° x 150°	830 warm white	3000 K	80
910925863564	BGP760 LED34-/740 I DX10 DGR 32-48	150° - 43° x 67°	740 neutral white	4000 K	70
910925863566	BGP760 LED44-/740 I DW50 DGR 32-48	152° - 24° x 66°	740 neutral white	4000 K	70
910925863567	BGP760 LED49-/740 II DX70 DGR 62	106° x 44°	740 neutral white	4000 K	70
910925866249	BGP763 LED300-/740 I DW50 DGR 62	152° - 24° x 66°	740 neutral white	4000 K	70
910925866250	BGP763 LED260-/740 I DX10 DGR 32-48	150° - 43° x 67°	740 neutral white	4000 K	70
910925866251	BGP763 LED340-/740 II DW10 DGR SRG10 62	61° x 150°	740 neutral white	4000 K	70
910925866253	BGP763 LED320-/740 II DX70 DGR 76	106° x 44°	740 neutral white	4000 K	70
910925866230	BGP761 LED45-/740 I DM10 DGR 32-48	157° - 33° x 55°	740 neutral white	4000 K	70
910925866231	BGP761 LED74-/740 I DM50 DGR 32-48	154° - 31° x 54°	740 neutral white	4000 K	70
910925866232	BGP761 LED94-/740 I DX10 DGR 32-48	150° - 43° x 67°	740 neutral white	4000 K	70
910925866234	BGP761 LED55-/740 I DN10 DGR 32-48	68° x 157°	740 neutral white	4000 K	70
910925866235	BGP761 LED84-/740 I DS50 DGR 32-48	32° x 29°	740 neutral white	4000 K	70

		Luminaire	Light	Correlated	Color
	Full Product	light beam	source	Color	rendering
Order Code	Name	spread	color	Temperature (Nom)	index (CRI)
910925866238	BGP761	160° - 42° x	830	3000 K	80
	LED50-/830 II	54°	warm		
	DM11 DGR D9 62		white		
910925866239	BGP761	-	830	3000 K	80
	LED79-/830 II		warm		
	DM70 DGR		white		
	DDF27 D18				
910925866240	BGP761	53° x 71°	830	3000 K	80
	LED59-/830 II		warm		
	DN11 DGR D11 62		white		

		Luminaire	Light	Correlated	Color
	Full Product	light beam	source	Color	rendering
Order Code	Name	spread	color	Temperature (Nom)	index (CRI)
910925866241	BGP761	61° x 150°	740	4000 K	70
	LED90-/740 II		neutral		
	DW10 DGR 62		white		
910925866497	BGP761	157° - 33° x	740	4000 K	70
	LED119/740 I	55°	neutral		
	DM10 DGR 62 S		white		

Light Technical (2/2)

		Luminous	Number	Optic type
	Full Product Name	Flux	of light	outdoor
Order Code			sources	
910925866220	BGP762 LED120-/830 II	10,800 lm	-	Distribution
	DN11 DGR D11 76			narrow 11
910925866221	BGP762 LED159-/830 II	13,920 lm	-	Distribution
	DM70 DGR DDF27 D18			medium 70
910925866222	BGP762 LED129-/740 I	11,830 lm	-	Distribution
	DM11 DGR 32-48			medium 11
910925866224	BGP762 LED110-/740 I	10,010 lm	-	Distribution
	DN10 DGR 32-48			narrow 10
910925866225	BGP762 LED149-/740 I	13,500 lm	-	Distribution
	DM50 DGR 32-48			medium 50
910925866226	BGP762 LED180-/740 I	15,480 lm	-	Distribution extra
	DX10 DGR 32-48			wide 10
910925866227	BGP762 LED100-/830 II	9,100 lm	-	Distribution
	DM11 DGR D9 62			medium 11
910925866228	BGP762 LED139-/830 II	12,740 lm	-	Distribution
	DM11 DGR D9 62			medium 11
910925866229	BGP762 LED170-/830 II	15,300 lm	-	Distribution wide
	DW10 DGR 76			10
910925866245	BGP762 LED200-/740 I	17,200 lm	-	Distribution wide
	DW50 DGR 62			50
910925866246	BGP762 LED210-/740 II	18,060 lm	-	Distribution extra
	DX70 DGR 76			wide 70
910925866252	BGP762 LED220-/740 II	19,800 lm	-	Distribution wide
	DW10 DGR SRG10 62			10
910925866492	BGP762 LED120/740 I	10,800 lm	-	Distribution
	DM10 DGR 62 S			medium 10
910925863554	BGP760 LED10-/740 I	900 lm	1	Distribution
	DM10 DGR 32-48			medium 10
910925863555	BGP760 LED12-/830 II	1,092 lm	1	Distribution
	DM11 DGR D9 62			medium 11
910925863556	BGP760 LED14-/740 I	1,274 lm	1	Distribution
	DN10 DGR 32-48			narrow 10

		Luminous	Number	Optic type
	Full Product Name	Flux	of light	outdoor
Order Code			sources	
910925863557	BGP760 LED16-/830 II	1,456 lm	1	Distribution
	DN11 DGR D11 62			narrow 11
910925863560	BGP760 LED22-/740 I	2,002 lm	1	Distribution
	DM50 DGR 32-48			medium 50
910925863561	BGP760 LED24-/830 II	2,136 lm	1	Distribution
	DM70 DGR DDF27 D18			medium 70
910925863562	BGP760 LED27-/740 I	2,403 lm	1	Distribution
	DS50 DGR 32-48			symmetrical 50
910925863563	BGP760 LED30-/830 II	2,730 lm	1	Distribution wide
	DW10 DGR 62			10
910925863564	BGP760 LED34-/740 I	2,958 lm	1	Distribution extra
	DX10 DGR 32-48			wide 10
910925863566	BGP760 LED44-/740 I	3,784 lm	1	Distribution wide
	DW50 DGR 32-48			50
910925863567	BGP760 LED49-/740 II	4,263 lm	1	Distribution extra
	DX70 DGR 62			wide 70
910925866249	BGP763 LED300-/740 I	25,200 lm	-	Distribution wide
	DW50 DGR 62			50
910925866250	BGP763 LED260-/740 I	22,100 lm	-	Distribution extra
	DX10 DGR 32-48			wide 10
910925866251	BGP763 LED340-/740 II	29,920 lm	-	Distribution wide
	DW10 DGR SRG10 62			10
910925866253	BGP763 LED320-/740 II	26,880 lm	-	Distribution extra
	DX70 DGR 76			wide 70
910925866230	BGP761 LED45-/740 I	4,050 lm	-	Distribution
	DM10 DGR 32-48			medium 10
910925866231	BGP761 LED74-/740 I	6,660 lm	-	Distribution
	DM50 DGR 32-48			medium 50
910925866232	BGP761 LED94-/740 I	8,084 lm	-	Distribution extra
	DX10 DGR 32-48			wide 10
910925866234	BGP761 LED55-/740 I	5,096 lm	-	Distribution
	DN10 DGR 32-48			narrow 10

Order Code	Full Product Name	Luminous Flux	Number of light sources	Optic type outdoor
910925866235	BGP761 LED84-/740 I DS50 DGR 32-48	7,392 lm	-	Distribution symmetrical 50
910925866238	BGP761 LED50-/830 II DM11 DGR D9 62	4,550 lm	-	Distribution medium 11
910925866239	BGP761 LED79-/830 II DM70 DGR DDF27 D18	6,688 lm	-	Distribution medium 70

Order Code	Full Product Name	Luminous Flux	Number of light sources	Optic type outdoor
910925866240	BGP761 LED59-/830 II DN11 DGR D11 62	5,400 lm	-	Distribution narrow 11
910925866241	BGP761 LED90-/740 II DW10 DGR 62	8,100 lm	-	Distribution wide 10
910925866497	BGP761 LED119/740 I DM10 DGR 62 S	10,680 lm	-	Distribution medium 10

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/ Differential)
910925866220	BGP762 LED120-/830 II DN11 DGR D11 76	81 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866221	BGP762 LED159-/830 II DM70 DGR DDF27 D18	106 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866222	BGP762 LED129-/740 I DM11 DGR 32-48	72 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866224	BGP762 LED110-/740 I DN10 DGR 32-48	61 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866225	BGP762 LED149-/740 I DM50 DGR 32-48	85 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866226	BGP762 LED180-/740 I DX10 DGR 32-48	100 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866227	BGP762 LED100-/830 II DM11 DGR D9 62	66 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866228	BGP762 LED139-/830 II DM11 DGR D9 62	91 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866229	BGP762 LED170-/830 II DW10 DGR 76	114 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866245	BGP762 LED200-/740 I DW50 DGR 62	114 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866246	BGP762 LED210-/740 II DX70 DGR 76	120 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866252	BGP762 LED220-/740 II DW10 DGR SRG10 62	126 W	Surge protection level until 10 kV differential mode and 10 kV common mode
910925866492	BGP762 LED120/740 I DM10 DGR 62 S	70 W	Surge protection level until 6 kV differential mode and 8 kV common mode

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/ Differential)
910925863554	BGP760 LED10-/740 I DM10 DGR 32-48	6.8 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925863555	BGP760 LED12-/830 II DM11 DGR D9 62	8 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925863556	BGP760 LED14-/740 I DN10 DGR 32-48	9 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925863557	BGP760 LED16-/830 II DN11 DGR D11 62	11.8 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925863560	BGP760 LED22-/740 I DM50 DGR 32-48	13.8 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925863561	BGP760 LED24-/830 II DM70 DGR DDF27 D18	17 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925863562	BGP760 LED27-/740 I DS50 DGR 32-48	16 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925863563	BGP760 LED30-/830 II DW10 DGR 62	21 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925863564	BGP760 LED34-/740 I DX10 DGR 32-48	20 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925863566	BGP760 LED44-/740 I DW50 DGR 32-48	26 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925863567	BGP760 LED49-/740 II DX70 DGR 62	29.5 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866249	BGP763 LED300-/740 I DW50 DGR 62	176 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866250	BGP763 LED260-/740 I DX10 DGR 32-48	150 W	Surge protection level until 6 kV differential mode and 8 kV common mode

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
910925866251	BGP763 LED340-/740 II DW10 DGR SRG10 62	196 W	Surge protection level until 10 kV differential mode and 10 kV common mode
910925866253	BGP763 LED320-/740 II DX70 DGR 76	182 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866230	BGP761 LED45-/740 I DM10 DGR 32-48	27 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866231	BGP761 LED74-/740 I DM50 DGR 32-48	43.5 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866232	BGP761 LED94-/740 I DX10 DGR 32-48	54 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866234	BGP761 LED55-/740 I DN10 DGR 32-48	31.5 W	Surge protection level until 6 kV differential mode and 8 kV common mode

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
910925866235	BGP761 LED84-/740 I DS50 DGR 32-48	49.5 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866238	BGP761 LED50-/830 II DM11 DGR D9 62	34 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866239	BGP761 LED79-/830 II DM70 DGR DDF27 D18	54 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866240	BGP761 LED59-/830 II DN11 DGR D11 62	41 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866241	BGP761 LED90-/740 II DW10 DGR 62	51 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866497	BGP761 LED119/740 I DM10 DGR 62 S	72 W	Surge protection level until 6 kV differential mode and 8 kV common mode

Controls and Dimming

Order Code	Full Product Name	Dimmable	Maximum dim level
910925866220	BGP762 LED120-/830 II DN11 DGR D11 76	Yes	Not applicable
910925866221	BGP762 LED159-/830 II DM70 DGR DDF27 D18	Yes	50%
910925866222	BGP762 LED129-/740 I DM11 DGR 32-48	No	Not applicable
910925866224	BGP762 LED110-/740 I DN10 DGR 32-48	No	Not applicable
910925866225	BGP762 LED149-/740 I DM50 DGR 32-48	No	Not applicable
910925866226	BGP762 LED180-/740 I DX10 DGR 32-48	No	Not applicable
910925866227	BGP762 LED100-/830 II DM11 DGR D9 62	Yes	Not applicable
910925866228	BGP762 LED139-/830 II DM11 DGR D9 62	Yes	Not applicable
910925866229	BGP762 LED170-/830 II DW10 DGR 76	No	Not applicable
910925866245	BGP762 LED200-/740 I DW50 DGR 62	No	Not applicable
910925866246	BGP762 LED210-/740 II DX70 DGR 76	No	Not applicable
910925866252	BGP762 LED220-/740 II DW10 DGR SRG10 62	No	Not applicable
910925866492	BGP762 LED120/740 I DM10 DGR 62 S	Yes	Not applicable
910925863554	BGP760 LED10-/740 I DM10 DGR 32-48	No	Not applicable
910925863555	BGP760 LED12-/830 II DM11 DGR D9 62	Yes	Not applicable
910925863556	BGP760 LED14-/740 I DN10 DGR 32-48	No	Not applicable
910925863557	BGP760 LED16-/830 II DN11 DGR D11 62	Yes	Not applicable
910925863560	BGP760 LED22-/740 I DM50 DGR 32-48	No	Not applicable

Order Code	Full Product Name	Dimmable	Maximum dim level
910925863561	BGP760 LED24-/830 II DM70 DGR DDF27 D18	Yes	50%
910925863562	BGP760 LED27-/740 I DS50 DGR 32-48	No	Not applicable
910925863563	BGP760 LED30-/830 II DW10 DGR 62	No	Not applicable
910925863564	BGP760 LED34-/740 I DX10 DGR 32-48	No	Not applicable
910925863566	BGP760 LED44-/740 I DW50 DGR 32-48	No	Not applicable
910925863567	BGP760 LED49-/740 II DX70 DGR 62	No	Not applicable
910925866249	BGP763 LED300-/740 I DW50 DGR 62	No	Not applicable
910925866250	BGP763 LED260-/740 I DX10 DGR 32-48	No	Not applicable
910925866251	BGP763 LED340-/740 II DW10 DGR SRG10 62	No	Not applicable
910925866253	BGP763 LED320-/740 II DX70 DGR 76	No	Not applicable
910925866230	BGP761 LED45-/740 I DM10 DGR 32-48	No	Not applicable
910925866231	BGP761 LED74-/740 I DM50 DGR 32-48	No	Not applicable
910925866232	BGP761 LED94-/740 I DX10 DGR 32-48	No	Not applicable
910925866234	BGP761 LED55-/740 I DN10 DGR 32-48	No	Not applicable
910925866235	BGP761 LED84-/740 I DS50 DGR 32-48	No	Not applicable
910925866238	BGP761 LED50-/830 II DM11 DGR D9 62	Yes	Not applicable
910925866239	BGP761 LED79-/830 II DM70 DGR DDF27 D18	Yes	50%
910925866240	BGP761 LED59-/830 II DN11 DGR D11 62	Yes	Not applicable
910925866241	BGP761 LED90-/740 II DW10 DGR 62	No	Not applicable
910925866497	BGP761 LED119/740 I DM10 DGR 62 S	Yes	Not applicable

Approval and Application

Order Code	Full Product Name	Glow-wire test
910925866220	BGP762 LED120- /830 II DN11 DGR D11 76	-
910925866221	BGP762 LED159- /830 II DM70 DGR DDF27 D18	-
910925866222	BGP762 LED129- /740 I DM11 DGR 32-48	-
910925866224	BGP762 LED110- /740 I DN10 DGR 32-48	-
910925866225	BGP762 LED149- /740 I DM50 DGR 32-48	-
910925866226	BGP762 LED180- /740 I DX10 DGR 32-48	-
910925866227	BGP762 LED100- /830 II DM11 DGR D9 62	-
910925866228	BGP762 LED139- /830 II DM11 DGR D9 62	-
910925866229	BGP762 LED170- /830 II DW10 DGR 76	-
910925866245	BGP762 LED200- /740 I DW50 DGR 62	-
910925866246	BGP762 LED210- /740 II DX70 DGR 76	-
910925866252	BGP762 LED220- /740 II DW10 DGR SRG10 62	-
910925866492	BGP762 LED120/740 I DM10 DGR 62 S	-
910925863554	BGP760 LED10- /740 I DM10 DGR 32-48	Temperature 650 °C, duration 5 s
910925863555	BGP760 LED12- /830 II DM11 DGR D9 62	Temperature 650 °C, duration 5 s
910925863556	BGP760 LED14- /740 I DN10 DGR 32-48	Temperature 650 °C, duration 5 s
910925863557	BGP760 LED16- /830 II DN11 DGR D11 62	Temperature 650 °C, duration 5 s
910925863560	BGP760 LED22- /740 I DM50 DGR 32-48	Temperature 650 °C, duration 5 s
910925863561	BGP760 LED24- /830 II DM70 DGR DDF27 D18	Temperature 650 °C, duration 5 s


Product Data

Order Code	Full Product Name	Product family code
910925866220	BGP762 LED120- /830 II DN11 DGR D11 76	BGP762
910925866221	BGP762 LED159- /830 II DM70 DGR DDF27 D18	BGP762
910925866222	BGP762 LED129- /740 I DM11 DGR 32-48	BGP762
910925866224	BGP762 LED110- /740 I DN10 DGR 32-48	BGP762
910925866225	BGP762 LED149- /740 I DM50 DGR 32-48	BGP762
910925866226	BGP762 LED180- /740 I DX10 DGR 32-48	BGP762
910925866227	BGP762 LED100- /830 II DM11 DGR D9 62	BGP762
910925866228	BGP762 LED139- /830 II DM11 DGR D9 62	BGP762
910925866229	BGP762 LED170- /830 II DW10 DGR 76	BGP762
910925866245	BGP762 LED200- /740 I DW50 DGR 62	BGP762
910925866246	BGP762 LED210- /740 II DX70 DGR 76	BGP762
910925866252	BGP762 LED220- /740 II DW10 DGR SRG10 62	BGP762
910925866492	BGP762 LED120/740 I DM10 DGR 62 S	BGP762
910925863554	BGP760 LED10- /740 I DM10 DGR 32-48	BGP760
910925863555	BGP760 LED12- /830 II DM11 DGR D9 62	BGP760
910925863556	BGP760 LED14- /740 I DN10 DGR 32-48	BGP760
910925863557	BGP760 LED16- /830 II DN11 DGR D11 62	BGP760
910925863560	BGP760 LED22- /740 I DM50 DGR 32-48	BGP760
910925863561	BGP760 LED24- /830 II DM70 DGR DDF27 D18	BGP760


Order Code	Full Product Name	Glow-wire test
910925863562	BGP760 LED27- /740 I DS50 DGR 32-48	Temperature 650 °C, duration 5 s
910925863563	BGP760 LED30- /830 II DW10 DGR 62	Temperature 650 °C, duration 5 s
910925863564	BGP760 LED34- /740 I DX10 DGR 32-48	Temperature 650 °C, duration 5 s
910925863566	BGP760 LED44- /740 I DW50 DGR 32-48	Temperature 650 °C, duration 5 s
910925863567	BGP760 LED49- /740 II DX70 DGR 62	Temperature 650 °C, duration 5 s
910925866249	BGP763 LED300- /740 I DW50 DGR 62	-
910925866250	BGP763 LED260- /740 I DX10 DGR 32-48	-
910925866251	BGP763 LED340- /740 II DW10 DGR SRG10 62	-
910925866253	BGP763 LED320- /740 II DX70 DGR 76	-
910925866230	BGP761 LED45- /740 I DM10 DGR 32-48	-
910925866231	BGP761 LED74- /740 I DM50 DGR 32-48	-
910925866232	BGP761 LED94- /740 I DX10 DGR 32-48	-
910925866234	BGP761 LED55- /740 I DN10 DGR 32-48	-
910925866235	BGP761 LED84- /740 I DS50 DGR 32-48	-
910925866238	BGP761 LED50- /830 II DM11 DGR D9 62	-
910925866239	BGP761 LED79- /830 II DM70 DGR DDF27 D18	-
910925866240	BGP761 LED59- /830 II DN11 DGR D11 62	-
910925866241	BGP761 LED90- /740 II DW10 DGR 62	-
910925866497	BGP761 LED119/740 I DM10 DGR 62 S	-

Order Code	Full Product Name	Product family code
910925863562	BGP760 LED27- /740 I DS50 DGR 32-48	BGP760
910925863563	BGP760 LED30- /830 II DW10 DGR 62	BGP760
910925863564	BGP760 LED34- /740 I DX10 DGR 32-48	BGP760
910925863566	BGP760 LED44- /740 I DW50 DGR 32-48	BGP760
910925863567	BGP760 LED49- /740 II DX70 DGR 62	BGP760
910925866249	BGP763 LED300- /740 I DW50 DGR 62	BGP763
910925866250	BGP763 LED260- /740 I DX10 DGR 32-48	BGP763
910925866251	BGP763 LED340- /740 II DW10 DGR SRG10 62	BGP763
910925866253	BGP763 LED320- /740 II DX70 DGR 76	BGP763
910925866230	BGP761 LED45- /740 I DM10 DGR 32-48	BGP761
910925866231	BGP761 LED74- /740 I DM50 DGR 32-48	BGP761
910925866232	BGP761 LED94- /740 I DX10 DGR 32-48	BGP761
910925866234	BGP761 LED55- /740 I DN10 DGR 32-48	BGP761
910925866235	BGP761 LED84- /740 I DS50 DGR 32-48	BGP761
910925866238	BGP761 LED50- /830 II DM11 DGR D9 62	BGP761
910925866239	BGP761 LED79- /830 II DM70 DGR DDF27 D18	BGP761
910925866240	BGP761 LED59- /830 II DN11 DGR D11 62	BGP761
910925866241	BGP761 LED90- /740 II DW10 DGR 62	BGP761
910925866497	BGP761 LED119/740 I DM10 DGR 62 S	BGP761


Polar Wide Diagrams




Polar Normal (separate) - BGP762I - 910925866229




Polar Normal (separate) - BGP761I - 910925866232




Polar Normal (separate) - BGP761I - 910925866242




Polar Normal (separate) - BGP762I - 910925866225




Polar Normal (separate) - BGP763I - 910925866249




Polar Normal (separate) - BGP762I - 910925866228



Polar Normal (separate) - BGP763I - 910925866251




Polar Normal (separate) - BGP762I - 910925866220




Polar Normal (separate) - BGP762I - 910925866221


Polar Wide Diagrams




Polar Normal (separate) - BGP762I - 910925866246




Polar Normal (separate) - BGP761I - 910925866497




Polar Normal (separate) - BGP762I - 910925866492




Polar Normal (separate) - BGP760I - 910925863562




Polar Normal (separate) - BGP760I - 910925863561




Polar Normal (separate) - BGP760I - 910925863564



Polar Normal (separate) - BGP760I - 910925863554






Polar Normal (separate) - BGP760I - 910925863567



Polar Normal (separate) - BGP760I - 910925863563




Polar Wide Diagrams



Polar Normal (separate) - BGP760I - 910925863566

Polar Normal (separate) - BGP760I - 910925863560




Polar Normal (separate) - BGP761I - 910925866230



Polar Normal (separate) - BGP761I - 910925866238

Polar Normal (separate) - BGP763I - 910925866250

Polar Normal (separate) - BGP762I - 910925866227




Polar Normal (separate) - BGP762I - 910925866224


Polar Normal (separate) - BGP761I - 910925866235

Polar Normal (separate) - BGP761I - 910925866241


Polar Wide Diagrams




Polar Normal (separate) - BGP762I - 910925866222




Polar Normal (separate) - BGP761I - 910925866234




Polar Normal (separate) - BGP762I - 910925866252




Polar Normal (separate) - BGP762I - 910925866226




Polar Normal (separate) - BGP761I - 910925866239




Polar Normal (separate) - BGP761I - 910925866240



Polar Normal (separate) - BGP762I - 910925866245




Polar Normal (separate) - BGP763I -
910925866253




Polar Normal (separate) - BGP760I - 910925863556

Polar Wide Diagrams



Polar Normal (separate) - BGP760I - 910925863557



Polar Normal (separate) - BGP760I - 910925863555

