



Philips Ledinaire batten – For your everyday lighting jobs: simply unbox and install.

Ledinaire Batten

The Ledinaire batten (BN021C) range contains a selection of popular off-the-shelf batten LED luminaires that come with Philips high-quality levels at a competitive price. Reliable, energy-efficient and affordable. Ledinaire enables, simple and flexible installation, with a light-line creation option.

Benefits

- Philips quality and reliability
- Energy saving
- Compact design
- Easy and flexible installation, with line connection option

Features





- Light line, up to ten battens
- Mounting accessories included
- Available from 30 cm to 1.8 m length
- 2 CCT: 3,000 K, 4,000 K

Application

- General lighting
- Storage rooms
- Cove lighting

Ledinaire Batten

Dimensional drawing



Product details



Ledinaire batten, BN021C,
Connection



Ledinaire batten, BN021C,
Accessories included



Ledinaire batten, BN021C, Light-
line via connection cable



Ledinaire batten, BN021C, Light-
line pin-to-pin



Ledinaire batten, BN021C, Light-
line pin-to-pin

General Information	
Driver included	Yes
Light source replaceable	No
Number of gear units	Unit
Light Technical	
Colour rendering index (CRI)	>80
Optic type	Very wide beam
Operating and Electrical	
Protection class IEC	Safety class II
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Suitable for random switching	Not applicable
Controls and Dimming	
Dimmable	No
Maximum dim level	Not applicable
Mechanical and Housing	
Housing Colour	White
Mech. impact protection code	IK02
Ingress protection code	IP20
Approval and Application	
Ambient temperature range	-20 to +40 °C
CE mark	Yes
ENEC mark	-
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

Light Technical

Order Code	Full Product Name	Correlated Colour	Luminous efficacy	
		Temperature (Nom)	(rated) (nom.)	Luminous Flux
911401842382	BN021C LED20S/840 L1200	4000 K	105 lm/W	2,100 lm
911401842582	BN021C LED25S/840 L1500	4000 K	108 lm/W	2,600 lm
911401842682	BN021C LED24S/830 L1500	3000 K	100 lm/W	2,400 lm
911401841982	BN021C LED10S/840 L600	4000 K	105 lm/W	1,050 lm
911401842082	BN021C LED10S/830 L600	3000 K	96 lm/W	960 lm
911401842282	BN021C LED14S/830 L900	3000 K	97 lm/W	1,450 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401842382	BN021C LED20S/840 L1200	20 W
911401842582	BN021C LED25S/840 L1500	24 W
911401842682	BN021C LED24S/830 L1500	24 W

Order Code	Full Product Name	Power Consumption
911401841982	BN021C LED10S/840 L600	10 W
911401842082	BN021C LED10S/830 L600	10 W
911401842282	BN021C LED14S/830 L900	15 W

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
911401842382	BN021C LED20S/840 L1200	0.38, 0.38, SDCM≤5
911401842582	BN021C LED25S/840 L1500	0.38, 0.38, SDCM≤5
911401842682	BN021C LED24S/830 L1500	0.43, 0.40, SDCM≤5

Order Code	Full Product Name	Initial chromaticity
911401841982	BN021C LED10S/840 L600	0.38, 0.38, SDCM≤5
911401842082	BN021C LED10S/830 L600	0.43, 0.40, SDCM≤5
911401842282	BN021C LED14S/830 L900	0.43, 0.40, SDCM≤5

