



# Ledinaire Streetlight – Simple and Reliable

## Ledinaire StreetLight

Ledinaire Streetlight has been designed with Led transition in mind. Whether to refurbish old HID lanterns, or on a new country street, where you want citizens to feel safe. Ledinaire Streetlight offers simple benefits and reliable performance

### Benefits

- Insulation class II
- Standard surge protection level of 4 kV
- High efficacy up to 117 lm/W

### Features

- Easy to install
- Suitable for different applications thanks to medium wide light distribution
- Warm or neutral white color temperatures can accommodate various places
- Easy logistics

### Application

- Residential
- Road and Street

# Ledinaire StreetLight



## Versions



Ledinaire StreetLight BRP056

Ledinaire StreetLight BRP062

## Dimensional drawing



## Product details



Product Detail Photo Coreline



Product Detail Photo Coreline

Ledinaire StreetLight

|  |  |
|--|--|
| General Information                        |  |
| Driver included                            | Yes  |
| Light source replaceable                   | No   |
| Number of gear units                       | 1 unit   |
| Light Technical                            |  |
| Luminaire light beam spread                | -  |
| Color rendering index (CRI)                | 70   |
| Optic type outdoor                         | -  |
| Upward light output ratio                  | 0  |
| Operating and Electrical                   |  |
| Surge Protection (Common/<br>Differential) | Surge protection<br>level until 4 kV<br>differential mode<br>and 4 kV common<br>mode |
| Controls and Dimming                       |  |
| Dimmable                                   | No   |
| Maximum dim level                          | Not applicable   |
| Mechanical and Housing                     |  |
| Optical cover type                         | Polycarbonate  |
| Housing Color                              | Dark gray  |
| Mech. impact protection code               | IK07   |
| Ingress protection code                    | IP65   |
| Standard tilt angle side entry             | 0°   |
| Standard tilt angle posttop                | -  |
| Approval and Application                   |  |
| CE mark                                    | Yes  |
| Flammability mark                          | -  |

General Information

| Order Code   | Full Product Name               | Lamp family code |
|--------------|---------------------------------|------------------|
| 919515814268 | BRP056 LED34/730 PSU 27W SLF CE | LED34            |
| 919515814269 | BRP056 LED53/730 PSU 42W SLF CE | LED53            |
| 919515814271 | BRP056 LED35/740 PSU 27W SLF CE | LED35            |
| 919515814272 | BRP056 LED55/740 PSU 42W SLF CE | LED55            |
| 919515814270 | BRP062 LED70/730 PSU 54W SLA CE | LED70            |
| 919515814273 | BRP062 LED72/740 PSU 54W SLA CE | LED72            |

Light Technical

| Order Code   | Full Product Name                  | Light source<br>color | Correlated Color     |                  |
|--------------|------------------------------------|-----------------------|----------------------|------------------|
|              |                                    |                       | Temperature<br>(Nom) | Luminous<br>Flux |
| 919515814268 | BRP056 LED34/730<br>PSU 27W SLF CE | 730 warm<br>white     | 3000 K               | 2,952 lm         |
| 919515814269 | BRP056 LED53/730<br>PSU 42W SLF CE | 730 warm<br>white     | 3000 K               | 4,606 lm         |
| 919515814271 | BRP056 LED35/740<br>PSU 27W SLF CE | 740 neutral<br>white  | 4000 K               | 3,101 lm         |

| Order Code   | Full Product Name                  | Light source<br>color | Correlated Color     |                  |
|--------------|------------------------------------|-----------------------|----------------------|------------------|
|              |                                    |                       | Temperature<br>(Nom) | Luminous<br>Flux |
| 919515814272 | BRP056 LED55/740<br>PSU 42W SLF CE | 740 neutral<br>white  | 4000 K               | 4,850 lm         |
| 919515814270 | BRP062 LED70/730<br>PSU 54W SLA CE | 730 warm<br>white     | 3000 K               | 6,107 lm         |
| 919515814273 | BRP062 LED72/740<br>PSU 54W SLA CE | 740 neutral<br>white  | 4000 K               | 6,302 lm         |

Operating and Electrical

| Order Code   | Full Product Name               | Power Consumption |
|--------------|---------------------------------|-------------------|
| 919515814268 | BRP056 LED34/730 PSU 27W SLF CE | 27 W              |
| 919515814269 | BRP056 LED53/730 PSU 42W SLF CE | 42 W              |
| 919515814271 | BRP056 LED35/740 PSU 27W SLF CE | 27 W              |

| Order Code   | Full Product Name               | Power Consumption |
|--------------|---------------------------------|-------------------|
| 919515814272 | BRP056 LED55/740 PSU 42W SLF CE | 42 W              |
| 919515814270 | BRP062 LED70/730 PSU 54W SLA CE | 54 W              |
| 919515814273 | BRP062 LED72/740 PSU 54W SLA CE | 54 W              |

