



Ledinaire Streetlight – Simple and Reliable

Ledinaire StreetLight

Ledinaire Streetlight has been designed with Led transition in mind. Whether to refurbish old HID lanterns, or on a new country street, where you want citizens to feel safe. Ledinaire Streetlight offers simple benefits and reliable performance

Benefits

- Insulation class II
- Standard surge protection level of 4 kV
- High efficacy up to 117 lm/W

Features

- Easy to install
- Suitable for different applications thanks to medium wide light distribution
- Warm or neutral white color temperatures can accommodate various places
- Easy logistics

Application

- Residential
- Road and Street



Ledinaire StreetLight

Versions



Ledinaire StreetLight BRP062

Dimensional drawing



Product details



Product Detail Photo Coreline



Product Detail Photo Coreline

Ledinaire StreetLight

General Information	
Driver included	Yes
Light source replaceable	No
Number of gear units	1 unit
Light Technical	
Luminaire light beam spread	-
Color rendering index (CRI)	70
Optic type outdoor	-
Upward light output ratio	0
Operating and Electrical	
Surge Protection (Common/ Differential)	Surge protection level until 4 kV differential mode and 4 kV common mode
Controls and Dimming	
Dimmable	No
Maximum dim level	Not applicable
Mechanical and Housing	
Optical cover type	Polycarbonate
Housing Color	Dark gray
Mech. impact protection code	IK07
Ingress protection code	IP65
Standard tilt angle side entry	0°
Standard tilt angle posttop	-
Approval and Application	
CE mark	Yes
Flammability mark	-

General Information

Order Code	Full Product Name	Lamp family code
51211599	BRP056 LED34/730 PSU 27W SLF CE	LED34
51212299	BRP056 LED53/730 PSU 42W SLF CE	LED53
51208599	BRP056 LED35/740 PSU 27W SLF CE	LED35
51209299	BRP056 LED55/740 PSU 42W SLF CE	LED55
51213999	BRP062 LED70/730 PSU 54W SLA CE	LED70
51210899	BRP062 LED72/740 PSU 54W SLA CE	LED72

Light Technical

Order Code	Full Product Name	Light source color	Correlated Color	
			Temperature (Nom)	Luminous Flux
51211599	BRP056 LED34/730 PSU 27W SLF CE	730 warm white	3000 K	2,952 lm
51212299	BRP056 LED53/730 PSU 42W SLF CE	730 warm white	3000 K	4,606 lm
51208599	BRP056 LED35/740 PSU 27W SLF CE	740 neutral white	4000 K	3,101 lm

Order Code	Full Product Name	Light source color	Correlated Color	
			Temperature (Nom)	Luminous Flux
51209299	BRP056 LED55/740 PSU 42W SLF CE	740 neutral white	4000 K	4,850 lm
51213999	BRP062 LED70/730 PSU 54W SLA CE	730 warm white	3000 K	6,107 lm
51210899	BRP062 LED72/740 PSU 54W SLA CE	740 neutral white	4000 K	6,302 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
51211599	BRP056 LED34/730 PSU 27W SLF CE	27 W
51212299	BRP056 LED53/730 PSU 42W SLF CE	42 W
51208599	BRP056 LED35/740 PSU 27W SLF CE	27 W

Order Code	Full Product Name	Power Consumption
51209299	BRP056 LED55/740 PSU 42W SLF CE	42 W
51213999	BRP062 LED70/730 PSU 54W SLA CE	54 W
51210899	BRP062 LED72/740 PSU 54W SLA CE	54 W

