



Make roads safer and sustainable.

GreenVision Xceed Gen2

Sustainability, citizen well-being and connectivity are key players in the game of differentiation among cities all over the world. And a way of achieving these goals is lighting. Lighting up streets and roads enhance the comfort, security and overall safety of our rapidly growing urban environments. Our GreenVision Xceed Gen2 makes an affordable LED road lighting solution that ensures sufficient light on your roads and streets. The GreenVision Xceed Gen2 family from Signify provides your city with a flexible lighting system which can be deployed anywhere in urban spaces, roadways and rural areas – our luminaires provide optimal light for all application areas. Additionally, the GreenVision Xceed Gen2 is ready to be connected to, and work with, smart city ecosystems. Our new GreenVision Xceed Gen2 range is enhanced to give city lighting departments even more control – to choose the right light

Benefits

- Robust & Reliable with a long service lifetime
- Elegant finless design
- Equipped with a Service tag, a QR-based identification system that makes each luminaire uniquely identifiable and provides maintenance, installation, and spare part information

Features

- System efficacy 140lm/W $\pm 10\%$
- Long service lifetime 100Khrs L70@Ta 35°C
- With 10kV or 15kV Surge protection Device

GreenVision Xceed Gen2

Application

- Pedestrian category roads (P1-P6)
- Vehicle category roads (M1-M6)
- Traffic routes and main access road
- Urban and residential area

Specifications

Material	Housing: die-cast aluminiumOptic: polycarbonateOptic cover: glass
Light Source	3030 LED5050 LEDHigh Power LED
Installation	Side entry 42-60mmOptional adjustable spigot
Luminous flux	System flux up to 55000lm
Correlated color temperature - CCT	5700K4000K3000K2700K2200K
Luminaire efficacy	4000K: 140lm/WOptional 4000K 160lm/W
Color Rendering index - 70 CRI	

Power	up to 390W
Mains Voltage	220-240V / 50-60HzOptional 120-277V / 50-60Hz
Control system input	DALI / 1-10V / D4i
Dimming	PSR: 1-10VPSD: DALIPSC: Coded mainsSPRD: 1-10V, Step dimming, AOCSR: D4i
Operating Temperature range	-40 to +50C Ta
Ingress protection	IP66
Certification	IECEE CB, CE, CQC, RCM, D4i


Versions




BRP383

BRP382

Dimensional drawing



Dimensional drawing



General Information	
Driver included	Yes
Light source replaceable	No
Service tag	Yes
Light Technical	
Color rendering index (CRI)	>70
Controls and Dimming	
Dimmable	Yes
Maximum dim level	10%
Mechanical and Housing	
Optical cover type	Polycarbonate micro lens optic
Housing Color	Gray
Mech. impact protection code	IK08
Ingress protection code	IP66
Approval and Application	
CE mark	Yes
Flammability mark	For mounting on normally flammable surfaces

Light Technical

Order Code	Full Product Name	Light source color	Correlated Color	
			Temperature (Nom)	Luminous Flux
911401874198	BRP383 LED386/NW 280W 220-240V DM PSR	740 neutral white	4000 K	38,600 lm
911401874698	BRP383 LED315/NW 225W 220-240V DM PSR	740 neutral white	4000 K	31,500 lm
911401874898	BRP383 LED280/NW 200W 220-240V DM PSR	740 neutral white	4000 K	28,000 lm
911401874998	BRP383 LED268/NW 190W 220-240V DM PSR	740 neutral white	4000 K	26,800 lm
911401875098	BRP383 LED243/NW 175W 220-240V DM PSR	740 neutral white	4000 K	24,300 lm
911401875298	BRP383 LED220/NW 160W 220-240V DM PSR	740 neutral white	4000 K	22,000 lm
911401877098	BRP383 LED232/WW 175W 220-240V DM PSR	730 warm white	3000 K	23,200 lm
911401877298	BRP383 LED210/WW 160W 220-240V DM PSR	730 warm white	3000 K	21,000 lm
911401869297	BRP381 LED127/WW 95W 220-240V DW2 PSR	730 warm white	3000 K	12,700 lm
911401869497	BRP381 LED94/WW 70W 220-240V DW2 PSR	730 warm white	3000 K	9,400 lm
911401875698	BRP381 LED145/NW 105W 220-240V DM PSR	740 neutral white	4000 K	14,500 lm
911401875798	BRP381 LED133/NW 95W 220-240V DM PSR	740 neutral white	4000 K	13,300 lm
911401875898	BRP381 LED122/NW 85W 220-240V DM PSR	740 neutral white	4000 K	12,200 lm
911401875998	BRP381 LED99/NW 70W 220-240V DM PSR	740 neutral white	4000 K	9,900 lm
911401876098	BRP381 LED87/NW 60W 220-240V DM PSR	740 neutral white	4000 K	8,700 lm
911401877698	BRP381 LED138/WW 105W 220-240V DM PSR	730 warm white	3000 K	13,800 lm
911401877798	BRP381 LED127/WW 95W 220-240V DM PSR	730 warm white	3000 K	12,700 lm

Order Code	Full Product Name	Light source color	Correlated Color	
			Temperature (Nom)	Luminous Flux
911401878098	BRP381 LED83/WW 60W 220-240V DM PSR	730 warm white	3000 K	8,300 lm
911401878198	BRP381 LED75/NW 55W 220-240V DM PSR	740 neutral white	4000 K	7,500 lm
911401867097	BRP382 LED170/NW 120W 220-240V DW2 PSR	740 neutral white	4000 K	17,000 lm
911401875398	BRP382 LED193/NW 140W 220-240V DM PSR	740 neutral white	4000 K	19,300 lm
911401875598	BRP382 LED170/NW 120W 220-240V DM PSR	740 neutral white	4000 K	17,000 lm
911401877398	BRP382 LED184/WW 140W 220-240V DM PSR	730 warm white	3000 K	18,400 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
911401874198	BRP383 LED386/NW 280W 220-240V DM PSR	280 W	911401875898	BRP381 LED122/NW 85W 220-240V DM PSR	85 W
911401874698	BRP383 LED315/NW 225W 220-240V DM PSR	225 W	911401875998	BRP381 LED99/NW 70W 220-240V DM PSR	70 W
911401874898	BRP383 LED280/NW 200W 220-240V DM PSR	200 W	911401876098	BRP381 LED87/NW 60W 220-240V DM PSR	60 W
911401874998	BRP383 LED268/NW 190W 220-240V DM PSR	190 W	911401877698	BRP381 LED138/WW 105W 220-240V DM PSR	105 W
911401875098	BRP383 LED243/NW 175W 220-240V DM PSR	175 W	911401877798	BRP381 LED127/WW 95W 220-240V DM PSR	95 W
911401875298	BRP383 LED220/NW 160W 220-240V DM PSR	160 W	911401878098	BRP381 LED83/WW 60W 220-240V DM PSR	60 W
911401877098	BRP383 LED232/WW 175W 220-240V DM PSR	175 W	911401878198	BRP381 LED75/NW 55W 220-240V DM PSR	55 W
911401877298	BRP383 LED210/WW 160W 220-240V DM PSR	160 W	911401867097	BRP382 LED170/NW 120W 220-240V DW2 PSR	120 W
911401869297	BRP381 LED127/WW 95W 220-240V DW2 PSR	95 W	911401875398	BRP382 LED193/NW 140W 220-240V DM PSR	140 W
911401869497	BRP381 LED94/WW 70W 220-240V DW2 PSR	70 W	911401875598	BRP382 LED170/NW 120W 220-240V DM PSR	120 W
911401875698	BRP381 LED145/NW 105W 220-240V DM PSR	105 W	911401877398	BRP382 LED184/WW 140W 220-240V DM PSR	140 W
911401875798	BRP381 LED133/NW 95W 220-240V DM PSR	95 W			

