



Reliable, Energy saving LED Floodlight

Essential SmartBright G5 LED Floodlight

The Essential SmartBright G5 LED Floodlight is the new successor with robust die-cast aluminum housing suitable for general outdoor application. Lightweight, with a robust die-cast aluminum housing and corrosion-proof coating, it's suitable for general outdoor applications. Plus, with a higher efficacy than the previous generation, it also saves more energy.

Benefits

- Reliable quality and performance
- Outstanding savings
- Easy to install & adjust

Features

- CCT: 3000K, 4000K, 6500K
- Power: 10W, 20W, 30W, 50W, 70W, 100W, 150W and 200W
- Input voltage: 220V-240V
- Lumen efficacy up to 100lm/w
- Working temperature: -40°C to +50°C
- 20khrs life

Application

- Warehouses
- Landscape
- Arena and Sports
- Billboard
- Parking area lighting
- Amenity

Essential SmartBright G5 LED Floodlight

Versions



ESSENTIAL SMARTBRIGHT G5
LED FLOODLIGHT



ESSENTIAL SMARTBRIGHT G5
LED FLOODLIGHT



ESSENTIAL SMARTBRIGHT G5
LED FLOODLIGHT



ESSENTIAL SMARTBRIGHT G5
LED FLOODLIGHT



ESSENTIAL SMARTBRIGHT G5
LED FLOODLIGHT



ESSENTIAL SMARTBRIGHT G5
LED FLOODLIGHT





ESSENTIAL SMARTBRIGHT G5
LED FLOODLIGHT









ESSENTIAL SMARTBRIGHT G5
LED FLOODLIGHT

Dimensional drawing



Essential SmartBright G5 LED Floodlight

Dimensional drawing



Essential SmartBright G5 LED Floodlight

General Information	
Driver included	Yes
Gear	-
Number of gear units	1 unit
Light Technical	
Luminaire light beam spread	110°
Light source color	840 neutral white
Correlated Color Temperature (Nom)	4000 K
Color rendering index (CRI)	80
Number of light sources	1
Controls and Dimming	
Dimmable	No
Maximum dim level	Not applicable
Mechanical and Housing	
Optical cover type	Tempered glass
Housing Color	Black
Mech. impact protection code	IK06
Ingress protection code	IP65
Approval and Application	
CE mark	No
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s

Light Technical

Order Code	Full Product Name	Luminous Flux
911401825286	BVP150 LED70/NW PSU 70W SWB G3 GM	7,000 lm
911401801986	BVP150 LED30/NW PSU 30W SWB MDU G3 GM	3,000 lm
911401824286	BVP150 LED50/NW PSU 50W SWB G3 GM	5,000 lm
911401822286	BVP150 LED20/NW PSU 20W SWB G3 GM	2,000 lm
911401823286	BVP150 LED30/NW PSU 30W SWB G3 GM	3,000 lm
911401821286	BVP150 LED10/NW PSU 10W SWB G3 GM	1,000 lm
911401801686	BVP150 LED20/NW PSU 20W SWB MDU G3 GM	2,000 lm
911401802286	BVP150 LED50/NW PSU 50W SWB MDU G3 GM	5,000 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401825286	BVP150 LED70/NW PSU 70W SWB G3 GM	70 W
911401801986	BVP150 LED30/NW PSU 30W SWB MDU G3 GM	30 W
911401824286	BVP150 LED50/NW PSU 50W SWB G3 GM	50 W
911401822286	BVP150 LED20/NW PSU 20W SWB G3 GM	20 W

Order Code	Full Product Name	Power Consumption
911401823286	BVP150 LED30/NW PSU 30W SWB G3 GM	30 W
911401821286	BVP150 LED10/NW PSU 10W SWB G3 GM	10 W
911401801686	BVP150 LED20/NW PSU 20W SWB MDU G3 GM	20 W
911401802286	BVP150 LED50/NW PSU 50W SWB MDU G3 GM	50 W

