



Philips UniFlood M gen2: A high power floodlight with true modularity

UniFlood M G2

Philips UniFlood M gen2 is a cost-effective, exterior-rated architectural LED floodlight that's designed for façade, landscape and outdoor flood lighting applications. The robust, modular, rectangular design features highly-efficient optics, making it ideal for illuminating everything from multi-storey façades and bridges to landmarks and monuments. This LED floodlight is available in white, monochromatic colors, RGB, RGBW and tunable white. It comes with six different spread lenses ranging from narrow spot to wide flood and has DMX512/RDM control option. A truly modular floodlight that gives architects and designers the freedom to explore a wide range of concepts and designs with no limitations.

Benefits

- Great design flexibility with individually tilting heads and controls
- Create the right lighting effect with six different spread lenses (narrow spot to wide flood)
- Easy to control with DMX512/RDM
- A robust choice that's IP66-rated for outdoor use

Features

- Standard: RGBW, RGB, 2700K, 3000K and 4000K
- Optional 5000K, monochromatic colors and tunable white
- Flexible lengths from 155 to 569 mm
- Adjustable tilting angles for each head and for the whole set
- Steel brackets

UniFlood M G2


Application

- Bridges, Monuments, Facades
- Parks and Plazas
- Landscape


Warnings and Safety

- For outdoor use only.


Versions



Dimensional drawing



Dimensional drawing



General Information	
Driver included	Yes
Light Technical	
Color rendering index (CRI)	>80
Mechanical and Housing	
Optical cover type	Clear glass
Housing Color	Dark gray
Mech. impact protection code	IK06
Ingress protection code	IP66
Approval and Application	
CE mark	Yes
Flammability mark	For mounting on normally flammable surfaces

Light Technical

		Light source color	Correlated Color Temperature (Nom)	Luminous Flux
Order Code	Full Product Name			
911401748303	BVP353 72LED 27K 220V L57 10	827 warm white	2700 K	11,380 lm
911401748313	BVP353 72LED 30K 220V L57 10	830 warm white	3000 K	11,870 lm
911401748323	BVP353 72LED 40K 220V L57 10	840 neutral white	4000 K	13,245 lm
911401748333	BVP353 72LED 27K 220V L57 10 DMX	827 warm white	2700 K	10,845 lm
911401748343	BVP353 72LED 30K 220V L57 10 DMX	830 warm white	3000 K	11,310 lm
911401748353	BVP353 72LED 40K 220V L57 10 DMX	840 neutral white	4000 K	12,620 lm
911401748363	BVP353 72LED RGB 220V L57 10 DMX	RGB	-	6,705 lm
911401748373	BVP353 72LED RGBWW 220V L57 10 DMX	RGBW	-	7,195 lm
911401748383	BVP353 72LED RGBNW 220V L57 10 DMX	RGBW	-	7,515 lm
911401748393	BVP353 72LED 27K 220V L57 15	827 warm white	2700 K	11,950 lm
911401748403	BVP353 72LED 30K 220V L57 15	830 warm white	3000 K	12,465 lm
911401748413	BVP353 72LED 40K 220V L57 15	840 neutral white	4000 K	13,905 lm
911401748423	BVP353 72LED 27K 220V L57 15 DMX	827 warm white	2700 K	11,385 lm
911401748433	BVP353 72LED 30K 220V L57 15 DMX	830 warm white	3000 K	11,875 lm
911401748443	BVP353 72LED 40K 220V L57 15 DMX	840 neutral white	4000 K	13,250 lm
911401748453	BVP353 72LED RGB 220V L57 15 DMX	RGB	-	7,040 lm
911401748463	BVP353 72LED RGBWW 220V L57 15 DMX	RGBW	-	7,555 lm
911401748483	BVP353 72LED 27K 220V L57 30	827 warm white	2700 K	12,375 lm
911401748493	BVP353 72LED 30K 220V L57 30	830 warm white	3000 K	12,910 lm
911401748503	BVP353 72LED 40K 220V L57 30	840 neutral white	4000 K	14,405 lm
911401748513	BVP353 72LED 27K 220V L57 30 DMX	827 warm white	2700 K	11,790 lm
911401748523	BVP353 72LED 30K 220V L57 30 DMX	830 warm white	3000 K	12,300 lm
911401748533	BVP353 72LED 40K 220V L57 30 DMX	840 neutral white	4000 K	13,725 lm
911401748543	BVP353 72LED RGB 220V L57 30 DMX	RGB	-	7,290 lm
911401748553	BVP353 72LED RGBWW 220V L57 30 DMX	RGBW	-	7,825 lm
911401748563	BVP353 72LED RGBNW 220V L57 30 DMX	RGBW	-	8,170 lm
911401748583	BVP353 72LED 30K 220V L57 45	830 warm white	3000 K	12,465 lm
911401746523	BVP353 24LED 40K 220V L24 10	840 neutral white	4000 K	4,205 lm
911401746753	BVP353 24LED RGBWW 220V L24 30 DMX	RGBW	-	2,555 lm

Order Code	Full Product Name	Light source	Correlated Color	
		color	Temperature (Nom)	Luminous Flux
911401748133	BVP353 60LED 30K 220V L50 30	830 warm white	3000 K	10,380 lm
911401746033	BVP353 16LED RGBWW 220V L18 30 DMX	RGBW	-	1,550 lm
911401747833	BVP353 48LED RGBWW 220V L40 30 DMX	RGBW	-	5,710 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401748303	BVP353 72LED 27K 220V L57 10	150 W
911401748313	BVP353 72LED 30K 220V L57 10	150 W
911401748323	BVP353 72LED 40K 220V L57 10	150 W
911401748333	BVP353 72LED 27K 220V L57 10 DMX	150 W
911401748343	BVP353 72LED 30K 220V L57 10 DMX	150 W
911401748353	BVP353 72LED 40K 220V L57 10 DMX	150 W
911401748363	BVP353 72LED RGB 220V L57 10 DMX	150 W
911401748373	BVP353 72LED RGBWW 220V L57 10 DMX	150 W
911401748383	BVP353 72LED RGBNW 220V L57 10 DMX	150 W
911401748393	BVP353 72LED 27K 220V L57 15	150 W
911401748403	BVP353 72LED 30K 220V L57 15	150 W
911401748413	BVP353 72LED 40K 220V L57 15	150 W
911401748423	BVP353 72LED 27K 220V L57 15 DMX	150 W
911401748433	BVP353 72LED 30K 220V L57 15 DMX	150 W
911401748443	BVP353 72LED 40K 220V L57 15 DMX	150 W
911401748453	BVP353 72LED RGB 220V L57 15 DMX	150 W

Order Code	Full Product Name	Power Consumption
911401748463	BVP353 72LED RGBWW 220V L57 15 DMX	150 W
911401748483	BVP353 72LED 27K 220V L57 30	150 W
911401748493	BVP353 72LED 30K 220V L57 30	150 W
911401748503	BVP353 72LED 40K 220V L57 30	150 W
911401748513	BVP353 72LED 27K 220V L57 30 DMX	150 W
911401748523	BVP353 72LED 30K 220V L57 30 DMX	150 W
911401748533	BVP353 72LED 40K 220V L57 30 DMX	150 W
911401748543	BVP353 72LED RGB 220V L57 30 DMX	150 W
911401748553	BVP353 72LED RGBWW 220V L57 30 DMX	150 W
911401748563	BVP353 72LED RGBNW 220V L57 30 DMX	150 W
911401748583	BVP353 72LED 30K 220V L57 45	150 W
911401746523	BVP353 24LED 40K 220V L24 10	50 W
911401746753	BVP353 24LED RGBWW 220V L24 30 DMX	50 W
911401748133	BVP353 60LED 30K 220V L50 30	120 W
911401746033	BVP353 16LED RGBWW 220V L18 30 DMX	30 W
911401747833	BVP353 48LED RGBWW 220V L40 30 DMX	100 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
911401748303	BVP353 72LED 27K 220V L57 10	No
911401748313	BVP353 72LED 30K 220V L57 10	No
911401748323	BVP353 72LED 40K 220V L57 10	No
911401748333	BVP353 72LED 27K 220V L57 10 DMX	Yes
911401748343	BVP353 72LED 30K 220V L57 10 DMX	Yes
911401748353	BVP353 72LED 40K 220V L57 10 DMX	Yes
911401748363	BVP353 72LED RGB 220V L57 10 DMX	Yes
911401748373	BVP353 72LED RGBWW 220V L57 10 DMX	Yes
911401748383	BVP353 72LED RGBNW 220V L57 10 DMX	Yes
911401748393	BVP353 72LED 27K 220V L57 15	No
911401748403	BVP353 72LED 30K 220V L57 15	No
911401748413	BVP353 72LED 40K 220V L57 15	No
911401748423	BVP353 72LED 27K 220V L57 15 DMX	Yes
911401748433	BVP353 72LED 30K 220V L57 15 DMX	Yes
911401748443	BVP353 72LED 40K 220V L57 15 DMX	Yes
911401748453	BVP353 72LED RGB 220V L57 15 DMX	Yes

Order Code	Full Product Name	Dimmable
911401748463	BVP353 72LED RGBWW 220V L57 15 DMX	Yes
911401748483	BVP353 72LED 27K 220V L57 30	No
911401748493	BVP353 72LED 30K 220V L57 30	No
911401748503	BVP353 72LED 40K 220V L57 30	No
911401748513	BVP353 72LED 27K 220V L57 30 DMX	Yes
911401748523	BVP353 72LED 30K 220V L57 30 DMX	Yes
911401748533	BVP353 72LED 40K 220V L57 30 DMX	Yes
911401748543	BVP353 72LED RGB 220V L57 30 DMX	Yes
911401748553	BVP353 72LED RGBWW 220V L57 30 DMX	Yes
911401748563	BVP353 72LED RGBNW 220V L57 30 DMX	Yes
911401748583	BVP353 72LED 30K 220V L57 45	No
911401746523	BVP353 24LED 40K 220V L24 10	No
911401746753	BVP353 24LED RGBWW 220V L24 30 DMX	Yes
911401748133	BVP353 60LED 30K 220V L50 30	No
911401746033	BVP353 16LED RGBWW 220V L18 30 DMX	Yes
911401747833	BVP353 48LED RGBWW 220V L40 30 DMX	Yes

