



Philips UniFlood M gen2: A high power floodlight with true modularity

UniFlood M G2

Philips UniFlood M gen2 is a cost-effective, exterior-rated architectural LED floodlight that's designed for façade, landscape and outdoor flood lighting applications. The robust, modular, rectangular design features highly-efficient optics, making it ideal for illuminating everything from multi-storey façades and bridges to landmarks and monuments. This LED floodlight is available in white, monochromatic colors, RGB, RGBW and tunable white. It comes with six different spread lenses ranging from narrow spot to wide flood and has DMX512/RDM control option. A truly modular floodlight that gives architects and designers the freedom to explore a wide range of concepts and designs with no limitations.

Benefits

- Great design flexibility with individually tilting heads and controls
- Create the right lighting effect with six different spread lenses (narrow spot to wide flood)
- Easy to control with DMX512/RDM
- A robust choice that's IP66-rated for outdoor use

Features

- Standard: RGBW, RGB, 2700K, 3000K and 4000K
- Optional 5000K, monochromatic colors and tunable white
- Flexible lengths from 155 to 569 mm
- Adjustable tilting angles for each head and for the whole set
- Steel brackets

UniFlood M G2


Application

- Bridges, Monuments, Facades
- Parks and Plazas
- Landscape

Warnings and Safety

- For outdoor use only.

Versions







UniFlood M Gen2

UniFlood M Gen2

UniFlood M Gen2

UniFlood M Gen2

Dimensional drawing



Dimensional drawing



General Information	
Driver included	Yes
Light Technical	
Color rendering index (CRI)	>80
Mechanical and Housing	
Optical cover type	Clear glass
Housing Color	Dark gray
Mech. impact protection code	IK06
Ingress protection code	IP66
Approval and Application	
CE mark	Yes
Flammability mark	For mounting on normally flammable surfaces

Light Technical

Order Code	Full Product Name	Light source color	Correlated Color Temperature (Nom)	Luminous Flux
911401746873	BVP353 30LED 30K 220V L30 10	830 warm white	3000 K	4,710 lm
911401749463	BVP354 144LED RGBNW 220V L57 10 DMX	RGBW	-	15,030 lm
911401749733	BVP354 144LED RGBNW 220V L57 45 DMX	RGBW	-	15,785 lm
911401748463	BVP353 72LED RGBWW 220V L57 15 DMX	RGBW	-	7,555 lm
911401748653	BVP353 72LED RGBNW 220V L57 45 DMX	RGBW	-	7,890 lm
911401745493	BVP353 12LED RGBWW 220V L15 10 DMX	RGBW	-	1,175 lm
911401745523	BVP353 12LED 30K 220V L15 15	830 warm white	3000 K	1,925 lm
911401745673	BVP353 12LED RGBWW 220V L15 30 DMX	RGBW	-	1,275 lm
911401746573	BVP353 24LED RGBWW 220V L24 10 DMX	RGBW	-	2,350 lm
911401746673	BVP353 24LED RGBNW 220V L24 15 DMX	RGBW	-	2,575 lm
911401747863	BVP353 48LED 30K 220V L40 45	830 warm white	3000 K	8,145 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401746873	BVP353 30LED 30K 220V L30 10	60 W
911401749463	BVP354 144LED RGBNW 220V L57 10 DMX	300 W
911401749733	BVP354 144LED RGBNW 220V L57 45 DMX	300 W
911401748463	BVP353 72LED RGBWW 220V L57 15 DMX	150 W
911401748653	BVP353 72LED RGBNW 220V L57 45 DMX	150 W
911401745493	BVP353 12LED RGBWW 220V L15 10 DMX	24 W

Order Code	Full Product Name	Power Consumption
911401745523	BVP353 12LED 30K 220V L15 15	24 W
911401745673	BVP353 12LED RGBWW 220V L15 30 DMX	24 W
911401746573	BVP353 24LED RGBWW 220V L24 10 DMX	50 W
911401746673	BVP353 24LED RGBNW 220V L24 15 DMX	50 W
911401747863	BVP353 48LED 30K 220V L40 45	100 W

Controls and Dimming

UniFlood M G2

Order Code	Full Product Name	Dimmable
911401746873	BVP353 30LED 30K 220V L30 10	No
911401749463	BVP354 144LED RGBNW 220V L57 10 DMX	Yes
911401749733	BVP354 144LED RGBNW 220V L57 45 DMX	Yes
911401748463	BVP353 72LED RGBWW 220V L57 15 DMX	Yes
911401748653	BVP353 72LED RGBNW 220V L57 45 DMX	Yes
911401745493	BVP353 12LED RGBWW 220V L15 10 DMX	Yes

Order Code	Full Product Name	Dimmable
911401745523	BVP353 12LED 30K 220V L15 15	No
911401745673	BVP353 12LED RGBWW 220V L15 30 DMX	Yes
911401746573	BVP353 24LED RGBWW 220V L24 10 DMX	Yes
911401746673	BVP353 24LED RGBNW 220V L24 15 DMX	Yes
911401747863	BVP353 48LED 30K 220V L40 45	No

