



Architectural LED floodlight for fixed or dynamic lighting

UniFlood C Pro

Philips UniFlood C Pro offers a unique rugged elegance, with a cylindrical form and flowing lines that connect the front and back housings beautifully. This is compact architectural floodlighting design where every element has a purpose; the front section provides exceptional lighting, while the back section houses all the electrical components. Between the two, the fins dissipate heat and also serve as a decorative element. Exterior-rated, Philips UniFlood C Pro is a cost-effective, architectural LED floodlight that is designed for façade, landscape and outdoor floodlighting applications. The robust mechanical design and high-efficiency optics make it ideal for illuminating multi-story exterior façades, bridges, landmarks and monuments. Architects and designers have the freedom to explore a wide range of concepts and designs with no limitations, thanks to a range of colors, multiple spread lenses and a DMX512/RDM control option.

Benefits

- Available in white, monochromatic colors, RGB, RGBW and tunable white
- Wide range of beam angles from Narrow Spot to Wide Flood
- Available in DMX512/RDM control interface option

Features

- Robust design, IP66 rated for outdoor use
- Optical distributions: 3.5°, 10°, 15°, 30°, 45° and 60°
- Adjustable ±90° tilting angle
- Through wiring for DMX signal via dedicated cables with IP67 connectors

UniFlood C Pro

Application

- Bridges, Monuments, Façades
- Landscape
- Parks and Plazas

Warnings and Safety

- For outdoor use only

Versions






UniFlood C Pro



UniFlood C Pro

Dimensional drawing



General Information	
Driver included	Yes
Mechanical and Housing	
Optical cover type	Clear glass
Housing Color	Dark gray
Mech. impact protection code	IK06
Ingress protection code	IP66
Approval and Application	
CE mark	Yes

Light Technical

Order Code	Full Product Name	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Flux
911401773683	BVP371 12LED 27K 220V 60 24W HE	827 warm white	2700 K	>80	1,345 lm
911401774063	BVP372 15LED RGB 220V 15 DMX 40W HP	RGB	-	N.A.	1,350 lm
911401774203	BVP372 16LED 30K 220V 10 40W HP	830 warm white	3000 K	>80	2,570 lm
911401774603	BVP372 18LED 30K 220V 10 50W HP	830 warm white	3000 K	>80	3,070 lm
911401774643	BVP372 18LED 30K 220V 30 50W HP	830 warm white	3000 K	>80	3,635 lm
911401774663	BVP372 18LED 30K 220V 45 50W HP	830 warm white	3000 K	>80	2,725 lm
911401774743	BVP372 18LED 40K 220V 30 50W HP	840 neutral white	4000 K	>80	4,055 lm
911401774823	BVP372 18LED RGB 220V 30 DMX 50W HP	RGB	-	N.A.	1,855 lm
911401775503	BVP373 36LED 30K 220V 10 100W HP	830 warm white	3000 K	>80	6,445 lm

Order Code	Full Product Name	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Flux
911401775523	BVP373 36LED 30K 220V 15 100W HP	830 warm white	3000 K	>80	6,715 lm
911401775823	BVP373 36LED RGBWW 220V 30 DMX 100W HP	RGBW	-	N.A.	4,730 lm
911401775993	BVP374 48LED 30K 220V 30 120W HP	830 warm white	3000 K	>80	9,305 lm
911401776093	BVP374 48LED 40K 220V 30 120W HP	840 neutral white	4000 K	>80	10,380 lm
911401776403	BVP374 60LED 30K 220V 10 150W HP	830 warm white	3000 K	>80	9,830 lm
911401776503	BVP374 60LED 40K 220V 10 150W HP	840 neutral white	4000 K	>80	10,965 lm
911401776693	BVP374 60LED RGBNW 220V 60 DMX 150W HP	RGBW	-	N.A.	5,700 lm
911401776713	BVP374 60LED RGBWW 220V 15 DMX 150W HP	RGBW	-	N.A.	6,640 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401773683	BVP371 12LED 27K 220V 60 24W HE	24 W
911401774063	BVP372 15LED RGB 220V 15 DMX 40W HP	40 W
911401774203	BVP372 16LED 30K 220V 10 40W HP	40 W

Order Code	Full Product Name	Power Consumption
911401774603	BVP372 18LED 30K 220V 10 50W HP	50 W
911401774643	BVP372 18LED 30K 220V 30 50W HP	50 W
911401774663	BVP372 18LED 30K 220V 45 50W HP	50 W

Order Code	Full Product Name	Power Consumption
911401774743	BVP372 18LED 40K 220V 30 50W HP	50 W
911401774823	BVP372 18LED RGB 220V 30 DMX 50W HP	50 W
911401775503	BVP373 36LED 30K 220V 10 100W HP	100 W
911401775523	BVP373 36LED 30K 220V 15 100W HP	100 W
911401775823	BVP373 36LED RGBWW 220V 30 DMX 100W HP	100 W
911401775993	BVP374 48LED 30K 220V 30 120W HP	120 W

Order Code	Full Product Name	Power Consumption
911401776093	BVP374 48LED 40K 220V 30 120W HP	120 W
911401776403	BVP374 60LED 30K 220V 10 150W HP	150 W
911401776503	BVP374 60LED 40K 220V 10 150W HP	150 W
911401776693	BVP374 60LED RGBNW 220V 60 DMX 150W HP	150 W
911401776713	BVP374 60LED RGBWW 220V 15 DMX 150W HP	150 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
911401773683	BVP371 12LED 27K 220V 60 24W HE	No
911401774063	BVP372 15LED RGB 220V 15 DMX 40W HP	Yes
911401774203	BVP372 16LED 30K 220V 10 40W HP	No
911401774603	BVP372 18LED 30K 220V 10 50W HP	No
911401774643	BVP372 18LED 30K 220V 30 50W HP	No
911401774663	BVP372 18LED 30K 220V 45 50W HP	No
911401774743	BVP372 18LED 40K 220V 30 50W HP	No
911401774823	BVP372 18LED RGB 220V 30 DMX 50W HP	Yes
911401775503	BVP373 36LED 30K 220V 10 100W HP	No

Order Code	Full Product Name	Dimmable
911401775523	BVP373 36LED 30K 220V 15 100W HP	No
911401775823	BVP373 36LED RGBWW 220V 30 DMX 100W HP	Yes
911401775993	BVP374 48LED 30K 220V 30 120W HP	No
911401776093	BVP374 48LED 40K 220V 30 120W HP	No
911401776403	BVP374 60LED 30K 220V 10 150W HP	No
911401776503	BVP374 60LED 40K 220V 10 150W HP	No
911401776693	BVP374 60LED RGBNW 220V 60 DMX 150W HP	Yes
911401776713	BVP374 60LED RGBWW 220V 15 DMX 150W HP	Yes

