



Philips GreenPerform Highbay G5: a versatile LED highbay with optimized performance and future-proof control system

GreenPerform Highbay G5

The GreenPerform Highbay G5 continues the GreenPerform family's enviable reputation for reliable performance. Not only does it deliver leading system efficacy and extended long-term quality, it also promises Unified Glare Rating (UGR) control with compact dimensions. GreenPerform Highbay G5 is also fully compatible with IoT software such as Interact, which is a scalable, future-proof control system. The family also has a series that supports cold room applications with 100% humidity and no condensation. All benefits that make this robust, optimized, and versatile family suitable for almost all industrial applications.

Benefits

- Excellent energy savings
- Long-term quality and reliability
- Visual comfort
- Wide range of applications
- Connected ready for cloud-based IoT software applications

GreenPerform Highbay G5

Features

- 170 lm/W system efficacy
- 75,000 hours L70B50 lifetime @Ta 35°
- Glare control (Narrow Beam), uniform illuminance (Wide Beam)
- Works seamlessly with the Interact IoT software and platform
- Cold room application support

Application



- Manufacturing
- Warehouses
- Logistic center
- Exhibition hall

Specifications


Mounting type	Suspended
	Pipe
	Surface
Operating Temperature range	-30 to +50 °C
Light Source	LED
Mains Voltage	220-240V / 50-60Hz
Mains connection	Flying cable
Mechanical Accessories	Hook for suspension
	Mounting bracket for surface
Dimming	PSU: non-dimmable
	PSD: Dimmable via Dali-broadcasting
	Connected: Wireless control, compatible with SNH210 sensor
Control system input	DALI/Wireless
Integrated sensors	SNH210
Material	Housing: die-cast aluminium
Main color of the luminaire	RAL7012
Flicker / Pst / SVM	PSU: <30%
	PSD/Connected: <3.2%
Luminous flux	10klm-30klm
Power consumption	67W-205W

Luminaire efficacy	Up to 160lm/W
Correlated color	4000K
temperature - CCT	6500K
Color Rendering index - 80	
CRI	
Beam angle	WB: 85°
	NB: 55°
Optical cover/lens material	PC
Optical cover/lens finish	Clear
Protection Class	Class I
IEC61140	
Mechanical impact protection	IK08
Ingress protection	IP65
Driver replaceable	Yes
UGR	WB: 25
	NB: 22
Installation	Suspended
	Pipe
	Surface

Dimensional drawing




Dimensional drawing



GreenPerform Highbay G5

Dimensional drawing



Product details



GreenPerform Highbay G5



GreenPerform Highbay G5

General Information	
Driver included	Yes
Gear	-
Number of gear units	1 unit
Light Technical	
Beam angle of light source	115 degree(s)
Color rendering index (CRI)	80
Number of light sources	1
Operating and Electrical	
Protection class IEC	Safety class I
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Suitable for random switching	Yes
Mechanical and Housing	
Optical cover type	Clear dome
Housing Color	Grey
Approval and Application	
CE mark	Yes
ENEC mark	-
Flammability mark	For mounting on normally flammable surfaces

Light Technical

Order Code	Full Product Name	Correlated Color	Luminous	Luminous Flux	Optic type
		Temperature (Nom)	Efficacy (rated) (Nom)		
911401549545	BY698X G5 LED105/NW L1W PIR WB GC	4000 K	166 lm/W	10,500 lm	Wide beam
911401549645	BY698X G5 LED105/CW L1W PIR WB GC	6500 K	166 lm/W	10,500 lm	Wide beam
911401549745	BY698X G5 LED150/NW L1W PIR WB GC	4000 K	170 lm/W	15,000 lm	Wide beam
911401549845	BY698X G5 LED150/CW L1W PIR WB GC	6500 K	170 lm/W	15,000 lm	Wide beam
911401549945	BY698X G5 LED200/NW L1W PIR WB GC	4000 K	169 lm/W	20,500 lm	Wide beam
911401550045	BY698X G5 LED200/CW L1W PIR WB GC	6500 K	169 lm/W	20,500 lm	Wide beam
911401550145	BY698X G5 LED250/NW L1W PIR WB GC	4000 K	173 lm/W	25,000 lm	Wide beam
911401550245	BY698X G5 LED250/CW L1W PIR WB GC	6500 K	173 lm/W	25,000 lm	Wide beam
911401550345	BY698X G5 LED300/NW L1W PIR WB GC	4000 K	171 lm/W	31,000 lm	Wide beam
911401550445	BY698X G5 LED300/CW L1W PIR WB GC	6500 K	171 lm/W	31,000 lm	Wide beam
30803000	BY698X G5 LED105/NW L1W PIR WB GM	4000 K	166 lm/W	10,500 lm	Wide beam
30804700	BY698X G5 LED105/CW L1W PIR WB GM	6500 K	166 lm/W	10,500 lm	Wide beam
30805400	BY698X G5 LED150/NW L1W PIR WB GM	4000 K	170 lm/W	15,000 lm	Wide beam
30806100	BY698X G5 LED150/CW L1W PIR WB GM	6500 K	170 lm/W	15,000 lm	Wide beam
30807800	BY698X G5 LED200/NW L1W PIR WB GM	4000 K	169 lm/W	20,500 lm	Wide beam
30808500	BY698X G5 LED200/CW L1W PIR WB GM	6500 K	169 lm/W	20,500 lm	Wide beam
30809200	BY698X G5 LED250/NW L1W PIR WB GM	4000 K	173 lm/W	25,000 lm	Wide beam
30810800	BY698X G5 LED250/CW L1W PIR WB GM	6500 K	173 lm/W	25,000 lm	Wide beam
30811500	BY698X G5 LED300/NW L1W PIR WB GM	4000 K	171 lm/W	31,000 lm	Wide beam
30812200	BY698X G5 LED300/CW L1W PIR WB GM	6500 K	171 lm/W	31,000 lm	Wide beam
30813900	BY698X G5 LED105/840 L1W PIR WB CAU	4000 K	166 lm/W	10,500 lm	Wide beam
30814600	BY698X G5 LED150/840 L1W PIR WB CAU	4000 K	170 lm/W	15,000 lm	Wide beam
30815300	BY698X G5 LED200/840 L1W PIR WB CAU	4000 K	169 lm/W	20,500 lm	Wide beam
30816000	BY698X G5 LED250/840 L1W PIR WB CAU	4000 K	173 lm/W	25,000 lm	Wide beam

Order Code	Full Product Name	Correlated Color	Luminous	Luminous Flux	Optic type
		Temperature (Nom)	Efficacy (rated) (Nom)		
30817700	BY698X G5 LED300/840 L1W PIR WB CAU	4000 K	171 lm/W	31,000 lm	Wide beam
30818400	BY698X G5 LED105/NW L1W PIR WB GM L3m	4000 K	166 lm/W	10,500 lm	Wide beam
30819100	BY698X G5 LED105/CW L1W PIR WB GM L3m	6500 K	166 lm/W	10,500 lm	Wide beam
30820700	BY698X G5 LED150/NW L1W PIR WB GM L3m	4000 K	170 lm/W	15,000 lm	Wide beam
30821400	BY698X G5 LED150/CW L1W PIR WB GM L3m	6500 K	170 lm/W	15,000 lm	Wide beam
30822100	BY698X G5 LED200/NW L1W PIR WB GM L3m	4000 K	169 lm/W	20,500 lm	Wide beam
30823800	BY698X G5 LED200/CW L1W PIR WB GM L3m	6500 K	169 lm/W	20,500 lm	Wide beam
30824500	BY698X G5 LED250/NW L1W PIR WB GM L3m	4000 K	173 lm/W	25,000 lm	Wide beam
30825200	BY698X G5 LED250/CW L1W PIR WB GM L3m	6500 K	173 lm/W	25,000 lm	Wide beam
30826900	BY698X G5 LED300/NW L1W PIR WB GM L3m	4000 K	171 lm/W	31,000 lm	Wide beam
30827600	BY698X G5 LED300/CW L1W PIR WB GM L3m	6500 K	171 lm/W	31,000 lm	Wide beam
99445600	BY698P G5 LED105/NW PSU WB GM	4000 K	166 lm/W	10,500 lm	Wide beam
911401528345	BY698P G5 LED105/NW PSU NB GM	4000 K	166 lm/W	10,500 lm	Narrow beam
99444900	BY698P G5 LED105/CW PSU WB GM	6500 K	166 lm/W	10,500 lm	Wide beam
911401528545	BY698P G5 LED105/CW PSU NB GM	6500 K	166 lm/W	10,500 lm	Narrow beam
99446300	BY698P G5 LED150/NW PSU WB GM	4000 K	170 lm/W	15,000 lm	Wide beam
911401528745	BY698P G5 LED150/NW PSU NB GM	4000 K	170 lm/W	15,000 lm	Narrow beam
99447000	BY698P G5 LED150/CW PSU WB GM	6500 K	170 lm/W	15,000 lm	Wide beam
911401528945	BY698P G5 LED150/CW PSU NB GM	6500 K	170 lm/W	15,000 lm	Narrow beam
99448700	BY698P G5 LED200/NW PSU WB GM	4000 K	169 lm/W	20,500 lm	Wide beam
911401529145	BY698P G5 LED200/NW PSU NB GM	4000 K	169 lm/W	20,500 lm	Narrow beam
99449400	BY698P G5 LED200/CW PSU WB GM	6500 K	169 lm/W	20,500 lm	Wide beam
911401529345	BY698P G5 LED200/CW PSU NB GM	6500 K	169 lm/W	20,500 lm	Narrow beam
911401529445	BY698P G5 LED250/NW PSU WB GM	4000 K	173 lm/W	25,000 lm	Wide beam
911401529545	BY698P G5 LED250/NW PSU NB GM	4000 K	173 lm/W	25,000 lm	Narrow beam

Order Code	Full Product Name	Correlated Color	Luminous	Luminous	Optic type
		Temperature	Efficacy (rated)		
(Nom)	(Nom)	Flux			
32705500	BY698P G5 LED250/CW PSU WB GM	6500 K	173 lm/W	25,000 lm	Wide beam
911401529745	BY698P G5 LED250/CW PSU NB GM	6500 K	173 lm/W	25,000 lm	Narrow beam
911401529845	BY698P G5 LED300/NW PSU WB GM	4000 K	171 lm/W	31,000 lm	Wide beam
911401529945	BY698P G5 LED300/NW PSU NB GM	4000 K	171 lm/W	31,000 lm	Narrow beam
32704800	BY698P G5 LED300/CW PSU WB GM	6500 K	171 lm/W	31,000 lm	Wide beam
911401530145	BY698P G5 LED300/CW PSU NB GM	6500 K	171 lm/W	31,000 lm	Narrow beam
911401533145	BY698P G5 LED105/NW PSD WB GM	4000 K	152 lm/W	10,500 lm	Wide beam
911401533245	BY698P G5 LED105/NW PSD NB GM	4000 K	152 lm/W	10,500 lm	Narrow beam
911401533345	BY698P G5 LED105/CW PSD WB GM	6500 K	152 lm/W	10,500 lm	Wide beam
911401533445	BY698P G5 LED105/CW PSD NB GM	6500 K	152 lm/W	10,500 lm	Narrow beam
911401533545	BY698P G5 LED150/NW PSD WB GM	4000 K	161 lm/W	15,000 lm	Wide beam
911401533645	BY698P G5 LED150/NW PSD NB GM	4000 K	161 lm/W	15,000 lm	Narrow beam
911401533745	BY698P G5 LED150/CW PSD WB GM	6500 K	161 lm/W	15,000 lm	Wide beam
911401533845	BY698P G5 LED150/CW PSD NB GM	6500 K	161 lm/W	15,000 lm	Narrow beam
911401533945	BY698P G5 LED200/NW PSD WB GM	4000 K	162 lm/W	20,500 lm	Wide beam
911401534045	BY698P G5 LED200/NW PSD NB GM	4000 K	162 lm/W	20,500 lm	Narrow beam
911401534145	BY698P G5 LED200/CW PSD WB GM	6500 K	162 lm/W	20,500 lm	Wide beam
911401534245	BY698P G5 LED200/CW PSD NB GM	6500 K	162 lm/W	20,500 lm	Narrow beam
911401534345	BY698P G5 LED250/NW PSD WB GM	4000 K	162 lm/W	25,000 lm	Wide beam
911401534445	BY698P G5 LED250/NW PSD NB GM	4000 K	162 lm/W	25,000 lm	Narrow beam
911401534545	BY698P G5 LED250/CW PSD WB GM	6500 K	162 lm/W	25,000 lm	Wide beam
911401534645	BY698P G5 LED250/CW PSD NB GM	6500 K	162 lm/W	25,000 lm	Narrow beam
911401534745	BY698P G5 LED300/NW PSD WB GM	4000 K	163 lm/W	31,000 lm	Wide beam
911401534845	BY698P G5 LED300/NW PSD NB GM	4000 K	163 lm/W	31,000 lm	Narrow beam
911401534945	BY698P G5 LED300/CW PSD WB GM	6500 K	163 lm/W	31,000 lm	Wide beam

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
911401535045	BY698P G5 LED300/CW PSD NB GM	6500 K	163 lm/W	31,000 lm	Narrow beam
30783500	BY698P G5 LED105/NW PSU WB GM L3m	4000 K	166 lm/W	10,500 lm	Wide beam
30784200	BY698P G5 LED105/NW PSU NB GM L3m	4000 K	166 lm/W	10,500 lm	Narrow beam
30785900	BY698P G5 LED105/CW PSU WB GM L3m	6500 K	166 lm/W	10,500 lm	Wide beam
30786600	BY698P G5 LED105/CW PSU NB GM L3m	6500 K	166 lm/W	10,500 lm	Narrow beam
30787300	BY698P G5 LED150/NW PSU WB GM L3m	4000 K	170 lm/W	15,000 lm	Wide beam
30788000	BY698P G5 LED150/NW PSU NB GM L3m	4000 K	170 lm/W	15,000 lm	Narrow beam
30789700	BY698P G5 LED150/CW PSU WB GM L3m	6500 K	170 lm/W	15,000 lm	Wide beam
30790300	BY698P G5 LED150/CW PSU NB GM L3m	6500 K	170 lm/W	15,000 lm	Narrow beam
30791000	BY698P G5 LED200/NW PSU WB GM L3m	4000 K	169 lm/W	20,500 lm	Wide beam
30792700	BY698P G5 LED200/NW PSU NB GM L3m	4000 K	169 lm/W	20,500 lm	Narrow beam
30793400	BY698P G5 LED200/CW PSU WB GM L3m	6500 K	169 lm/W	20,500 lm	Wide beam
30794100	BY698P G5 LED200/CW PSU NB GM L3m	6500 K	169 lm/W	20,500 lm	Narrow beam
30795800	BY698P G5 LED250/NW PSU WB GM L3m	4000 K	173 lm/W	25,000 lm	Wide beam
30796500	BY698P G5 LED250/NW PSU NB GM L3m	4000 K	173 lm/W	25,000 lm	Narrow beam
30797200	BY698P G5 LED250/CW PSU WB GM L3m	6500 K	173 lm/W	25,000 lm	Wide beam
30798900	BY698P G5 LED250/CW PSU NB GM L3m	6500 K	173 lm/W	25,000 lm	Narrow beam
30799600	BY698P G5 LED300/NW PSU WB GM L3m	4000 K	171 lm/W	31,000 lm	Wide beam
30800900	BY698P G5 LED300/NW PSU NB GM L3m	4000 K	171 lm/W	31,000 lm	Narrow beam
30801600	BY698P G5 LED300/CW PSU WB GM L3m	6500 K	171 lm/W	31,000 lm	Wide beam
30802300	BY698P G5 LED300/CW PSU NB GM L3m	6500 K	171 lm/W	31,000 lm	Narrow beam
911401541745	BY690P LED105/NW PSU WB GM	4000 K	166 lm/W	10,500 lm	Wide beam
911401541845	BY690P LED105/CW PSU WB GM	6500 K	166 lm/W	10,500 lm	Wide beam
911401541945	BY690P LED150/NW PSU WB GM	4000 K	170 lm/W	15,000 lm	Wide beam
911401542045	BY690P LED150/CW PSU WB GM	6500 K	170 lm/W	15,000 lm	Wide beam

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
911401542145	BY690P LED200/NW PSU WB GM	4000 K	181 lm/W	20,000 lm	Wide beam
911401542245	BY690P LED200/CW PSU WB GM	6500 K	181 lm/W	20,000 lm	Wide beam
911401542345	BY690P LED250/NW PSU WB GM	4000 K	177 lm/W	25,500 lm	Wide beam
911401542445	BY690P LED250/CW PSU WB GM	6500 K	177 lm/W	25,500 lm	Wide beam
911401542545	BY690P LED300/NW PSU WB GM	4000 K	176 lm/W	30,000 lm	Wide beam
911401542645	BY690P LED300/CW PSU WB GM	6500 K	176 lm/W	30,000 lm	Wide beam
911401544245	BY698X G5 LED150/NW Connected WB GM	4000 K	174 lm/W	15,000 lm	Wide beam
911401544345	BY698X G5 LED150/NW Connected NB GM	4000 K	174 lm/W	15,000 lm	Narrow beam
911401544445	BY698X G5 LED150/CW Connected WB GM	6500 K	174 lm/W	15,000 lm	Wide beam
911401544545	BY698X G5 LED150/CW Connected NB GM	6500 K	174 lm/W	15,000 lm	Narrow beam
911401544645	BY698X G5 LED200/NW Connected WB GM	4000 K	168 lm/W	20,500 lm	Wide beam
911401544745	BY698X G5 LED200/NW Connected NB GM	4000 K	168 lm/W	20,500 lm	Narrow beam
911401544845	BY698X G5 LED200/CW Connected WB GM	6500 K	168 lm/W	20,500 lm	Wide beam
911401544945	BY698X G5 LED200/CW Connected NB GM	6500 K	168 lm/W	20,500 lm	Narrow beam
911401545045	BY698X G5 LED250/NW Connected WB GM	4000 K	170 lm/W	25,000 lm	Wide beam
911401545145	BY698X G5 LED250/NW Connected NB GM	4000 K	170 lm/W	25,000 lm	Narrow beam
911401545245	BY698X G5 LED250/CW Connected WB GM	6500 K	170 lm/W	25,000 lm	Wide beam
911401545345	BY698X G5 LED250/CW Connected NB GM	6500 K	170 lm/W	25,000 lm	Narrow beam
911401545445	BY698X G5 LED300/NW Connected WB GM	4000 K	170 lm/W	31,000 lm	Wide beam
911401545545	BY698X G5 LED300/NW Connected NB GM	4000 K	170 lm/W	31,000 lm	Narrow beam
911401545645	BY698X G5 LED300/CW Connected WB GM	6500 K	170 lm/W	31,000 lm	Wide beam
911401545745	BY698X G5 LED300/CW Connected NB GM	6500 K	170 lm/W	31,000 lm	Narrow beam
30828300	BY698X G5 LED105/NW L1W MW WB GM	4000 K	166 lm/W	10,500 lm	Wide beam
30829000	BY698X G5 LED105/CW L1W MW WB GM	6500 K	166 lm/W	10,500 lm	Wide beam
30830600	BY698X G5 LED150/NW L1W MW WB GM	4000 K	170 lm/W	15,000 lm	Wide beam

Order Code	Full Product Name	Correlated Color	Luminous	Luminous	Optic type
		Temperature	Efficacy (rated)		
		(Nom)	(Nom)	Flux	
30831300	BY698X G5 LED150/CW L1W MW WB GM	6500 K	170 lm/W	15,000 lm	Wide beam
30832000	BY698X G5 LED200/NW L1W MW WB GM	4000 K	169 lm/W	20,500 lm	Wide beam
30833700	BY698X G5 LED200/CW L1W MW WB GM	6500 K	169 lm/W	20,500 lm	Wide beam
30834400	BY698X G5 LED250/NW L1W MW WB GM	4000 K	173 lm/W	25,000 lm	Wide beam
30835100	BY698X G5 LED250/CW L1W MW WB GM	6500 K	173 lm/W	25,000 lm	Wide beam
30836800	BY698X G5 LED300/NW L1W MW WB GM	4000 K	171 lm/W	31,000 lm	Wide beam
30837500	BY698X G5 LED300/CW L1W MW WB GM	6500 K	171 lm/W	31,000 lm	Wide beam
30838200	BY698X G5 LED105/NW L1W MW WB GM L3m	4000 K	166 lm/W	10,500 lm	Wide beam
30839900	BY698X G5 LED105/CW L1W MW WB GM L3m	6500 K	166 lm/W	10,500 lm	Wide beam
30840500	BY698X G5 LED150/NW L1W MW WB GM L3m	4000 K	170 lm/W	15,000 lm	Wide beam
30841200	BY698X G5 LED150/CW L1W MW WB GM L3m	6500 K	170 lm/W	15,000 lm	Wide beam
30842900	BY698X G5 LED200/NW L1W MW WB GM L3m	4000 K	169 lm/W	20,500 lm	Wide beam
30843600	BY698X G5 LED200/CW L1W MW WB GM L3m	6500 K	169 lm/W	20,500 lm	Wide beam
30844300	BY698X G5 LED250/NW L1W MW WB GM L3m	4000 K	173 lm/W	25,000 lm	Wide beam
30845000	BY698X G5 LED250/CW L1W MW WB GM L3m	6500 K	173 lm/W	25,000 lm	Wide beam
30846700	BY698X G5 LED300/NW L1W MW WB GM L3m	4000 K	171 lm/W	31,000 lm	Wide beam
30847400	BY698X G5 LED300/CW L1W MW WB GM L3m	6500 K	171 lm/W	31,000 lm	Wide beam

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
911401549545	BY698X G5 LED105/NW L1W PIR WB GC	63 W	30805400	BY698X G5 LED150/NW L1W PIR WB GM	88 W
911401549645	BY698X G5 LED105/CW L1W PIR WB GC	63 W	30806100	BY698X G5 LED150/CW L1W PIR WB GM	88 W
911401549745	BY698X G5 LED150/NW L1W PIR WB GC	88 W	30807800	BY698X G5 LED200/NW L1W PIR WB GM	121 W
911401549845	BY698X G5 LED150/CW L1W PIR WB GC	88 W	30808500	BY698X G5 LED200/CW L1W PIR WB GM	121 W
911401549945	BY698X G5 LED200/NW L1W PIR WB GC	121 W	30809200	BY698X G5 LED250/NW L1W PIR WB GM	144 W
911401550045	BY698X G5 LED200/CW L1W PIR WB GC	121 W	30810800	BY698X G5 LED250/CW L1W PIR WB GM	144 W
911401550145	BY698X G5 LED250/NW L1W PIR WB GC	144 W	30811500	BY698X G5 LED300/NW L1W PIR WB GM	181 W
911401550245	BY698X G5 LED250/CW L1W PIR WB GC	144 W	30812200	BY698X G5 LED300/CW L1W PIR WB GM	181 W
911401550345	BY698X G5 LED300/NW L1W PIR WB GC	181 W	30813900	BY698X G5 LED105/840 L1W PIR WB CAU	63 W
911401550445	BY698X G5 LED300/CW L1W PIR WB GC	181 W	30814600	BY698X G5 LED150/840 L1W PIR WB CAU	88 W
30803000	BY698X G5 LED105/NW L1W PIR WB GM	63 W	30815300	BY698X G5 LED200/840 L1W PIR WB CAU	121 W
30804700	BY698X G5 LED105/CW L1W PIR WB GM	63 W	30816000	BY698X G5 LED250/840 L1W PIR WB CAU	144 W

GreenPerform Highbay G5

Order Code	Full Product Name	Power Consumption
30817700	BY698X G5 LED300/840 L1W PIR WB CAU	181 W
30818400	BY698X G5 LED105/NW L1W PIR WB GM L3m	63 W
30819100	BY698X G5 LED105/CW L1W PIR WB GM L3m	63 W
30820700	BY698X G5 LED150/NW L1W PIR WB GM L3m	88 W
30821400	BY698X G5 LED150/CW L1W PIR WB GM L3m	88 W
30822100	BY698X G5 LED200/NW L1W PIR WB GM L3m	121 W
30823800	BY698X G5 LED200/CW L1W PIR WB GM L3m	121 W
30824500	BY698X G5 LED250/NW L1W PIR WB GM L3m	144 W
30825200	BY698X G5 LED250/CW L1W PIR WB GM L3m	144 W
30826900	BY698X G5 LED300/NW L1W PIR WB GM L3m	181 W
30827600	BY698X G5 LED300/CW L1W PIR WB GM L3m	181 W
99445600	BY698P G5 LED105/NW PSU WB GM	63 W
911401528345	BY698P G5 LED105/NW PSU NB GM	63 W
99444900	BY698P G5 LED105/CW PSU WB GM	63 W
911401528545	BY698P G5 LED105/CW PSU NB GM	63 W
99446300	BY698P G5 LED150/NW PSU WB GM	88 W
911401528745	BY698P G5 LED150/NW PSU NB GM	88 W
99447000	BY698P G5 LED150/CW PSU WB GM	88 W
911401528945	BY698P G5 LED150/CW PSU NB GM	88 W
99448700	BY698P G5 LED200/NW PSU WB GM	121 W
911401529145	BY698P G5 LED200/NW PSU NB GM	121 W
99449400	BY698P G5 LED200/CW PSU WB GM	121 W
911401529345	BY698P G5 LED200/CW PSU NB GM	121 W
911401529445	BY698P G5 LED250/NW PSU WB GM	144 W
911401529545	BY698P G5 LED250/NW PSU NB GM	144 W
32705500	BY698P G5 LED250/CW PSU WB GM	144 W
911401529745	BY698P G5 LED250/CW PSU NB GM	144 W
911401529845	BY698P G5 LED300/NW PSU WB GM	181 W
911401529945	BY698P G5 LED300/NW PSU NB GM	181 W
32704800	BY698P G5 LED300/CW PSU WB GM	181 W
911401530145	BY698P G5 LED300/CW PSU NB GM	181 W
911401533145	BY698P G5 LED105/NW PSD WB GM	69 W
911401533245	BY698P G5 LED105/NW PSD NB GM	69 W
911401533345	BY698P G5 LED105/CW PSD WB GM	69 W
911401533445	BY698P G5 LED105/CW PSD NB GM	69 W
911401533545	BY698P G5 LED150/NW PSD WB GM	93 W
911401533645	BY698P G5 LED150/NW PSD NB GM	93 W
911401533745	BY698P G5 LED150/CW PSD WB GM	93 W
911401533845	BY698P G5 LED150/CW PSD NB GM	93 W
911401533945	BY698P G5 LED200/NW PSD WB GM	126 W
911401534045	BY698P G5 LED200/NW PSD NB GM	126 W
911401534145	BY698P G5 LED200/CW PSD WB GM	126 W
911401534245	BY698P G5 LED200/CW PSD NB GM	126 W
911401534345	BY698P G5 LED250/NW PSD WB GM	154 W
911401534445	BY698P G5 LED250/NW PSD NB GM	154 W
911401534545	BY698P G5 LED250/CW PSD WB GM	154 W
911401534645	BY698P G5 LED250/CW PSD NB GM	154 W
911401534745	BY698P G5 LED300/NW PSD WB GM	190 W
911401534845	BY698P G5 LED300/NW PSD NB GM	190 W
911401534945	BY698P G5 LED300/CW PSD WB GM	190 W
911401535045	BY698P G5 LED300/CW PSD NB GM	190 W
30783500	BY698P G5 LED105/NW PSU WB GM L3m	63 W

Order Code	Full Product Name	Power Consumption
30784200	BY698P G5 LED105/NW PSU NB GM L3m	63 W
30785900	BY698P G5 LED105/CW PSU WB GM L3m	63 W
30786600	BY698P G5 LED105/CW PSU NB GM L3m	63 W
30787300	BY698P G5 LED150/NW PSU WB GM L3m	88 W
30788000	BY698P G5 LED150/NW PSU NB GM L3m	88 W
30789700	BY698P G5 LED150/CW PSU WB GM L3m	88 W
30790300	BY698P G5 LED150/CW PSU NB GM L3m	88 W
30791000	BY698P G5 LED200/NW PSU WB GM L3m	121 W
30792700	BY698P G5 LED200/NW PSU NB GM L3m	121 W
30793400	BY698P G5 LED200/CW PSU WB GM L3m	121 W
30794100	BY698P G5 LED200/CW PSU NB GM L3m	121 W
30795800	BY698P G5 LED250/NW PSU WB GM L3m	144 W
30796500	BY698P G5 LED250/NW PSU NB GM L3m	144 W
30797200	BY698P G5 LED250/CW PSU WB GM L3m	144 W
30798900	BY698P G5 LED250/CW PSU NB GM L3m	144 W
30799600	BY698P G5 LED300/NW PSU WB GM L3m	181 W
30800900	BY698P G5 LED300/NW PSU NB GM L3m	181 W
30801600	BY698P G5 LED300/CW PSU WB GM L3m	181 W
30802300	BY698P G5 LED300/CW PSU NB GM L3m	181 W
911401541745	BY690P LED105/NW PSU WB GM	63 W
911401541845	BY690P LED105/CW PSU WB GM	63 W
911401541945	BY690P LED150/NW PSU WB GM	88 W
911401542045	BY690P LED150/CW PSU WB GM	88 W
911401542145	BY690P LED200/NW PSU WB GM	110 W
911401542245	BY690P LED200/CW PSU WB GM	110 W
911401542345	BY690P LED250/NW PSU WB GM	144 W
911401542445	BY690P LED250/CW PSU WB GM	144 W
911401542545	BY690P LED300/NW PSU WB GM	170 W
911401542645	BY690P LED300/CW PSU WB GM	170 W
911401544245	BY698X G5 LED150/NW Connected WB GM	86 W
911401544345	BY698X G5 LED150/NW Connected NB GM	86 W
911401544445	BY698X G5 LED150/CW Connected WB GM	86 W
911401544545	BY698X G5 LED150/CW Connected NB GM	86 W
911401544645	BY698X G5 LED200/NW Connected WB GM	122 W
911401544745	BY698X G5 LED200/NW Connected NB GM	122 W
911401544845	BY698X G5 LED200/CW Connected WB GM	122 W
911401544945	BY698X G5 LED200/CW Connected NB GM	122 W
911401545045	BY698X G5 LED250/NW Connected WB GM	147 W
911401545145	BY698X G5 LED250/NW Connected NB GM	147 W
911401545245	BY698X G5 LED250/CW Connected WB GM	147 W
911401545345	BY698X G5 LED250/CW Connected NB GM	147 W
911401545445	BY698X G5 LED300/NW Connected WB GM	182 W
911401545545	BY698X G5 LED300/NW Connected NB GM	182 W
911401545645	BY698X G5 LED300/CW Connected WB GM	182 W
911401545745	BY698X G5 LED300/CW Connected NB GM	182 W
30828300	BY698X G5 LED105/NW L1W MW WB GM	63 W
30829000	BY698X G5 LED105/CW L1W MW WB GM	63 W
30830600	BY698X G5 LED150/NW L1W MW WB GM	88 W
30831300	BY698X G5 LED150/CW L1W MW WB GM	88 W
30832000	BY698X G5 LED200/NW L1W MW WB GM	121 W
30833700	BY698X G5 LED200/CW L1W MW WB GM	121 W
30834400	BY698X G5 LED250/NW L1W MW WB GM	144 W

GreenPerform Highbay G5

Order Code	Full Product Name	Power Consumption
30835100	BY698X G5 LED250/CW L1W MW WB GM	144 W
30836800	BY698X G5 LED300/NW L1W MW WB GM	181 W
30837500	BY698X G5 LED300/CW L1W MW WB GM	181 W
30838200	BY698X G5 LED105/NW L1W MW WB GM L3m	63 W
30839900	BY698X G5 LED105/CW L1W MW WB GM L3m	63 W
30840500	BY698X G5 LED150/NW L1W MW WB GM L3m	88 W
30841200	BY698X G5 LED150/CW L1W MW WB GM L3m	88 W

Order Code	Full Product Name	Power Consumption
30842900	BY698X G5 LED200/NW L1W MW WB GM L3m	121 W
30843600	BY698X G5 LED200/CW L1W MW WB GM L3m	121 W
30844300	BY698X G5 LED250/NW L1W MW WB GM L3m	144 W
30845000	BY698X G5 LED250/CW L1W MW WB GM L3m	144 W
30846700	BY698X G5 LED300/NW L1W MW WB GM L3m	181 W
30847400	BY698X G5 LED300/CW L1W MW WB GM L3m	181 W

Controls and Dimming

Order Code	Full Product Name	Dimmable	Maximum dim level
911401549545	BY698X G5 LED105/NW L1W PIR WB GC	Wireless Dim - Do not use with dimmer	0% (digital)
911401549645	BY698X G5 LED105/CW L1W PIR WB GC	Wireless Dim - Do not use with dimmer	0% (digital)
911401549745	BY698X G5 LED150/NW L1W PIR WB GC	Wireless Dim - Do not use with dimmer	0% (digital)
911401549845	BY698X G5 LED150/CW L1W PIR WB GC	Wireless Dim - Do not use with dimmer	0% (digital)
911401549945	BY698X G5 LED200/NW L1W PIR WB GC	Wireless Dim - Do not use with dimmer	0% (digital)
911401550045	BY698X G5 LED200/CW L1W PIR WB GC	Wireless Dim - Do not use with dimmer	0% (digital)
911401550145	BY698X G5 LED250/NW L1W PIR WB GC	Wireless Dim - Do not use with dimmer	0% (digital)
911401550245	BY698X G5 LED250/CW L1W PIR WB GC	Wireless Dim - Do not use with dimmer	0% (digital)
911401550345	BY698X G5 LED300/NW L1W PIR WB GC	Wireless Dim - Do not use with dimmer	0% (digital)
911401550445	BY698X G5 LED300/CW L1W PIR WB GC	Wireless Dim - Do not use with dimmer	0% (digital)
30803000	BY698X G5 LED105/NW L1W PIR WB GM	Wireless Dim - Do not use with dimmer	0% (digital)
30804700	BY698X G5 LED105/CW L1W PIR WB GM	Wireless Dim - Do not use with dimmer	0% (digital)
30805400	BY698X G5 LED150/NW L1W PIR WB GM	Wireless Dim - Do not use with dimmer	0% (digital)

Order Code	Full Product Name	Dimmable	Maximum dim level
30806100	BY698X G5 LED150/CW L1W PIR WB GM	Wireless Dim - Do not use with dimmer	0% (digital)
30807800	BY698X G5 LED200/NW L1W PIR WB GM	Wireless Dim - Do not use with dimmer	0% (digital)
30808500	BY698X G5 LED200/CW L1W PIR WB GM	Wireless Dim - Do not use with dimmer	0% (digital)
30809200	BY698X G5 LED250/NW L1W PIR WB GM	Wireless Dim - Do not use with dimmer	0% (digital)
30810800	BY698X G5 LED250/CW L1W PIR WB GM	Wireless Dim - Do not use with dimmer	0% (digital)
30811500	BY698X G5 LED300/NW L1W PIR WB GM	Wireless Dim - Do not use with dimmer	0% (digital)
30812200	BY698X G5 LED300/CW L1W PIR WB GM	Wireless Dim - Do not use with dimmer	0% (digital)
30813900	BY698X G5 LED105/840 L1W PIR WB CAU	Wireless Dim - Do not use with dimmer	0% (digital)
30814600	BY698X G5 LED150/840 L1W PIR WB CAU	Wireless Dim - Do not use with dimmer	0% (digital)
30815300	BY698X G5 LED200/840 L1W PIR WB CAU	Wireless Dim - Do not use with dimmer	0% (digital)
30816000	BY698X G5 LED250/840 L1W PIR WB CAU	Wireless Dim - Do not use with dimmer	0% (digital)
30817700	BY698X G5 LED300/840 L1W PIR WB CAU	Wireless Dim - Do not use with dimmer	0% (digital)
30818400	BY698X G5 LED105/NW L1W PIR WB GM L3m	Wireless Dim - Do not use with dimmer	0% (digital)

GreenPerform Highbay G5

Order Code	Full Product Name	Dimmable	Maximum dim level
30819100	BY698X G5 LED105/CW L1W PIR WB GM L3m	Wireless Dim - Do not use with dimmer	0% (digital)
30820700	BY698X G5 LED150/NW L1W PIR WB GM L3m	Wireless Dim - Do not use with dimmer	0% (digital)
30821400	BY698X G5 LED150/CW L1W PIR WB GM L3m	Wireless Dim - Do not use with dimmer	0% (digital)
30822100	BY698X G5 LED200/NW L1W PIR WB GM L3m	Wireless Dim - Do not use with dimmer	0% (digital)
30823800	BY698X G5 LED200/CW L1W PIR WB GM L3m	Wireless Dim - Do not use with dimmer	0% (digital)
30824500	BY698X G5 LED250/NW L1W PIR WB GM L3m	Wireless Dim - Do not use with dimmer	0% (digital)
30825200	BY698X G5 LED250/CW L1W PIR WB GM L3m	Wireless Dim - Do not use with dimmer	0% (digital)
30826900	BY698X G5 LED300/NW L1W PIR WB GM L3m	Wireless Dim - Do not use with dimmer	0% (digital)
30827600	BY698X G5 LED300/CW L1W PIR WB GM L3m	Wireless Dim - Do not use with dimmer	0% (digital)
99445600	BY698P G5 LED105/NW PSU WB GM	-	Not applicable
911401528345	BY698P G5 LED105/NW PSU NB GM	-	Not applicable
99444900	BY698P G5 LED105/CW PSU WB GM	-	Not applicable
911401528545	BY698P G5 LED105/CW PSU NB GM	-	Not applicable
99446300	BY698P G5 LED150/NW PSU WB GM	-	Not applicable
911401528745	BY698P G5 LED150/NW PSU NB GM	-	Not applicable
99447000	BY698P G5 LED150/CW PSU WB GM	-	Not applicable
911401528945	BY698P G5 LED150/CW PSU NB GM	-	Not applicable
99448700	BY698P G5 LED200/NW PSU WB GM	-	Not applicable
911401529145	BY698P G5 LED200/NW PSU NB GM	-	Not applicable
99449400	BY698P G5 LED200/CW PSU WB GM	-	Not applicable
911401529345	BY698P G5 LED200/CW PSU NB GM	-	Not applicable

Order Code	Full Product Name	Dimmable	Maximum dim level
911401529445	BY698P G5 LED250/NW PSU WB GM	-	Not applicable
911401529545	BY698P G5 LED250/NW PSU NB GM	-	Not applicable
32705500	BY698P G5 LED250/CW PSU WB GM	-	Not applicable
911401529745	BY698P G5 LED250/CW PSU NB GM	-	Not applicable
911401529845	BY698P G5 LED300/NW PSU WB GM	-	Not applicable
911401529945	BY698P G5 LED300/NW PSU NB GM	-	Not applicable
32704800	BY698P G5 LED300/CW PSU WB GM	-	Not applicable
911401530145	BY698P G5 LED300/CW PSU NB GM	-	Not applicable
911401533145	BY698P G5 LED105/NW PSD WB GM	DALI	20%
911401533245	BY698P G5 LED105/NW PSD NB GM	DALI	20%
911401533345	BY698P G5 LED105/CW PSD WB GM	DALI	20%
911401533445	BY698P G5 LED105/CW PSD NB GM	DALI	20%
911401533545	BY698P G5 LED150/NW PSD WB GM	DALI	20%
911401533645	BY698P G5 LED150/NW PSD NB GM	DALI	20%
911401533745	BY698P G5 LED150/CW PSD WB GM	DALI	20%
911401533845	BY698P G5 LED150/CW PSD NB GM	DALI	20%
911401533945	BY698P G5 LED200/NW PSD WB GM	DALI	10%
911401534045	BY698P G5 LED200/NW PSD NB GM	DALI	10%
911401534145	BY698P G5 LED200/CW PSD WB GM	DALI	10%
911401534245	BY698P G5 LED200/CW PSD NB GM	DALI	10%
911401534345	BY698P G5 LED250/NW PSD WB GM	DALI	20%
911401534445	BY698P G5 LED250/NW PSD NB GM	DALI	20%
911401534545	BY698P G5 LED250/CW PSD WB GM	DALI	20%
911401534645	BY698P G5 LED250/CW PSD NB GM	DALI	20%
911401534745	BY698P G5 LED300/NW PSD WB GM	DALI	20%

GreenPerform Highbay G5

Order Code	Full Product Name	Dimmable	Maximum dim level
911401534845	BY698P G5 LED300/NW PSD NB GM	DALI	20%
911401534945	BY698P G5 LED300/CW PSD WB GM	DALI	20%
911401535045	BY698P G5 LED300/CW PSD NB GM	DALI	20%
30783500	BY698P G5 LED105/NW PSU WB GM L3m	-	Not applicable
30784200	BY698P G5 LED105/NW PSU NB GM L3m	-	Not applicable
30785900	BY698P G5 LED105/CW PSU WB GM L3m	-	Not applicable
30786600	BY698P G5 LED105/CW PSU NB GM L3m	-	Not applicable
30787300	BY698P G5 LED150/NW PSU WB GM L3m	-	Not applicable
30788000	BY698P G5 LED150/NW PSU NB GM L3m	-	Not applicable
30789700	BY698P G5 LED150/CW PSU WB GM L3m	-	Not applicable
30790300	BY698P G5 LED150/CW PSU NB GM L3m	-	Not applicable
30791000	BY698P G5 LED200/NW PSU WB GM L3m	-	Not applicable
30792700	BY698P G5 LED200/NW PSU NB GM L3m	-	Not applicable
30793400	BY698P G5 LED200/CW PSU WB GM L3m	-	Not applicable
30794100	BY698P G5 LED200/CW PSU NB GM L3m	-	Not applicable
30795800	BY698P G5 LED250/NW PSU WB GM L3m	-	Not applicable
30796500	BY698P G5 LED250/NW PSU NB GM L3m	-	Not applicable
30797200	BY698P G5 LED250/CW PSU WB GM L3m	-	Not applicable
30798900	BY698P G5 LED250/CW PSU NB GM L3m	-	Not applicable
30799600	BY698P G5 LED300/NW PSU WB GM L3m	-	Not applicable
30800900	BY698P G5 LED300/NW PSU NB GM L3m	-	Not applicable
30801600	BY698P G5 LED300/CW PSU WB GM L3m	-	Not applicable
30802300	BY698P G5 LED300/CW PSU NB GM L3m	-	Not applicable
911401541745	BY690P LED105/NW PSU WB GM	-	Not applicable
911401541845	BY690P LED105/CW PSU WB GM	-	Not applicable
911401541945	BY690P LED150/NW PSU WB GM	-	Not applicable
911401542045	BY690P LED150/CW PSU WB GM	-	Not applicable

Order Code	Full Product Name	Dimmable	Maximum dim level
911401542145	BY690P LED200/NW PSU WB GM	-	Not applicable
911401542245	BY690P LED200/CW PSU WB GM	-	Not applicable
911401542345	BY690P LED250/NW PSU WB GM	-	Not applicable
911401542445	BY690P LED250/CW PSU WB GM	-	Not applicable
911401542545	BY690P LED300/NW PSU WB GM	-	Not applicable
911401542645	BY690P LED300/CW PSU WB GM	-	Not applicable
911401544245	BY698X G5 LED150/NW Connected WB GM	-	3%
911401544345	BY698X G5 LED150/NW Connected NB GM	-	3%
911401544445	BY698X G5 LED150/CW Connected WB GM	-	3%
911401544545	BY698X G5 LED150/CW Connected NB GM	-	3%
911401544645	BY698X G5 LED200/NW Connected WB GM	-	1%
911401544745	BY698X G5 LED200/NW Connected NB GM	-	1%
911401544845	BY698X G5 LED200/CW Connected WB GM	-	1%
911401544945	BY698X G5 LED200/CW Connected NB GM	-	1%
911401545045	BY698X G5 LED250/NW Connected WB GM	-	3%
911401545145	BY698X G5 LED250/NW Connected NB GM	-	3%
911401545245	BY698X G5 LED250/CW Connected WB GM	-	3%
911401545345	BY698X G5 LED250/CW Connected NB GM	-	3%
911401545445	BY698X G5 LED300/NW Connected WB GM	-	3%
911401545545	BY698X G5 LED300/NW Connected NB GM	-	3%
911401545645	BY698X G5 LED300/CW Connected WB GM	-	3%
911401545745	BY698X G5 LED300/CW Connected NB GM	-	3%
30828300	BY698X G5 LED105/NW L1W MW WB GM	Wireless Dim - Do not use with dimmer	0% (digital)
30829000	BY698X G5 LED105/CW L1W MW WB GM	Wireless Dim - Do not use with dimmer	0% (digital)

GreenPerform Highbay G5

Order Code	Full Product Name	Dimmable	Maximum dim level
30830600	BY698X G5 LED150/NW L1W MW WB GM	Wireless Dim - Do not use with dimmer	0% (digital)
30831300	BY698X G5 LED150/CW L1W MW WB GM	Wireless Dim - Do not use with dimmer	0% (digital)
30832000	BY698X G5 LED200/NW L1W MW WB GM	Wireless Dim - Do not use with dimmer	0% (digital)
30833700	BY698X G5 LED200/CW L1W MW WB GM	Wireless Dim - Do not use with dimmer	0% (digital)
30834400	BY698X G5 LED250/NW L1W MW WB GM	Wireless Dim - Do not use with dimmer	0% (digital)
30835100	BY698X G5 LED250/CW L1W MW WB GM	Wireless Dim - Do not use with dimmer	0% (digital)
30836800	BY698X G5 LED300/NW L1W MW WB GM	Wireless Dim - Do not use with dimmer	0% (digital)
30837500	BY698X G5 LED300/CW L1W MW WB GM	Wireless Dim - Do not use with dimmer	0% (digital)
30838200	BY698X G5 LED105/NW L1W MW WB GM L3m	Wireless Dim - Do not use with dimmer	0% (digital)

Order Code	Full Product Name	Dimmable	Maximum dim level
30839900	BY698X G5 LED105/CW L1W MW WB GM L3m	Wireless Dim - Do not use with dimmer	0% (digital)
30840500	BY698X G5 LED150/NW L1W MW WB GM L3m	Wireless Dim - Do not use with dimmer	0% (digital)
30841200	BY698X G5 LED150/CW L1W MW WB GM L3m	Wireless Dim - Do not use with dimmer	0% (digital)
30842900	BY698X G5 LED200/NW L1W MW WB GM L3m	Wireless Dim - Do not use with dimmer	0% (digital)
30843600	BY698X G5 LED200/CW L1W MW WB GM L3m	Wireless Dim - Do not use with dimmer	0% (digital)
30844300	BY698X G5 LED250/NW L1W MW WB GM L3m	Wireless Dim - Do not use with dimmer	0% (digital)
30845000	BY698X G5 LED250/CW L1W MW WB GM L3m	Wireless Dim - Do not use with dimmer	0% (digital)
30846700	BY698X G5 LED300/NW L1W MW WB GM L3m	Wireless Dim - Do not use with dimmer	0% (digital)
30847400	BY698X G5 LED300/CW L1W MW WB GM L3m	Wireless Dim - Do not use with dimmer	0% (digital)

Mechanical and Housing

Order Code	Full Product Name	Mech. impact protection code	Ingress protection code
911401549545	BY698X G5 LED105/NW L1W PIR WB GC	IK03	IP65
911401549645	BY698X G5 LED105/CW L1W PIR WB GC	IK03	IP65
911401549745	BY698X G5 LED150/NW L1W PIR WB GC	IK03	IP65
911401549845	BY698X G5 LED150/CW L1W PIR WB GC	IK03	IP65
911401549945	BY698X G5 LED200/NW L1W PIR WB GC	IK03	IP65
911401550045	BY698X G5 LED200/CW L1W PIR WB GC	IK03	IP65
911401550145	BY698X G5 LED250/NW L1W PIR WB GC	IK03	IP65
911401550245	BY698X G5 LED250/CW L1W PIR WB GC	IK03	IP65
911401550345	BY698X G5 LED300/NW L1W PIR WB GC	IK03	IP65
911401550445	BY698X G5 LED300/CW L1W PIR WB GC	IK03	IP65
30803000	BY698X G5 LED105/NW L1W PIR WB GM	IK03	IP65
30804700	BY698X G5 LED105/CW L1W PIR WB GM	IK03	IP65
30805400	BY698X G5 LED150/NW L1W PIR WB GM	IK03	IP65
30806100	BY698X G5 LED150/CW L1W PIR WB GM	IK03	IP65
30807800	BY698X G5 LED200/NW L1W PIR WB GM	IK03	IP65
30808500	BY698X G5 LED200/CW L1W PIR WB GM	IK03	IP65

Order Code	Full Product Name	Mech. impact protection code	Ingress protection code
30809200	BY698X G5 LED250/NW L1W PIR WB GM	IK03	IP65
30810800	BY698X G5 LED250/CW L1W PIR WB GM	IK03	IP65
30811500	BY698X G5 LED300/NW L1W PIR WB GM	IK03	IP65
30812200	BY698X G5 LED300/CW L1W PIR WB GM	IK03	IP65
30813900	BY698X G5 LED105/840 L1W PIR WB CAU	IK03	IP65
30814600	BY698X G5 LED150/840 L1W PIR WB CAU	IK03	IP65
30815300	BY698X G5 LED200/840 L1W PIR WB CAU	IK03	IP65
30816000	BY698X G5 LED250/840 L1W PIR WB CAU	IK03	IP65
30817700	BY698X G5 LED300/840 L1W PIR WB CAU	IK03	IP65

GreenPerform Highbay G5

Order Code	Full Product Name	Mech. impact protection code	Ingress protection code
30818400	BY698X G5 LED105/NW L1W PIR WB GM L3m	IK03	IP65
30819100	BY698X G5 LED105/CW L1W PIR WB GM L3m	IK03	IP65
30820700	BY698X G5 LED150/NW L1W PIR WB GM L3m	IK03	IP65
30821400	BY698X G5 LED150/CW L1W PIR WB GM L3m	IK03	IP65
30822100	BY698X G5 LED200/NW L1W PIR WB GM L3m	IK03	IP65
30823800	BY698X G5 LED200/CW L1W PIR WB GM L3m	IK03	IP65
30824500	BY698X G5 LED250/NW L1W PIR WB GM L3m	IK03	IP65
30825200	BY698X G5 LED250/CW L1W PIR WB GM L3m	IK03	IP65
30826900	BY698X G5 LED300/NW L1W PIR WB GM L3m	IK03	IP65
30827600	BY698X G5 LED300/CW L1W PIR WB GM L3m	IK03	IP65
99445600	BY698P G5 LED105/NW PSU WB GM	IK08	IP65
911401528345	BY698P G5 LED105/NW PSU NB GM	IK08	IP65
99444900	BY698P G5 LED105/CW PSU WB GM	IK08	IP65
911401528545	BY698P G5 LED105/CW PSU NB GM	IK08	IP65
99446300	BY698P G5 LED150/NW PSU WB GM	IK08	IP65
911401528745	BY698P G5 LED150/NW PSU NB GM	IK08	IP65
99447000	BY698P G5 LED150/CW PSU WB GM	IK08	IP65
911401528945	BY698P G5 LED150/CW PSU NB GM	IK08	IP65
99448700	BY698P G5 LED200/NW PSU WB GM	IK08	IP65
911401529145	BY698P G5 LED200/NW PSU NB GM	IK08	IP65
99449400	BY698P G5 LED200/CW PSU WB GM	IK08	IP65
911401529345	BY698P G5 LED200/CW PSU NB GM	IK08	IP65
911401529445	BY698P G5 LED250/NW PSU WB GM	IK08	IP65
911401529545	BY698P G5 LED250/NW PSU NB GM	IK08	IP65
32705500	BY698P G5 LED250/CW PSU WB GM	IK08	IP65
911401529745	BY698P G5 LED250/CW PSU NB GM	IK08	IP65
911401529845	BY698P G5 LED300/NW PSU WB GM	IK08	IP65
911401529945	BY698P G5 LED300/NW PSU NB GM	IK08	IP65
32704800	BY698P G5 LED300/CW PSU WB GM	IK08	IP65
911401530145	BY698P G5 LED300/CW PSU NB GM	IK08	IP65
911401533145	BY698P G5 LED105/NW PSD WB GM	IK08	IP65
911401533245	BY698P G5 LED105/NW PSD NB GM	IK08	IP65
911401533345	BY698P G5 LED105/CW PSD WB GM	IK08	IP65
911401533445	BY698P G5 LED105/CW PSD NB GM	IK08	IP65
911401533545	BY698P G5 LED150/NW PSD WB GM	IK08	IP65
911401533645	BY698P G5 LED150/NW PSD NB GM	IK08	IP65
911401533745	BY698P G5 LED150/CW PSD WB GM	IK08	IP65
911401533845	BY698P G5 LED150/CW PSD NB GM	IK08	IP65
911401533945	BY698P G5 LED200/NW PSD WB GM	IK08	IP65
911401534045	BY698P G5 LED200/NW PSD NB GM	IK08	IP65

Order Code	Full Product Name	Mech. impact protection code	Ingress protection code
911401534145	BY698P G5 LED200/CW PSD WB GM	IK08	IP65
911401534245	BY698P G5 LED200/CW PSD NB GM	IK08	IP65
911401534345	BY698P G5 LED250/NW PSD WB GM	IK08	IP65
911401534445	BY698P G5 LED250/NW PSD NB GM	IK08	IP65
911401534545	BY698P G5 LED250/CW PSD WB GM	IK08	IP65
911401534645	BY698P G5 LED250/CW PSD NB GM	IK08	IP65
911401534745	BY698P G5 LED300/NW PSD WB GM	IK08	IP65
911401534845	BY698P G5 LED300/NW PSD NB GM	IK08	IP65
911401534945	BY698P G5 LED300/CW PSD WB GM	IK08	IP65
911401535045	BY698P G5 LED300/CW PSD NB GM	IK08	IP65
30783500	BY698P G5 LED105/NW PSU WB GM L3m	IK08	IP65
30784200	BY698P G5 LED105/NW PSU NB GM L3m	IK08	IP65
30785900	BY698P G5 LED105/CW PSU WB GM L3m	IK08	IP65
30786600	BY698P G5 LED105/CW PSU NB GM L3m	IK08	IP65
30787300	BY698P G5 LED150/NW PSU WB GM L3m	IK08	IP65
30788000	BY698P G5 LED150/NW PSU NB GM L3m	IK08	IP65
30789700	BY698P G5 LED150/CW PSU WB GM L3m	IK08	IP65
30790300	BY698P G5 LED150/CW PSU NB GM L3m	IK08	IP65
30791000	BY698P G5 LED200/NW PSU WB GM L3m	IK08	IP65
30792700	BY698P G5 LED200/NW PSU NB GM L3m	IK08	IP65
30793400	BY698P G5 LED200/CW PSU WB GM L3m	IK08	IP65
30794100	BY698P G5 LED200/CW PSU NB GM L3m	IK08	IP65
30795800	BY698P G5 LED250/NW PSU WB GM L3m	IK08	IP65
30796500	BY698P G5 LED250/NW PSU NB GM L3m	IK08	IP65
30797200	BY698P G5 LED250/CW PSU WB GM L3m	IK08	IP65
30798900	BY698P G5 LED250/CW PSU NB GM L3m	IK08	IP65
30799600	BY698P G5 LED300/NW PSU WB GM L3m	IK08	IP65
30800900	BY698P G5 LED300/NW PSU NB GM L3m	IK08	IP65
30801600	BY698P G5 LED300/CW PSU WB GM L3m	IK08	IP65
30802300	BY698P G5 LED300/CW PSU NB GM L3m	IK08	IP65

Order Code	Full Product Name	Mech. impact protection code	Ingress protection code
911401541745	BY690P LED105/NW PSU WB GM	IK08	IP66
911401541845	BY690P LED105/CW PSU WB GM	IK08	IP66
911401541945	BY690P LED150/NW PSU WB GM	IK08	IP66
911401542045	BY690P LED150/CW PSU WB GM	IK08	IP66
911401542145	BY690P LED200/NW PSU WB GM	IK08	IP66
911401542245	BY690P LED200/CW PSU WB GM	IK08	IP66
911401542345	BY690P LED250/NW PSU WB GM	IK08	IP66
911401542445	BY690P LED250/CW PSU WB GM	IK08	IP66
911401542545	BY690P LED300/NW PSU WB GM	IK08	IP66
911401542645	BY690P LED300/CW PSU WB GM	IK08	IP66
911401544245	BY698X G5 LED150/NW Connected WB GM	IK05	IP65
911401544345	BY698X G5 LED150/NW Connected NB GM	IK05	IP65
911401544445	BY698X G5 LED150/CW Connected WB GM	IK05	IP65
911401544545	BY698X G5 LED150/CW Connected NB GM	IK05	IP65
911401544645	BY698X G5 LED200/NW Connected WB GM	IK05	IP65
911401544745	BY698X G5 LED200/NW Connected NB GM	IK05	IP65
911401544845	BY698X G5 LED200/CW Connected WB GM	IK05	IP65
911401544945	BY698X G5 LED200/CW Connected NB GM	IK05	IP65
911401545045	BY698X G5 LED250/NW Connected WB GM	IK05	IP65
911401545145	BY698X G5 LED250/NW Connected NB GM	IK05	IP65
911401545245	BY698X G5 LED250/CW Connected WB GM	IK05	IP65
911401545345	BY698X G5 LED250/CW Connected NB GM	IK05	IP65
911401545445	BY698X G5 LED300/NW Connected WB GM	IK05	IP65
911401545545	BY698X G5 LED300/NW Connected NB GM	IK05	IP65
911401545645	BY698X G5 LED300/CW Connected WB GM	IK05	IP65
911401545745	BY698X G5 LED300/CW Connected NB GM	IK05	IP65

Approval and Application

Order Code	Full Product Name	Ambient temperature range	Glow-wire test
911401549545	BY698X G5 LED105/NW L1W PIR WB GC	-30 to +50 °C	Temperature 750 °C, duration 30 s

Order Code	Full Product Name	Mech. impact protection code	Ingress protection code
30828300	BY698X G5 LED105/NW L1W MW WB GM	IK06	IP65
30829000	BY698X G5 LED105/CW L1W MW WB GM	IK06	IP65
30830600	BY698X G5 LED150/NW L1W MW WB GM	IK06	IP65
30831300	BY698X G5 LED150/CW L1W MW WB GM	IK06	IP65
30832000	BY698X G5 LED200/NW L1W MW WB GM	IK06	IP65
30833700	BY698X G5 LED200/CW L1W MW WB GM	IK06	IP65
30834400	BY698X G5 LED250/NW L1W MW WB GM	IK06	IP65
30835100	BY698X G5 LED250/CW L1W MW WB GM	IK06	IP65
30836800	BY698X G5 LED300/NW L1W MW WB GM	IK06	IP65
30837500	BY698X G5 LED300/CW L1W MW WB GM	IK06	IP65
30838200	BY698X G5 LED105/NW L1W MW WB GM L3m	IK06	IP65
30839900	BY698X G5 LED105/CW L1W MW WB GM L3m	IK06	IP65
30840500	BY698X G5 LED150/NW L1W MW WB GM L3m	IK06	IP65
30841200	BY698X G5 LED150/CW L1W MW WB GM L3m	IK06	IP65
30842900	BY698X G5 LED200/NW L1W MW WB GM L3m	IK06	IP65
30843600	BY698X G5 LED200/CW L1W MW WB GM L3m	IK06	IP65
30844300	BY698X G5 LED250/NW L1W MW WB GM L3m	IK06	IP65
30845000	BY698X G5 LED250/CW L1W MW WB GM L3m	IK06	IP65
30846700	BY698X G5 LED300/NW L1W MW WB GM L3m	IK06	IP65
30847400	BY698X G5 LED300/CW L1W MW WB GM L3m	IK06	IP65

Order Code	Full Product Name	Ambient temperature range	Glow-wire test
911401549645	BY698X G5 LED105/CW L1W PIR WB GC	-30 to +50 °C	Temperature 750 °C, duration 30 s

GreenPerform Highbay G5

Order Code	Full Product Name	Ambient	Glow-wire test
		temperature range	
911401549745	BY698X G5 LED150/NW L1W PIR WB GC	-30 to +50 °C	Temperature 750 °C, duration 30 s
911401549845	BY698X G5 LED150/CW L1W PIR WB GC	-30 to +50 °C	Temperature 750 °C, duration 30 s
911401549945	BY698X G5 LED200/NW L1W PIR WB GC	-30 to +50 °C	Temperature 750 °C, duration 30 s
911401550045	BY698X G5 LED200/CW L1W PIR WB GC	-30 to +50 °C	Temperature 750 °C, duration 30 s
911401550145	BY698X G5 LED250/NW L1W PIR WB GC	-30 to +50 °C	Temperature 750 °C, duration 30 s
911401550245	BY698X G5 LED250/CW L1W PIR WB GC	-30 to +50 °C	Temperature 750 °C, duration 30 s
911401550345	BY698X G5 LED300/NW L1W PIR WB GC	-30 to +50 °C	Temperature 750 °C, duration 30 s
911401550445	BY698X G5 LED300/CW L1W PIR WB GC	-30 to +50 °C	Temperature 750 °C, duration 30 s
30803000	BY698X G5 LED105/NW L1W PIR WB GM	-30 to +50 °C	Temperature 750 °C, duration 30 s
30804700	BY698X G5 LED105/CW L1W PIR WB GM	-30 to +50 °C	Temperature 750 °C, duration 30 s
30805400	BY698X G5 LED150/NW L1W PIR WB GM	-30 to +50 °C	Temperature 750 °C, duration 30 s
30806100	BY698X G5 LED150/CW L1W PIR WB GM	-30 to +50 °C	Temperature 750 °C, duration 30 s
30807800	BY698X G5 LED200/NW L1W PIR WB GM	-30 to +50 °C	Temperature 750 °C, duration 30 s
30808500	BY698X G5 LED200/CW L1W PIR WB GM	-30 to +50 °C	Temperature 750 °C, duration 30 s
30809200	BY698X G5 LED250/NW L1W PIR WB GM	-30 to +50 °C	Temperature 750 °C, duration 30 s
30810800	BY698X G5 LED250/CW L1W PIR WB GM	-30 to +50 °C	Temperature 750 °C, duration 30 s
30811500	BY698X G5 LED300/NW L1W PIR WB GM	-30 to +50 °C	Temperature 750 °C, duration 30 s
30812200	BY698X G5 LED300/CW L1W PIR WB GM	-30 to +50 °C	Temperature 750 °C, duration 30 s
30813900	BY698X G5 LED105/840 L1W PIR WB CAU	-30 to +50 °C	Temperature 750 °C, duration 30 s
30814600	BY698X G5 LED150/840 L1W PIR WB CAU	-30 to +50 °C	Temperature 750 °C, duration 30 s
30815300	BY698X G5 LED200/840 L1W PIR WB CAU	-30 to +50 °C	Temperature 750 °C, duration 30 s
30816000	BY698X G5 LED250/840 L1W PIR WB CAU	-30 to +50 °C	Temperature 750 °C, duration 30 s
30817700	BY698X G5 LED300/840 L1W PIR WB CAU	-30 to +50 °C	Temperature 750 °C, duration 30 s
30818400	BY698X G5 LED105/NW L1W PIR WB GM L3m	-30 to +50 °C	Temperature 750 °C, duration 30 s
30819100	BY698X G5 LED105/CW L1W PIR WB GM L3m	-30 to +50 °C	Temperature 750 °C, duration 30 s

Order Code	Full Product Name	Ambient	Glow-wire test
		temperature range	
30820700	BY698X G5 LED150/NW L1W PIR WB GM L3m	-30 to +50 °C	Temperature 750 °C, duration 30 s
30821400	BY698X G5 LED150/CW L1W PIR WB GM L3m	-30 to +50 °C	Temperature 750 °C, duration 30 s
30822100	BY698X G5 LED200/NW L1W PIR WB GM L3m	-30 to +50 °C	Temperature 750 °C, duration 30 s
30823800	BY698X G5 LED200/CW L1W PIR WB GM L3m	-30 to +50 °C	Temperature 750 °C, duration 30 s
30824500	BY698X G5 LED250/NW L1W PIR WB GM L3m	-30 to +50 °C	Temperature 750 °C, duration 30 s
30825200	BY698X G5 LED250/CW L1W PIR WB GM L3m	-30 to +50 °C	Temperature 750 °C, duration 30 s
30826900	BY698X G5 LED300/NW L1W PIR WB GM L3m	-30 to +50 °C	Temperature 750 °C, duration 30 s
30827600	BY698X G5 LED300/CW L1W PIR WB GM L3m	-30 to +50 °C	Temperature 750 °C, duration 30 s
99445600	BY698P G5 LED105/NW PSU WB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401528345	BY698P G5 LED105/NW PSU NB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
99444900	BY698P G5 LED105/CW PSU WB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401528545	BY698P G5 LED105/CW PSU NB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
99446300	BY698P G5 LED150/NW PSU WB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401528745	BY698P G5 LED150/NW PSU NB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
99447000	BY698P G5 LED150/CW PSU WB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401528945	BY698P G5 LED150/CW PSU NB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
99448700	BY698P G5 LED200/NW PSU WB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401529145	BY698P G5 LED200/NW PSU NB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
99449400	BY698P G5 LED200/CW PSU WB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401529345	BY698P G5 LED200/CW PSU NB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401529445	BY698P G5 LED250/NW PSU WB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401529545	BY698P G5 LED250/NW PSU NB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
32705500	BY698P G5 LED250/CW PSU WB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401529745	BY698P G5 LED250/CW PSU NB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401529845	BY698P G5 LED300/NW PSU WB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s

GreenPerform Highbay G5

Order Code	Full Product Name	Ambient temperature range	Glow-wire test
911401529945	BY698P G5 LED300/NW PSU NB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
32704800	BY698P G5 LED300/CW PSU WB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401530145	BY698P G5 LED300/CW PSU NB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401533145	BY698P G5 LED105/NW PSD WB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401533245	BY698P G5 LED105/NW PSD NB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401533345	BY698P G5 LED105/CW PSD WB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401533445	BY698P G5 LED105/CW PSD NB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401533545	BY698P G5 LED150/NW PSD WB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401533645	BY698P G5 LED150/NW PSD NB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401533745	BY698P G5 LED150/CW PSD WB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401533845	BY698P G5 LED150/CW PSD NB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401533945	BY698P G5 LED200/NW PSD WB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401534045	BY698P G5 LED200/NW PSD NB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401534145	BY698P G5 LED200/CW PSD WB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401534245	BY698P G5 LED200/CW PSD NB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401534345	BY698P G5 LED250/NW PSD WB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401534445	BY698P G5 LED250/NW PSD NB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401534545	BY698P G5 LED250/CW PSD WB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401534645	BY698P G5 LED250/CW PSD NB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401534745	BY698P G5 LED300/NW PSD WB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401534845	BY698P G5 LED300/NW PSD NB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401534945	BY698P G5 LED300/CW PSD WB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401535045	BY698P G5 LED300/CW PSD NB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
30783500	BY698P G5 LED105/NW PSU WB GM L3m	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
30784200	BY698P G5 LED105/NW PSU NB GM L3m	-30 °C to 50 °C	Temperature 650 °C, duration 30 s

Order Code	Full Product Name	Ambient temperature range	Glow-wire test
30785900	BY698P G5 LED105/CW PSU WB GM L3m	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
30786600	BY698P G5 LED105/CW PSU NB GM L3m	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
30787300	BY698P G5 LED150/NW PSU WB GM L3m	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
30788000	BY698P G5 LED150/NW PSU NB GM L3m	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
30789700	BY698P G5 LED150/CW PSU WB GM L3m	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
30790300	BY698P G5 LED150/CW PSU NB GM L3m	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
30791000	BY698P G5 LED200/NW PSU WB GM L3m	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
30792700	BY698P G5 LED200/NW PSU NB GM L3m	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
30793400	BY698P G5 LED200/CW PSU WB GM L3m	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
30794100	BY698P G5 LED200/CW PSU NB GM L3m	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
30795800	BY698P G5 LED250/NW PSU WB GM L3m	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
30796500	BY698P G5 LED250/NW PSU NB GM L3m	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
30797200	BY698P G5 LED250/CW PSU WB GM L3m	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
30798900	BY698P G5 LED250/CW PSU NB GM L3m	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
30799600	BY698P G5 LED300/NW PSU WB GM L3m	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
30800900	BY698P G5 LED300/NW PSU NB GM L3m	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
30801600	BY698P G5 LED300/CW PSU WB GM L3m	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
30802300	BY698P G5 LED300/CW PSU NB GM L3m	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401541745	BY690P LED105/NW PSU WB GM	-40 °C to 50 °C	Temperature 650 °C, duration 30 s
911401541845	BY690P LED105/CW PSU WB GM	-40 °C to 50 °C	Temperature 650 °C, duration 30 s
911401541945	BY690P LED150/NW PSU WB GM	-40 °C to 50 °C	Temperature 650 °C, duration 30 s
911401542045	BY690P LED150/CW PSU WB GM	-40 °C to 50 °C	Temperature 650 °C, duration 30 s
911401542145	BY690P LED200/NW PSU WB GM	-40 °C to 50 °C	Temperature 650 °C, duration 30 s
911401542245	BY690P LED200/CW PSU WB GM	-40 °C to 50 °C	Temperature 650 °C, duration 30 s
911401542345	BY690P LED250/NW PSU WB GM	-35 °C to 50 °C	Temperature 650 °C, duration 30 s

GreenPerform Highbay G5

Order Code	Full Product Name	Ambient	Glow-wire test
		temperature range	
911401542445	BY690P LED250/CW PSU WB GM	-35 °C to 50 °C	Temperature 650 °C, duration 30 s
911401542545	BY690P LED300/NW PSU WB GM	-35 °C to 50 °C	Temperature 650 °C, duration 30 s
911401542645	BY690P LED300/CW PSU WB GM	-35 °C to 50 °C	Temperature 650 °C, duration 30 s
911401544245	BY698X G5 LED150/NW Connected WB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401544345	BY698X G5 LED150/NW Connected NB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401544445	BY698X G5 LED150/CW Connected WB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401544545	BY698X G5 LED150/CW Connected NB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401544645	BY698X G5 LED200/NW Connected WB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401544745	BY698X G5 LED200/NW Connected NB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401544845	BY698X G5 LED200/CW Connected WB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401544945	BY698X G5 LED200/CW Connected NB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401545045	BY698X G5 LED250/NW Connected WB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401545145	BY698X G5 LED250/NW Connected NB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401545245	BY698X G5 LED250/CW Connected WB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401545345	BY698X G5 LED250/CW Connected NB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401545445	BY698X G5 LED300/NW Connected WB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401545545	BY698X G5 LED300/NW Connected NB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401545645	BY698X G5 LED300/CW Connected WB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401545745	BY698X G5 LED300/CW Connected NB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
30828300	BY698X G5 LED105/NW L1W MW WB GM	-30 to +50 °C	Temperature 750 °C, duration 30 s

Order Code	Full Product Name	Ambient	Glow-wire test
		temperature range	
30829000	BY698X G5 LED105/CW L1W MW WB GM	-30 to +50 °C	Temperature 750 °C, duration 30 s
30830600	BY698X G5 LED150/NW L1W MW WB GM	-30 to +50 °C	Temperature 750 °C, duration 30 s
30831300	BY698X G5 LED150/CW L1W MW WB GM	-30 to +50 °C	Temperature 750 °C, duration 30 s
30832000	BY698X G5 LED200/NW L1W MW WB GM	-30 to +50 °C	Temperature 750 °C, duration 30 s
30833700	BY698X G5 LED200/CW L1W MW WB GM	-30 to +50 °C	Temperature 750 °C, duration 30 s
30834400	BY698X G5 LED250/NW L1W MW WB GM	-30 to +50 °C	Temperature 750 °C, duration 30 s
30835100	BY698X G5 LED250/CW L1W MW WB GM	-30 to +50 °C	Temperature 750 °C, duration 30 s
30836800	BY698X G5 LED300/NW L1W MW WB GM	-30 to +50 °C	Temperature 750 °C, duration 30 s
30837500	BY698X G5 LED300/CW L1W MW WB GM	-30 to +50 °C	Temperature 750 °C, duration 30 s
30838200	BY698X G5 LED105/NW L1W MW WB GM L3m	-30 to +50 °C	Temperature 750 °C, duration 30 s
30839900	BY698X G5 LED105/CW L1W MW WB GM L3m	-30 to +50 °C	Temperature 750 °C, duration 30 s
30840500	BY698X G5 LED150/NW L1W MW WB GM L3m	-30 to +50 °C	Temperature 750 °C, duration 30 s
30841200	BY698X G5 LED150/CW L1W MW WB GM L3m	-30 to +50 °C	Temperature 750 °C, duration 30 s
30842900	BY698X G5 LED200/NW L1W MW WB GM L3m	-30 to +50 °C	Temperature 750 °C, duration 30 s
30843600	BY698X G5 LED200/CW L1W MW WB GM L3m	-30 to +50 °C	Temperature 750 °C, duration 30 s
30844300	BY698X G5 LED250/NW L1W MW WB GM L3m	-30 to +50 °C	Temperature 750 °C, duration 30 s
30845000	BY698X G5 LED250/CW L1W MW WB GM L3m	-30 to +50 °C	Temperature 750 °C, duration 30 s
30846700	BY698X G5 LED300/NW L1W MW WB GM L3m	-30 to +50 °C	Temperature 750 °C, duration 30 s
30847400	BY698X G5 LED300/CW L1W MW WB GM L3m	-30 to +50 °C	Temperature 750 °C, duration 30 s

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity	Luminous flux
			tolerance
911401549545	BY698X G5 LED105/NW L1W PIR WB GC	(0.386, 0.384) SDCM<5	+/-10%
911401549645	BY698X G5 LED105/CW L1W PIR WB GC	(0.317, 0.338) SDCM<5	+/-10%
911401549745	BY698X G5 LED150/NW L1W PIR WB GC	(0.386, 0.384) SDCM<5	+/-10%

Order Code	Full Product Name	Initial chromaticity	Luminous flux
			tolerance
911401549845	BY698X G5 LED150/CW L1W PIR WB GC	(0.317, 0.338) SDCM<5	+/-10%
911401549945	BY698X G5 LED200/NW L1W PIR WB GC	(0.386, 0.384) SDCM<5	+/-10%
911401550045	BY698X G5 LED200/CW L1W PIR WB GC	(0.317, 0.338) SDCM<5	+/-10%

GreenPerform Highbay G5

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
911401550145	BY698X G5 LED250/NW L1W PIR WB GC	(0.386, 0.384) SDCM<5	+/-10%
911401550245	BY698X G5 LED250/CW L1W PIR WB GC	(0.317, 0.338) SDCM<5	+/-10%
911401550345	BY698X G5 LED300/NW L1W PIR WB GC	(0.386, 0.384) SDCM<5	+/-10%
911401550445	BY698X G5 LED300/CW L1W PIR WB GC	(0.317, 0.338) SDCM<5	+/-10%
30803000	BY698X G5 LED105/NW L1W PIR WB GM	(0.386, 0.384) SDCM<5	+/-10%
30804700	BY698X G5 LED105/CW L1W PIR WB GM	(0.317, 0.338) SDCM<5	+/-10%
30805400	BY698X G5 LED150/NW L1W PIR WB GM	(0.386, 0.384) SDCM<5	+/-10%
30806100	BY698X G5 LED150/CW L1W PIR WB GM	(0.317, 0.338) SDCM<5	+/-10%
30807800	BY698X G5 LED200/NW L1W PIR WB GM	(0.386, 0.384) SDCM<5	+/-10%
30808500	BY698X G5 LED200/CW L1W PIR WB GM	(0.317, 0.338) SDCM<5	+/-10%
30809200	BY698X G5 LED250/NW L1W PIR WB GM	(0.386, 0.384) SDCM<5	+/-10%
30810800	BY698X G5 LED250/CW L1W PIR WB GM	(0.317, 0.338) SDCM<5	+/-10%
30811500	BY698X G5 LED300/NW L1W PIR WB GM	(0.386, 0.384) SDCM<5	+/-10%
30812200	BY698X G5 LED300/CW L1W PIR WB GM	(0.317, 0.338) SDCM<5	+/-10%
30813900	BY698X G5 LED105/840 L1W PIR WB CAU	-	+/-10%
30814600	BY698X G5 LED150/840 L1W PIR WB CAU	-	+/-10%
30815300	BY698X G5 LED200/840 L1W PIR WB CAU	-	+/-10%
30816000	BY698X G5 LED250/840 L1W PIR WB CAU	-	+/-10%
30817700	BY698X G5 LED300/840 L1W PIR WB CAU	-	+/-10%
30818400	BY698X G5 LED105/NW L1W PIR WB GM L3m	(0.386, 0.384) SDCM<5	+/-10%
30819100	BY698X G5 LED105/CW L1W PIR WB GM L3m	(0.317, 0.338) SDCM<5	+/-10%
30820700	BY698X G5 LED150/NW L1W PIR WB GM L3m	(0.386, 0.384) SDCM<5	+/-10%
30821400	BY698X G5 LED150/CW L1W PIR WB GM L3m	(0.317, 0.338) SDCM<5	+/-10%
30822100	BY698X G5 LED200/NW L1W PIR WB GM L3m	(0.386, 0.384) SDCM<5	+/-10%
30823800	BY698X G5 LED200/CW L1W PIR WB GM L3m	(0.317, 0.338) SDCM<5	+/-10%

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
30824500	BY698X G5 LED250/NW L1W PIR WB GM L3m	(0.386, 0.384) SDCM<5	+/-10%
30825200	BY698X G5 LED250/CW L1W PIR WB GM L3m	(0.317, 0.338) SDCM<5	+/-10%
30826900	BY698X G5 LED300/NW L1W PIR WB GM L3m	(0.386, 0.384) SDCM<5	+/-10%
30827600	BY698X G5 LED300/CW L1W PIR WB GM L3m	(0.317, 0.338) SDCM<5	+/-10%
99445600	BY698P G5 LED105/NW PSU WB GM	(0.386, 0.384) SDCM<5	-10% / +10%
911401528345	BY698P G5 LED105/NW PSU NB GM	(0.386, 0.384) SDCM<5	-10% / +10%
99444900	BY698P G5 LED105/CW PSU WB GM	(0.317, 0.338) SDCM<5	-10% / +10%
911401528545	BY698P G5 LED105/CW PSU NB GM	(0.317, 0.338) SDCM<5	-10% / +10%
99446300	BY698P G5 LED150/NW PSU WB GM	(0.386, 0.384) SDCM<5	-10% / +10%
911401528745	BY698P G5 LED150/NW PSU NB GM	(0.386, 0.384) SDCM<5	-10% / +10%
99447000	BY698P G5 LED150/CW PSU WB GM	(0.317, 0.338) SDCM<5	-10% / +10%
911401528945	BY698P G5 LED150/CW PSU NB GM	(0.317, 0.338) SDCM<5	-10% / +10%
99448700	BY698P G5 LED200/NW PSU WB GM	(0.386, 0.384) SDCM<5	-10% / +10%
911401529145	BY698P G5 LED200/NW PSU NB GM	(0.386, 0.384) SDCM<5	-10% / +10%
99449400	BY698P G5 LED200/CW PSU WB GM	(0.317, 0.338) SDCM<5	-10% / +10%
911401529345	BY698P G5 LED200/CW PSU NB GM	(0.317, 0.338) SDCM<5	-10% / +10%
911401529445	BY698P G5 LED250/NW PSU WB GM	(0.386, 0.384) SDCM<5	-10% / +10%
911401529545	BY698P G5 LED250/NW PSU NB GM	(0.386, 0.384) SDCM<5	-10% / +10%
32705500	BY698P G5 LED250/CW PSU WB GM	(0.317, 0.338) SDCM<5	-10% / +10%
911401529745	BY698P G5 LED250/CW PSU NB GM	(0.317, 0.338) SDCM<5	-10% / +10%
911401529845	BY698P G5 LED300/NW PSU WB GM	(0.386, 0.384) SDCM<5	-10% / +10%
911401529945	BY698P G5 LED300/NW PSU NB GM	(0.386, 0.384) SDCM<5	-10% / +10%
32704800	BY698P G5 LED300/CW PSU WB GM	(0.317, 0.338) SDCM<5	-10% / +10%
911401530145	BY698P G5 LED300/CW PSU NB GM	(0.317, 0.338) SDCM<5	-10% / +10%
911401533145	BY698P G5 LED105/NW PSD WB GM	(0.386, 0.384) SDCM<5	-10% / +10%

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
911401533245	BY698P G5 LED105/NW PSD NB GM	(0.386, 0.384) SDCM<5	-10% / +10%
911401533345	BY698P G5 LED105/CW PSD WB GM	(0.317, 0.338) SDCM<5	-10% / +10%
911401533445	BY698P G5 LED105/CW PSD NB GM	(0.317, 0.338) SDCM<5	-10% / +10%
911401533545	BY698P G5 LED150/NW PSD WB GM	(0.386, 0.384) SDCM<5	-10% / +10%
911401533645	BY698P G5 LED150/NW PSD NB GM	(0.386, 0.384) SDCM<5	-10% / +10%
911401533745	BY698P G5 LED150/CW PSD WB GM	(0.317, 0.338) SDCM<5	-10% / +10%
911401533845	BY698P G5 LED150/CW PSD NB GM	(0.317, 0.338) SDCM<5	-10% / +10%
911401533945	BY698P G5 LED200/NW PSD WB GM	(0.386, 0.384) SDCM<5	-10% / +10%
911401534045	BY698P G5 LED200/NW PSD NB GM	(0.386, 0.384) SDCM<5	-10% / +10%
911401534145	BY698P G5 LED200/CW PSD WB GM	(0.317, 0.338) SDCM<5	-10% / +10%
911401534245	BY698P G5 LED200/CW PSD NB GM	(0.317, 0.338) SDCM<5	-10% / +10%
911401534345	BY698P G5 LED250/NW PSD WB GM	(0.386, 0.384) SDCM<5	-10% / +10%
911401534445	BY698P G5 LED250/NW PSD NB GM	(0.386, 0.384) SDCM<5	-10% / +10%
911401534545	BY698P G5 LED250/CW PSD WB GM	(0.317, 0.338) SDCM<5	-10% / +10%
911401534645	BY698P G5 LED250/CW PSD NB GM	(0.317, 0.338) SDCM<5	-10% / +10%
911401534745	BY698P G5 LED300/NW PSD WB GM	(0.386, 0.384) SDCM<5	-10% / +10%
911401534845	BY698P G5 LED300/NW PSD NB GM	(0.386, 0.384) SDCM<5	-10% / +10%
911401534945	BY698P G5 LED300/CW PSD WB GM	(0.317, 0.338) SDCM<5	-10% / +10%
911401535045	BY698P G5 LED300/CW PSD NB GM	(0.317, 0.338) SDCM<5	-10% / +10%
30783500	BY698P G5 LED105/NW PSU WB GM L3m	(0.386, 0.384) SDCM<5	-10% / +10%
30784200	BY698P G5 LED105/NW PSU NB GM L3m	(0.386, 0.384) SDCM<5	-10% / +10%
30785900	BY698P G5 LED105/CW PSU WB GM L3m	(0.317, 0.338) SDCM<5	-10% / +10%
30786600	BY698P G5 LED105/CW PSU NB GM L3m	(0.317, 0.338) SDCM<5	-10% / +10%
30787300	BY698P G5 LED150/NW PSU WB GM L3m	(0.386, 0.384) SDCM<5	-10% / +10%
30788000	BY698P G5 LED150/NW PSU NB GM L3m	(0.386, 0.384) SDCM<5	-10% / +10%

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
30789700	BY698P G5 LED150/CW PSU WB GM L3m	(0.317, 0.338) SDCM<5	-10% / +10%
30790300	BY698P G5 LED150/CW PSU NB GM L3m	(0.317, 0.338) SDCM<5	-10% / +10%
30791000	BY698P G5 LED200/NW PSU WB GM L3m	(0.386, 0.384) SDCM<5	-10% / +10%
30792700	BY698P G5 LED200/NW PSU NB GM L3m	(0.386, 0.384) SDCM<5	-10% / +10%
30793400	BY698P G5 LED200/CW PSU WB GM L3m	(0.317, 0.338) SDCM<5	-10% / +10%
30794100	BY698P G5 LED200/CW PSU NB GM L3m	(0.317, 0.338) SDCM<5	-10% / +10%
30795800	BY698P G5 LED250/NW PSU WB GM L3m	(0.386, 0.384) SDCM<5	-10% / +10%
30796500	BY698P G5 LED250/NW PSU NB GM L3m	(0.386, 0.384) SDCM<5	-10% / +10%
30797200	BY698P G5 LED250/CW PSU WB GM L3m	(0.317, 0.338) SDCM<5	-10% / +10%
30798900	BY698P G5 LED250/CW PSU NB GM L3m	(0.317, 0.338) SDCM<5	-10% / +10%
30799600	BY698P G5 LED300/NW PSU WB GM L3m	(0.386, 0.384) SDCM<5	-10% / +10%
30800900	BY698P G5 LED300/NW PSU NB GM L3m	(0.386, 0.384) SDCM<5	-10% / +10%
30801600	BY698P G5 LED300/CW PSU WB GM L3m	(0.317, 0.338) SDCM<5	-10% / +10%
30802300	BY698P G5 LED300/CW PSU NB GM L3m	(0.317, 0.338) SDCM<5	-10% / +10%
911401541745	BY690P LED105/NW PSU WB GM	-	-10% / +10%
911401541845	BY690P LED105/CW PSU WB GM	-	-10% / +10%
911401541945	BY690P LED150/NW PSU WB GM	-	-10% / +10%
911401542045	BY690P LED150/CW PSU WB GM	-	-10% / +10%
911401542145	BY690P LED200/NW PSU WB GM	-	-10% / +10%
911401542245	BY690P LED200/CW PSU WB GM	-	-10% / +10%
911401542345	BY690P LED250/NW PSU WB GM	-	-10% / +10%
911401542445	BY690P LED250/CW PSU WB GM	-	-10% / +10%
911401542545	BY690P LED300/NW PSU WB GM	-	-10% / +10%
911401542645	BY690P LED300/CW PSU WB GM	-	-10% / +10%
911401544245	BY698X G5 LED150/NW Connected WB GM	(0.386, 0.384) SDCM<5	-10% / +10%
911401544345	BY698X G5 LED150/NW Connected NB GM	(0.386, 0.384) SDCM<5	-10% / +10%
911401544445	BY698X G5 LED150/CW Connected WB GM	(0.317, 0.338) SDCM<5	-10% / +10%
911401544545	BY698X G5 LED150/CW Connected NB GM	(0.317, 0.338) SDCM<5	-10% / +10%
911401544645	BY698X G5 LED200/NW Connected WB GM	(0.386, 0.384) SDCM<5	-10% / +10%
911401544745	BY698X G5 LED200/NW Connected NB GM	(0.386, 0.384) SDCM<5	-10% / +10%

GreenPerform Highbay G5

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
911401544845	BY698X G5 LED200/CW Connected WB GM	(0.317, 0.338) SDCM<5	-10% / +10%
911401544945	BY698X G5 LED200/CW Connected NB GM	(0.317, 0.338) SDCM<5	-10% / +10%
911401545045	BY698X G5 LED250/NW Connected WB GM	(0.386, 0.384) SDCM<5	-10% / +10%
911401545145	BY698X G5 LED250/NW Connected NB GM	(0.386, 0.384) SDCM<5	-10% / +10%
911401545245	BY698X G5 LED250/CW Connected WB GM	(0.317, 0.338) SDCM<5	-10% / +10%
911401545345	BY698X G5 LED250/CW Connected NB GM	(0.317, 0.338) SDCM<5	-10% / +10%
911401545445	BY698X G5 LED300/NW Connected WB GM	(0.386, 0.384) SDCM<5	-10% / +10%
911401545545	BY698X G5 LED300/NW Connected NB GM	(0.386, 0.384) SDCM<5	-10% / +10%
911401545645	BY698X G5 LED300/CW Connected WB GM	(0.317, 0.338) SDCM<5	-10% / +10%
911401545745	BY698X G5 LED300/CW Connected NB GM	(0.317, 0.338) SDCM<5	-10% / +10%
30828300	BY698X G5 LED105/NW L1W MW WB GM	(0.386, 0.384) SDCM<5	+/-10%
30829000	BY698X G5 LED105/CW L1W MW WB GM	(0.317, 0.338) SDCM<5	+/-10%
30830600	BY698X G5 LED150/NW L1W MW WB GM	(0.386, 0.384) SDCM<5	+/-10%
30831300	BY698X G5 LED150/CW L1W MW WB GM	(0.317, 0.338) SDCM<5	+/-10%
30832000	BY698X G5 LED200/NW L1W MW WB GM	(0.386, 0.384) SDCM<5	+/-10%

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
30833700	BY698X G5 LED200/CW L1W MW WB GM	(0.317, 0.338) SDCM<5	+/-10%
30834400	BY698X G5 LED250/NW L1W MW WB GM	(0.386, 0.384) SDCM<5	+/-10%
30835100	BY698X G5 LED250/CW L1W MW WB GM	(0.317, 0.338) SDCM<5	+/-10%
30836800	BY698X G5 LED300/NW L1W MW WB GM	(0.386, 0.384) SDCM<5	+/-10%
30837500	BY698X G5 LED300/CW L1W MW WB GM	(0.317, 0.338) SDCM<5	+/-10%
30838200	BY698X G5 LED105/NW L1W MW WB GM L3m	(0.386, 0.384) SDCM<5	+/-10%
30839900	BY698X G5 LED105/CW L1W MW WB GM L3m	(0.317, 0.338) SDCM<5	+/-10%
30840500	BY698X G5 LED150/NW L1W MW WB GM L3m	(0.386, 0.384) SDCM<5	+/-10%
30841200	BY698X G5 LED150/CW L1W MW WB GM L3m	(0.317, 0.338) SDCM<5	+/-10%
30842900	BY698X G5 LED200/NW L1W MW WB GM L3m	(0.386, 0.384) SDCM<5	+/-10%
30843600	BY698X G5 LED200/CW L1W MW WB GM L3m	(0.317, 0.338) SDCM<5	+/-10%
30844300	BY698X G5 LED250/NW L1W MW WB GM L3m	(0.386, 0.384) SDCM<5	+/-10%
30845000	BY698X G5 LED250/CW L1W MW WB GM L3m	(0.317, 0.338) SDCM<5	+/-10%
30846700	BY698X G5 LED300/NW L1W MW WB GM L3m	(0.386, 0.384) SDCM<5	+/-10%
30847400	BY698X G5 LED300/CW L1W MW WB GM L3m	(0.317, 0.338) SDCM<5	+/-10%

