



Philips GreenPerform Highbay G5: a versatile LED highbay with optimized performance and future-proof control system

GreenPerform Highbay G5

The GreenPerform Highbay G5 continues the GreenPerform family's enviable reputation for reliable performance. Not only does it deliver leading system efficacy and extended long-term quality, it also promises Unified Glare Rating (UGR) control with compact dimensions. GreenPerform Highbay G5 is also fully compatible with IoT software such as Interact, which is a scalable, future-proof control system. The family also has a series that supports cold room applications with 100% humidity and no condensation. All benefits that make this robust, optimized, and versatile family suitable for almost all industrial applications.

Benefits

- Excellent energy savings
- Long-term quality and reliability
- Visual comfort
- Wide range of applications
- Connected ready for cloud-based IoT software applications

GreenPerform Highbay G5

Features

- 170 lm/W system efficacy
- 75,000 hours L70B50 lifetime @Ta 35°
- Glare control (Narrow Beam), uniform illuminance (Wide Beam)
- Works seamlessly with the Interact IoT software and platform
- Cold room application support

Application



- Manufacturing
- Warehouses
- Logistic center
- Exhibition hall

Specifications


Mounting type	Suspended
	Pipe
	Surface
Operating Temperature range	-30 to +50 °C
Light Source	LED
Mains Voltage	220-240V / 50-60Hz
Mains connection	Flying cable
Mechanical Accessories	Hook for suspension
	Mounting bracket for surface
Dimming	PSU: non-dimmable
	PSD: Dimmable via Dali-broadcasting
	Connected: Wireless control, compatible with SNH210 sensor
Control system input	DALI/Wireless
Integrated sensors	SNH210
Material	Housing: die-cast aluminium
Main color of the luminaire	RAL7012
Flicker / Pst / SVM	PSU: <30%
	PSD/Connected: <3.2%
Luminous flux	10klm-30klm
Power consumption	67W-205W

Luminaire efficacy	Up to 160lm/W
Correlated color	4000K
temperature - CCT	6500K
Color Rendering index - 80	
CRI	
Beam angle	WB: 85°
	NB: 55°
Optical cover/lens material	PC
Optical cover/lens finish	Clear
Protection Class	Class I
IEC61140	
Mechanical impact protection	IK08
Ingress protection	IP65
Driver replaceable	Yes
UGR	WB: 25
	NB: 22
Installation	Suspended
	Pipe
	Surface

Dimensional drawing




Dimensional drawing



GreenPerform Highbay G5

Dimensional drawing



Product details



GreenPerform Highbay G5



GreenPerform Highbay G5

General Information	
Driver included	Yes
Gear	-
Number of gear units	1 unit
Light Technical	
Beam angle of light source	115 degree(s)
Color rendering index (CRI)	80
Number of light sources	1
Operating and Electrical	
Protection class IEC	Safety class I
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Suitable for random switching	Yes
Mechanical and Housing	
Optical cover type	Clear dome
Housing Color	Grey
Approval and Application	
CE mark	Yes
ENEC mark	-
Flammability mark	For mounting on normally flammable surfaces

Light Technical

Order Code	Full Product Name	Correlated Color	Luminous	Luminous	Optic type
		Temperature (Nom)	Efficacy (rated) (Nom)		
911401550545	BY698X G5 LED105/NW L1W PIR WB GM	4000 K	166 lm/W	10,500 lm	Wide beam
911401550645	BY698X G5 LED105/CW L1W PIR WB GM	6500 K	166 lm/W	10,500 lm	Wide beam
911401550745	BY698X G5 LED150/NW L1W PIR WB GM	4000 K	170 lm/W	15,000 lm	Wide beam
911401550845	BY698X G5 LED150/CW L1W PIR WB GM	6500 K	170 lm/W	15,000 lm	Wide beam
911401550945	BY698X G5 LED200/NW L1W PIR WB GM	4000 K	169 lm/W	20,500 lm	Wide beam
911401551045	BY698X G5 LED200/CW L1W PIR WB GM	6500 K	169 lm/W	20,500 lm	Wide beam
911401551145	BY698X G5 LED250/NW L1W PIR WB GM	4000 K	173 lm/W	25,000 lm	Wide beam
911401551245	BY698X G5 LED250/CW L1W PIR WB GM	6500 K	173 lm/W	25,000 lm	Wide beam
911401551345	BY698X G5 LED300/NW L1W PIR WB GM	4000 K	171 lm/W	31,000 lm	Wide beam
911401551445	BY698X G5 LED300/CW L1W PIR WB GM	6500 K	171 lm/W	31,000 lm	Wide beam
911401552045	BY698X G5 LED105/NW L1W PIR WB GM L3m	4000 K	166 lm/W	10,500 lm	Wide beam
911401552145	BY698X G5 LED105/CW L1W PIR WB GM L3m	6500 K	166 lm/W	10,500 lm	Wide beam
911401552245	BY698X G5 LED150/NW L1W PIR WB GM L3m	4000 K	170 lm/W	15,000 lm	Wide beam
911401552345	BY698X G5 LED150/CW L1W PIR WB GM L3m	6500 K	170 lm/W	15,000 lm	Wide beam
911401552445	BY698X G5 LED200/NW L1W PIR WB GM L3m	4000 K	169 lm/W	20,500 lm	Wide beam
911401552545	BY698X G5 LED200/CW L1W PIR WB GM L3m	6500 K	169 lm/W	20,500 lm	Wide beam
911401552645	BY698X G5 LED250/NW L1W PIR WB GM L3m	4000 K	173 lm/W	25,000 lm	Wide beam
911401552745	BY698X G5 LED250/CW L1W PIR WB GM L3m	6500 K	173 lm/W	25,000 lm	Wide beam
911401552845	BY698X G5 LED300/NW L1W PIR WB GM L3m	4000 K	171 lm/W	31,000 lm	Wide beam
911401552945	BY698X G5 LED300/CW L1W PIR WB GM L3m	6500 K	171 lm/W	31,000 lm	Wide beam
911401526245	BY698P G5 LED105/NW PSU WB GC	4000 K	166 lm/W	10,500 lm	Wide beam
911401526345	BY698P G5 LED105/NW PSU NB GC	4000 K	166 lm/W	10,500 lm	Narrow beam
911401526445	BY698P G5 LED105/CW PSU WB GC	6500 K	166 lm/W	10,500 lm	Wide beam
911401526545	BY698P G5 LED105/CW PSU NB GC	6500 K	166 lm/W	10,500 lm	Narrow beam

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
911401526645	BY698P G5 LED150/NW PSU WB GC	4000 K	170 lm/W	15,000 lm	Wide beam
911401526745	BY698P G5 LED150/NW PSU NB GC	4000 K	170 lm/W	15,000 lm	Narrow beam
911401526845	BY698P G5 LED150/CW PSU WB GC	6500 K	170 lm/W	15,000 lm	Wide beam
911401526945	BY698P G5 LED150/CW PSU NB GC	6500 K	170 lm/W	15,000 lm	Narrow beam
911401527045	BY698P G5 LED200/NW PSU WB GC	4000 K	169 lm/W	20,500 lm	Wide beam
911401527145	BY698P G5 LED200/NW PSU NB GC	4000 K	169 lm/W	20,500 lm	Narrow beam
911401527245	BY698P G5 LED200/CW PSU WB GC	6500 K	169 lm/W	20,500 lm	Wide beam
911401527345	BY698P G5 LED200/CW PSU NB GC	6500 K	169 lm/W	20,500 lm	Narrow beam
911401527445	BY698P G5 LED250/NW PSU WB GC	4000 K	173 lm/W	25,000 lm	Wide beam
911401527545	BY698P G5 LED250/NW PSU NB GC	4000 K	173 lm/W	25,000 lm	Narrow beam
911401527645	BY698P G5 LED250/CW PSU WB GC	6500 K	173 lm/W	25,000 lm	Wide beam
911401527745	BY698P G5 LED250/CW PSU NB GC	6500 K	173 lm/W	25,000 lm	Narrow beam
911401527845	BY698P G5 LED300/NW PSU WB GC	4000 K	171 lm/W	31,000 lm	Wide beam
911401527945	BY698P G5 LED300/NW PSU NB GC	4000 K	171 lm/W	31,000 lm	Narrow beam
911401528045	BY698P G5 LED300/CW PSU WB GC	6500 K	171 lm/W	31,000 lm	Wide beam
911401528145	BY698P G5 LED300/CW PSU NB GC	6500 K	171 lm/W	31,000 lm	Narrow beam
911401528245	BY698P G5 LED105/NW PSU WB GM	4000 K	166 lm/W	10,500 lm	Wide beam
911401528345	BY698P G5 LED105/NW PSU NB GM	4000 K	166 lm/W	10,500 lm	Narrow beam
911401528445	BY698P G5 LED105/CW PSU WB GM	6500 K	166 lm/W	10,500 lm	Wide beam
911401528545	BY698P G5 LED105/CW PSU NB GM	6500 K	166 lm/W	10,500 lm	Narrow beam
911401528645	BY698P G5 LED150/NW PSU WB GM	4000 K	170 lm/W	15,000 lm	Wide beam
911401528745	BY698P G5 LED150/NW PSU NB GM	4000 K	170 lm/W	15,000 lm	Narrow beam
911401528845	BY698P G5 LED150/CW PSU WB GM	6500 K	170 lm/W	15,000 lm	Wide beam
911401528945	BY698P G5 LED150/CW PSU NB GM	6500 K	170 lm/W	15,000 lm	Narrow beam
911401529045	BY698P G5 LED200/NW PSU WB GM	4000 K	169 lm/W	20,500 lm	Wide beam

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
911401529145	BY698P G5 LED200/NW PSU NB GM	4000 K	169 lm/W	20,500 lm	Narrow beam
911401529245	BY698P G5 LED200/CW PSU WB GM	6500 K	169 lm/W	20,500 lm	Wide beam
911401529345	BY698P G5 LED200/CW PSU NB GM	6500 K	169 lm/W	20,500 lm	Narrow beam
911401529445	BY698P G5 LED250/NW PSU WB GM	4000 K	173 lm/W	25,000 lm	Wide beam
911401529545	BY698P G5 LED250/NW PSU NB GM	4000 K	173 lm/W	25,000 lm	Narrow beam
911401529645	BY698P G5 LED250/CW PSU WB GM	6500 K	173 lm/W	25,000 lm	Wide beam
911401529745	BY698P G5 LED250/CW PSU NB GM	6500 K	173 lm/W	25,000 lm	Narrow beam
911401529845	BY698P G5 LED300/NW PSU WB GM	4000 K	171 lm/W	31,000 lm	Wide beam
911401529945	BY698P G5 LED300/NW PSU NB GM	4000 K	171 lm/W	31,000 lm	Narrow beam
911401530045	BY698P G5 LED300/CW PSU WB GM	6500 K	171 lm/W	31,000 lm	Wide beam
911401530145	BY698P G5 LED300/CW PSU NB GM	6500 K	171 lm/W	31,000 lm	Narrow beam
911401530245	BY698P G5 LED200/840 PSU WB CAU	6500 K	169 lm/W	20,500 lm	Wide beam
911401530345	BY698P G5 LED250/840 PSU WB CAU	6500 K	173 lm/W	25,000 lm	Wide beam
911401530445	BY698P G5 LED300/840 PSU WB CAU	6500 K	171 lm/W	31,000 lm	Wide beam
911401530545	BY698P G5 LED200/840 PSU WB CAU CL	6500 K	169 lm/W	20,500 lm	Wide beam
911401530645	BY698P G5 LED200/850 PSU WB CAU CL	5000 K	169 lm/W	20,500 lm	Wide beam
911401530745	BY698P G5 LED250/840 PSU WB CAU CL	4000 K	173 lm/W	25,000 lm	Wide beam
911401530845	BY698P G5 LED250/850 PSU WB CAU CL	5000 K	173 lm/W	25,000 lm	Wide beam
911401530945	BY698P G5 LED300/840 PSU WB CAU CL	4000 K	171 lm/W	31,000 lm	Wide beam
911401531045	BY698P G5 LED300/850 PSU WB CAU CL	5000 K	171 lm/W	31,000 lm	Wide beam
911401531145	BY698P G5 LED105/NW PSD WB GC	4000 K	152 lm/W	10,500 lm	Wide beam
911401531245	BY698P G5 LED105/NW PSD NB GC	4000 K	152 lm/W	10,500 lm	Narrow beam
911401531345	BY698P G5 LED105/CW PSD WB GC	6500 K	152 lm/W	10,500 lm	Wide beam
911401531445	BY698P G5 LED105/CW PSD NB GC	6500 K	152 lm/W	10,500 lm	Narrow beam
911401531545	BY698P G5 LED150/NW PSD WB GC	4000 K	161 lm/W	15,000 lm	Wide beam

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
911401531645	BY698P G5 LED150/NW PSD NB GC	4000 K	161 lm/W	15,000 lm	Narrow beam
911401531745	BY698P G5 LED150/CW PSD WB GC	6500 K	161 lm/W	15,000 lm	Wide beam
911401531845	BY698P G5 LED150/CW PSD NB GC	6500 K	161 lm/W	15,000 lm	Narrow beam
911401531945	BY698P G5 LED200/NW PSD WB GC	4000 K	162 lm/W	20,500 lm	Wide beam
911401532045	BY698P G5 LED200/NW PSD NB GC	4000 K	162 lm/W	20,500 lm	Narrow beam
911401532145	BY698P G5 LED200/CW PSD WB GC	6500 K	162 lm/W	20,500 lm	Wide beam
911401532245	BY698P G5 LED200/CW PSD NB GC	6500 K	162 lm/W	20,500 lm	Narrow beam
911401532345	BY698P G5 LED250/NW PSD WB GC	4000 K	162 lm/W	25,000 lm	Wide beam
911401532445	BY698P G5 LED250/NW PSD NB GC	4000 K	162 lm/W	25,000 lm	Narrow beam
911401532545	BY698P G5 LED250/CW PSD WB GC	6500 K	162 lm/W	25,000 lm	Wide beam
911401532645	BY698P G5 LED250/CW PSD NB GC	6500 K	162 lm/W	25,000 lm	Narrow beam
911401532745	BY698P G5 LED300/NW PSD WB GC	4000 K	163 lm/W	31,000 lm	Wide beam
911401532845	BY698P G5 LED300/NW PSD NB GC	4000 K	163 lm/W	31,000 lm	Narrow beam
911401532945	BY698P G5 LED300/CW PSD WB GC	6500 K	163 lm/W	31,000 lm	Wide beam
911401533045	BY698P G5 LED300/CW PSD NB GC	6500 K	163 lm/W	31,000 lm	Narrow beam
911401533145	BY698P G5 LED105/NW PSD WB GM	4000 K	152 lm/W	10,500 lm	Wide beam
911401533245	BY698P G5 LED105/NW PSD NB GM	4000 K	152 lm/W	10,500 lm	Narrow beam
911401533345	BY698P G5 LED105/CW PSD WB GM	6500 K	152 lm/W	10,500 lm	Wide beam
911401533445	BY698P G5 LED105/CW PSD NB GM	6500 K	152 lm/W	10,500 lm	Narrow beam
911401533545	BY698P G5 LED150/NW PSD WB GM	4000 K	161 lm/W	15,000 lm	Wide beam
911401533645	BY698P G5 LED150/NW PSD NB GM	4000 K	161 lm/W	15,000 lm	Narrow beam
911401533745	BY698P G5 LED150/CW PSD WB GM	6500 K	161 lm/W	15,000 lm	Wide beam
911401533845	BY698P G5 LED150/CW PSD NB GM	6500 K	161 lm/W	15,000 lm	Narrow beam
911401533945	BY698P G5 LED200/NW PSD WB GM	4000 K	162 lm/W	20,500 lm	Wide beam
911401534045	BY698P G5 LED200/NW PSD NB GM	4000 K	162 lm/W	20,500 lm	Narrow beam

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
911401534145	BY698P G5 LED200/CW PSD WB GM	6500 K	162 lm/W	20,500 lm	Wide beam
911401534245	BY698P G5 LED200/CW PSD NB GM	6500 K	162 lm/W	20,500 lm	Narrow beam
911401534345	BY698P G5 LED250/NW PSD WB GM	4000 K	162 lm/W	25,000 lm	Wide beam
911401534445	BY698P G5 LED250/NW PSD NB GM	4000 K	162 lm/W	25,000 lm	Narrow beam
911401534545	BY698P G5 LED250/CW PSD WB GM	6500 K	162 lm/W	25,000 lm	Wide beam
911401534645	BY698P G5 LED250/CW PSD NB GM	6500 K	162 lm/W	25,000 lm	Narrow beam
911401534745	BY698P G5 LED300/NW PSD WB GM	4000 K	163 lm/W	31,000 lm	Wide beam
911401534845	BY698P G5 LED300/NW PSD NB GM	4000 K	163 lm/W	31,000 lm	Narrow beam
911401534945	BY698P G5 LED300/CW PSD WB GM	6500 K	163 lm/W	31,000 lm	Wide beam
911401535045	BY698P G5 LED300/CW PSD NB GM	6500 K	163 lm/W	31,000 lm	Narrow beam
911401535145	BY698P G5 LED200/840 PSD WB CAU	4000 K	162 lm/W	20,500 lm	Wide beam
911401535245	BY698P G5 LED250/840 PSD WB CAU	4000 K	162 lm/W	25,000 lm	Wide beam
911401535445	BY698P G5 LED300/840 PSD WB CAU	4000 K	163 lm/W	31,000 lm	Wide beam
911401535545	BY698P G5 LED105/NW PSU WB LA	4000 K	166 lm/W	10,500 lm	Wide beam
911401535645	BY698P G5 LED105/CW PSU WB LA	6500 K	166 lm/W	10,500 lm	Wide beam
911401535745	BY698P G5 LED150/NW PSU WB LA	4000 K	170 lm/W	15,000 lm	Wide beam
911401535845	BY698P G5 LED150/CW PSU WB LA	6500 K	170 lm/W	15,000 lm	Wide beam
911401535945	BY698P G5 LED200/NW PSU WB LA	4000 K	169 lm/W	20,500 lm	Wide beam
911401536045	BY698P G5 LED200/NW PSU NB LA	4000 K	169 lm/W	20,500 lm	Narrow beam
911401536145	BY698P G5 LED200/CW PSU WB LA	6500 K	169 lm/W	20,500 lm	Wide beam
911401536245	BY698P G5 LED200/CW PSU NB LA	6500 K	169 lm/W	20,500 lm	Narrow beam
911401536345	BY698P G5 LED250/NW PSU WB LA	4000 K	173 lm/W	25,000 lm	Wide beam
911401536445	BY698P G5 LED250/NW PSU NB LA	4000 K	173 lm/W	25,000 lm	Narrow beam
911401536545	BY698P G5 LED250/CW PSU WB LA	6500 K	173 lm/W	25,000 lm	Wide beam
911401536645	BY698P G5 LED250/CW PSU NB LA	6500 K	173 lm/W	25,000 lm	Narrow beam

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
911401536745	BY698P G5 LED300/NW PSU WB LA	4000 K	171 lm/W	31,000 lm	Wide beam
911401536845	BY698P G5 LED300/NW PSU NB LA	4000 K	171 lm/W	31,000 lm	Narrow beam
911401536945	BY698P G5 LED300/CW PSU WB LA	6500 K	171 lm/W	31,000 lm	Wide beam
911401537045	BY698P G5 LED300/CW PSU NB LA	6500 K	171 lm/W	31,000 lm	Narrow beam
911401537145	BY698P G5 LED105/NW PSD WB LA	4000 K	152 lm/W	10,500 lm	Wide beam
911401537245	BY698P G5 LED105/CW PSD WB LA	6500 K	152 lm/W	10,500 lm	Wide beam
911401537345	BY698P G5 LED150/NW PSD WB LA	4000 K	161 lm/W	15,000 lm	Wide beam
911401537445	BY698P G5 LED150/CW PSD WB LA	6500 K	161 lm/W	15,000 lm	Wide beam
911401537545	BY698P G5 LED200/NW PSD WB LA	4000 K	162 lm/W	20,500 lm	Wide beam
911401537645	BY698P G5 LED200/NW PSD NB LA	4000 K	162 lm/W	20,500 lm	Narrow beam
911401537745	BY698P G5 LED200/CW PSD WB LA	6500 K	162 lm/W	20,500 lm	Wide beam
911401537845	BY698P G5 LED200/CW PSD NB LA	6500 K	162 lm/W	20,500 lm	Narrow beam
911401537945	BY698P G5 LED250/NW PSD WB LA	4000 K	162 lm/W	25,000 lm	Wide beam
911401538045	BY698P G5 LED250/NW PSD NB LA	4000 K	162 lm/W	25,000 lm	Narrow beam
911401538145	BY698P G5 LED250/CW PSD WB LA	6500 K	162 lm/W	25,000 lm	Wide beam
911401538245	BY698P G5 LED250/CW PSD NB LA	6500 K	162 lm/W	25,000 lm	Narrow beam
911401538345	BY698P G5 LED300/NW PSD WB LA	4000 K	163 lm/W	31,000 lm	Wide beam
911401538445	BY698P G5 LED300/NW PSD NB LA	4000 K	163 lm/W	31,000 lm	Narrow beam
911401538545	BY698P G5 LED300/CW PSD WB LA	6500 K	163 lm/W	31,000 lm	Wide beam
911401538645	BY698P G5 LED300/CW PSD NB LA	6500 K	163 lm/W	31,000 lm	Narrow beam
911401538745	BY698P G5 LED105/NW PSU WB GM L3m	4000 K	166 lm/W	10,500 lm	Wide beam
911401538845	BY698P G5 LED105/NW PSU NB GM L3m	4000 K	166 lm/W	10,500 lm	Narrow beam
911401538945	BY698P G5 LED105/CW PSU WB GM L3m	6500 K	166 lm/W	10,500 lm	Wide beam
911401539045	BY698P G5 LED105/CW PSU NB GM L3m	6500 K	166 lm/W	10,500 lm	Narrow beam
911401539145	BY698P G5 LED150/NW PSU WB GM L3m	4000 K	170 lm/W	15,000 lm	Wide beam

Order Code	Full Product Name	Correlated Color	Luminous	Luminous	Optic type
		Temperature	Efficacy (rated)		
(Nom)	(Nom)	Flux			
911401539245	BY698P G5 LED150/NW PSU NB GM L3m	4000 K	170 lm/W	15,000 lm	Narrow beam
911401539345	BY698P G5 LED150/CW PSU WB GM L3m	6500 K	170 lm/W	15,000 lm	Wide beam
911401539445	BY698P G5 LED150/CW PSU NB GM L3m	6500 K	170 lm/W	15,000 lm	Narrow beam
911401539545	BY698P G5 LED200/NW PSU WB GM L3m	4000 K	169 lm/W	20,500 lm	Wide beam
911401539645	BY698P G5 LED200/NW PSU NB GM L3m	4000 K	169 lm/W	20,500 lm	Narrow beam
911401539745	BY698P G5 LED200/CW PSU WB GM L3m	6500 K	169 lm/W	20,500 lm	Wide beam
911401539845	BY698P G5 LED200/CW PSU NB GM L3m	6500 K	169 lm/W	20,500 lm	Narrow beam
911401539945	BY698P G5 LED250/NW PSU WB GM L3m	4000 K	173 lm/W	25,000 lm	Wide beam
911401540045	BY698P G5 LED250/NW PSU NB GM L3m	4000 K	173 lm/W	25,000 lm	Narrow beam
911401540145	BY698P G5 LED250/CW PSU WB GM L3m	6500 K	173 lm/W	25,000 lm	Wide beam
911401540245	BY698P G5 LED250/CW PSU NB GM L3m	6500 K	173 lm/W	25,000 lm	Narrow beam
911401540345	BY698P G5 LED300/NW PSU WB GM L3m	4000 K	171 lm/W	31,000 lm	Wide beam
911401540445	BY698P G5 LED300/NW PSU NB GM L3m	4000 K	171 lm/W	31,000 lm	Narrow beam
911401540545	BY698P G5 LED300/CW PSU WB GM L3m	6500 K	171 lm/W	31,000 lm	Wide beam
911401540645	BY698P G5 LED300/CW PSU NB GM L3m	6500 K	171 lm/W	31,000 lm	Narrow beam
911401540745	BY690P LED105/NW PSU WB GC	4000 K	166 lm/W	10,500 lm	Wide beam
911401540845	BY690P LED105/CW PSU WB GC	6500 K	166 lm/W	10,500 lm	Wide beam
911401540945	BY690P LED150/NW PSU WB GC	4000 K	170 lm/W	15,000 lm	Wide beam
911401541045	BY690P LED150/CW PSU WB GC	6500 K	170 lm/W	15,000 lm	Wide beam
911401541145	BY690P LED200/NW PSU WB GC	4000 K	181 lm/W	20,000 lm	Wide beam
911401541245	BY690P LED200/CW PSU WB GC	6500 K	181 lm/W	20,000 lm	Wide beam
911401541345	BY690P LED250/NW PSU WB GC	4000 K	177 lm/W	25,500 lm	Wide beam
911401541445	BY690P LED250/CW PSU WB GC	6500 K	177 lm/W	25,500 lm	Wide beam
911401541545	BY690P LED300/NW PSU WB GC	4000 K	176 lm/W	30,000 lm	Wide beam
911401541645	BY690P LED300/CW PSU WB GC	6500 K	176 lm/W	30,000 lm	Wide beam

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
911401541745	BY690P LED105/NW PSU WB GM	4000 K	166 lm/W	10,500 lm	Wide beam
911401541845	BY690P LED105/CW PSU WB GM	6500 K	166 lm/W	10,500 lm	Wide beam
911401541945	BY690P LED150/NW PSU WB GM	4000 K	170 lm/W	15,000 lm	Wide beam
911401542045	BY690P LED150/CW PSU WB GM	6500 K	170 lm/W	15,000 lm	Wide beam
911401542145	BY690P LED200/NW PSU WB GM	4000 K	181 lm/W	20,000 lm	Wide beam
911401542245	BY690P LED200/CW PSU WB GM	6500 K	181 lm/W	20,000 lm	Wide beam
911401542345	BY690P LED250/NW PSU WB GM	4000 K	177 lm/W	25,500 lm	Wide beam
911401542445	BY690P LED250/CW PSU WB GM	6500 K	177 lm/W	25,500 lm	Wide beam
911401542545	BY690P LED300/NW PSU WB GM	4000 K	176 lm/W	30,000 lm	Wide beam
911401542645	BY690P LED300/CW PSU WB GM	6500 K	176 lm/W	30,000 lm	Wide beam
911401580944	BY698P G5 LED105/NW PSU WB TW	4000 K	166 lm/W	10,500 lm	Wide beam
911401581044	BY698P G5 LED105/NW PSU NB TW	4000 K	166 lm/W	10,500 lm	Narrow beam
911401581144	BY698P G5 LED105/CW PSU WB TW	6500 K	166 lm/W	10,500 lm	Wide beam
911401581244	BY698P G5 LED105/CW PSU NB TW	6500 K	166 lm/W	10,500 lm	Narrow beam
911401581344	BY698P G5 LED150/NW PSU WB TW	4000 K	170 lm/W	15,000 lm	Wide beam
911401581444	BY698P G5 LED150/NW PSU NB TW	4000 K	170 lm/W	15,000 lm	Narrow beam
911401581544	BY698P G5 LED150/CW PSU WB TW	6500 K	170 lm/W	15,000 lm	Wide beam
911401581644	BY698P G5 LED150/CW PSU NB TW	6500 K	170 lm/W	15,000 lm	Narrow beam
911401581744	BY698P G5 LED200/NW PSU WB TW	4000 K	169 lm/W	20,500 lm	Wide beam
911401581844	BY698P G5 LED200/NW PSU NB TW	4000 K	169 lm/W	20,500 lm	Narrow beam
911401581944	BY698P G5 LED200/CW PSU WB TW	6500 K	169 lm/W	20,500 lm	Wide beam
911401582044	BY698P G5 LED200/CW PSU NB TW	6500 K	169 lm/W	20,500 lm	Narrow beam
911401582144	BY698P G5 LED250/NW PSU WB TW	4000 K	173 lm/W	25,000 lm	Wide beam
911401582244	BY698P G5 LED250/NW PSU NB TW	4000 K	173 lm/W	25,000 lm	Narrow beam
911401582344	BY698P G5 LED250/CW PSU WB TW	6500 K	173 lm/W	25,000 lm	Wide beam

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
911401582444	BY698P G5 LED250/CW PSU NB TW	6500 K	173 lm/W	25,000 lm	Narrow beam
911401582544	BY698P G5 LED300/NW PSU WB TW	4000 K	171 lm/W	31,000 lm	Wide beam
911401582644	BY698P G5 LED300/NW PSU NB TW	4000 K	171 lm/W	31,000 lm	Narrow beam
911401582744	BY698P G5 LED300/CW PSU WB TW	6500 K	171 lm/W	31,000 lm	Wide beam
911401582844	BY698P G5 LED300/CW PSU NB TW	6500 K	171 lm/W	31,000 lm	Narrow beam
911401543245	BY698X G5 LED150/NW Connected WB GC	4000 K	174 lm/W	15,000 lm	Wide beam
911401543345	BY698X G5 LED150/CW Connected WB GC	6500 K	174 lm/W	15,000 lm	Wide beam
911401543445	BY698X G5 LED200/NW Connected WB GC	4000 K	168 lm/W	20,500 lm	Wide beam
911401543545	BY698X G5 LED200/CW Connected WB GC	6500 K	168 lm/W	20,500 lm	Wide beam
911401543645	BY698X G5 LED250/NW Connected WB GC	4000 K	170 lm/W	25,000 lm	Wide beam
911401543745	BY698X G5 LED250/CW Connected WB GC	6500 K	170 lm/W	25,000 lm	Wide beam
911401543845	BY698X G5 LED300/NW Connected WB GC	4000 K	170 lm/W	31,000 lm	Wide beam
911401543945	BY698X G5 LED300/NW Connected NB GC	4000 K	170 lm/W	31,000 lm	Narrow beam
911401544045	BY698X G5 LED300/CW Connected WB GC	6500 K	170 lm/W	31,000 lm	Wide beam
911401544145	BY698X G5 LED300/CW Connected NB GC	6500 K	170 lm/W	31,000 lm	Narrow beam
911401544245	BY698X G5 LED150/NW Connected WB GM	4000 K	174 lm/W	15,000 lm	Wide beam
911401544345	BY698X G5 LED150/NW Connected NB GM	4000 K	174 lm/W	15,000 lm	Narrow beam
911401544445	BY698X G5 LED150/CW Connected WB GM	6500 K	174 lm/W	15,000 lm	Wide beam
911401544545	BY698X G5 LED150/CW Connected NB GM	6500 K	174 lm/W	15,000 lm	Narrow beam
911401544645	BY698X G5 LED200/NW Connected WB GM	4000 K	168 lm/W	20,500 lm	Wide beam
911401544745	BY698X G5 LED200/NW Connected NB GM	4000 K	168 lm/W	20,500 lm	Narrow beam
911401544845	BY698X G5 LED200/CW Connected WB GM	6500 K	168 lm/W	20,500 lm	Wide beam
911401544945	BY698X G5 LED200/CW Connected NB GM	6500 K	168 lm/W	20,500 lm	Narrow beam
911401545045	BY698X G5 LED250/NW Connected WB GM	4000 K	170 lm/W	25,000 lm	Wide beam
911401545145	BY698X G5 LED250/NW Connected NB GM	4000 K	170 lm/W	25,000 lm	Narrow beam

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
911401545245	BY698X G5 LED250/CW Connected WB GM	6500 K	170 lm/W	25,000 lm	Wide beam
911401545345	BY698X G5 LED250/CW Connected NB GM	6500 K	170 lm/W	25,000 lm	Narrow beam
911401545445	BY698X G5 LED300/NW Connected WB GM	4000 K	170 lm/W	31,000 lm	Wide beam
911401545545	BY698X G5 LED300/NW Connected NB GM	4000 K	170 lm/W	31,000 lm	Narrow beam
911401545645	BY698X G5 LED300/CW Connected WB GM	6500 K	170 lm/W	31,000 lm	Wide beam
911401545745	BY698X G5 LED300/CW Connected NB GM	6500 K	170 lm/W	31,000 lm	Narrow beam
911401545845	BY698X G5 LED200/840 Connected WB CAU	4000 K	168 lm/W	20,500 lm	Wide beam
911401545945	BY698X G5 LED250/840 Connected WB CAU	4000 K	170 lm/W	25,000 lm	Wide beam
911401546045	BY698X G5 LED300/840 Connected WB CAU	4000 K	170 lm/W	31,000 lm	Wide beam
911401546145	BY698X G5 LED150/NW Connected WB LA	4000 K	174 lm/W	15,000 lm	Wide beam
911401546245	BY698X G5 LED150/CW Connected WB LA	6500 K	174 lm/W	15,000 lm	Wide beam
911401546345	BY698X G5 LED200/NW Connected WB LA	4000 K	168 lm/W	20,500 lm	Wide beam
911401546445	BY698X G5 LED200/NW Connected NB LA	4000 K	168 lm/W	20,500 lm	Narrow beam
911401546545	BY698X G5 LED200/CW Connected WB LA	6500 K	168 lm/W	20,500 lm	Wide beam
911401546645	BY698X G5 LED200/CW Connected NB LA	6500 K	168 lm/W	20,500 lm	Narrow beam
911401546745	BY698X G5 LED250/NW Connected WB LA	4000 K	170 lm/W	25,000 lm	Wide beam
911401546845	BY698X G5 LED250/NW Connected NB LA	4000 K	170 lm/W	25,000 lm	Narrow beam
911401546945	BY698X G5 LED250/CW Connected WB LA	6500 K	170 lm/W	25,000 lm	Wide beam
911401547045	BY698X G5 LED250/CW Connected NB LA	6500 K	170 lm/W	25,000 lm	Narrow beam
911401547145	BY698X G5 LED300/NW Connected WB LA	4000 K	170 lm/W	31,000 lm	Wide beam
911401547245	BY698X G5 LED300/NW Connected NB LA	4000 K	170 lm/W	31,000 lm	Narrow beam
911401547345	BY698X G5 LED300/CW Connected WB LA	6500 K	170 lm/W	31,000 lm	Wide beam
911401547445	BY698X G5 LED300/CW Connected NB LA	6500 K	170 lm/W	31,000 lm	Narrow beam
911401547545	BY698X G5 LED105/NW L1W MW WB GM	4000 K	166 lm/W	10,500 lm	Wide beam
911401547645	BY698X G5 LED105/CW L1W MW WB GM	6500 K	166 lm/W	10,500 lm	Wide beam

Order Code	Full Product Name	Correlated Color	Luminous	Luminous	Optic type
		Temperature	Efficacy (rated)		
(Nom)	(Nom)	Flux			
911401547745	BY698X G5 LED150/NW L1W MW WB GM	4000 K	170 lm/W	15,000 lm	Wide beam
911401547845	BY698X G5 LED150/CW L1W MW WB GM	6500 K	170 lm/W	15,000 lm	Wide beam
911401547945	BY698X G5 LED200/NW L1W MW WB GM	4000 K	169 lm/W	20,500 lm	Wide beam
911401548045	BY698X G5 LED200/CW L1W MW WB GM	6500 K	169 lm/W	20,500 lm	Wide beam
911401548145	BY698X G5 LED250/NW L1W MW WB GM	4000 K	173 lm/W	25,000 lm	Wide beam
911401548245	BY698X G5 LED250/CW L1W MW WB GM	6500 K	173 lm/W	25,000 lm	Wide beam
911401548345	BY698X G5 LED300/NW L1W MW WB GM	4000 K	171 lm/W	31,000 lm	Wide beam
911401548445	BY698X G5 LED300/CW L1W MW WB GM	6500 K	171 lm/W	31,000 lm	Wide beam
911401548545	BY698X G5 LED105/NW L1W MW WB GM L3m	4000 K	166 lm/W	10,500 lm	Wide beam
911401548645	BY698X G5 LED105/CW L1W MW WB GM L3m	6500 K	166 lm/W	10,500 lm	Wide beam
911401548745	BY698X G5 LED150/NW L1W MW WB GM L3m	4000 K	170 lm/W	15,000 lm	Wide beam
911401548845	BY698X G5 LED150/CW L1W MW WB GM L3m	6500 K	170 lm/W	15,000 lm	Wide beam
911401548945	BY698X G5 LED200/NW L1W MW WB GM L3m	4000 K	169 lm/W	20,500 lm	Wide beam
911401549045	BY698X G5 LED200/CW L1W MW WB GM L3m	6500 K	169 lm/W	20,500 lm	Wide beam
911401549145	BY698X G5 LED250/NW L1W MW WB GM L3m	4000 K	173 lm/W	25,000 lm	Wide beam
911401549245	BY698X G5 LED250/CW L1W MW WB GM L3m	6500 K	173 lm/W	25,000 lm	Wide beam
911401549345	BY698X G5 LED300/NW L1W MW WB GM L3m	4000 K	171 lm/W	31,000 lm	Wide beam
911401549445	BY698X G5 LED300/CW L1W MW WB GM L3m	6500 K	171 lm/W	31,000 lm	Wide beam

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
911401550545	BY698X G5 LED105/NW L1W PIR WB GM	63 W	911401552045	BY698X G5 LED105/NW L1W PIR WB GM L3m	63 W
911401550645	BY698X G5 LED105/CW L1W PIR WB GM	63 W	911401552145	BY698X G5 LED105/CW L1W PIR WB GM L3m	63 W
911401550745	BY698X G5 LED150/NW L1W PIR WB GM	88 W	911401552245	BY698X G5 LED150/NW L1W PIR WB GM L3m	88 W
911401550845	BY698X G5 LED150/CW L1W PIR WB GM	88 W	911401552345	BY698X G5 LED150/CW L1W PIR WB GM L3m	88 W
911401550945	BY698X G5 LED200/NW L1W PIR WB GM	121 W	911401552445	BY698X G5 LED200/NW L1W PIR WB GM L3m	121 W
911401551045	BY698X G5 LED200/CW L1W PIR WB GM	121 W	911401552545	BY698X G5 LED200/CW L1W PIR WB GM L3m	121 W
911401551145	BY698X G5 LED250/NW L1W PIR WB GM	144 W	911401552645	BY698X G5 LED250/NW L1W PIR WB GM L3m	144 W
911401551245	BY698X G5 LED250/CW L1W PIR WB GM	144 W	911401552745	BY698X G5 LED250/CW L1W PIR WB GM L3m	144 W
911401551345	BY698X G5 LED300/NW L1W PIR WB GM	181 W	911401552845	BY698X G5 LED300/NW L1W PIR WB GM L3m	181 W
911401551445	BY698X G5 LED300/CW L1W PIR WB GM	181 W	911401552945	BY698X G5 LED300/CW L1W PIR WB GM L3m	181 W

GreenPerform Highbay G5

Order Code	Full Product Name	Power Consumption
911401526245	BY698P G5 LED105/NW PSU WB GC	63 W
911401526345	BY698P G5 LED105/NW PSU NB GC	63 W
911401526445	BY698P G5 LED105/CW PSU WB GC	63 W
911401526545	BY698P G5 LED105/CW PSU NB GC	63 W
911401526645	BY698P G5 LED150/NW PSU WB GC	88 W
911401526745	BY698P G5 LED150/NW PSU NB GC	88 W
911401526845	BY698P G5 LED150/CW PSU WB GC	88 W
911401526945	BY698P G5 LED150/CW PSU NB GC	88 W
911401527045	BY698P G5 LED200/NW PSU WB GC	121 W
911401527145	BY698P G5 LED200/NW PSU NB GC	121 W
911401527245	BY698P G5 LED200/CW PSU WB GC	121 W
911401527345	BY698P G5 LED200/CW PSU NB GC	121 W
911401527445	BY698P G5 LED250/NW PSU WB GC	144 W
911401527545	BY698P G5 LED250/NW PSU NB GC	144 W
911401527645	BY698P G5 LED250/CW PSU WB GC	144 W
911401527745	BY698P G5 LED250/CW PSU NB GC	144 W
911401527845	BY698P G5 LED300/NW PSU WB GC	181 W
911401527945	BY698P G5 LED300/NW PSU NB GC	181 W
911401528045	BY698P G5 LED300/CW PSU WB GC	181 W
911401528145	BY698P G5 LED300/CW PSU NB GC	181 W
911401528245	BY698P G5 LED105/NW PSU WB GM	63 W
911401528345	BY698P G5 LED105/NW PSU NB GM	63 W
911401528445	BY698P G5 LED105/CW PSU WB GM	63 W
911401528545	BY698P G5 LED105/CW PSU NB GM	63 W
911401528645	BY698P G5 LED150/NW PSU WB GM	88 W
911401528745	BY698P G5 LED150/NW PSU NB GM	88 W
911401528845	BY698P G5 LED150/CW PSU WB GM	88 W
911401528945	BY698P G5 LED150/CW PSU NB GM	88 W
911401529045	BY698P G5 LED200/NW PSU WB GM	121 W
911401529145	BY698P G5 LED200/NW PSU NB GM	121 W
911401529245	BY698P G5 LED200/CW PSU WB GM	121 W
911401529345	BY698P G5 LED200/CW PSU NB GM	121 W
911401529445	BY698P G5 LED250/NW PSU WB GM	144 W
911401529545	BY698P G5 LED250/NW PSU NB GM	144 W
911401529645	BY698P G5 LED250/CW PSU WB GM	144 W
911401529745	BY698P G5 LED250/CW PSU NB GM	144 W
911401529845	BY698P G5 LED300/NW PSU WB GM	181 W
911401529945	BY698P G5 LED300/NW PSU NB GM	181 W
911401530045	BY698P G5 LED300/CW PSU WB GM	181 W
911401530145	BY698P G5 LED300/CW PSU NB GM	181 W
911401530245	BY698P G5 LED200/840 PSU WB CAU	121 W
911401530345	BY698P G5 LED250/840 PSU WB CAU	144 W
911401530445	BY698P G5 LED300/840 PSU WB CAU	181 W
911401530545	BY698P G5 LED200/840 PSU WB CAU CL	121 W
911401530645	BY698P G5 LED200/850 PSU WB CAU CL	121 W
911401530745	BY698P G5 LED250/840 PSU WB CAU CL	144 W
911401530845	BY698P G5 LED250/850 PSU WB CAU CL	144 W
911401530945	BY698P G5 LED300/840 PSU WB CAU CL	181 W
911401531045	BY698P G5 LED300/850 PSU WB CAU CL	181 W
911401531145	BY698P G5 LED105/NW PSD WB GC	69 W
911401531245	BY698P G5 LED105/NW PSD NB GC	69 W
911401531345	BY698P G5 LED105/CW PSD WB GC	69 W

Order Code	Full Product Name	Power Consumption
911401531445	BY698P G5 LED105/CW PSD NB GC	69 W
911401531545	BY698P G5 LED150/NW PSD WB GC	93 W
911401531645	BY698P G5 LED150/NW PSD NB GC	93 W
911401531745	BY698P G5 LED150/CW PSD WB GC	93 W
911401531845	BY698P G5 LED150/CW PSD NB GC	93 W
911401531945	BY698P G5 LED200/NW PSD WB GC	126 W
911401532045	BY698P G5 LED200/NW PSD NB GC	126 W
911401532145	BY698P G5 LED200/CW PSD WB GC	126 W
911401532245	BY698P G5 LED200/CW PSD NB GC	126 W
911401532345	BY698P G5 LED250/NW PSD WB GC	154 W
911401532445	BY698P G5 LED250/NW PSD NB GC	154 W
911401532545	BY698P G5 LED250/CW PSD WB GC	154 W
911401532645	BY698P G5 LED250/CW PSD NB GC	154 W
911401532745	BY698P G5 LED300/NW PSD WB GC	190 W
911401532845	BY698P G5 LED300/NW PSD NB GC	190 W
911401532945	BY698P G5 LED300/CW PSD WB GC	190 W
911401533045	BY698P G5 LED300/CW PSD NB GC	190 W
911401533145	BY698P G5 LED105/NW PSD WB GM	69 W
911401533245	BY698P G5 LED105/NW PSD NB GM	69 W
911401533345	BY698P G5 LED105/CW PSD WB GM	69 W
911401533445	BY698P G5 LED105/CW PSD NB GM	69 W
911401533545	BY698P G5 LED150/NW PSD WB GM	93 W
911401533645	BY698P G5 LED150/NW PSD NB GM	93 W
911401533745	BY698P G5 LED150/CW PSD WB GM	93 W
911401533845	BY698P G5 LED150/CW PSD NB GM	93 W
911401533945	BY698P G5 LED200/NW PSD WB GM	126 W
911401534045	BY698P G5 LED200/NW PSD NB GM	126 W
911401534145	BY698P G5 LED200/CW PSD WB GM	126 W
911401534245	BY698P G5 LED200/CW PSD NB GM	126 W
911401534345	BY698P G5 LED250/NW PSD WB GM	154 W
911401534445	BY698P G5 LED250/NW PSD NB GM	154 W
911401534545	BY698P G5 LED250/CW PSD WB GM	154 W
911401534645	BY698P G5 LED250/CW PSD NB GM	154 W
911401534745	BY698P G5 LED300/NW PSD WB GM	190 W
911401534845	BY698P G5 LED300/NW PSD NB GM	190 W
911401534945	BY698P G5 LED300/CW PSD WB GM	190 W
911401535045	BY698P G5 LED300/CW PSD NB GM	190 W
911401535145	BY698P G5 LED200/840 PSD WB CAU	126 W
911401535245	BY698P G5 LED250/840 PSD WB CAU	154 W
911401535445	BY698P G5 LED300/840 PSD WB CAU	190 W
911401535545	BY698P G5 LED105/NW PSU WB LA	63 W
911401535645	BY698P G5 LED105/CW PSU WB LA	63 W
911401535745	BY698P G5 LED150/NW PSU WB LA	88 W
911401535845	BY698P G5 LED150/CW PSU WB LA	88 W
911401535945	BY698P G5 LED200/NW PSU WB LA	121 W
911401536045	BY698P G5 LED200/NW PSU NB LA	121 W
911401536145	BY698P G5 LED200/CW PSU WB LA	121 W
911401536245	BY698P G5 LED200/CW PSU NB LA	121 W
911401536345	BY698P G5 LED250/NW PSU WB LA	144 W
911401536445	BY698P G5 LED250/NW PSU NB LA	144 W
911401536545	BY698P G5 LED250/CW PSU WB LA	144 W
911401536645	BY698P G5 LED250/CW PSU NB LA	144 W

Order Code	Full Product Name	Power Consumption
911401536745	BY698P G5 LED300/NW PSU WB LA	181 W
911401536845	BY698P G5 LED300/NW PSU NB LA	181 W
911401536945	BY698P G5 LED300/CW PSU WB LA	181 W
911401537045	BY698P G5 LED300/CW PSU NB LA	181 W
911401537145	BY698P G5 LED105/NW PSD WB LA	69 W
911401537245	BY698P G5 LED105/CW PSD WB LA	69 W
911401537345	BY698P G5 LED150/NW PSD WB LA	93 W
911401537445	BY698P G5 LED150/CW PSD WB LA	93 W
911401537545	BY698P G5 LED200/NW PSD WB LA	126 W
911401537645	BY698P G5 LED200/NW PSD NB LA	126 W
911401537745	BY698P G5 LED200/CW PSD WB LA	126 W
911401537845	BY698P G5 LED200/CW PSD NB LA	126 W
911401537945	BY698P G5 LED250/NW PSD WB LA	154 W
911401538045	BY698P G5 LED250/NW PSD NB LA	154 W
911401538145	BY698P G5 LED250/CW PSD WB LA	154 W
911401538245	BY698P G5 LED250/CW PSD NB LA	154 W
911401538345	BY698P G5 LED300/NW PSD WB LA	190 W
911401538445	BY698P G5 LED300/NW PSD NB LA	190 W
911401538545	BY698P G5 LED300/CW PSD WB LA	190 W
911401538645	BY698P G5 LED300/CW PSD NB LA	190 W
911401538745	BY698P G5 LED105/NW PSU WB GM L3m	63 W
911401538845	BY698P G5 LED105/NW PSU NB GM L3m	63 W
911401538945	BY698P G5 LED105/CW PSU WB GM L3m	63 W
911401539045	BY698P G5 LED105/CW PSU NB GM L3m	63 W
911401539145	BY698P G5 LED150/NW PSU WB GM L3m	88 W
911401539245	BY698P G5 LED150/NW PSU NB GM L3m	88 W
911401539345	BY698P G5 LED150/CW PSU WB GM L3m	88 W
911401539445	BY698P G5 LED150/CW PSU NB GM L3m	88 W
911401539545	BY698P G5 LED200/NW PSU WB GM L3m	121 W
911401539645	BY698P G5 LED200/NW PSU NB GM L3m	121 W
911401539745	BY698P G5 LED200/CW PSU WB GM L3m	121 W
911401539845	BY698P G5 LED200/CW PSU NB GM L3m	121 W
911401539945	BY698P G5 LED250/NW PSU WB GM L3m	144 W
911401540045	BY698P G5 LED250/NW PSU NB GM L3m	144 W
911401540145	BY698P G5 LED250/CW PSU WB GM L3m	144 W
911401540245	BY698P G5 LED250/CW PSU NB GM L3m	144 W
911401540345	BY698P G5 LED300/NW PSU WB GM L3m	181 W
911401540445	BY698P G5 LED300/NW PSU NB GM L3m	181 W
911401540545	BY698P G5 LED300/CW PSU WB GM L3m	181 W
911401540645	BY698P G5 LED300/CW PSU NB GM L3m	181 W
911401540745	BY690P LED105/NW PSU WB GC	63 W
911401540845	BY690P LED105/CW PSU WB GC	63 W
911401540945	BY690P LED150/NW PSU WB GC	88 W
911401541045	BY690P LED150/CW PSU WB GC	88 W
911401541145	BY690P LED200/NW PSU WB GC	110 W
911401541245	BY690P LED200/CW PSU WB GC	110 W
911401541345	BY690P LED250/NW PSU WB GC	144 W
911401541445	BY690P LED250/CW PSU WB GC	144 W
911401541545	BY690P LED300/NW PSU WB GC	170 W
911401541645	BY690P LED300/CW PSU WB GC	170 W
911401541745	BY690P LED105/NW PSU WB GM	63 W
911401541845	BY690P LED105/CW PSU WB GM	63 W

Order Code	Full Product Name	Power Consumption
911401541945	BY690P LED150/NW PSU WB GM	88 W
911401542045	BY690P LED150/CW PSU WB GM	88 W
911401542145	BY690P LED200/NW PSU WB GM	110 W
911401542245	BY690P LED200/CW PSU WB GM	110 W
911401542345	BY690P LED250/NW PSU WB GM	144 W
911401542445	BY690P LED250/CW PSU WB GM	144 W
911401542545	BY690P LED300/NW PSU WB GM	170 W
911401542645	BY690P LED300/CW PSU WB GM	170 W
911401580944	BY698P G5 LED105/NW PSU WB TW	63 W
911401581044	BY698P G5 LED105/NW PSU NB TW	63 W
911401581144	BY698P G5 LED105/CW PSU WB TW	63 W
911401581244	BY698P G5 LED105/CW PSU NB TW	63 W
911401581344	BY698P G5 LED150/NW PSU WB TW	88 W
911401581444	BY698P G5 LED150/NW PSU NB TW	88 W
911401581544	BY698P G5 LED150/CW PSU WB TW	88 W
911401581644	BY698P G5 LED150/CW PSU NB TW	88 W
911401581744	BY698P G5 LED200/NW PSU WB TW	121 W
911401581844	BY698P G5 LED200/NW PSU NB TW	121 W
911401581944	BY698P G5 LED200/CW PSU WB TW	121 W
911401582044	BY698P G5 LED200/CW PSU NB TW	121 W
911401582144	BY698P G5 LED250/NW PSU WB TW	144 W
911401582244	BY698P G5 LED250/NW PSU NB TW	144 W
911401582344	BY698P G5 LED250/CW PSU WB TW	144 W
911401582444	BY698P G5 LED250/CW PSU NB TW	144 W
911401582544	BY698P G5 LED300/NW PSU WB TW	181 W
911401582644	BY698P G5 LED300/NW PSU NB TW	181 W
911401582744	BY698P G5 LED300/CW PSU WB TW	181 W
911401582844	BY698P G5 LED300/CW PSU NB TW	181 W
911401543245	BY698X G5 LED150/NW Connected WB GC	86 W
911401543345	BY698X G5 LED150/CW Connected WB GC	86 W
911401543445	BY698X G5 LED200/NW Connected WB GC	122 W
911401543545	BY698X G5 LED200/CW Connected WB GC	122 W
911401543645	BY698X G5 LED250/NW Connected WB GC	147 W
911401543745	BY698X G5 LED250/CW Connected WB GC	147 W
911401543845	BY698X G5 LED300/NW Connected WB GC	182 W
911401543945	BY698X G5 LED300/NW Connected NB GC	182 W
911401544045	BY698X G5 LED300/CW Connected WB GC	182 W
911401544145	BY698X G5 LED300/CW Connected NB GC	182 W
911401544245	BY698X G5 LED150/NW Connected WB GM	86 W
911401544345	BY698X G5 LED150/NW Connected NB GM	86 W
911401544445	BY698X G5 LED150/CW Connected WB GM	86 W
911401544545	BY698X G5 LED150/CW Connected NB GM	86 W
911401544645	BY698X G5 LED200/NW Connected WB GM	122 W
911401544745	BY698X G5 LED200/NW Connected NB GM	122 W
911401544845	BY698X G5 LED200/CW Connected WB GM	122 W
911401544945	BY698X G5 LED200/CW Connected NB GM	122 W
911401545045	BY698X G5 LED250/NW Connected WB GM	147 W
911401545145	BY698X G5 LED250/NW Connected NB GM	147 W
911401545245	BY698X G5 LED250/CW Connected WB GM	147 W
911401545345	BY698X G5 LED250/CW Connected NB GM	147 W
911401545445	BY698X G5 LED300/NW Connected WB GM	182 W
911401545545	BY698X G5 LED300/NW Connected NB GM	182 W

GreenPerform Highbay G5

Order Code	Full Product Name	Power Consumption
911401545645	BY698X G5 LED300/CW Connected WB GM	182 W
911401545745	BY698X G5 LED300/CW Connected NB GM	182 W
911401545845	BY698X G5 LED200/840 Connected WB CAU	122 W
911401545945	BY698X G5 LED250/840 Connected WB CAU	147 W
911401546045	BY698X G5 LED300/840 Connected WB CAU	182 W
911401546145	BY698X G5 LED150/NW Connected WB LA	86 W
911401546245	BY698X G5 LED150/CW Connected WB LA	86 W
911401546345	BY698X G5 LED200/NW Connected WB LA	122 W
911401546445	BY698X G5 LED200/NW Connected NB LA	122 W
911401546545	BY698X G5 LED200/CW Connected WB LA	122 W
911401546645	BY698X G5 LED200/CW Connected NB LA	122 W
911401546745	BY698X G5 LED250/NW Connected WB LA	147 W
911401546845	BY698X G5 LED250/NW Connected NB LA	147 W
911401546945	BY698X G5 LED250/CW Connected WB LA	147 W
911401547045	BY698X G5 LED250/CW Connected NB LA	147 W
911401547145	BY698X G5 LED300/NW Connected WB LA	182 W
911401547245	BY698X G5 LED300/NW Connected NB LA	182 W
911401547345	BY698X G5 LED300/CW Connected WB LA	182 W
911401547445	BY698X G5 LED300/CW Connected NB LA	182 W
911401547545	BY698X G5 LED105/NW L1W MW WB GM	63 W

Order Code	Full Product Name	Power Consumption
911401547645	BY698X G5 LED105/CW L1W MW WB GM	63 W
911401547745	BY698X G5 LED150/NW L1W MW WB GM	88 W
911401547845	BY698X G5 LED150/CW L1W MW WB GM	88 W
911401547945	BY698X G5 LED200/NW L1W MW WB GM	121 W
911401548045	BY698X G5 LED200/CW L1W MW WB GM	121 W
911401548145	BY698X G5 LED250/NW L1W MW WB GM	144 W
911401548245	BY698X G5 LED250/CW L1W MW WB GM	144 W
911401548345	BY698X G5 LED300/NW L1W MW WB GM	181 W
911401548445	BY698X G5 LED300/CW L1W MW WB GM	181 W
911401548545	BY698X G5 LED105/NW L1W MW WB GM L3m	63 W
911401548645	BY698X G5 LED105/CW L1W MW WB GM L3m	63 W
911401548745	BY698X G5 LED150/NW L1W MW WB GM L3m	88 W
911401548845	BY698X G5 LED150/CW L1W MW WB GM L3m	88 W
911401548945	BY698X G5 LED200/NW L1W MW WB GM L3m	121 W
911401549045	BY698X G5 LED200/CW L1W MW WB GM L3m	121 W
911401549145	BY698X G5 LED250/NW L1W MW WB GM L3m	144 W
911401549245	BY698X G5 LED250/CW L1W MW WB GM L3m	144 W
911401549345	BY698X G5 LED300/NW L1W MW WB GM L3m	181 W
911401549445	BY698X G5 LED300/CW L1W MW WB GM L3m	181 W

Controls and Dimming

Order Code	Full Product Name	Dimmable	Maximum dim level
911401550545	BY698X G5 LED105/NW L1W PIR WB GM	Wireless Dim - Do not use with dimmer	0% (digital)
911401550645	BY698X G5 LED105/CW L1W PIR WB GM	Wireless Dim - Do not use with dimmer	0% (digital)
911401550745	BY698X G5 LED150/NW L1W PIR WB GM	Wireless Dim - Do not use with dimmer	0% (digital)
911401550845	BY698X G5 LED150/CW L1W PIR WB GM	Wireless Dim - Do not use with dimmer	0% (digital)
911401550945	BY698X G5 LED200/NW L1W PIR WB GM	Wireless Dim - Do not use with dimmer	0% (digital)
911401551045	BY698X G5 LED200/CW L1W PIR WB GM	Wireless Dim - Do not use with dimmer	0% (digital)
911401551145	BY698X G5 LED250/NW L1W PIR WB GM	Wireless Dim - Do not use with dimmer	0% (digital)
911401551245	BY698X G5 LED250/CW L1W PIR WB GM	Wireless Dim - Do not use with dimmer	0% (digital)
911401551345	BY698X G5 LED300/NW L1W PIR WB GM	Wireless Dim - Do not use with dimmer	0% (digital)

Order Code	Full Product Name	Dimmable	Maximum dim level
911401551445	BY698X G5 LED300/CW L1W PIR WB GM	Wireless Dim - Do not use with dimmer	0% (digital)
911401552045	BY698X G5 LED105/NW L1W PIR WB GM L3m	Wireless Dim - Do not use with dimmer	0% (digital)
911401552145	BY698X G5 LED105/CW L1W PIR WB GM L3m	Wireless Dim - Do not use with dimmer	0% (digital)
911401552245	BY698X G5 LED150/NW L1W PIR WB GM L3m	Wireless Dim - Do not use with dimmer	0% (digital)
911401552345	BY698X G5 LED150/CW L1W PIR WB GM L3m	Wireless Dim - Do not use with dimmer	0% (digital)
911401552445	BY698X G5 LED200/NW L1W PIR WB GM L3m	Wireless Dim - Do not use with dimmer	0% (digital)
911401552545	BY698X G5 LED200/CW L1W PIR WB GM L3m	Wireless Dim - Do not use with dimmer	0% (digital)
911401552645	BY698X G5 LED250/NW L1W PIR WB GM L3m	Wireless Dim - Do not use with dimmer	0% (digital)
911401552745	BY698X G5 LED250/CW L1W PIR WB GM L3m	Wireless Dim - Do not use with dimmer	0% (digital)

GreenPerform Highbay G5

Order Code	Full Product Name	Dimmable	Maximum dim level
911401552845	BY698X G5 LED300/NW L1W PIR WB GM L3m	Wireless Dim - Do not use with dimmer	0% (digital)
911401552945	BY698X G5 LED300/CW L1W PIR WB GM L3m	Wireless Dim - Do not use with dimmer	0% (digital)
911401526245	BY698P G5 LED105/NW PSU WB GC	-	Not applicable
911401526345	BY698P G5 LED105/NW PSU NB GC	-	Not applicable
911401526445	BY698P G5 LED105/CW PSU WB GC	-	Not applicable
911401526545	BY698P G5 LED105/CW PSU NB GC	-	Not applicable
911401526645	BY698P G5 LED150/NW PSU WB GC	-	Not applicable
911401526745	BY698P G5 LED150/NW PSU NB GC	-	Not applicable
911401526845	BY698P G5 LED150/CW PSU WB GC	-	Not applicable
911401526945	BY698P G5 LED150/CW PSU NB GC	-	Not applicable
911401527045	BY698P G5 LED200/NW PSU WB GC	-	Not applicable
911401527145	BY698P G5 LED200/NW PSU NB GC	-	Not applicable
911401527245	BY698P G5 LED200/CW PSU WB GC	-	Not applicable
911401527345	BY698P G5 LED200/CW PSU NB GC	-	Not applicable
911401527445	BY698P G5 LED250/NW PSU WB GC	-	Not applicable
911401527545	BY698P G5 LED250/NW PSU NB GC	-	Not applicable
911401527645	BY698P G5 LED250/CW PSU WB GC	-	Not applicable
911401527745	BY698P G5 LED250/CW PSU NB GC	-	Not applicable
911401527845	BY698P G5 LED300/NW PSU WB GC	-	Not applicable
911401527945	BY698P G5 LED300/NW PSU NB GC	-	Not applicable
911401528045	BY698P G5 LED300/CW PSU WB GC	-	Not applicable
911401528145	BY698P G5 LED300/CW PSU NB GC	-	Not applicable
911401528245	BY698P G5 LED105/NW PSU WB GM	-	Not applicable
911401528345	BY698P G5 LED105/NW PSU NB GM	-	Not applicable
911401528445	BY698P G5 LED105/CW PSU WB GM	-	Not applicable

Order Code	Full Product Name	Dimmable	Maximum dim level
911401528545	BY698P G5 LED105/CW PSU NB GM	-	Not applicable
911401528645	BY698P G5 LED150/NW PSU WB GM	-	Not applicable
911401528745	BY698P G5 LED150/NW PSU NB GM	-	Not applicable
911401528845	BY698P G5 LED150/CW PSU WB GM	-	Not applicable
911401528945	BY698P G5 LED150/CW PSU NB GM	-	Not applicable
911401529045	BY698P G5 LED200/NW PSU WB GM	-	Not applicable
911401529145	BY698P G5 LED200/NW PSU NB GM	-	Not applicable
911401529245	BY698P G5 LED200/CW PSU WB GM	-	Not applicable
911401529345	BY698P G5 LED200/CW PSU NB GM	-	Not applicable
911401529445	BY698P G5 LED250/NW PSU WB GM	-	Not applicable
911401529545	BY698P G5 LED250/NW PSU NB GM	-	Not applicable
911401529645	BY698P G5 LED250/CW PSU WB GM	-	Not applicable
911401529745	BY698P G5 LED250/CW PSU NB GM	-	Not applicable
911401529845	BY698P G5 LED300/NW PSU WB GM	-	Not applicable
911401529945	BY698P G5 LED300/NW PSU NB GM	-	Not applicable
911401530045	BY698P G5 LED300/CW PSU WB GM	-	Not applicable
911401530145	BY698P G5 LED300/CW PSU NB GM	-	Not applicable
911401530245	BY698P G5 LED200/840 PSU WB CAU	-	Not applicable
911401530345	BY698P G5 LED250/840 PSU WB CAU	-	Not applicable
911401530445	BY698P G5 LED300/840 PSU WB CAU	-	Not applicable
911401530545	BY698P G5 LED200/840 PSU WB CAU CL	-	Not applicable
911401530645	BY698P G5 LED200/850 PSU WB CAU CL	-	Not applicable
911401530745	BY698P G5 LED250/840 PSU WB CAU CL	-	Not applicable
911401530845	BY698P G5 LED250/850 PSU WB CAU CL	-	Not applicable
911401530945	BY698P G5 LED300/840 PSU WB CAU CL	-	Not applicable

GreenPerform Highbay G5

Order Code	Full Product Name	Dimmable	Maximum dim level
911401531045	BY698P G5 LED300/850 PSU WB CAU CL	-	Not applicable
911401531145	BY698P G5 LED105/NW PSD WB GC	DALI	20%
911401531245	BY698P G5 LED105/NW PSD NB GC	DALI	20%
911401531345	BY698P G5 LED105/CW PSD WB GC	DALI	20%
911401531445	BY698P G5 LED105/CW PSD NB GC	DALI	20%
911401531545	BY698P G5 LED150/NW PSD WB GC	DALI	20%
911401531645	BY698P G5 LED150/NW PSD NB GC	DALI	20%
911401531745	BY698P G5 LED150/CW PSD WB GC	DALI	20%
911401531845	BY698P G5 LED150/CW PSD NB GC	DALI	20%
911401531945	BY698P G5 LED200/NW PSD WB GC	DALI	10%
911401532045	BY698P G5 LED200/NW PSD NB GC	DALI	10%
911401532145	BY698P G5 LED200/CW PSD WB GC	DALI	10%
911401532245	BY698P G5 LED200/CW PSD NB GC	DALI	10%
911401532345	BY698P G5 LED250/NW PSD WB GC	DALI	20%
911401532445	BY698P G5 LED250/NW PSD NB GC	DALI	20%
911401532545	BY698P G5 LED250/CW PSD WB GC	DALI	20%
911401532645	BY698P G5 LED250/CW PSD NB GC	DALI	20%
911401532745	BY698P G5 LED300/NW PSD WB GC	DALI	20%
911401532845	BY698P G5 LED300/NW PSD NB GC	DALI	20%
911401532945	BY698P G5 LED300/CW PSD WB GC	DALI	20%
911401533045	BY698P G5 LED300/CW PSD NB GC	DALI	20%
911401533145	BY698P G5 LED105/NW PSD WB GM	DALI	20%
911401533245	BY698P G5 LED105/NW PSD NB GM	DALI	20%
911401533345	BY698P G5 LED105/CW PSD WB GM	DALI	20%
911401533445	BY698P G5 LED105/CW PSD NB GM	DALI	20%
911401533545	BY698P G5 LED150/NW PSD WB GM	DALI	20%

Order Code	Full Product Name	Dimmable	Maximum dim level
911401533645	BY698P G5 LED150/NW PSD NB GM	DALI	20%
911401533745	BY698P G5 LED150/CW PSD WB GM	DALI	20%
911401533845	BY698P G5 LED150/CW PSD NB GM	DALI	20%
911401533945	BY698P G5 LED200/NW PSD WB GM	DALI	10%
911401534045	BY698P G5 LED200/NW PSD NB GM	DALI	10%
911401534145	BY698P G5 LED200/CW PSD WB GM	DALI	10%
911401534245	BY698P G5 LED200/CW PSD NB GM	DALI	10%
911401534345	BY698P G5 LED250/NW PSD WB GM	DALI	20%
911401534445	BY698P G5 LED250/NW PSD NB GM	DALI	20%
911401534545	BY698P G5 LED250/CW PSD WB GM	DALI	20%
911401534645	BY698P G5 LED250/CW PSD NB GM	DALI	20%
911401534745	BY698P G5 LED300/NW PSD WB GM	DALI	20%
911401534845	BY698P G5 LED300/NW PSD NB GM	DALI	20%
911401534945	BY698P G5 LED300/CW PSD WB GM	DALI	20%
911401535045	BY698P G5 LED300/CW PSD NB GM	DALI	20%
911401535145	BY698P G5 LED200/840 PSD WB CAU	DALI	10%
911401535245	BY698P G5 LED250/840 PSD WB CAU	DALI	20%
911401535445	BY698P G5 LED300/840 PSD WB CAU	DALI	20%
911401535545	BY698P G5 LED105/NW PSU WB LA	-	Not applicable
911401535645	BY698P G5 LED105/CW PSU WB LA	-	Not applicable
911401535745	BY698P G5 LED150/NW PSU WB LA	-	Not applicable
911401535845	BY698P G5 LED150/CW PSU WB LA	-	Not applicable
911401535945	BY698P G5 LED200/NW PSU WB LA	-	Not applicable
911401536045	BY698P G5 LED200/NW PSU NB LA	-	Not applicable
911401536145	BY698P G5 LED200/CW PSU WB LA	-	Not applicable

GreenPerform Highbay G5

Order Code	Full Product Name	Dimmable	Maximum dim level
911401536245	BY698P G5 LED200/CW PSU NB LA	-	Not applicable
911401536345	BY698P G5 LED250/NW PSU WB LA	-	Not applicable
911401536445	BY698P G5 LED250/NW PSU NB LA	-	Not applicable
911401536545	BY698P G5 LED250/CW PSU WB LA	-	Not applicable
911401536645	BY698P G5 LED250/CW PSU NB LA	-	Not applicable
911401536745	BY698P G5 LED300/NW PSU WB LA	-	Not applicable
911401536845	BY698P G5 LED300/NW PSU NB LA	-	Not applicable
911401536945	BY698P G5 LED300/CW PSU WB LA	-	Not applicable
911401537045	BY698P G5 LED300/CW PSU NB LA	-	Not applicable
911401537145	BY698P G5 LED105/NW PSD WB LA	DALI	20%
911401537245	BY698P G5 LED105/CW PSD WB LA	DALI	20%
911401537345	BY698P G5 LED150/NW PSD WB LA	DALI	20%
911401537445	BY698P G5 LED150/CW PSD WB LA	DALI	20%
911401537545	BY698P G5 LED200/NW PSD WB LA	DALI	10%
911401537645	BY698P G5 LED200/NW PSD NB LA	DALI	10%
911401537745	BY698P G5 LED200/CW PSD WB LA	DALI	10%
911401537845	BY698P G5 LED200/CW PSD NB LA	DALI	10%
911401537945	BY698P G5 LED250/NW PSD WB LA	DALI	20%
911401538045	BY698P G5 LED250/NW PSD NB LA	DALI	20%
911401538145	BY698P G5 LED250/CW PSD WB LA	DALI	20%
911401538245	BY698P G5 LED250/CW PSD NB LA	DALI	20%
911401538345	BY698P G5 LED300/NW PSD WB LA	DALI	20%
911401538445	BY698P G5 LED300/NW PSD NB LA	DALI	20%
911401538545	BY698P G5 LED300/CW PSD WB LA	DALI	20%
911401538645	BY698P G5 LED300/CW PSD NB LA	DALI	20%
911401538745	BY698P G5 LED105/NW PSU WB GM L3m	-	Not applicable

Order Code	Full Product Name	Dimmable	Maximum dim level
911401538845	BY698P G5 LED105/NW PSU NB GM L3m	-	Not applicable
911401538945	BY698P G5 LED105/CW PSU WB GM L3m	-	Not applicable
911401539045	BY698P G5 LED105/CW PSU NB GM L3m	-	Not applicable
911401539145	BY698P G5 LED150/NW PSU WB GM L3m	-	Not applicable
911401539245	BY698P G5 LED150/NW PSU NB GM L3m	-	Not applicable
911401539345	BY698P G5 LED150/CW PSU WB GM L3m	-	Not applicable
911401539445	BY698P G5 LED150/CW PSU NB GM L3m	-	Not applicable
911401539545	BY698P G5 LED200/NW PSU WB GM L3m	-	Not applicable
911401539645	BY698P G5 LED200/NW PSU NB GM L3m	-	Not applicable
911401539745	BY698P G5 LED200/CW PSU WB GM L3m	-	Not applicable
911401539845	BY698P G5 LED200/CW PSU NB GM L3m	-	Not applicable
911401539945	BY698P G5 LED250/NW PSU WB GM L3m	-	Not applicable
911401540045	BY698P G5 LED250/NW PSU NB GM L3m	-	Not applicable
911401540145	BY698P G5 LED250/CW PSU WB GM L3m	-	Not applicable
911401540245	BY698P G5 LED250/CW PSU NB GM L3m	-	Not applicable
911401540345	BY698P G5 LED300/NW PSU WB GM L3m	-	Not applicable
911401540445	BY698P G5 LED300/NW PSU NB GM L3m	-	Not applicable
911401540545	BY698P G5 LED300/CW PSU WB GM L3m	-	Not applicable
911401540645	BY698P G5 LED300/CW PSU NB GM L3m	-	Not applicable
911401540745	BY690P LED105/NW PSU WB GC	-	Not applicable
911401540845	BY690P LED105/CW PSU WB GC	-	Not applicable
911401540945	BY690P LED150/NW PSU WB GC	-	Not applicable
911401541045	BY690P LED150/CW PSU WB GC	-	Not applicable
911401541145	BY690P LED200/NW PSU WB GC	-	Not applicable
911401541245	BY690P LED200/CW PSU WB GC	-	Not applicable
911401541345	BY690P LED250/NW PSU WB GC	-	Not applicable
911401541445	BY690P LED250/CW PSU WB GC	-	Not applicable
911401541545	BY690P LED300/NW PSU WB GC	-	Not applicable
911401541645	BY690P LED300/CW PSU WB GC	-	Not applicable
911401541745	BY690P LED105/NW PSU WB GM	-	Not applicable
911401541845	BY690P LED105/CW PSU WB GM	-	Not applicable
911401541945	BY690P LED150/NW PSU WB GM	-	Not applicable

GreenPerform Highbay G5

Order Code	Full Product Name	Dimmable	Maximum dim level
911401542045	BY690P LED150/CW PSU WB GM	-	Not applicable
911401542145	BY690P LED200/NW PSU WB GM	-	Not applicable
911401542245	BY690P LED200/CW PSU WB GM	-	Not applicable
911401542345	BY690P LED250/NW PSU WB GM	-	Not applicable
911401542445	BY690P LED250/CW PSU WB GM	-	Not applicable
911401542545	BY690P LED300/NW PSU WB GM	-	Not applicable
911401542645	BY690P LED300/CW PSU WB GM	-	Not applicable
91140158094	BY698P G5 LED105/NW PSU WB	-	Not applicable
4	TW		
911401581044	BY698P G5 LED105/NW PSU NB	-	Not applicable
	TW		
911401581144	BY698P G5 LED105/CW PSU WB	-	Not applicable
	TW		
911401581244	BY698P G5 LED105/CW PSU NB	-	Not applicable
	TW		
911401581344	BY698P G5 LED150/NW PSU WB	-	Not applicable
	TW		
911401581444	BY698P G5 LED150/NW PSU NB	-	Not applicable
	TW		
911401581544	BY698P G5 LED150/CW PSU WB	-	Not applicable
	TW		
911401581644	BY698P G5 LED150/CW PSU NB	-	Not applicable
	TW		
911401581744	BY698P G5 LED200/NW PSU WB	-	Not applicable
	TW		
911401581844	BY698P G5 LED200/NW PSU NB	-	Not applicable
	TW		
911401581944	BY698P G5 LED200/CW PSU WB	-	Not applicable
	TW		
911401582044	BY698P G5 LED200/CW PSU NB	-	Not applicable
	TW		
911401582144	BY698P G5 LED250/NW PSU WB	-	Not applicable
	TW		
911401582244	BY698P G5 LED250/NW PSU NB	-	Not applicable
	TW		
911401582344	BY698P G5 LED250/CW PSU WB	-	Not applicable
	TW		
911401582444	BY698P G5 LED250/CW PSU NB	-	Not applicable
	TW		
911401582544	BY698P G5 LED300/NW PSU WB	-	Not applicable
	TW		
911401582644	BY698P G5 LED300/NW PSU NB	-	Not applicable
	TW		
911401582744	BY698P G5 LED300/CW PSU WB	-	Not applicable
	TW		
911401582844	BY698P G5 LED300/CW PSU NB	-	Not applicable
	TW		
911401543245	BY698X G5 LED150/NW Connected	-	3%
	WB GC		
911401543345	BY698X G5 LED150/CW Connected	-	3%
	WB GC		

Order Code	Full Product Name	Dimmable	Maximum dim level
911401543445	BY698X G5 LED200/NW	-	1%
	Connected WB GC		
911401543545	BY698X G5 LED200/CW	-	1%
	Connected WB GC		
911401543645	BY698X G5 LED250/NW	-	3%
	Connected WB GC		
911401543745	BY698X G5 LED250/CW Connected	-	3%
	WB GC		
911401543845	BY698X G5 LED300/NW	-	3%
	Connected WB GC		
911401543945	BY698X G5 LED300/NW	-	3%
	Connected NB GC		
911401544045	BY698X G5 LED300/CW	-	3%
	Connected WB GC		
911401544145	BY698X G5 LED300/CW	-	3%
	Connected NB GC		
911401544245	BY698X G5 LED150/NW Connected	-	3%
	WB GM		
911401544345	BY698X G5 LED150/NW Connected	-	3%
	NB GM		
911401544445	BY698X G5 LED150/CW Connected	-	3%
	WB GM		
911401544545	BY698X G5 LED150/CW Connected	-	3%
	NB GM		
911401544645	BY698X G5 LED200/NW	-	1%
	Connected WB GM		
911401544745	BY698X G5 LED200/NW	-	1%
	Connected NB GM		
911401544845	BY698X G5 LED200/CW	-	1%
	Connected WB GM		
911401544945	BY698X G5 LED200/CW	-	1%
	Connected NB GM		
911401545045	BY698X G5 LED250/NW	-	3%
	Connected WB GM		
911401545145	BY698X G5 LED250/NW	-	3%
	Connected NB GM		
911401545245	BY698X G5 LED250/CW Connected	-	3%
	WB GM		
911401545345	BY698X G5 LED250/CW Connected	-	3%
	NB GM		
911401545445	BY698X G5 LED300/NW	-	3%
	Connected WB GM		
911401545545	BY698X G5 LED300/NW	-	3%
	Connected NB GM		
911401545645	BY698X G5 LED300/CW	-	3%
	Connected WB GM		
911401545745	BY698X G5 LED300/CW	-	3%
	Connected NB GM		
911401545845	BY698X G5 LED200/840	-	3%
	Connected WB CAU		

GreenPerform Highbay G5

Order Code	Full Product Name	Dimmable	Maximum dim level
911401545945	BY698X G5 LED250/840 Connected WB CAU	-	3%
911401546045	BY698X G5 LED300/840 Connected WB CAU	-	3%
911401546145	BY698X G5 LED150/NW Connected WB LA	-	3%
911401546245	BY698X G5 LED150/CW Connected WB LA	-	3%
911401546345	BY698X G5 LED200/NW Connected WB LA	-	1%
911401546445	BY698X G5 LED200/NW Connected NB LA	-	1%
911401546545	BY698X G5 LED200/CW Connected WB LA	-	1%
911401546645	BY698X G5 LED200/CW Connected NB LA	-	1%
911401546745	BY698X G5 LED250/NW Connected WB LA	-	3%
911401546845	BY698X G5 LED250/NW Connected NB LA	-	3%
911401546945	BY698X G5 LED250/CW Connected WB LA	-	3%
911401547045	BY698X G5 LED250/CW Connected NB LA	-	3%
911401547145	BY698X G5 LED300/NW Connected WB LA	-	3%
911401547245	BY698X G5 LED300/NW Connected NB LA	-	3%
911401547345	BY698X G5 LED300/CW Connected WB LA	-	3%
911401547445	BY698X G5 LED300/CW Connected NB LA	-	3%
911401547545	BY698X G5 LED105/NW L1W MW WB GM	Wireless Dim - Do not use with dimmer	0% (digital)
911401547645	BY698X G5 LED105/CW L1W MW WB GM	Wireless Dim - Do not use with dimmer	0% (digital)
911401547745	BY698X G5 LED150/NW L1W MW WB GM	Wireless Dim - Do not use with dimmer	0% (digital)
911401547845	BY698X G5 LED150/CW L1W MW WB GM	Wireless Dim - Do not use with dimmer	0% (digital)
911401547945	BY698X G5 LED200/NW L1W MW WB GM	Wireless Dim - Do not use with dimmer	0% (digital)

Mechanical and Housing

Order Code	Full Product Name	Dimmable	Maximum dim level
911401548045	BY698X G5 LED200/CW L1W MW WB GM	Wireless Dim - Do not use with dimmer	0% (digital)
911401548145	BY698X G5 LED250/NW L1W MW WB GM	Wireless Dim - Do not use with dimmer	0% (digital)
911401548245	BY698X G5 LED250/CW L1W MW WB GM	Wireless Dim - Do not use with dimmer	0% (digital)
911401548345	BY698X G5 LED300/NW L1W MW WB GM	Wireless Dim - Do not use with dimmer	0% (digital)
911401548445	BY698X G5 LED300/CW L1W MW WB GM	Wireless Dim - Do not use with dimmer	0% (digital)
911401548545	BY698X G5 LED105/NW L1W MW WB GM L3m	Wireless Dim - Do not use with dimmer	0% (digital)
911401548645	BY698X G5 LED105/CW L1W MW WB GM L3m	Wireless Dim - Do not use with dimmer	0% (digital)
911401548745	BY698X G5 LED150/NW L1W MW WB GM L3m	Wireless Dim - Do not use with dimmer	0% (digital)
911401548845	BY698X G5 LED150/CW L1W MW WB GM L3m	Wireless Dim - Do not use with dimmer	0% (digital)
911401548945	BY698X G5 LED200/NW L1W MW WB GM L3m	Wireless Dim - Do not use with dimmer	0% (digital)
911401549045	BY698X G5 LED200/CW L1W MW WB GM L3m	Wireless Dim - Do not use with dimmer	0% (digital)
911401549145	BY698X G5 LED250/NW L1W MW WB GM L3m	Wireless Dim - Do not use with dimmer	0% (digital)
911401549245	BY698X G5 LED250/CW L1W MW WB GM L3m	Wireless Dim - Do not use with dimmer	0% (digital)
911401549345	BY698X G5 LED300/NW L1W MW WB GM L3m	Wireless Dim - Do not use with dimmer	0% (digital)
911401549445	BY698X G5 LED300/CW L1W MW WB GM L3m	Wireless Dim - Do not use with dimmer	0% (digital)

GreenPerform Highbay G5

Order Code	Full Product Name	Mech. impact protection code	Ingress protection code
911401550545	BY698X G5 LED105/NW L1W PIR WB GM	IK03	IP65
911401550645	BY698X G5 LED105/CW L1W PIR WB GM	IK03	IP65
911401550745	BY698X G5 LED150/NW L1W PIR WB GM	IK03	IP65
911401550845	BY698X G5 LED150/CW L1W PIR WB GM	IK03	IP65
911401550945	BY698X G5 LED200/NW L1W PIR WB GM	IK03	IP65
911401551045	BY698X G5 LED200/CW L1W PIR WB GM	IK03	IP65
911401551145	BY698X G5 LED250/NW L1W PIR WB GM	IK03	IP65
911401551245	BY698X G5 LED250/CW L1W PIR WB GM	IK03	IP65
911401551345	BY698X G5 LED300/NW L1W PIR WB GM	IK03	IP65
911401551445	BY698X G5 LED300/CW L1W PIR WB GM	IK03	IP65
911401552045	BY698X G5 LED105/NW L1W PIR WB GM L3m	IK03	IP65
911401552145	BY698X G5 LED105/CW L1W PIR WB GM L3m	IK03	IP65
911401552245	BY698X G5 LED150/NW L1W PIR WB GM L3m	IK03	IP65
911401552345	BY698X G5 LED150/CW L1W PIR WB GM L3m	IK03	IP65
911401552445	BY698X G5 LED200/NW L1W PIR WB GM L3m	IK03	IP65
911401552545	BY698X G5 LED200/CW L1W PIR WB GM L3m	IK03	IP65
911401552645	BY698X G5 LED250/NW L1W PIR WB GM L3m	IK03	IP65
911401552745	BY698X G5 LED250/CW L1W PIR WB GM L3m	IK03	IP65
911401552845	BY698X G5 LED300/NW L1W PIR WB GM L3m	IK03	IP65
911401552945	BY698X G5 LED300/CW L1W PIR WB GM L3m	IK03	IP65
911401526245	BY698P G5 LED105/NW PSU WB GC	IK08	IP65
911401526345	BY698P G5 LED105/NW PSU NB GC	IK08	IP65
911401526445	BY698P G5 LED105/CW PSU WB GC	IK08	IP65
911401526545	BY698P G5 LED105/CW PSU NB GC	IK08	IP65
911401526645	BY698P G5 LED150/NW PSU WB GC	IK08	IP65
911401526745	BY698P G5 LED150/NW PSU NB GC	IK08	IP65
911401526845	BY698P G5 LED150/CW PSU WB GC	IK08	IP65
911401526945	BY698P G5 LED150/CW PSU NB GC	IK08	IP65
911401527045	BY698P G5 LED200/NW PSU WB GC	IK08	IP65
911401527145	BY698P G5 LED200/NW PSU NB GC	IK08	IP65
911401527245	BY698P G5 LED200/CW PSU WB GC	IK08	IP65
911401527345	BY698P G5 LED200/CW PSU NB GC	IK08	IP65
911401527445	BY698P G5 LED250/NW PSU WB GC	IK08	IP65
911401527545	BY698P G5 LED250/NW PSU NB GC	IK08	IP65

Order Code	Full Product Name	Mech. impact protection code	Ingress protection code
911401527645	BY698P G5 LED250/CW PSU WB GC	IK08	IP65
911401527745	BY698P G5 LED250/CW PSU NB GC	IK08	IP65
911401527845	BY698P G5 LED300/NW PSU WB GC	IK08	IP65
911401527945	BY698P G5 LED300/NW PSU NB GC	IK08	IP65
911401528045	BY698P G5 LED300/CW PSU WB GC	IK08	IP65
911401528145	BY698P G5 LED300/CW PSU NB GC	IK08	IP65
911401528245	BY698P G5 LED105/NW PSU WB GM	IK08	IP65
911401528345	BY698P G5 LED105/NW PSU NB GM	IK08	IP65
911401528445	BY698P G5 LED105/CW PSU WB GM	IK08	IP65
911401528545	BY698P G5 LED105/CW PSU NB GM	IK08	IP65
911401528645	BY698P G5 LED150/NW PSU WB GM	IK08	IP65
911401528745	BY698P G5 LED150/NW PSU NB GM	IK08	IP65
911401528845	BY698P G5 LED150/CW PSU WB GM	IK08	IP65
911401528945	BY698P G5 LED150/CW PSU NB GM	IK08	IP65
911401529045	BY698P G5 LED200/NW PSU WB GM	IK08	IP65
911401529145	BY698P G5 LED200/NW PSU NB GM	IK08	IP65
911401529245	BY698P G5 LED200/CW PSU WB GM	IK08	IP65
911401529345	BY698P G5 LED200/CW PSU NB GM	IK08	IP65
911401529445	BY698P G5 LED250/NW PSU WB GM	IK08	IP65
911401529545	BY698P G5 LED250/NW PSU NB GM	IK08	IP65
911401529645	BY698P G5 LED250/CW PSU WB GM	IK08	IP65
911401529745	BY698P G5 LED250/CW PSU NB GM	IK08	IP65
911401529845	BY698P G5 LED300/NW PSU WB GM	IK08	IP65
911401529945	BY698P G5 LED300/NW PSU NB GM	IK08	IP65
911401530045	BY698P G5 LED300/CW PSU WB GM	IK08	IP65
911401530145	BY698P G5 LED300/CW PSU NB GM	IK08	IP65
911401530245	BY698P G5 LED200/840 PSU WB CAU	IK08	IP65
911401530345	BY698P G5 LED250/840 PSU WB CAU	IK08	IP65
911401530445	BY698P G5 LED300/840 PSU WB CAU	IK08	IP65
911401530545	BY698P G5 LED200/840 PSU WB CAU CL	IK08	IP65
911401530645	BY698P G5 LED200/850 PSU WB CAU CL	IK08	IP65
911401530745	BY698P G5 LED250/840 PSU WB CAU CL	IK08	IP65
911401530845	BY698P G5 LED250/850 PSU WB CAU CL	IK08	IP65
911401530945	BY698P G5 LED300/840 PSU WB CAU CL	IK08	IP65
911401531045	BY698P G5 LED300/850 PSU WB CAU CL	IK08	IP65
911401531145	BY698P G5 LED105/NW PSD WB GC	IK08	IP65
911401531245	BY698P G5 LED105/NW PSD NB GC	IK08	IP65
911401531345	BY698P G5 LED105/CW PSD WB GC	IK08	IP65
911401531445	BY698P G5 LED105/CW PSD NB GC	IK08	IP65
911401531545	BY698P G5 LED150/NW PSD WB GC	IK08	IP65
911401531645	BY698P G5 LED150/NW PSD NB GC	IK08	IP65
911401531745	BY698P G5 LED150/CW PSD WB GC	IK08	IP65
911401531845	BY698P G5 LED150/CW PSD NB GC	IK08	IP65
911401531945	BY698P G5 LED200/NW PSD WB GC	IK08	IP65

GreenPerform Highbay G5

Order Code	Full Product Name	Mech. impact protection code	Ingress protection code
911401532045	BY698P G5 LED200/NW PSD NB GC	IK08	IP65
911401532145	BY698P G5 LED200/CW PSD WB GC	IK08	IP65
911401532245	BY698P G5 LED200/CW PSD NB GC	IK08	IP65
911401532345	BY698P G5 LED250/NW PSD WB GC	IK08	IP65
911401532445	BY698P G5 LED250/NW PSD NB GC	IK08	IP65
911401532545	BY698P G5 LED250/CW PSD WB GC	IK08	IP65
911401532645	BY698P G5 LED250/CW PSD NB GC	IK08	IP65
911401532745	BY698P G5 LED300/NW PSD WB GC	IK08	IP65
911401532845	BY698P G5 LED300/NW PSD NB GC	IK08	IP65
911401532945	BY698P G5 LED300/CW PSD WB GC	IK08	IP65
911401533045	BY698P G5 LED300/CW PSD NB GC	IK08	IP65
911401533145	BY698P G5 LED105/NW PSD WB GM	IK08	IP65
911401533245	BY698P G5 LED105/NW PSD NB GM	IK08	IP65
911401533345	BY698P G5 LED105/CW PSD WB GM	IK08	IP65
911401533445	BY698P G5 LED105/CW PSD NB GM	IK08	IP65
911401533545	BY698P G5 LED150/NW PSD WB GM	IK08	IP65
911401533645	BY698P G5 LED150/NW PSD NB GM	IK08	IP65
911401533745	BY698P G5 LED150/CW PSD WB GM	IK08	IP65
911401533845	BY698P G5 LED150/CW PSD NB GM	IK08	IP65
911401533945	BY698P G5 LED200/NW PSD WB GM	IK08	IP65
911401534045	BY698P G5 LED200/NW PSD NB GM	IK08	IP65
911401534145	BY698P G5 LED200/CW PSD WB GM	IK08	IP65
911401534245	BY698P G5 LED200/CW PSD NB GM	IK08	IP65
911401534345	BY698P G5 LED250/NW PSD WB GM	IK08	IP65
911401534445	BY698P G5 LED250/NW PSD NB GM	IK08	IP65
911401534545	BY698P G5 LED250/CW PSD WB GM	IK08	IP65
911401534645	BY698P G5 LED250/CW PSD NB GM	IK08	IP65
911401534745	BY698P G5 LED300/NW PSD WB GM	IK08	IP65
911401534845	BY698P G5 LED300/NW PSD NB GM	IK08	IP65
911401534945	BY698P G5 LED300/CW PSD WB GM	IK08	IP65
911401535045	BY698P G5 LED300/CW PSD NB GM	IK08	IP65
911401535145	BY698P G5 LED200/840 PSD WB CAU	IK08	IP65
911401535245	BY698P G5 LED250/840 PSD WB CAU	IK08	IP65
911401535445	BY698P G5 LED300/840 PSD WB CAU	IK08	IP65
911401535545	BY698P G5 LED105/NW PSU WB LA	IK08	IP65
911401535645	BY698P G5 LED105/CW PSU WB LA	IK08	IP65
911401535745	BY698P G5 LED150/NW PSU WB LA	IK08	IP65
911401535845	BY698P G5 LED150/CW PSU WB LA	IK08	IP65
911401535945	BY698P G5 LED200/NW PSU WB LA	IK08	IP65
911401536045	BY698P G5 LED200/NW PSU NB LA	IK08	IP65
911401536145	BY698P G5 LED200/CW PSU WB LA	IK08	IP65
911401536245	BY698P G5 LED200/CW PSU NB LA	IK08	IP65
911401536345	BY698P G5 LED250/NW PSU WB LA	IK08	IP65
911401536445	BY698P G5 LED250/NW PSU NB LA	IK08	IP65
911401536545	BY698P G5 LED250/CW PSU WB LA	IK08	IP65
911401536645	BY698P G5 LED250/CW PSU NB LA	IK08	IP65
911401536745	BY698P G5 LED300/NW PSU WB LA	IK08	IP65
911401536845	BY698P G5 LED300/NW PSU NB LA	IK08	IP65
911401536945	BY698P G5 LED300/CW PSU WB LA	IK08	IP65
911401537045	BY698P G5 LED300/CW PSU NB LA	IK08	IP65

Order Code	Full Product Name	Mech. impact protection code	Ingress protection code
911401537145	BY698P G5 LED105/NW PSD WB LA	IK08	IP65
911401537245	BY698P G5 LED105/CW PSD WB LA	IK08	IP65
911401537345	BY698P G5 LED150/NW PSD WB LA	IK08	IP65
911401537445	BY698P G5 LED150/CW PSD WB LA	IK08	IP65
911401537545	BY698P G5 LED200/NW PSD WB LA	IK08	IP65
911401537645	BY698P G5 LED200/NW PSD NB LA	IK08	IP65
911401537745	BY698P G5 LED200/CW PSD WB LA	IK08	IP65
911401537845	BY698P G5 LED200/CW PSD NB LA	IK08	IP65
911401537945	BY698P G5 LED250/NW PSD WB LA	IK08	IP65
911401538045	BY698P G5 LED250/NW PSD NB LA	IK08	IP65
911401538145	BY698P G5 LED250/CW PSD WB LA	IK08	IP65
911401538245	BY698P G5 LED250/CW PSD NB LA	IK08	IP65
911401538345	BY698P G5 LED300/NW PSD WB LA	IK08	IP65
911401538445	BY698P G5 LED300/NW PSD NB LA	IK08	IP65
911401538545	BY698P G5 LED300/CW PSD WB LA	IK08	IP65
911401538645	BY698P G5 LED300/CW PSD NB LA	IK08	IP65
911401538745	BY698P G5 LED105/NW PSU WB GM	IK08	IP65
	L3m		
911401538845	BY698P G5 LED105/NW PSU NB GM	IK08	IP65
	L3m		
911401538945	BY698P G5 LED105/CW PSU WB GM	IK08	IP65
	L3m		
911401539045	BY698P G5 LED105/CW PSU NB GM	IK08	IP65
	L3m		
911401539145	BY698P G5 LED150/NW PSU WB GM	IK08	IP65
	L3m		
911401539245	BY698P G5 LED150/NW PSU NB GM	IK08	IP65
	L3m		
911401539345	BY698P G5 LED150/CW PSU WB GM	IK08	IP65
	L3m		
911401539445	BY698P G5 LED150/CW PSU NB GM	IK08	IP65
	L3m		
911401539545	BY698P G5 LED200/NW PSU WB GM	IK08	IP65
	L3m		
911401539645	BY698P G5 LED200/NW PSU NB GM	IK08	IP65
	L3m		
911401539745	BY698P G5 LED200/CW PSU WB GM	IK08	IP65
	L3m		
911401539845	BY698P G5 LED200/CW PSU NB GM	IK08	IP65
	L3m		
911401539945	BY698P G5 LED250/NW PSU WB GM	IK08	IP65
	L3m		
91140154004	BY698P G5 LED250/NW PSU NB GM	IK08	IP65
5	L3m		
911401540145	BY698P G5 LED250/CW PSU WB GM	IK08	IP65
	L3m		
911401540245	BY698P G5 LED250/CW PSU NB GM	IK08	IP65
	L3m		
911401540345	BY698P G5 LED300/NW PSU WB GM	IK08	IP65
	L3m		

GreenPerform Highbay G5

Order Code	Full Product Name	Mech. impact protection code	Ingress protection code
911401540445	BY698P G5 LED300/NW PSU NB GM L3m	IK08	IP65
911401540545	BY698P G5 LED300/CW PSU WB GM L3m	IK08	IP65
911401540645	BY698P G5 LED300/CW PSU NB GM L3m	IK08	IP65
911401540745	BY690P LED105/NW PSU WB GC	IK08	IP66
911401540845	BY690P LED105/CW PSU WB GC	IK08	IP66
911401540945	BY690P LED150/NW PSU WB GC	IK08	IP66
911401541045	BY690P LED150/CW PSU WB GC	IK08	IP66
911401541145	BY690P LED200/NW PSU WB GC	IK08	IP66
911401541245	BY690P LED200/CW PSU WB GC	IK08	IP66
911401541345	BY690P LED250/NW PSU WB GC	IK08	IP66
911401541445	BY690P LED250/CW PSU WB GC	IK08	IP66
911401541545	BY690P LED300/NW PSU WB GC	IK08	IP66
911401541645	BY690P LED300/CW PSU WB GC	IK08	IP66
911401541745	BY690P LED105/NW PSU WB GM	IK08	IP66
911401541845	BY690P LED105/CW PSU WB GM	IK08	IP66
911401541945	BY690P LED150/NW PSU WB GM	IK08	IP66
911401542045	BY690P LED150/CW PSU WB GM	IK08	IP66
911401542145	BY690P LED200/NW PSU WB GM	IK08	IP66
911401542245	BY690P LED200/CW PSU WB GM	IK08	IP66
911401542345	BY690P LED250/NW PSU WB GM	IK08	IP66
911401542445	BY690P LED250/CW PSU WB GM	IK08	IP66
911401542545	BY690P LED300/NW PSU WB GM	IK08	IP66
911401542645	BY690P LED300/CW PSU WB GM	IK08	IP66
911401580944	BY698P G5 LED105/NW PSU WB TW	IK08	IP65
911401581044	BY698P G5 LED105/NW PSU NB TW	IK08	IP65
911401581144	BY698P G5 LED105/CW PSU WB TW	IK08	IP65
911401581244	BY698P G5 LED105/CW PSU NB TW	IK08	IP65
911401581344	BY698P G5 LED150/NW PSU WB TW	IK08	IP65
911401581444	BY698P G5 LED150/NW PSU NB TW	IK08	IP65
911401581544	BY698P G5 LED150/CW PSU WB TW	IK08	IP65
911401581644	BY698P G5 LED150/CW PSU NB TW	IK08	IP65
911401581744	BY698P G5 LED200/NW PSU WB TW	IK08	IP65
911401581844	BY698P G5 LED200/NW PSU NB TW	IK08	IP65
911401581944	BY698P G5 LED200/CW PSU WB TW	IK08	IP65
911401582044	BY698P G5 LED200/CW PSU NB TW	IK08	IP65
911401582144	BY698P G5 LED250/NW PSU WB TW	IK08	IP65
911401582244	BY698P G5 LED250/NW PSU NB TW	IK08	IP65
911401582344	BY698P G5 LED250/CW PSU WB TW	IK08	IP65
911401582444	BY698P G5 LED250/CW PSU NB TW	IK08	IP65
911401582544	BY698P G5 LED300/NW PSU WB TW	IK08	IP65
911401582644	BY698P G5 LED300/NW PSU NB TW	IK08	IP65
911401582744	BY698P G5 LED300/CW PSU WB TW	IK08	IP65
911401582844	BY698P G5 LED300/CW PSU NB TW	IK08	IP65
911401543245	BY698X G5 LED150/NW Connected WB GC	IK05	IP65

Order Code	Full Product Name	Mech. impact protection code	Ingress protection code
911401543345	BY698X G5 LED150/CW Connected WB GC	IK05	IP65
911401543445	BY698X G5 LED200/NW Connected WB GC	IK05	IP65
911401543545	BY698X G5 LED200/CW Connected WB GC	IK05	IP65
911401543645	BY698X G5 LED250/NW Connected WB GC	IK05	IP65
911401543745	BY698X G5 LED250/CW Connected WB GC	IK05	IP65
911401543845	BY698X G5 LED300/NW Connected WB GC	IK05	IP65
911401543945	BY698X G5 LED300/NW Connected NB GC	IK05	IP65
911401544045	BY698X G5 LED300/CW Connected WB GC	IK05	IP65
911401544145	BY698X G5 LED300/CW Connected NB GC	IK05	IP65
911401544245	BY698X G5 LED150/NW Connected WB GM	IK05	IP65
911401544345	BY698X G5 LED150/NW Connected NB GM	IK05	IP65
911401544445	BY698X G5 LED150/CW Connected WB GM	IK05	IP65
911401544545	BY698X G5 LED150/CW Connected NB GM	IK05	IP65
911401544645	BY698X G5 LED200/NW Connected WB GM	IK05	IP65
911401544745	BY698X G5 LED200/NW Connected NB GM	IK05	IP65
911401544845	BY698X G5 LED200/CW Connected WB GM	IK05	IP65
911401544945	BY698X G5 LED200/CW Connected NB GM	IK05	IP65
911401545045	BY698X G5 LED250/NW Connected WB GM	IK05	IP65
911401545145	BY698X G5 LED250/NW Connected NB GM	IK05	IP65
911401545245	BY698X G5 LED250/CW Connected WB GM	IK05	IP65
911401545345	BY698X G5 LED250/CW Connected NB GM	IK05	IP65
911401545445	BY698X G5 LED300/NW Connected WB GM	IK05	IP65
911401545545	BY698X G5 LED300/NW Connected NB GM	IK05	IP65
911401545645	BY698X G5 LED300/CW Connected WB GM	IK05	IP65
911401545745	BY698X G5 LED300/CW Connected NB GM	IK05	IP65

GreenPerform Highbay G5

Order Code	Full Product Name	Mech. impact	Ingress
		protection code	protection code
911401545845	BY698X G5 LED200/840 Connected WB CAU	IK05	IP65
911401545945	BY698X G5 LED250/840 Connected WB CAU	IK05	IP65
911401546045	BY698X G5 LED300/840 Connected WB CAU	IK05	IP65
911401546145	BY698X G5 LED150/NW Connected WB LA	IK05	IP65
911401546245	BY698X G5 LED150/CW Connected WB LA	IK05	IP65
911401546345	BY698X G5 LED200/NW Connected WB LA	IK05	IP65
911401546445	BY698X G5 LED200/NW Connected NB LA	IK05	IP65
911401546545	BY698X G5 LED200/CW Connected WB LA	IK05	IP65
911401546645	BY698X G5 LED200/CW Connected NB LA	IK05	IP65
911401546745	BY698X G5 LED250/NW Connected WB LA	IK05	IP65
911401546845	BY698X G5 LED250/NW Connected NB LA	IK05	IP65
911401546945	BY698X G5 LED250/CW Connected WB LA	IK05	IP65
911401547045	BY698X G5 LED250/CW Connected NB LA	IK05	IP65
911401547145	BY698X G5 LED300/NW Connected WB LA	IK05	IP65
911401547245	BY698X G5 LED300/NW Connected NB LA	IK05	IP65
911401547345	BY698X G5 LED300/CW Connected WB LA	IK05	IP65
911401547445	BY698X G5 LED300/CW Connected NB LA	IK05	IP65
911401547545	BY698X G5 LED105/NW L1W MW WB GM	IK06	IP65
911401547645	BY698X G5 LED105/CW L1W MW WB GM	IK06	IP65

Approval and Application

Order Code	Full Product Name	Ambient	Glow-wire test
		temperature range	
911401550545	BY698X G5 LED105/NW L1W PIR WB GM	-30 to +50 °C	Temperature 750 °C, duration 30 s
911401550645	BY698X G5 LED105/CW L1W PIR WB GM	-30 to +50 °C	Temperature 750 °C, duration 30 s
911401550745	BY698X G5 LED150/NW L1W PIR WB GM	-30 to +50 °C	Temperature 750 °C, duration 30 s

Order Code	Full Product Name	Mech. impact	Ingress
		protection code	protection code
911401547745	BY698X G5 LED150/NW L1W MW WB GM	IK06	IP65
911401547845	BY698X G5 LED150/CW L1W MW WB GM	IK06	IP65
911401547945	BY698X G5 LED200/NW L1W MW WB GM	IK06	IP65
911401548045	BY698X G5 LED200/CW L1W MW WB GM	IK06	IP65
911401548145	BY698X G5 LED250/NW L1W MW WB GM	IK06	IP65
911401548245	BY698X G5 LED250/CW L1W MW WB GM	IK06	IP65
911401548345	BY698X G5 LED300/NW L1W MW WB GM	IK06	IP65
911401548445	BY698X G5 LED300/CW L1W MW WB GM	IK06	IP65
911401548545	BY698X G5 LED105/NW L1W MW WB GM L3m	IK06	IP65
911401548645	BY698X G5 LED105/CW L1W MW WB GM L3m	IK06	IP65
911401548745	BY698X G5 LED150/NW L1W MW WB GM L3m	IK06	IP65
911401548845	BY698X G5 LED150/CW L1W MW WB GM L3m	IK06	IP65
911401548945	BY698X G5 LED200/NW L1W MW WB GM L3m	IK06	IP65
911401549045	BY698X G5 LED200/CW L1W MW WB GM L3m	IK06	IP65
911401549145	BY698X G5 LED250/NW L1W MW WB GM L3m	IK06	IP65
911401549245	BY698X G5 LED250/CW L1W MW WB GM L3m	IK06	IP65
911401549345	BY698X G5 LED300/NW L1W MW WB GM L3m	IK06	IP65
911401549445	BY698X G5 LED300/CW L1W MW WB GM L3m	IK06	IP65

GreenPerform Highbay G5

Order Code	Full Product Name	Ambient temperature range	Glow-wire test
911401551145	BY698X G5 LED250/NW LIW PIR WB GM	-30 to +50 °C	Temperature 750 °C, duration 30 s
911401551245	BY698X G5 LED250/CW LIW PIR WB GM	-30 to +50 °C	Temperature 750 °C, duration 30 s
911401551345	BY698X G5 LED300/NW LIW PIR WB GM	-30 to +50 °C	Temperature 750 °C, duration 30 s
911401551445	BY698X G5 LED300/CW LIW PIR WB GM	-30 to +50 °C	Temperature 750 °C, duration 30 s
911401552045	BY698X G5 LED105/NW LIW PIR WB GM L3m	-30 to +50 °C	Temperature 750 °C, duration 30 s
911401552145	BY698X G5 LED105/CW LIW PIR WB GM L3m	-30 to +50 °C	Temperature 750 °C, duration 30 s
911401552245	BY698X G5 LED150/NW LIW PIR WB GM L3m	-30 to +50 °C	Temperature 750 °C, duration 30 s
911401552345	BY698X G5 LED150/CW LIW PIR WB GM L3m	-30 to +50 °C	Temperature 750 °C, duration 30 s
911401552445	BY698X G5 LED200/NW LIW PIR WB GM L3m	-30 to +50 °C	Temperature 750 °C, duration 30 s
911401552545	BY698X G5 LED200/CW LIW PIR WB GM L3m	-30 to +50 °C	Temperature 750 °C, duration 30 s
911401552645	BY698X G5 LED250/NW LIW PIR WB GM L3m	-30 to +50 °C	Temperature 750 °C, duration 30 s
911401552745	BY698X G5 LED250/CW LIW PIR WB GM L3m	-30 to +50 °C	Temperature 750 °C, duration 30 s
911401552845	BY698X G5 LED300/NW LIW PIR WB GM L3m	-30 to +50 °C	Temperature 750 °C, duration 30 s
911401552945	BY698X G5 LED300/CW LIW PIR WB GM L3m	-30 to +50 °C	Temperature 750 °C, duration 30 s
911401526245	BY698P G5 LED105/NW PSU WB GC	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401526345	BY698P G5 LED105/NW PSU NB GC	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401526445	BY698P G5 LED105/CW PSU WB GC	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401526545	BY698P G5 LED105/CW PSU NB GC	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401526645	BY698P G5 LED150/NW PSU WB GC	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401526745	BY698P G5 LED150/NW PSU NB GC	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401526845	BY698P G5 LED150/CW PSU WB GC	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401526945	BY698P G5 LED150/CW PSU NB GC	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401527045	BY698P G5 LED200/NW PSU WB GC	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401527145	BY698P G5 LED200/NW PSU NB GC	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401527245	BY698P G5 LED200/CW PSU WB GC	-30 °C to 50 °C	Temperature 650 °C, duration 30 s

Order Code	Full Product Name	Ambient temperature range	Glow-wire test
911401527345	BY698P G5 LED200/CW PSU NB GC	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401527445	BY698P G5 LED250/NW PSU WB GC	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401527545	BY698P G5 LED250/NW PSU NB GC	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401527645	BY698P G5 LED250/CW PSU WB GC	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401527745	BY698P G5 LED250/CW PSU NB GC	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401527845	BY698P G5 LED300/NW PSU WB GC	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401527945	BY698P G5 LED300/NW PSU NB GC	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401528045	BY698P G5 LED300/CW PSU WB GC	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401528145	BY698P G5 LED300/CW PSU NB GC	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401528245	BY698P G5 LED105/NW PSU WB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401528345	BY698P G5 LED105/NW PSU NB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401528445	BY698P G5 LED105/CW PSU WB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401528545	BY698P G5 LED105/CW PSU NB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401528645	BY698P G5 LED150/NW PSU WB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401528745	BY698P G5 LED150/NW PSU NB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401528845	BY698P G5 LED150/CW PSU WB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401528945	BY698P G5 LED150/CW PSU NB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401529045	BY698P G5 LED200/NW PSU WB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401529145	BY698P G5 LED200/NW PSU NB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401529245	BY698P G5 LED200/CW PSU WB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401529345	BY698P G5 LED200/CW PSU NB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401529445	BY698P G5 LED250/NW PSU WB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401529545	BY698P G5 LED250/NW PSU NB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401529645	BY698P G5 LED250/CW PSU WB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401529745	BY698P G5 LED250/CW PSU NB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s

GreenPerform Highbay G5

Order Code	Full Product Name	Ambient temperature range	Glow-wire test
911401529845	BY698P G5 LED300/NW PSU WB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401529945	BY698P G5 LED300/NW PSU NB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401530045	BY698P G5 LED300/CW PSU WB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401530145	BY698P G5 LED300/CW PSU NB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401530245	BY698P G5 LED200/840 PSU WB CAU	-30 °C to 50 °C	Temperature 750 °C, duration 30 s
911401530345	BY698P G5 LED250/840 PSU WB CAU	-30 °C to 50 °C	Temperature 750 °C, duration 30 s
911401530445	BY698P G5 LED300/840 PSU WB CAU	-30 °C to 50 °C	Temperature 750 °C, duration 30 s
911401530545	BY698P G5 LED200/840 PSU WB CAU CL	-30 °C to 50 °C	Temperature 750 °C, duration 30 s
911401530645	BY698P G5 LED200/850 PSU WB CAU CL	-30 °C to 50 °C	Temperature 750 °C, duration 30 s
911401530745	BY698P G5 LED250/840 PSU WB CAU CL	-30 °C to 50 °C	Temperature 750 °C, duration 30 s
911401530845	BY698P G5 LED250/850 PSU WB CAU CL	-30 °C to 50 °C	Temperature 750 °C, duration 30 s
911401530945	BY698P G5 LED300/840 PSU WB CAU CL	-30 °C to 50 °C	Temperature 750 °C, duration 30 s
911401531045	BY698P G5 LED300/850 PSU WB CAU CL	-30 °C to 50 °C	Temperature 750 °C, duration 30 s
911401531145	BY698P G5 LED105/NW PSD WB GC	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401531245	BY698P G5 LED105/NW PSD NB GC	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401531345	BY698P G5 LED105/CW PSD WB GC	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401531445	BY698P G5 LED105/CW PSD NB GC	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401531545	BY698P G5 LED150/NW PSD WB GC	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401531645	BY698P G5 LED150/NW PSD NB GC	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401531745	BY698P G5 LED150/CW PSD WB GC	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401531845	BY698P G5 LED150/CW PSD NB GC	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401531945	BY698P G5 LED200/NW PSD WB GC	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401532045	BY698P G5 LED200/NW PSD NB GC	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401532145	BY698P G5 LED200/CW PSD WB GC	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401532245	BY698P G5 LED200/CW PSD NB GC	-30 °C to 50 °C	Temperature 650 °C, duration 30 s

Order Code	Full Product Name	Ambient temperature range	Glow-wire test
911401532345	BY698P G5 LED250/NW PSD WB GC	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401532445	BY698P G5 LED250/NW PSD NB GC	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401532545	BY698P G5 LED250/CW PSD WB GC	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401532645	BY698P G5 LED250/CW PSD NB GC	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401532745	BY698P G5 LED300/NW PSD WB GC	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401532845	BY698P G5 LED300/NW PSD NB GC	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401532945	BY698P G5 LED300/CW PSD WB GC	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401533045	BY698P G5 LED300/CW PSD NB GC	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401533145	BY698P G5 LED105/NW PSD WB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401533245	BY698P G5 LED105/NW PSD NB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401533345	BY698P G5 LED105/CW PSD WB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401533445	BY698P G5 LED105/CW PSD NB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401533545	BY698P G5 LED150/NW PSD WB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401533645	BY698P G5 LED150/NW PSD NB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401533745	BY698P G5 LED150/CW PSD WB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401533845	BY698P G5 LED150/CW PSD NB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401533945	BY698P G5 LED200/NW PSD WB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401534045	BY698P G5 LED200/NW PSD NB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401534145	BY698P G5 LED200/CW PSD WB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401534245	BY698P G5 LED200/CW PSD NB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401534345	BY698P G5 LED250/NW PSD WB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401534445	BY698P G5 LED250/NW PSD NB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401534545	BY698P G5 LED250/CW PSD WB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401534645	BY698P G5 LED250/CW PSD NB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401534745	BY698P G5 LED300/NW PSD WB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s

GreenPerform Highbay G5

Order Code	Full Product Name	Ambient temperature range	Glow-wire test
911401534845	BY698P G5 LED300/NW PSD NB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401534945	BY698P G5 LED300/CW PSD WB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401535045	BY698P G5 LED300/CW PSD NB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401535145	BY698P G5 LED200/840 PSD WB CAU	-30 °C to 50 °C	Temperature 750 °C, duration 30 s
911401535245	BY698P G5 LED250/840 PSD WB CAU	-30 °C to 50 °C	Temperature 750 °C, duration 30 s
911401535445	BY698P G5 LED300/840 PSD WB CAU	-30 °C to 50 °C	Temperature 750 °C, duration 30 s
911401535545	BY698P G5 LED105/NW PSU WB LA	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401535645	BY698P G5 LED105/CW PSU WB LA	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401535745	BY698P G5 LED150/NW PSU WB LA	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401535845	BY698P G5 LED150/CW PSU WB LA	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401535945	BY698P G5 LED200/NW PSU WB LA	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401536045	BY698P G5 LED200/NW PSU NB LA	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401536145	BY698P G5 LED200/CW PSU WB LA	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401536245	BY698P G5 LED200/CW PSU NB LA	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401536345	BY698P G5 LED250/NW PSU WB LA	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401536445	BY698P G5 LED250/NW PSU NB LA	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401536545	BY698P G5 LED250/CW PSU WB LA	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401536645	BY698P G5 LED250/CW PSU NB LA	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401536745	BY698P G5 LED300/NW PSU WB LA	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401536845	BY698P G5 LED300/NW PSU NB LA	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401536945	BY698P G5 LED300/CW PSU WB LA	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401537045	BY698P G5 LED300/CW PSU NB LA	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401537145	BY698P G5 LED105/NW PSD WB LA	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401537245	BY698P G5 LED105/CW PSD WB LA	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401537345	BY698P G5 LED150/NW PSD WB LA	-30 °C to 50 °C	Temperature 650 °C, duration 30 s

Order Code	Full Product Name	Ambient temperature range	Glow-wire test
911401537445	BY698P G5 LED150/CW PSD WB LA	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401537545	BY698P G5 LED200/NW PSD WB LA	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401537645	BY698P G5 LED200/NW PSD NB LA	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401537745	BY698P G5 LED200/CW PSD WB LA	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401537845	BY698P G5 LED200/CW PSD NB LA	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401537945	BY698P G5 LED250/NW PSD WB LA	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401538045	BY698P G5 LED250/NW PSD NB LA	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401538145	BY698P G5 LED250/CW PSD WB LA	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401538245	BY698P G5 LED250/CW PSD NB LA	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401538345	BY698P G5 LED300/NW PSD WB LA	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401538445	BY698P G5 LED300/NW PSD NB LA	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401538545	BY698P G5 LED300/CW PSD WB LA	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401538645	BY698P G5 LED300/CW PSD NB LA	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401538745	BY698P G5 LED105/NW PSU WB GM L3m	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401538845	BY698P G5 LED105/NW PSU NB GM L3m	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401538945	BY698P G5 LED105/CW PSU WB GM L3m	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401539045	BY698P G5 LED105/CW PSU NB GM L3m	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401539145	BY698P G5 LED150/NW PSU WB GM L3m	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401539245	BY698P G5 LED150/NW PSU NB GM L3m	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401539345	BY698P G5 LED150/CW PSU WB GM L3m	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401539445	BY698P G5 LED150/CW PSU NB GM L3m	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401539545	BY698P G5 LED200/NW PSU WB GM L3m	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401539645	BY698P G5 LED200/NW PSU NB GM L3m	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401539745	BY698P G5 LED200/CW PSU WB GM L3m	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401539845	BY698P G5 LED200/CW PSU NB GM L3m	-30 °C to 50 °C	Temperature 650 °C, duration 30 s

Order Code	Full Product Name	Ambient temperature range	Glow-wire test
911401539945	BY698P G5 LED250/NW PSU WB GM L3m	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401540045	BY698P G5 LED250/NW PSU NB GM L3m	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401540145	BY698P G5 LED250/CW PSU WB GM L3m	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401540245	BY698P G5 LED250/CW PSU NB GM L3m	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401540345	BY698P G5 LED300/NW PSU WB GM L3m	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401540445	BY698P G5 LED300/NW PSU NB GM L3m	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401540545	BY698P G5 LED300/CW PSU WB GM L3m	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401540645	BY698P G5 LED300/CW PSU NB GM L3m	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401540745	BY690P LED105/NW PSU WB GC	-40 °C to 50 °C	Temperature 650 °C, duration 30 s
911401540845	BY690P LED105/CW PSU WB GC	-40 °C to 50 °C	Temperature 650 °C, duration 30 s
911401540945	BY690P LED150/NW PSU WB GC	-40 °C to 50 °C	Temperature 650 °C, duration 30 s
911401541045	BY690P LED150/CW PSU WB GC	-40 °C to 50 °C	Temperature 650 °C, duration 30 s
911401541145	BY690P LED200/NW PSU WB GC	-40 °C to 50 °C	Temperature 650 °C, duration 30 s
911401541245	BY690P LED200/CW PSU WB GC	-40 °C to 50 °C	Temperature 650 °C, duration 30 s
911401541345	BY690P LED250/NW PSU WB GC	-35 °C to 50 °C	Temperature 650 °C, duration 30 s
911401541445	BY690P LED250/CW PSU WB GC	-35 °C to 50 °C	Temperature 650 °C, duration 30 s
911401541545	BY690P LED300/NW PSU WB GC	-35 °C to 50 °C	Temperature 650 °C, duration 30 s
911401541645	BY690P LED300/CW PSU WB GC	-35 °C to 50 °C	Temperature 650 °C, duration 30 s
911401541745	BY690P LED105/NW PSU WB GM	-40 °C to 50 °C	Temperature 650 °C, duration 30 s
911401541845	BY690P LED105/CW PSU WB GM	-40 °C to 50 °C	Temperature 650 °C, duration 30 s
911401541945	BY690P LED150/NW PSU WB GM	-40 °C to 50 °C	Temperature 650 °C, duration 30 s
911401542045	BY690P LED150/CW PSU WB GM	-40 °C to 50 °C	Temperature 650 °C, duration 30 s
911401542145	BY690P LED200/NW PSU WB GM	-40 °C to 50 °C	Temperature 650 °C, duration 30 s
911401542245	BY690P LED200/CW PSU WB GM	-40 °C to 50 °C	Temperature 650 °C, duration 30 s
911401542345	BY690P LED250/NW PSU WB GM	-35 °C to 50 °C	Temperature 650 °C, duration 30 s

Order Code	Full Product Name	Ambient temperature range	Glow-wire test
911401542445	BY690P LED250/CW PSU WB GM	-35 °C to 50 °C	Temperature 650 °C, duration 30 s
911401542545	BY690P LED300/NW PSU WB GM	-35 °C to 50 °C	Temperature 650 °C, duration 30 s
911401542645	BY690P LED300/CW PSU WB GM	-35 °C to 50 °C	Temperature 650 °C, duration 30 s
911401580944	BY698P G5 LED105/NW PSU WB TW	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401581044	BY698P G5 LED105/NW PSU NB TW	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401581144	BY698P G5 LED105/CW PSU WB TW	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401581244	BY698P G5 LED105/CW PSU NB TW	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401581344	BY698P G5 LED150/NW PSU WB TW	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401581444	BY698P G5 LED150/NW PSU NB TW	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401581544	BY698P G5 LED150/CW PSU WB TW	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401581644	BY698P G5 LED150/CW PSU NB TW	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401581744	BY698P G5 LED200/NW PSU WB TW	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401581844	BY698P G5 LED200/NW PSU NB TW	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401581944	BY698P G5 LED200/CW PSU WB TW	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401582044	BY698P G5 LED200/CW PSU NB TW	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401582144	BY698P G5 LED250/NW PSU WB TW	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401582244	BY698P G5 LED250/NW PSU NB TW	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401582344	BY698P G5 LED250/CW PSU WB TW	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401582444	BY698P G5 LED250/CW PSU NB TW	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401582544	BY698P G5 LED300/NW PSU WB TW	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401582644	BY698P G5 LED300/NW PSU NB TW	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401582744	BY698P G5 LED300/CW PSU WB TW	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401582844	BY698P G5 LED300/CW PSU NB TW	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401543245	BY698X G5 LED150/NW Connected WB GC	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401543345	BY698X G5 LED150/CW Connected WB GC	-30 °C to 50 °C	Temperature 650 °C, duration 30 s

GreenPerform Highbay G5

Order Code	Full Product Name	Ambient temperature range	Glow-wire test
911401543445	BY698X G5 LED200/NW Connected WB GC	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401543545	BY698X G5 LED200/CW Connected WB GC	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401543645	BY698X G5 LED250/NW Connected WB GC	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401543745	BY698X G5 LED250/CW Connected WB GC	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401543845	BY698X G5 LED300/NW Connected WB GC	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401543945	BY698X G5 LED300/NW Connected NB GC	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401544045	BY698X G5 LED300/CW Connected WB GC	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401544145	BY698X G5 LED300/CW Connected NB GC	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401544245	BY698X G5 LED150/NW Connected WB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401544345	BY698X G5 LED150/NW Connected NB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401544445	BY698X G5 LED150/CW Connected WB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401544545	BY698X G5 LED150/CW Connected NB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401544645	BY698X G5 LED200/NW Connected WB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401544745	BY698X G5 LED200/NW Connected NB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401544845	BY698X G5 LED200/CW Connected WB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401544945	BY698X G5 LED200/CW Connected NB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401545045	BY698X G5 LED250/NW Connected WB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401545145	BY698X G5 LED250/NW Connected NB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401545245	BY698X G5 LED250/CW Connected WB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401545345	BY698X G5 LED250/CW Connected NB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401545445	BY698X G5 LED300/NW Connected WB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401545545	BY698X G5 LED300/NW Connected NB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401545645	BY698X G5 LED300/CW Connected WB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401545745	BY698X G5 LED300/CW Connected NB GM	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401545845	BY698X G5 LED200/840 Connected WB CAU	-30 °C to 50 °C	Temperature 750 °C, duration 30 s

Order Code	Full Product Name	Ambient temperature range	Glow-wire test
911401545945	BY698X G5 LED250/840 Connected WB CAU	-30 °C to 50 °C	Temperature 750 °C, duration 30 s
911401546045	BY698X G5 LED300/840 Connected WB CAU	-30 °C to 50 °C	Temperature 750 °C, duration 30 s
911401546145	BY698X G5 LED150/NW Connected WB LA	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401546245	BY698X G5 LED150/CW Connected WB LA	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401546345	BY698X G5 LED200/NW Connected WB LA	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401546445	BY698X G5 LED200/NW Connected NB LA	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401546545	BY698X G5 LED200/CW Connected WB LA	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401546645	BY698X G5 LED200/CW Connected NB LA	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401546745	BY698X G5 LED250/NW Connected WB LA	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401546845	BY698X G5 LED250/NW Connected NB LA	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401546945	BY698X G5 LED250/CW Connected WB LA	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401547045	BY698X G5 LED250/CW Connected NB LA	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401547145	BY698X G5 LED300/NW Connected WB LA	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401547245	BY698X G5 LED300/NW Connected NB LA	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401547345	BY698X G5 LED300/CW Connected WB LA	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401547445	BY698X G5 LED300/CW Connected NB LA	-30 °C to 50 °C	Temperature 650 °C, duration 30 s
911401547545	BY698X G5 LED105/NW L1W MW WB GM	-30 to +50 °C	Temperature 750 °C, duration 30 s
911401547645	BY698X G5 LED105/CW L1W MW WB GM	-30 to +50 °C	Temperature 750 °C, duration 30 s
911401547745	BY698X G5 LED150/NW L1W MW WB GM	-30 to +50 °C	Temperature 750 °C, duration 30 s
911401547845	BY698X G5 LED150/CW L1W MW WB GM	-30 to +50 °C	Temperature 750 °C, duration 30 s
911401547945	BY698X G5 LED200/NW L1W MW WB GM	-30 to +50 °C	Temperature 750 °C, duration 30 s
911401548045	BY698X G5 LED200/CW L1W MW WB GM	-30 to +50 °C	Temperature 750 °C, duration 30 s
911401548145	BY698X G5 LED250/NW L1W MW WB GM	-30 to +50 °C	Temperature 750 °C, duration 30 s
911401548245	BY698X G5 LED250/CW L1W MW WB GM	-30 to +50 °C	Temperature 750 °C, duration 30 s
911401548345	BY698X G5 LED300/NW L1W MW WB GM	-30 to +50 °C	Temperature 750 °C, duration 30 s

Order Code	Full Product Name	Ambient	Glow-wire test
		temperature range	
911401548445	BY698X G5 LED300/CW L1W MW WB GM	-30 to +50 °C	Temperature 750 °C, duration 30 s
911401548545	BY698X G5 LED105/NW L1W MW WB GM L3m	-30 to +50 °C	Temperature 750 °C, duration 30 s
911401548645	BY698X G5 LED105/CW L1W MW WB GM L3m	-30 to +50 °C	Temperature 750 °C, duration 30 s
911401548745	BY698X G5 LED150/NW L1W MW WB GM L3m	-30 to +50 °C	Temperature 750 °C, duration 30 s
911401548845	BY698X G5 LED150/CW L1W MW WB GM L3m	-30 to +50 °C	Temperature 750 °C, duration 30 s
911401548945	BY698X G5 LED200/NW L1W MW WB GM L3m	-30 to +50 °C	Temperature 750 °C, duration 30 s

Order Code	Full Product Name	Ambient	Glow-wire test
		temperature range	
911401549045	BY698X G5 LED200/CW L1W MW WB GM L3m	-30 to +50 °C	Temperature 750 °C, duration 30 s
911401549145	BY698X G5 LED250/NW L1W MW WB GM L3m	-30 to +50 °C	Temperature 750 °C, duration 30 s
911401549245	BY698X G5 LED250/CW L1W MW WB GM L3m	-30 to +50 °C	Temperature 750 °C, duration 30 s
911401549345	BY698X G5 LED300/NW L1W MW WB GM L3m	-30 to +50 °C	Temperature 750 °C, duration 30 s
911401549445	BY698X G5 LED300/CW L1W MW WB GM L3m	-30 to +50 °C	Temperature 750 °C, duration 30 s

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity	Luminous flux
			tolerance
911401550545	BY698X G5 LED105/NW L1W PIR WB GM	(0.386, 0.384) SDCM<5	+/-10%
911401550645	BY698X G5 LED105/CW L1W PIR WB GM	(0.317, 0.338) SDCM<5	+/-10%
911401550745	BY698X G5 LED150/NW L1W PIR WB GM	(0.386, 0.384) SDCM<5	+/-10%
911401550845	BY698X G5 LED150/CW L1W PIR WB GM	(0.317, 0.338) SDCM<5	+/-10%
911401550945	BY698X G5 LED200/NW L1W PIR WB GM	(0.386, 0.384) SDCM<5	+/-10%
911401551045	BY698X G5 LED200/CW L1W PIR WB GM	(0.317, 0.338) SDCM<5	+/-10%
911401551145	BY698X G5 LED250/NW L1W PIR WB GM	(0.386, 0.384) SDCM<5	+/-10%
911401551245	BY698X G5 LED250/CW L1W PIR WB GM	(0.317, 0.338) SDCM<5	+/-10%
911401551345	BY698X G5 LED300/NW L1W PIR WB GM	(0.386, 0.384) SDCM<5	+/-10%
911401551445	BY698X G5 LED300/CW L1W PIR WB GM	(0.317, 0.338) SDCM<5	+/-10%
911401552045	BY698X G5 LED105/NW L1W PIR WB GM L3m	(0.386, 0.384) SDCM<5	+/-10%
911401552145	BY698X G5 LED105/CW L1W PIR WB GM L3m	(0.317, 0.338) SDCM<5	+/-10%
911401552245	BY698X G5 LED150/NW L1W PIR WB GM L3m	(0.386, 0.384) SDCM<5	+/-10%
911401552345	BY698X G5 LED150/CW L1W PIR WB GM L3m	(0.317, 0.338) SDCM<5	+/-10%
911401552445	BY698X G5 LED200/NW L1W PIR WB GM L3m	(0.386, 0.384) SDCM<5	+/-10%
911401552545	BY698X G5 LED200/CW L1W PIR WB GM L3m	(0.317, 0.338) SDCM<5	+/-10%
911401552645	BY698X G5 LED250/NW L1W PIR WB GM L3m	(0.386, 0.384) SDCM<5	+/-10%

Order Code	Full Product Name	Initial chromaticity	Luminous flux
			tolerance
911401552745	BY698X G5 LED250/CW L1W PIR WB GM L3m	(0.317, 0.338) SDCM<5	+/-10%
911401552845	BY698X G5 LED300/NW L1W PIR WB GM L3m	(0.386, 0.384) SDCM<5	+/-10%
911401552945	BY698X G5 LED300/CW L1W PIR WB GM L3m	(0.317, 0.338) SDCM<5	+/-10%
911401526245	BY698P G5 LED105/NW PSU WB GC	(0.386, 0.384) SDCM<5	-10% / +10%
911401526345	BY698P G5 LED105/NW PSU NB GC	(0.386, 0.384) SDCM<5	-10% / +10%
911401526445	BY698P G5 LED105/CW PSU WB GC	(0.317, 0.338) SDCM<5	-10% / +10%
911401526545	BY698P G5 LED105/CW PSU NB GC	(0.317, 0.338) SDCM<5	-10% / +10%
911401526645	BY698P G5 LED150/NW PSU WB GC	(0.386, 0.384) SDCM<5	-10% / +10%
911401526745	BY698P G5 LED150/NW PSU NB GC	(0.386, 0.384) SDCM<5	-10% / +10%
911401526845	BY698P G5 LED150/CW PSU WB GC	(0.317, 0.338) SDCM<5	-10% / +10%
911401526945	BY698P G5 LED150/CW PSU NB GC	(0.317, 0.338) SDCM<5	-10% / +10%
911401527045	BY698P G5 LED200/NW PSU WB GC	(0.386, 0.384) SDCM<5	-10% / +10%
911401527145	BY698P G5 LED200/NW PSU NB GC	(0.386, 0.384) SDCM<5	-10% / +10%
911401527245	BY698P G5 LED200/CW PSU WB GC	(0.317, 0.338) SDCM<5	-10% / +10%
911401527345	BY698P G5 LED200/CW PSU NB GC	(0.317, 0.338) SDCM<5	-10% / +10%
911401527445	BY698P G5 LED250/NW PSU WB GC	(0.386, 0.384) SDCM<5	-10% / +10%
911401527545	BY698P G5 LED250/NW PSU NB GC	(0.386, 0.384) SDCM<5	-10% / +10%

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
911401527645	BY698P G5 LED250/CW PSU WB GC	(0.317, 0.338) SDCM<5	-10% / +10%
911401527745	BY698P G5 LED250/CW PSU NB GC	(0.317, 0.338) SDCM<5	-10% / +10%
911401527845	BY698P G5 LED300/NW PSU WB GC	(0.386, 0.384) SDCM<5	-10% / +10%
911401527945	BY698P G5 LED300/NW PSU NB GC	(0.386, 0.384) SDCM<5	-10% / +10%
911401528045	BY698P G5 LED300/CW PSU WB GC	(0.317, 0.338) SDCM<5	-10% / +10%
911401528145	BY698P G5 LED300/CW PSU NB GC	(0.317, 0.338) SDCM<5	-10% / +10%
911401528245	BY698P G5 LED105/NW PSU WB GM	(0.386, 0.384) SDCM<5	-10% / +10%
911401528345	BY698P G5 LED105/NW PSU NB GM	(0.386, 0.384) SDCM<5	-10% / +10%
911401528445	BY698P G5 LED105/CW PSU WB GM	(0.317, 0.338) SDCM<5	-10% / +10%
911401528545	BY698P G5 LED105/CW PSU NB GM	(0.317, 0.338) SDCM<5	-10% / +10%
911401528645	BY698P G5 LED150/NW PSU WB GM	(0.386, 0.384) SDCM<5	-10% / +10%
911401528745	BY698P G5 LED150/NW PSU NB GM	(0.386, 0.384) SDCM<5	-10% / +10%
911401528845	BY698P G5 LED150/CW PSU WB GM	(0.317, 0.338) SDCM<5	-10% / +10%
911401528945	BY698P G5 LED150/CW PSU NB GM	(0.317, 0.338) SDCM<5	-10% / +10%
911401529045	BY698P G5 LED200/NW PSU WB GM	(0.386, 0.384) SDCM<5	-10% / +10%
911401529145	BY698P G5 LED200/NW PSU NB GM	(0.386, 0.384) SDCM<5	-10% / +10%
911401529245	BY698P G5 LED200/CW PSU WB GM	(0.317, 0.338) SDCM<5	-10% / +10%
911401529345	BY698P G5 LED200/CW PSU NB GM	(0.317, 0.338) SDCM<5	-10% / +10%
911401529445	BY698P G5 LED250/NW PSU WB GM	(0.386, 0.384) SDCM<5	-10% / +10%
911401529545	BY698P G5 LED250/NW PSU NB GM	(0.386, 0.384) SDCM<5	-10% / +10%
911401529645	BY698P G5 LED250/CW PSU WB GM	(0.317, 0.338) SDCM<5	-10% / +10%
911401529745	BY698P G5 LED250/CW PSU NB GM	(0.317, 0.338) SDCM<5	-10% / +10%
911401529845	BY698P G5 LED300/NW PSU WB GM	(0.386, 0.384) SDCM<5	-10% / +10%
911401529945	BY698P G5 LED300/NW PSU NB GM	(0.386, 0.384) SDCM<5	-10% / +10%
911401530045	BY698P G5 LED300/CW PSU WB GM	(0.317, 0.338) SDCM<5	-10% / +10%

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
911401530145	BY698P G5 LED300/CW PSU NB GM	(0.317, 0.338) SDCM<5	-10% / +10%
911401530245	BY698P G5 LED200/840 PSU WB CAU	(0.386, 0.384) SDCM<5	-10% / +10%
911401530345	BY698P G5 LED250/840 PSU WB CAU	(0.386, 0.384) SDCM<5	-10% / +10%
911401530445	BY698P G5 LED300/840 PSU WB CAU	(0.386, 0.384) SDCM<5	-10% / +10%
911401530545	BY698P G5 LED200/840 PSU WB CAU CL	(0.386, 0.384) SDCM<5	-10% / +10%
911401530645	BY698P G5 LED200/850 PSU WB CAU CL	(0.386, 0.384) SDCM<5	-10% / +10%
911401530745	BY698P G5 LED250/840 PSU WB CAU CL	(0.386, 0.384) SDCM<5	-10% / +10%
911401530845	BY698P G5 LED250/850 PSU WB CAU CL	- SDCM<5	-10% / +10%
911401530945	BY698P G5 LED300/840 PSU WB CAU CL	(0.386, 0.384) SDCM<5	-10% / +10%
911401531045	BY698P G5 LED300/850 PSU WB CAU CL	- SDCM<5	-10% / +10%
911401531145	BY698P G5 LED105/NW PSD WB GC	(0.386, 0.384) SDCM<5	-10% / +10%
911401531245	BY698P G5 LED105/NW PSD NB GC	(0.386, 0.384) SDCM<5	-10% / +10%
911401531345	BY698P G5 LED105/CW PSD WB GC	(0.317, 0.338) SDCM<5	-10% / +10%
911401531445	BY698P G5 LED105/CW PSD NB GC	(0.317, 0.338) SDCM<5	-10% / +10%
911401531545	BY698P G5 LED150/NW PSD WB GC	(0.386, 0.384) SDCM<5	-10% / +10%
911401531645	BY698P G5 LED150/NW PSD NB GC	(0.386, 0.384) SDCM<5	-10% / +10%
911401531745	BY698P G5 LED150/CW PSD WB GC	(0.317, 0.338) SDCM<5	-10% / +10%
911401531845	BY698P G5 LED150/CW PSD NB GC	(0.317, 0.338) SDCM<5	-10% / +10%
911401531945	BY698P G5 LED200/NW PSD WB GC	(0.386, 0.384) SDCM<5	-10% / +10%
911401532045	BY698P G5 LED200/NW PSD NB GC	(0.386, 0.384) SDCM<5	-10% / +10%
911401532145	BY698P G5 LED200/CW PSD WB GC	(0.317, 0.338) SDCM<5	-10% / +10%
911401532245	BY698P G5 LED200/CW PSD NB GC	(0.317, 0.338) SDCM<5	-10% / +10%
911401532345	BY698P G5 LED250/NW PSD WB GC	(0.386, 0.384) SDCM<5	-10% / +10%
911401532445	BY698P G5 LED250/NW PSD NB GC	(0.386, 0.384) SDCM<5	-10% / +10%
911401532545	BY698P G5 LED250/CW PSD WB GC	(0.317, 0.338) SDCM<5	-10% / +10%

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
911401532645	BY698P G5 LED250/CW PSD NB GC	(0.317, 0.338) SDCM<5	-10% / +10%
911401532745	BY698P G5 LED300/NW PSD WB GC	(0.386, 0.384) SDCM<5	-10% / +10%
911401532845	BY698P G5 LED300/NW PSD NB GC	(0.386, 0.384) SDCM<5	-10% / +10%
911401532945	BY698P G5 LED300/CW PSD WB GC	(0.317, 0.338) SDCM<5	-10% / +10%
911401533045	BY698P G5 LED300/CW PSD NB GC	(0.317, 0.338) SDCM<5	-10% / +10%
911401533145	BY698P G5 LED105/NW PSD WB GM	(0.386, 0.384) SDCM<5	-10% / +10%
911401533245	BY698P G5 LED105/NW PSD NB GM	(0.386, 0.384) SDCM<5	-10% / +10%
911401533345	BY698P G5 LED105/CW PSD WB GM	(0.317, 0.338) SDCM<5	-10% / +10%
911401533445	BY698P G5 LED105/CW PSD NB GM	(0.317, 0.338) SDCM<5	-10% / +10%
911401533545	BY698P G5 LED150/NW PSD WB GM	(0.386, 0.384) SDCM<5	-10% / +10%
911401533645	BY698P G5 LED150/NW PSD NB GM	(0.386, 0.384) SDCM<5	-10% / +10%
911401533745	BY698P G5 LED150/CW PSD WB GM	(0.317, 0.338) SDCM<5	-10% / +10%
911401533845	BY698P G5 LED150/CW PSD NB GM	(0.317, 0.338) SDCM<5	-10% / +10%
911401533945	BY698P G5 LED200/NW PSD WB GM	(0.386, 0.384) SDCM<5	-10% / +10%
911401534045	BY698P G5 LED200/NW PSD NB GM	(0.386, 0.384) SDCM<5	-10% / +10%
911401534145	BY698P G5 LED200/CW PSD WB GM	(0.317, 0.338) SDCM<5	-10% / +10%
911401534245	BY698P G5 LED200/CW PSD NB GM	(0.317, 0.338) SDCM<5	-10% / +10%
911401534345	BY698P G5 LED250/NW PSD WB GM	(0.386, 0.384) SDCM<5	-10% / +10%
911401534445	BY698P G5 LED250/NW PSD NB GM	(0.386, 0.384) SDCM<5	-10% / +10%
911401534545	BY698P G5 LED250/CW PSD WB GM	(0.317, 0.338) SDCM<5	-10% / +10%
911401534645	BY698P G5 LED250/CW PSD NB GM	(0.317, 0.338) SDCM<5	-10% / +10%
911401534745	BY698P G5 LED300/NW PSD WB GM	(0.386, 0.384) SDCM<5	-10% / +10%
911401534845	BY698P G5 LED300/NW PSD NB GM	(0.386, 0.384) SDCM<5	-10% / +10%
911401534945	BY698P G5 LED300/CW PSD WB GM	(0.317, 0.338) SDCM<5	-10% / +10%
911401535045	BY698P G5 LED300/CW PSD NB GM	(0.317, 0.338) SDCM<5	-10% / +10%

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
911401535145	BY698P G5 LED200/840 PSD WB CAU	(0.386, 0.384) SDCM<5	-10% / +10%
911401535245	BY698P G5 LED250/840 PSD WB CAU	(0.386, 0.384) SDCM<5	-10% / +10%
911401535445	BY698P G5 LED300/840 PSD WB CAU	(0.386, 0.384) SDCM<5	-10% / +10%
911401535545	BY698P G5 LED105/NW PSU WB LA	(0.386, 0.384) SDCM<5	-10% / +10%
911401535645	BY698P G5 LED105/CW PSU WB LA	(0.317, 0.338) SDCM<5	-10% / +10%
911401535745	BY698P G5 LED150/NW PSU WB LA	(0.386, 0.384) SDCM<5	-10% / +10%
911401535845	BY698P G5 LED150/CW PSU WB LA	(0.317, 0.338) SDCM<5	-10% / +10%
911401535945	BY698P G5 LED200/NW PSU WB LA	(0.386, 0.384) SDCM<5	-10% / +10%
911401536045	BY698P G5 LED200/NW PSU NB LA	(0.386, 0.384) SDCM<5	-10% / +10%
911401536145	BY698P G5 LED200/CW PSU WB LA	(0.317, 0.338) SDCM<5	-10% / +10%
911401536245	BY698P G5 LED200/CW PSU NB LA	(0.317, 0.338) SDCM<5	-10% / +10%
911401536345	BY698P G5 LED250/NW PSU WB LA	(0.386, 0.384) SDCM<5	-10% / +10%
911401536445	BY698P G5 LED250/NW PSU NB LA	(0.386, 0.384) SDCM<5	-10% / +10%
911401536545	BY698P G5 LED250/CW PSU WB LA	(0.317, 0.338) SDCM<5	-10% / +10%
911401536645	BY698P G5 LED250/CW PSU NB LA	(0.317, 0.338) SDCM<5	-10% / +10%
911401536745	BY698P G5 LED300/NW PSU WB LA	(0.386, 0.384) SDCM<5	-10% / +10%
911401536845	BY698P G5 LED300/NW PSU NB LA	(0.386, 0.384) SDCM<5	-10% / +10%
911401536945	BY698P G5 LED300/CW PSU WB LA	(0.317, 0.338) SDCM<5	-10% / +10%
911401537045	BY698P G5 LED300/CW PSU NB LA	(0.317, 0.338) SDCM<5	-10% / +10%
911401537145	BY698P G5 LED105/NW PSD WB LA	(0.386, 0.384) SDCM<5	-10% / +10%
911401537245	BY698P G5 LED105/CW PSD WB LA	(0.317, 0.338) SDCM<5	-10% / +10%
911401537345	BY698P G5 LED150/NW PSD WB LA	(0.386, 0.384) SDCM<5	-10% / +10%
911401537445	BY698P G5 LED150/CW PSD WB LA	(0.317, 0.338) SDCM<5	-10% / +10%
911401537545	BY698P G5 LED200/NW PSD WB LA	(0.386, 0.384) SDCM<5	-10% / +10%
911401537645	BY698P G5 LED200/NW PSD NB LA	(0.386, 0.384) SDCM<5	-10% / +10%

GreenPerform Highbay G5

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
911401537745	BY698P G5 LED200/CW PSD WB LA	(0.317, 0.338) SDCM<5	-10% / +10%
911401537845	BY698P G5 LED200/CW PSD NB LA	(0.317, 0.338) SDCM<5	-10% / +10%
911401537945	BY698P G5 LED250/NW PSD WB LA	(0.386, 0.384) SDCM<5	-10% / +10%
911401538045	BY698P G5 LED250/NW PSD NB LA	(0.386, 0.384) SDCM<5	-10% / +10%
911401538145	BY698P G5 LED250/CW PSD WB LA	(0.317, 0.338) SDCM<5	-10% / +10%
911401538245	BY698P G5 LED250/CW PSD NB LA	(0.317, 0.338) SDCM<5	-10% / +10%
911401538345	BY698P G5 LED300/NW PSD WB LA	(0.386, 0.384) SDCM<5	-10% / +10%
911401538445	BY698P G5 LED300/NW PSD NB LA	(0.386, 0.384) SDCM<5	-10% / +10%
911401538545	BY698P G5 LED300/CW PSD WB LA	(0.317, 0.338) SDCM<5	-10% / +10%
911401538645	BY698P G5 LED300/CW PSD NB LA	(0.317, 0.338) SDCM<5	-10% / +10%
911401538745	BY698P G5 LED105/NW PSU WB GM L3m	(0.386, 0.384) SDCM<5	-10% / +10%
911401538845	BY698P G5 LED105/NW PSU NB GM L3m	(0.386, 0.384) SDCM<5	-10% / +10%
911401538945	BY698P G5 LED105/CW PSU WB GM L3m	(0.317, 0.338) SDCM<5	-10% / +10%
911401539045	BY698P G5 LED105/CW PSU NB GM L3m	(0.317, 0.338) SDCM<5	-10% / +10%
911401539145	BY698P G5 LED150/NW PSU WB GM L3m	(0.386, 0.384) SDCM<5	-10% / +10%
911401539245	BY698P G5 LED150/NW PSU NB GM L3m	(0.386, 0.384) SDCM<5	-10% / +10%
911401539345	BY698P G5 LED150/CW PSU WB GM L3m	(0.317, 0.338) SDCM<5	-10% / +10%
911401539445	BY698P G5 LED150/CW PSU NB GM L3m	(0.317, 0.338) SDCM<5	-10% / +10%
911401539545	BY698P G5 LED200/NW PSU WB GM L3m	(0.386, 0.384) SDCM<5	-10% / +10%
911401539645	BY698P G5 LED200/NW PSU NB GM L3m	(0.386, 0.384) SDCM<5	-10% / +10%
911401539745	BY698P G5 LED200/CW PSU WB GM L3m	(0.317, 0.338) SDCM<5	-10% / +10%
911401539845	BY698P G5 LED200/CW PSU NB GM L3m	(0.317, 0.338) SDCM<5	-10% / +10%
911401539945	BY698P G5 LED250/NW PSU WB GM L3m	(0.386, 0.384) SDCM<5	-10% / +10%
91140154004	BY698P G5 LED250/NW PSU NB GM L3m	(0.386, 0.384) SDCM<5	-10% / +10%
911401540145	BY698P G5 LED250/CW PSU WB GM L3m	(0.317, 0.338) SDCM<5	-10% / +10%

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
911401540245	BY698P G5 LED250/CW PSU NB GM L3m	(0.317, 0.338) SDCM<5	-10% / +10%
911401540345	BY698P G5 LED300/NW PSU WB GM L3m	(0.386, 0.384) SDCM<5	-10% / +10%
911401540445	BY698P G5 LED300/NW PSU NB GM L3m	(0.386, 0.384) SDCM<5	-10% / +10%
911401540545	BY698P G5 LED300/CW PSU WB GM L3m	(0.317, 0.338) SDCM<5	-10% / +10%
911401540645	BY698P G5 LED300/CW PSU NB GM L3m	(0.317, 0.338) SDCM<5	-10% / +10%
911401540745	BY690P LED105/NW PSU WB GC	-	-10% / +10%
911401540845	BY690P LED105/CW PSU WB GC	-	-10% / +10%
911401540945	BY690P LED150/NW PSU WB GC	-	-10% / +10%
911401541045	BY690P LED150/CW PSU WB GC	-	-10% / +10%
911401541145	BY690P LED200/NW PSU WB GC	-	-10% / +10%
911401541245	BY690P LED200/CW PSU WB GC	-	-10% / +10%
911401541345	BY690P LED250/NW PSU WB GC	-	-10% / +10%
911401541445	BY690P LED250/CW PSU WB GC	-	-10% / +10%
911401541545	BY690P LED300/NW PSU WB GC	-	-10% / +10%
911401541645	BY690P LED300/CW PSU WB GC	-	-10% / +10%
911401541745	BY690P LED105/NW PSU WB GM	-	-10% / +10%
911401541845	BY690P LED105/CW PSU WB GM	-	-10% / +10%
911401541945	BY690P LED150/NW PSU WB GM	-	-10% / +10%
911401542045	BY690P LED150/CW PSU WB GM	-	-10% / +10%
911401542145	BY690P LED200/NW PSU WB GM	-	-10% / +10%
911401542245	BY690P LED200/CW PSU WB GM	-	-10% / +10%
911401542345	BY690P LED250/NW PSU WB GM	-	-10% / +10%
911401542445	BY690P LED250/CW PSU WB GM	-	-10% / +10%
911401542545	BY690P LED300/NW PSU WB GM	-	-10% / +10%
911401542645	BY690P LED300/CW PSU WB GM	-	-10% / +10%
91140158094	BY698P G5 LED105/NW PSU WB 4	(0.386, 0.384) SDCM<5	-10% / +10%
911401581044	BY698P G5 LED105/NW PSU NB TW	(0.386, 0.384) SDCM<5	-10% / +10%
911401581144	BY698P G5 LED105/CW PSU WB TW	(0.317, 0.338) SDCM<5	-10% / +10%

GreenPerform Highbay G5

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
911401581244	BY698P G5 LED105/CW PSU NB TW	(0.317, 0.338) SDCM<5	-10% / +10%
911401581344	BY698P G5 LED150/NW PSU WB TW	(0.386, 0.384) SDCM<5	-10% / +10%
911401581444	BY698P G5 LED150/NW PSU NB TW	(0.386, 0.384) SDCM<5	-10% / +10%
911401581544	BY698P G5 LED150/CW PSU WB TW	(0.317, 0.338) SDCM<5	-10% / +10%
911401581644	BY698P G5 LED150/CW PSU NB TW	(0.317, 0.338) SDCM<5	-10% / +10%
911401581744	BY698P G5 LED200/NW PSU WB TW	(0.386, 0.384) SDCM<5	-10% / +10%
911401581844	BY698P G5 LED200/NW PSU NB TW	(0.386, 0.384) SDCM<5	-10% / +10%
911401581944	BY698P G5 LED200/CW PSU WB TW	(0.317, 0.338) SDCM<5	-10% / +10%
911401582044	BY698P G5 LED200/CW PSU NB TW	(0.317, 0.338) SDCM<5	-10% / +10%
911401582144	BY698P G5 LED250/NW PSU WB TW	(0.386, 0.384) SDCM<5	-10% / +10%
911401582244	BY698P G5 LED250/NW PSU NB TW	(0.386, 0.384) SDCM<5	-10% / +10%
911401582344	BY698P G5 LED250/CW PSU WB TW	(0.317, 0.338) SDCM<5	-10% / +10%
911401582444	BY698P G5 LED250/CW PSU NB TW	(0.317, 0.338) SDCM<5	-10% / +10%
911401582544	BY698P G5 LED300/NW PSU WB TW	(0.386, 0.384) SDCM<5	-10% / +10%
911401582644	BY698P G5 LED300/NW PSU NB TW	(0.386, 0.384) SDCM<5	-10% / +10%
911401582744	BY698P G5 LED300/CW PSU WB TW	(0.317, 0.338) SDCM<5	-10% / +10%
911401582844	BY698P G5 LED300/CW PSU NB TW	(0.317, 0.338) SDCM<5	-10% / +10%
911401543245	BY698X G5 LED150/NW Connected WB GC	(0.386, 0.384) SDCM<5	-10% / +10%
911401543345	BY698X G5 LED150/CW Connected WB GC	(0.317, 0.338) SDCM<5	-10% / +10%
911401543445	BY698X G5 LED200/NW Connected WB GC	(0.386, 0.384) SDCM<5	-10% / +10%
911401543545	BY698X G5 LED200/CW Connected WB GC	(0.317, 0.338) SDCM<5	-10% / +10%
911401543645	BY698X G5 LED250/NW Connected WB GC	(0.386, 0.384) SDCM<5	-10% / +10%
911401543745	BY698X G5 LED250/CW Connected WB GC	(0.317, 0.338) SDCM<5	-10% / +10%
911401543845	BY698X G5 LED300/NW Connected WB GC	(0.386, 0.384) SDCM<5	-10% / +10%
911401543945	BY698X G5 LED300/NW Connected NB GC	(0.386, 0.384) SDCM<5	-10% / +10%

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
911401544045	BY698X G5 LED300/CW Connected WB GC	(0.317, 0.338) SDCM<5	-10% / +10%
911401544145	BY698X G5 LED300/CW Connected NB GC	(0.317, 0.338) SDCM<5	-10% / +10%
911401544245	BY698X G5 LED150/NW Connected WB GM	(0.386, 0.384) SDCM<5	-10% / +10%
911401544345	BY698X G5 LED150/NW Connected NB GM	(0.386, 0.384) SDCM<5	-10% / +10%
911401544445	BY698X G5 LED150/CW Connected WB GM	(0.317, 0.338) SDCM<5	-10% / +10%
911401544545	BY698X G5 LED150/CW Connected NB GM	(0.317, 0.338) SDCM<5	-10% / +10%
911401544645	BY698X G5 LED200/NW Connected WB GM	(0.386, 0.384) SDCM<5	-10% / +10%
911401544745	BY698X G5 LED200/NW Connected NB GM	(0.386, 0.384) SDCM<5	-10% / +10%
911401544845	BY698X G5 LED200/CW Connected WB GM	(0.317, 0.338) SDCM<5	-10% / +10%
911401544945	BY698X G5 LED200/CW Connected NB GM	(0.317, 0.338) SDCM<5	-10% / +10%
911401545045	BY698X G5 LED250/NW Connected WB GM	(0.386, 0.384) SDCM<5	-10% / +10%
911401545145	BY698X G5 LED250/NW Connected NB GM	(0.386, 0.384) SDCM<5	-10% / +10%
911401545245	BY698X G5 LED250/CW Connected WB GM	(0.317, 0.338) SDCM<5	-10% / +10%
911401545345	BY698X G5 LED250/CW Connected NB GM	(0.317, 0.338) SDCM<5	-10% / +10%
911401545445	BY698X G5 LED300/NW Connected WB GM	(0.386, 0.384) SDCM<5	-10% / +10%
911401545545	BY698X G5 LED300/NW Connected NB GM	(0.386, 0.384) SDCM<5	-10% / +10%
911401545645	BY698X G5 LED300/CW Connected WB GM	(0.317, 0.338) SDCM<5	-10% / +10%
911401545745	BY698X G5 LED300/CW Connected NB GM	(0.317, 0.338) SDCM<5	-10% / +10%
911401545845	BY698X G5 LED200/840 Connected WB CAU	(0.386, 0.384) SDCM<5	-10% / +10%
911401545945	BY698X G5 LED250/840 Connected WB CAU	(0.386, 0.384) SDCM<5	-10% / +10%
911401546045	BY698X G5 LED300/840 Connected WB CAU	(0.386, 0.384) SDCM<5	-10% / +10%
911401546145	BY698X G5 LED150/NW Connected WB LA	(0.386, 0.384) SDCM<5	-10% / +10%
911401546245	BY698X G5 LED150/CW Connected WB LA	(0.317, 0.338) SDCM<5	-10% / +10%
911401546345	BY698X G5 LED200/NW Connected WB LA	(0.386, 0.384) SDCM<5	-10% / +10%
911401546445	BY698X G5 LED200/NW Connected NB LA	(0.386, 0.384) SDCM<5	-10% / +10%

GreenPerform Highbay G5

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
911401546545	BY698X G5 LED200/CW Connected WB LA	(0.317, 0.338) SDCM<5	-10% / +10%
911401546645	BY698X G5 LED200/CW Connected NB LA	(0.317, 0.338) SDCM<5	-10% / +10%
911401546745	BY698X G5 LED250/NW Connected WB LA	(0.386, 0.384) SDCM<5	-10% / +10%
911401546845	BY698X G5 LED250/NW Connected NB LA	(0.386, 0.384) SDCM<5	-10% / +10%
911401546945	BY698X G5 LED250/CW Connected WB LA	(0.317, 0.338) SDCM<5	-10% / +10%
911401547045	BY698X G5 LED250/CW Connected NB LA	(0.317, 0.338) SDCM<5	-10% / +10%
911401547145	BY698X G5 LED300/NW Connected WB LA	(0.386, 0.384) SDCM<5	-10% / +10%
911401547245	BY698X G5 LED300/NW Connected NB LA	(0.386, 0.384) SDCM<5	-10% / +10%
911401547345	BY698X G5 LED300/CW Connected WB LA	(0.317, 0.338) SDCM<5	-10% / +10%
911401547445	BY698X G5 LED300/CW Connected NB LA	(0.317, 0.338) SDCM<5	-10% / +10%
911401547545	BY698X G5 LED105/NW L1W MW WB GM	(0.386, 0.384) SDCM<5	+/-10%
911401547645	BY698X G5 LED105/CW L1W MW WB GM	(0.317, 0.338) SDCM<5	+/-10%
911401547745	BY698X G5 LED150/NW L1W MW WB GM	(0.386, 0.384) SDCM<5	+/-10%
911401547845	BY698X G5 LED150/CW L1W MW WB GM	(0.317, 0.338) SDCM<5	+/-10%
911401547945	BY698X G5 LED200/NW L1W MW WB GM	(0.386, 0.384) SDCM<5	+/-10%

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
911401548045	BY698X G5 LED200/CW L1W MW WB GM	(0.317, 0.338) SDCM<5	+/-10%
911401548145	BY698X G5 LED250/NW L1W MW WB GM	(0.386, 0.384) SDCM<5	+/-10%
911401548245	BY698X G5 LED250/CW L1W MW WB GM	(0.317, 0.338) SDCM<5	+/-10%
911401548345	BY698X G5 LED300/NW L1W MW WB GM	(0.386, 0.384) SDCM<5	+/-10%
911401548445	BY698X G5 LED300/CW L1W MW WB GM	(0.317, 0.338) SDCM<5	+/-10%
911401548545	BY698X G5 LED105/NW L1W MW WB GM L3m	(0.386, 0.384) SDCM<5	+/-10%
911401548645	BY698X G5 LED105/CW L1W MW WB GM L3m	(0.317, 0.338) SDCM<5	+/-10%
911401548745	BY698X G5 LED150/NW L1W MW WB GM L3m	(0.386, 0.384) SDCM<5	+/-10%
911401548845	BY698X G5 LED150/CW L1W MW WB GM L3m	(0.317, 0.338) SDCM<5	+/-10%
911401548945	BY698X G5 LED200/NW L1W MW WB GM L3m	(0.386, 0.384) SDCM<5	+/-10%
911401549045	BY698X G5 LED200/CW L1W MW WB GM L3m	(0.317, 0.338) SDCM<5	+/-10%
911401549145	BY698X G5 LED250/NW L1W MW WB GM L3m	(0.386, 0.384) SDCM<5	+/-10%
911401549245	BY698X G5 LED250/CW L1W MW WB GM L3m	(0.317, 0.338) SDCM<5	+/-10%
911401549345	BY698X G5 LED300/NW L1W MW WB GM L3m	(0.386, 0.384) SDCM<5	+/-10%
911401549445	BY698X G5 LED300/CW L1W MW WB GM L3m	(0.317, 0.338) SDCM<5	+/-10%

