



Just light that you can install and forget

Economy stick

Entry non-covered energy saving lamp, Long life with low energy consumption.
Product consists of Philips quality at everyday low price

Benefits

- Best "value for money" Energy saver
- Save your money with long life-time and high energy efficiency compare to incandescent lamp
- Flicker-free start & Fast run up

Features

- Long-Life and Energy saving alternative to Incandescent lamps
- Fast Run-up
- Recommended ambient temperature range to ensure almost constant light output (>90%): between 0°C and +50°C

Application

- Designed for incandescent lamp replacement in consumer applications where the lamp is not directly visible, especially suitable for indoor applications in functional areas
- Not suitable for use with dimmers or electronic gear

Warnings and Safety

- Breaking a lamp is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a closed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Compact fluorescent lamps have to be treated as special waste, they must be taken to your local waste facilities for recycling. The European Lighting Industry has set up an infrastructure, capable of recycling mercury, other metals, glass etc.


Economy stick

Versions



8718291216810 - RFT

Dimensional drawing



Product	D (max)	C (max)	F (max)
23 W (102 W) E27 Warm white Non-dimmable Stick energy saving bulb	36.0 mm	160 mm	48.4 mm

