



The original!

MASTER PL-S 2 Pin

MASTER PL-S is an efficient low-wattage compact fluorescent lamp, typically used for decorative and orientation purposes. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. The 2-pin version is designed for operation on electromagnetic gear and is provided with a plug-in/pull-out lamp base

Benefits

- Optimal light performance for short or long operation per switch-on
- Optimal light performance for short or long operation per switch-on
- Multiple light color choice
- Multiple light color choice
- Good color rendering (CRI >80)
- Good color rendering (CRI >80)

Features

- 2-pin base with a housing incorporating the special instant starter and capacitor
- 2-pin base with a housing incorporating the special instant starter and capacitor
- Fluorescent tri-phosphor technology
- Fluorescent tri-phosphor technology
- Low light depreciation over lamp life
- Low light depreciation over lamp life

Application

- Application
- Application
- Designed for use in hotels, restaurants, theatres and homes
- Designed for use in hotels, restaurants, theatres and homes
- Suitable for use in signs, corridors, security and orientation lighting
- Suitable for use in signs, corridors, security and orientation lighting

MASTER PL-S 2 Pin

Warnings and Safety


- Use only with electromagnetic control gear
- Use only with electromagnetic control gear
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position
- Dimming is not possible
- Dimming is not possible
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Versions



GLIM2012503 Wioleta Sadowska

Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-S 7W/865/2P 1CT/10	28 mm	13 mm	97 mm	113 mm	135 mm
MASTER PL-S 9W/827/2P 1CT/10	28 mm	13 mm	129 mm	145 mm	167 mm
MASTER PL-S 9W/865/2P 1CT/10	28 mm	13 mm	97 mm	113 mm	135 mm

MASTER PL-S 2 Pin

General Information	
Cap-Base	G23
Light Technical	
Color rendering index (CRI)	82
Controls and Dimming	
Dimmable	No
Approval and Application	
Mercury (Hg) Content (Nom)	1.4 mg

Light Technical

Order Code	Full Product Name	Color Designation	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
927935686565	MASTER PL-S 7W/ 865/2P 1CT/10	Cool Daylight	6500 K	56.3 lm/W	400 lm
927936082765	MASTER PL-S 9W/ White	Incandescent	2700 K	67 lm/W	600 lm

Order Code	Full Product Name	Color Designation	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
927935686565	MASTER PL-S 7W/ 865/2P 1CT/10	Cool Daylight	6500 K	56.3 lm/W	400 lm
927936086565	MASTER PL-S 9W/ 865/2P 1CT/10	Cool Daylight	6500 K	62 lm/W	540 lm

Operating and Electrical

Order Code	Full Product Name	Lamp Current (Nom)	Voltage (Nom)	Power Consumption
927935686565	MASTER PL-S 7W/ 865/2P 1CT/10	0.175 A	46 V	7.1 W
927936082765	MASTER PL-S 9W/ 827/2P 1CT/10	0.170 A	-	8.7 W

Order Code	Full Product Name	Lamp Current (Nom)	Voltage (Nom)	Power Consumption
927936086565	MASTER PL-S 9W/ 865/2P 1CT/10	0.170 A	60 V	8.6 W

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
927935686565	MASTER PL-S 7W/865/2P 1CT/10	-
927936082765	MASTER PL-S 9W/827/2P 1CT/10	11 kWh

Order Code	Full Product Name	Energy Consumption kWh/1000 h
927936086565	MASTER PL-S 9W/865/2P 1CT/10	-

MASTER PL-S 2 Pin

