



The affordable LEDspot solution

CorePro LEDspot MV

CorePro LEDspots are a perfect fit for spot lighting and deliver warm halogen-like light. They are compatible with most existing fixtures with a GU10 or E14 holder and are designed as a retrofit replacement for halogen or incandescent spots. LEDlamps deliver huge energy savings and minimize maintenance cost.

Benefits

- Warm white light
- Up to 80% energy saving compared with halogen lamps
- Lower maintenance costs
- Broad compatibility with transformers

Features

- Easy retrofit
- Lifetime of 15,000 hours
- Compatible with an extensive range of dimmers
- UV- and IR-free light
- Free of mercury and hazardous materials

Application

- Hotels, restaurants, bars, cafés, museums, shops
- Lobbies, corridors, stairwells, washrooms, reception areas , exhibitions, display cabinets

CorePro LEDspot MV

Versions






CLA LEDspotMV ND 5W PAR16 GU10



CorePro LEDspot MV 25W GU10 830 36D

Dimensional drawing



Product	D	C
Essential LED 4.6-50W GU10 865 36D	50 mm	54 mm

Product	D	C
Corepro LEDspot 550lm GU10 830 120D	50 mm	54 mm
Corepro LEDspot 550lm GU10 840 120D	50 mm	54 mm
Corepro LEDspot 550lm GU10 865 120D	50 mm	54 mm

Product	D	C
Corepro LEDspot 670lm GU10 830 60D	50 mm	54 mm
Corepro LEDspot 730lm GU10 840 60D	50 mm	54 mm

CorePro LEDspot MV

General Information	
Cap-Base	GU10
Switching Cycle	50,000
Light Technical	
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Line Frequency	50 to 60 Hz
Starting Time (Nom)	0.5 s
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Shape	PAR16

General Information

Order Code	Full Product Name	Nominal lifetime
30875600	Corepro LEDspot 550lm GU10 830 120D	15,000 hour(s)
30865700	Corepro LEDspot 550lm GU10 840 120D	15,000 hour(s)
30867100	Corepro LEDspot 550lm GU10 865 120D	15,000 hour(s)
76161800	Essential LED 4.6-50W GU10 865 36D	15,000 hour(s)
81333101	Corepro LEDspot 670lm GU10 830 60D	25,000 hour(s)
81335501	Corepro LEDspot 730lm GU10 840 60D	25,000 hour(s)

Light Technical (1/2)

		Correlated Color			
Order Code	Full Product Name	Beam Angle (Nom)	Temperature (Nom)	Color Code	Luminous Flux
30875600	Corepro LEDspot 550lm GU10 830 120D	120 degree(s)	3000 K	830	550 lm
30865700	Corepro LEDspot 550lm GU10 840 120D	120 degree(s)	4000 K	840	550 lm
30867100	Corepro LEDspot 550lm GU10 865 120D	120 degree(s)	6500 K	865	550 lm

		Correlated Color			
Order Code	Full Product Name	Beam Angle (Nom)	Temperature (Nom)	Color Code	Luminous Flux
76161800	Essential LED 4.6-50W GU10 865 36D	36 degree(s)	6500 K	865	430 lm
81333101	Corepro LEDspot 670lm GU10 830 60D	60 degree(s)	3000 K	830	670 lm
81335501	Corepro LEDspot 730lm GU10 840 60D	60 degree(s)	4000 K	840	730 lm

Light Technical (2/2)

Order Code	Full Product Name	Luminous Intensity (Nom)
30875600	Corepro LEDspot 550lm GU10 830 120D	-
30865700	Corepro LEDspot 550lm GU10 840 120D	-
30867100	Corepro LEDspot 550lm GU10 865 120D	-

Order Code	Full Product Name	Luminous Intensity (Nom)
76161800	Essential LED 4.6-50W GU10 865 36D	770 cd
81333101	Corepro LEDspot 670lm GU10 830 60D	750 cd
81335501	Corepro LEDspot 730lm GU10 840 60D	750 cd

Operating and Electrical

		Wattage	
Order Code	Full Product Name	Power Consumption	Equivalent
30875600	Corepro LEDspot 550lm GU10 830 120D	4.9 W	-
30865700	Corepro LEDspot 550lm GU10 840 120D	4.9 W	-
30867100	Corepro LEDspot 550lm GU10 865 120D	4.9 W	-

		Wattage	
Order Code	Full Product Name	Power Consumption	Equivalent
76161800	Essential LED 4.6-50W GU10 865 36D	4.6 W	50 W
81333101	Corepro LEDspot 670lm GU10 830 60D	6.7 W	90 W
81335501	Corepro LEDspot 730lm GU10 840 60D	6.7 W	100 W

CorePro LEDspot MV

Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
30875600	Corepro LEDspot 550lm GU10 830 120D	85 °C
30865700	Corepro LEDspot 550lm GU10 840 120D	85 °C
30867100	Corepro LEDspot 550lm GU10 865 120D	85 °C

Order Code	Full Product Name	T-Case Maximum (Nom)
76161800	Essential LED 4.6-50W GU10 865 36D	80 °C
81333101	Corepro LEDspot 670lm GU10 830 60D	75 °C
81335501	Corepro LEDspot 730lm GU10 840 60D	75 °C



Mechanical and Housing

Order Code	Full Product Name	Bulb Finish
30875600	Corepro LEDspot 550lm GU10 830 120D	-
30865700	Corepro LEDspot 550lm GU10 840 120D	-
30867100	Corepro LEDspot 550lm GU10 865 120D	-


Order Code	Full Product Name	Bulb Finish
76161800	Essential LED 4.6-50W GU10 865 36D	Clear
81333101	Corepro LEDspot 670lm GU10 830 60D	-
81335501	Corepro LEDspot 730lm GU10 840 60D	-

Approval and Application


Order Code	Full Product Name	Ambient temperature range	Energy Consumption kWh/1000 h
30875600	Corepro LEDspot 550lm GU10 830 120D	-	5 kWh
30865700	Corepro LEDspot 550lm GU10 840 120D	-	5 kWh
30867100	Corepro LEDspot 550lm GU10 865 120D	-	5 kWh
76161800	Essential LED 4.6-50W GU10 865 36D	-20 °C to 45 °C	-
81333101	Corepro LEDspot 670lm GU10 830 60D	-	7 kWh
81335501	Corepro LEDspot 730lm GU10 840 60D	-	7 kWh




Accent Diagrams



Accent Diagram - Essential LED 4.6-50W GU10
865 36D




Accent Diagram - Corepro LEDspot 730lm GU10
840 60D




Accent Diagram - Corepro LEDspot 670lm GU10
830 60D


Beam Diagrams



Beam diagram - Essential LED 4.6-50W GU10
865 36D



Beam diagram - Corepro LEDspot 730lm GU10
840 60D



Beam diagram - Corepro LEDspot 670lm GU10
830 60D

