



Product Description

MASTER PL-C 2 Pin

Energy-saving compact fluorescent lamps. Compact long-arc low-pressure mercury discharge lamp. Envelope consists of 4 parallel narrow fluorescent tubes

Benefits

- Optimal light performance for short or long operation per switch on
- Long life and sustainable light output

Features

- 2-pin base with a housing incorporating the special instant starter and capacitor
- Lamp characteristics are influenced by operating conditions and control gear used
- Dimming is not possible

Application

- Designed for general or supplementary lighting in professional or home environments
- Recessed or surface-mounted downlighters, wall units, table lamps and pendant lamps

Warnings and Safety

- Use only with electromagnetic control gear
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position
- Dimming is not possible
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


MASTER PL-C 2 Pin

Versions



LPPR PLC2P 26W

Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-C 10W/827/2P 1CT/5X10BOX	27.1 mm	27.1 mm	75.5 mm	95.0 mm	117.4 mm
MASTER PL-C 10W/840/2P 1CT/5X10BOX	27.1 mm	27.1 mm	75.5 mm	95.0 mm	117.4 mm
MASTER PL-C 26W/830/2P 1CT/5X10BOX	27.1 mm	27.1 mm	130.5 mm	149.0 mm	171.4 mm

Controls and Dimming	
Dimmable	No
Approval and Application	
Mercury (Hg) Content (Nom)	1.4 mg

General Information

Order Code	Full Product Name	Cap-Base
927903882701	MASTER PL-C 10W/827/2P 1CT/5X10BOX	G24d-1
927903884002	MASTER PL-C 10W/840/2P 1CT/5X10BOX	G24d-1

Order Code	Full Product Name	Cap-Base
927906183001	MASTER PL-C 26W/830/2P 1CT/5X10BOX	G24d-3

Light Technical

Order Code	Full Product Name	Color Designation	Correlated Color	Color rendering	Luminous Efficacy (rated)	Luminous Flux
			Temperature (Nom)	index (CRI)	(Nom)	
927903882701	MASTER PL-C 10W/827/2P 1CT/5X10BOX	Incandescent White	2700 K	>80	60 lm/W	600 lm
927903884002	MASTER PL-C 10W/840/2P 1CT/5X10BOX	Cool White (CW)	4000 K	82	60 lm/W	600 lm
927906183001	MASTER PL-C 26W/830/2P 1CT/5X10BOX	Warm White (WW)	3000 K	82	68 lm/W	1,800 lm

Operating and Electrical

MASTER PL-C 2 Pin

Order Code	Full Product Name	Lamp Current	
		(Nom)	Power Consumption
927903882701	MASTER PL-C 10W/827/2P 1CT/5X10BOX	0.190 A	10.0 W
927903884002	MASTER PL-C 10W/840/2P 1CT/5X10BOX	0.190 A	10.0 W

Order Code	Full Product Name	Lamp Current	
		(Nom)	Power Consumption
927906183001	MASTER PL-C 26W/830/2P 1CT/5X10BOX	0.335 A	26.5 W

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/
		1000 h
927903882701	MASTER PL-C 10W/827/2P 1CT/ 5X10BOX	13 kWh
927903884002	MASTER PL-C 10W/840/2P 1CT/ 5X10BOX	13 kWh

Order Code	Full Product Name	Energy Consumption kWh/
		1000 h
927906183001	MASTER PL-C 26W/830/2P 1CT/ 5X10BOX	32 kWh

