



# 10-15% more efficient!

## MASTER PL-C 2 Pin

MASTER PL-C is an efficient medium-wattage compact fluorescent lamp, typically used in general downlights for retail, hospitality and office applications. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. The 2-pin version is designed for operation on electromagnetic gear and is provided with a plug-in/pull-out lamp base.

### Benefits

- Optimal light performance for short or long operation per switch-on
- Multiple light color choice
- Good color rendering (CRI >80)

### Features

- 2-pin base with a housing incorporating the special instant starter
- Fluorescent tri-phosphor technology
- Low light depreciation over lamp life

### Application

- Designed for general or supplementary lighting in professional or home environments
- Recessed or surface-mounted downlighters, wall units, table lamps and pendant lamps

### Warnings and Safety

- Use only with electromagnetic control gear
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position
- Dimming is not possible
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

MASTER PL-C 2 Pin

Versions



LPPR PLC2P 10W




LPPR PLC2P 13W



LPPR PLC2P 26W

Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-C 10W/827/2P 1CT/5X10BOX	27.1 mm	27.1 mm	75.5 mm	95.0 mm	117.4 mm
MASTER PL-C 13W/827/2P 1CT/5X10BOX	27.1 mm	27.1 mm	97.5 mm	117.0 mm	139.4 mm
MASTER PL-C 13W/840/2P 1CT/5X10BOX	27.1 mm	27.1 mm	97.5 mm	117.0 mm	139.4 mm
MASTER PL-C 26W/865/2P 1CT/5X10BOX	27.1 mm	27.1 mm	130.5 mm	149.0 mm	171.4 mm

Controls and Dimming	
Dimmable	No
Approval and Application	
Mercury (Hg) Content (Max)	1.4 mg
Mercury (Hg) Content (Nom)	1.4 mg

General Information

Order Code	Full Product Name	Cap-Base
927903882740	MASTER PL-C 10W/827/2P 1CT/5X10BOX	G24d-1
927904882740	MASTER PL-C 13W/827/2P 1CT/5X10BOX	G24d-1

Order Code	Full Product Name	Cap-Base
927904884040	MASTER PL-C 13W/840/2P 1CT/5X10BOX	G24d-1
927906186540	MASTER PL-C 26W/865/2P 1CT/5X10BOX	G24d-3

Light Technical

Order Code	Full Product Name	Chromaticity Coordinate X	Chromaticity Coordinate Y	Color Designation	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
		(Nom)	(Nom)					
927903882740	MASTER PL-C 10W/827/2P 1CT/5X10BOX	0.463	0.42	Incandescent White	2700 K	82	60 lm/W	600 lm
927904882740	MASTER PL-C 13W/827/2P 1CT/5X10BOX	0.463	0.42	Incandescent White	2700 K	82	69 lm/W	925 lm

## MASTER PL-C 2 Pin

Order Code	Full Product Name	Chromaticity	Chromaticity	Color Designation	Correlated Color Temperature (Nom)	Color	Luminous Efficacy (rated) (Nom)	Luminous Flux
		Coordinate X (Nom)	Coordinate Y (Nom)			rendering index (CRI)		
927904884040	MASTER PL-C 13W/840/2P 1CT/5X10BOX	0.38	0.38	Cool White (CW)	4000 K	80	69 lm/W	925 lm
927906186540	MASTER PL-C 26W/865/2P 1CT/5X10BOX	0.313	0.337	Cool Daylight	6500 K	80	66 lm/W	1,740 lm

### Operating and Electrical

Order Code	Full Product Name	Lamp Current	Power Consumption
		(Nom)	
927903882740	MASTER PL-C 10W/827/2P 1CT/5X10BOX	0.190 A	10.4 W
927904882740	MASTER PL-C 13W/827/2P 1CT/5X10BOX	0.170 A	13.8 W

Order Code	Full Product Name	Lamp Current	Power Consumption
		(Nom)	
927904884040	MASTER PL-C 13W/840/2P 1CT/5X10BOX	0.170 A	13.8 W
927906186540	MASTER PL-C 26W/865/2P 1CT/5X10BOX	0.335 A	26.5 W

### Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/
		1000 h
927903882740	MASTER PL-C 10W/827/2P 1CT/5X10BOX	11 kWh
927904882740	MASTER PL-C 13W/827/2P 1CT/5X10BOX	14 kWh

Order Code	Full Product Name	Energy Consumption kWh/
		1000 h
927904884040	MASTER PL-C 13W/840/2P 1CT/5X10BOX	14 kWh
927906186540	MASTER PL-C 26W/865/2P 1CT/5X10BOX	27 kWh

