



# Product Description

## MASTER PL-C 4 Pin

Energy-saving compact fluorescent lamps. Compact long-arc low-pressure mercury discharge lamp. Envelope consists of 4 parallel narrow fluorescent tubes

### Benefits

- Optimal light performance for short or long operation per switch on
- Long life and sustainable light output

### Features

- 4-pin base without starter and capacitor
- Lamp characteristics are influenced by operating conditions and control gear used
- Dimming is possible

### Application

- Designed for general or supplementary lighting in professional or home environments
- Recessed or surface-mounted downlighters, wall units, table lamps and pendant lamps

### Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

# MASTER PL-C 4 Pin

## Versions




LPPR PLC4P 18W



LPPR PLC4P 26W

## Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-C 13W/827/4P 1CT/5X10BOX	27.1 mm	27.1 mm	97.5 mm	117.0 mm	131.9 mm
MASTER PL-C 13W/830/4P 1CT/5X10BOX	27.1 mm	27.1 mm	97.5 mm	117.0 mm	131.9 mm
MASTER PL-C 18W/827/4P 1CT/5X10BOX	27.1 mm	27.1 mm	109.5 mm	128.0 mm	142.9 mm
MASTER PL-C 26W/840/4P 1CT/5X10BOX	27.1 mm	27.1 mm	130.5 mm	149.0 mm	163.9 mm

### Controls and Dimming

Dimmable	Yes
----------	-----

### Approval and Application

Mercury (Hg) Content (Max)	1.4 mg
Mercury (Hg) Content (Nom)	1.4 mg

## General Information

Order Code	Full Product Name	Cap-Base
62326370	MASTER PL-C 13W/827/4P 1CT/5X10BOX	G24q-1
62331770	MASTER PL-C 13W/830/4P 1CT/5X10BOX	G24q-1

Order Code	Full Product Name	Cap-Base
62327070	MASTER PL-C 18W/827/4P 1CT/5X10BOX	G24q-2
62336270	MASTER PL-C 26W/840/4P 1CT/5X10BOX	G24q-3

## Light Technical

Order Code	Full Product Name	Chromaticity	Chromaticity	Color Designation	Correlated Color Temperature (Nom)	Color	Luminous Efficacy (rated) (Nom)	Luminous Flux
		Coordinate X (Nom)	Coordinate Y (Nom)			rendering index (CRI)		
62326370	MASTER PL-C 13W/827/4P 1CT/5X10BOX	0.463	0.42	Incandescent White	2700 K	82	69 lm/W	925 lm
62331770	MASTER PL-C 13W/830/4P 1CT/5X10BOX	0.44	0.403	Warm White (WW)	3000 K	82	72 lm/W	925 lm

## MASTER PL-C 4 Pin

Order Code	Full Product Name	Chromaticity	Chromaticity	Color Designation	Correlated Color Temperature (Nom)	Color	Luminous Efficacy (rated) (Nom)	Luminous Flux
		Coordinate X (Nom)	Coordinate Y (Nom)			rendering index (CRI)		
62327070	MASTER PL-C 18W/827/4P 1CT/5X10BOX	0.463	0.42	Incandescent White	2700 K	82	67 lm/W	1,200 lm
62336270	MASTER PL-C 26W/840/4P 1CT/5X10BOX	0.38	0.38	Cool White (CW)	4000 K	80	67 lm/W	1,800 lm

### Operating and Electrical

Order Code	Full Product Name	Lamp Current	Power Consumption
		(Nom)	
62326370	MASTER PL-C 13W/827/4P 1CT/5X10BOX	0.170 A	13.8 W
62331770	MASTER PL-C 13W/830/4P 1CT/5X10BOX	0.170 A	13.8 W

Order Code	Full Product Name	Lamp Current	Power Consumption
		(Nom)	
62327070	MASTER PL-C 18W/827/4P 1CT/5X10BOX	0.230 A	18.4 W
62336270	MASTER PL-C 26W/840/4P 1CT/5X10BOX	0.335 A	27.4 W

### Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/
		1000 h
62326370	MASTER PL-C 13W/827/4P 1CT/5X10BOX	14 kWh
62331770	MASTER PL-C 13W/830/4P 1CT/5X10BOX	14 kWh

Order Code	Full Product Name	Energy Consumption kWh/
		1000 h
62327070	MASTER PL-C 18W/827/4P 1CT/5X10BOX	19 kWh
62336270	MASTER PL-C 26W/840/4P 1CT/5X10BOX	28 kWh

