



10-15% more efficient!

MASTER PL-C 4 Pin

MASTER PL-C is an efficient medium-wattage compact fluorescent lamp, typically used in general downlights for retail, hospitality and office applications. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. The 4-pin version is designed for operation on electronic HF control gear with integrated pre-heat and is provided with a plug-in/pull-out lamp base.

Benefits

- Optimal light performance for short or long operation per switch-on
- Multiple light color choice
- Good color rendering (CRI >80)
- Dimming possible down to 10%

Features

- 4-pin base
- Fluorescent tri-phosphor technology
- Low light depreciation over lamp life

Application

- Designed for general or supplementary lighting in professional or home environments
- Recessed or surface-mounted downlighters, wall units, table lamps and pendant lamps

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


MASTER PL-C 4 Pin

Versions



26 W 4 Pin Non integrated
compact fluorescent - RFT

Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
26 W 4 Pin Cool white Non integrated compact fluorescent	27.1 mm	27.1 mm	130.5 mm	149.0 mm	163.9 mm

