



The alternative!

PL-Q 4 Pin

PL-Q is an efficient, square-shaped compact fluorescent lamp, typically used in decorative-lighting luminaires. While offering the advantage of energy-efficient operation, it also provides design freedom for flat ceiling or wall fixtures in particular, due to its low built-in height and uniform spread of light. The 4-pin version is designed for operation on electronic gear.

Benefits

- Low built-in height
- Multiple light color choice
- Good color rendering (CRI >80)
- Dimming possible down to 10%

Features

- 4-pin base
- Fluorescent tri-phosphor technology

Application


- Ideal for applications such as corridors, toilets, stairwells and reception areas

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

PL-Q 4 Pin

Dimensional drawing



Product	U (max)	D (max)	D1 (max)	C (max)	C1 (max)	F (max)	E (max)
PL-Q 28W/827/4P 1CT/10BOX	46.5 mm	18.9 mm	33 mm	203 mm	76 mm	41 mm	200 mm
PL-Q 28W/840/4P 1CT/10BOX	46.5 mm	18.9 mm	33 mm	203 mm	76 mm	41 mm	200 mm
PL-Q 38W/830/4P 1CT/10BOX	46.5 mm	18.9 mm	33 mm	203 mm	76 mm	41 mm	200 mm

General Information	
Cap-Base	GR10q
Light Technical	
Color rendering index (CRI)	81
Controls and Dimming	
Dimmable	Yes
Approval and Application	
Mercury (Hg) Content (Max)	3 mg
Mercury (Hg) Content (Nom)	4 mg

Light Technical

Order Code	Full Product Name	Chromaticity	Chromaticity	Correlated Color Temperature (Nom)	Luminous Efficacy	
		Coordinate X (Nom)	Coordinate Y (Nom)		(rated) (Nom)	Luminous Flux
927939382740	PL-Q 28W/827/4P 1CT/10BOX	0.463	0.42	Incandescent White 2700 K	73.2 lm/W	2,050 lm
927939384040	PL-Q 28W/840/4P 1CT/10BOX	0.38	0.38	Cool White (CW) 4000 K	73.2 lm/W	2,050 lm
927939483040	PL-Q 38W/830/4P 1CT/10BOX	0.44	0.403	Warm White (WW) 3000 K	75 lm/W	2,750 lm

Operating and Electrical

Order Code	Full Product Name	Lamp Current	Power Consumption
		(Nom)	
927939382740	PL-Q 28W/827/4P 1CT/10BOX	0.320 A	28.4 W
927939384040	PL-Q 28W/840/4P 1CT/10BOX	0.320 A	28.4 W

Order Code	Full Product Name	Lamp Current	Power Consumption
		(Nom)	
927939483040	PL-Q 38W/830/4P 1CT/10BOX	0.430 A	38.4 W

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
927939382740	PL-Q 28W/827/4P 1CT/10BOX	29 kWh
927939384040	PL-Q 28W/840/4P 1CT/10BOX	29 kWh

Order Code	Full Product Name	Energy Consumption kWh/1000 h
927939483040	PL-Q 38W/830/4P 1CT/10BOX	39 kWh

