



Philips Cleanroom: when light has to be hygienic, excellent quality and high- definition

Cleanroom CR350B

When operating a highly hygienic facility, the demands placed on light are very high and it must comply with strict standards; it must be easy to clean, dust-free, sealed and waterproof – all while offering exceptional optical performance. Philips CR350B Cleanroom luminaires are designed specifically for facilities where hygiene is critical, such as hospitals, laboratories, surgical and examination rooms, as well as applications in the pharmaceutical industry. These energy-efficient, durable cleanroom lighting solutions deliver excellent quality of light that complies with the strictest norms, as well as legislation that requires special IP65, easy-to-clean, dust-free luminaires. Thanks to excellent quality of light and colour rendering, Cleanroom luminaires also reduce eye strain. This can make all the difference in industries such as cleanroom production, graphics and textile manufacturing where high lumen and low glare light are so important.

Benefits

- Excellent quality of light
- Complies with cleanroom norms and legislation
- High reliability, low maintenance

Cleanroom CR350B



Features

- Fully IP65 and ENEC compliant
- Excellent colour rendering CRI >90
- Lumen output up to 6,000 lm
- Low glare UGR <19
- Surface-mounted bracket and safety cable available as an accessory

Application

- Surgical and examination rooms
- Laboratories and pharmaceutical facilities
- Cleanroom production areas

Dimensional drawing



Product details



Photo



Photo




Photo



Photo

Cleanroom CR350B

Product details



Photo



Photo

General Information

Driver included	Yes
Light source replaceable	No
Number of gear units	Unit
Service Tag	Yes

Light Technical

Beam angle of light source	120 degree(s)
Correlated Colour Temperature (Nom)	4000 K
Optic type	Wide beam

Operating and Electrical

Protection class IEC	Safety class I
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	No

Mechanical and Housing

Housing Colour	White
Mech. impact protection code	IK07
Ingress protection code	IP65

Approval and Application

Ambient temperature range	-20 to +35 °C
CE mark	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	-

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Light Technical

Order Code	Full Product Name	Colour rendering index (CRI)	Luminous efficacy (rated) (nom.)	Luminous Flux
79707200	CR350B LED40S/940 PSU W60L60 OC	>90	98 lm/W	4,000 lm
79708900	CR350B LED40S/840 PSD W60L60 OC	>80	108 lm/W	4,000 lm
79710200	CR350B LED40S/940 PSD W60L60 OC	>90	98 lm/W	4,000 lm
79713300	CR350B LED60S/940 PSU W60L60 OC	>90	100 lm/W	6,000 lm
79714000	CR350B LED60S/840 PSD W60L60 OC	>80	109 lm/W	6,000 lm
79716400	CR350B LED60S/940 PSD W60L60 OC	>90	100 lm/W	6,000 lm
79719500	CR350B LED40S/940 PSU W30L120 OC	>90	98 lm/W	4,000 lm
79720100	CR350B LED40S/840 PSD W30L120 OC	>80	108 lm/W	4,000 lm
79722500	CR350B LED40S/940 PSD W30L120 OC	>90	98 lm/W	4,000 lm
79725600	CR350B LED60S/940 PSU W30L120 OC	>90	100 lm/W	6,000 lm
79726300	CR350B LED60S/840 PSD W30L120 OC	>80	109 lm/W	6,000 lm
79728700	CR350B LED60S/940 PSD W30L120 OC	>90	100 lm/W	6,000 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
79707200	CR350B LED40S/940 PSU W60L60 OC	41 W

Order Code	Full Product Name	Power Consumption
79708900	CR350B LED40S/840 PSD W60L60 OC	37 W

Cleanroom CR350B

Order Code	Full Product Name	Power Consumption
79710200	CR350B LED40S/940 PSD W60L60 OC	41 W
79713300	CR350B LED60S/940 PSU W60L60 OC	60 W
79714000	CR350B LED60S/840 PSD W60L60 OC	55 W
79716400	CR350B LED60S/940 PSD W60L60 OC	60 W
79719500	CR350B LED40S/940 PSU W30L120 OC	41 W

Order Code	Full Product Name	Power Consumption
79720100	CR350B LED40S/840 PSD W30L120 OC	37 W
79722500	CR350B LED40S/940 PSD W30L120 OC	41 W
79725600	CR350B LED60S/940 PSU W30L120 OC	60 W
79726300	CR350B LED60S/840 PSD W30L120 OC	55 W
79728700	CR350B LED60S/940 PSD W30L120 OC	60 W

Controls and Dimming

Order Code	Full Product Name	Dimmable	Maximum dim level
79707200	CR350B LED40S/940 PSU W60L60 OC	No	Not applicable
79708900	CR350B LED40S/840 PSD W60L60 OC	Yes	1%
79710200	CR350B LED40S/940 PSD W60L60 OC	Yes	1%
79713300	CR350B LED60S/940 PSU W60L60 OC	No	Not applicable
79714000	CR350B LED60S/840 PSD W60L60 OC	Yes	1%
79716400	CR350B LED60S/940 PSD W60L60 OC	Yes	1%


Order Code	Full Product Name	Dimmable	Maximum dim level
79719500	CR350B LED40S/940 PSU W30L120 OC	No	Not applicable
79720100	CR350B LED40S/840 PSD W30L120 OC	Yes	1%
79722500	CR350B LED40S/940 PSD W30L120 OC	Yes	1%
79725600	CR350B LED60S/940 PSU W30L120 OC	No	Not applicable
79726300	CR350B LED60S/840 PSD W30L120 OC	Yes	1%
79728700	CR350B LED60S/940 PSD W30L120 OC	Yes	1%

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
79707200	CR350B LED40S/940 PSU W60L60 OC	(0.39, 0.38) SDCM <3
79708900	CR350B LED40S/840 PSD W60L60 OC	(0.38, 0.38) SDCM <3
79710200	CR350B LED40S/940 PSD W60L60 OC	(0.39, 0.38) SDCM <3
79713300	CR350B LED60S/940 PSU W60L60 OC	(0.39, 0.38) SDCM <3
79714000	CR350B LED60S/840 PSD W60L60 OC	(0.38, 0.38) SDCM <3
79716400	CR350B LED60S/940 PSD W60L60 OC	(0.39, 0.38) SDCM <3

Order Code	Full Product Name	Initial chromaticity
79719500	CR350B LED40S/940 PSU W30L120 OC	(0.39, 0.38) SDCM <3
79720100	CR350B LED40S/840 PSD W30L120 OC	(0.38, 0.38) SDCM <3
79722500	CR350B LED40S/940 PSD W30L120 OC	(0.39, 0.38) SDCM <3
79725600	CR350B LED60S/940 PSU W30L120 OC	(0.39, 0.38) SDCM <3
79726300	CR350B LED60S/840 PSD W30L120 OC	(0.38, 0.38) SDCM <3
79728700	CR350B LED60S/940 PSD W30L120 OC	(0.39, 0.38) SDCM <3

Polar Wide Diagrams






Polar Normal (separate) - null - 912401483355

Polar Normal (separate) - null - 912401483357

Polar Normal (separate) - null - 912401483360




Polar Wide Diagrams



Polar Normal (separate) - null - 912401483367

Polar Normal (separate) - null - 912401483366




Polar Normal (separate) - null - 912401483361



Polar Normal (separate) - null - 912401483372

Polar Normal (separate) - null - 912401483354

Polar Normal (separate) - null - 912401483373



Polar Normal (separate) - null - 912401483375

Polar Normal (separate) - null - 912401483369

Polar Normal (separate) - null - 912401483363

