



Philips Cleanroom: when light has to be hygienic, excellent quality and high- definition

Cleanroom CR350B

When operating a facility where the highest levels of hygiene are required, the demands placed on light are also very high. It must comply with strict standards; it must be easy to clean, dust-free, sealed and waterproof – all while offering exceptional optical performance. Philips Cleanroom CR350B luminaires are designed specifically for facilities where hygiene is critical, such as hospitals, laboratories, surgical and examination rooms, as well as applications in the pharmaceutical industry. These energy-efficient, durable cleanroom lighting solutions deliver excellent quality of light that complies with the strictest norms, as well as legislation that requires special IP65, easy-to-clean, dust-free luminaires. Thanks to excellent quality of light and colour rendering, these Philips cleanroom luminaires also reduce eye strain. This can make all the difference in industries such as cleanroom production, graphics and textile manufacturing where high lumen and low glare light are so important.

Benefits

- Excellent quality of light
- Complies with cleanroom norms and legislation
- High reliability, low maintenance

Cleanroom CR350B



Features

- Fully IP65 and ENEC compliant
- Excellent colour rendering CRI >90
- Lumen output up to 6,000 lm
- Low glare UGR <19
- Surface-mounted bracket and safety cable available as an accessory

Application

- Surgical and examination rooms
- Laboratories and pharmaceutical facilities
- Cleanroom production areas

Dimensional drawing



Product details



Photo



Photo




Photo



Photo

Cleanroom CR350B

Product details



Photo



Photo

General Information	
Driver included	Yes
Light source replaceable	No
Number of gear units	Unit
Service Tag	Yes
Light Technical	
Beam angle of light source	120 degree(s)
Correlated Colour Temperature (Nom)	4000 K
Colour rendering index (CRI)	>90
Optic type	Wide beam
Operating and Electrical	
Protection class IEC	Safety class I
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	No
Mechanical and Housing	
Housing Colour	White
Mech. impact protection code	IK09
Ingress protection code	IP65
Approval and Application	
Ambient temperature range	-20 to +35 °C
CE mark	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	-
Initial Performance (IEC Compliant)	
Initial chromaticity	(0.39, 0.38) SDCM <3
Luminous flux tolerance	+/-10%

Light Technical

Order Code	Full Product Name	Luminous efficacy (rated) (nom.)	Luminous Flux
912401483354	CR350B LED40S/940 PSU W60L60	98 lm/W	4,000 lm
912401483360	CR350B LED60S/940 PSU W60L60	100 lm/W	6,000 lm
912401483363	CR350B LED60S/940 PSD W60L60	100 lm/W	6,000 lm
912401483366	CR350B LED40S/940 PSU W30L120	98 lm/W	4,000 lm
912401483372	CR350B LED60S/940 PSU W30L120	100 lm/W	6,000 lm
912401483375	CR350B LED60S/940 PSD W30L120	100 lm/W	6,000 lm

Operating and Electrical

Cleanroom CR350B

Order Code	Full Product Name	Power Consumption
912401483354	CR350B LED40S/940 PSU W60L60	41 W
912401483360	CR350B LED60S/940 PSU W60L60	60 W
912401483363	CR350B LED60S/940 PSD W60L60	60 W




Order Code	Full Product Name	Power Consumption
912401483366	CR350B LED40S/940 PSU W30L120	41 W
912401483372	CR350B LED60S/940 PSU W30L120	60 W
912401483375	CR350B LED60S/940 PSD W30L120	60 W

Controls and Dimming

Order Code	Full Product Name	Dimmable	Maximum dim level
912401483354	CR350B LED40S/940 PSU W60L60	No	Not applicable
912401483360	CR350B LED60S/940 PSU W60L60	No	Not applicable
912401483363	CR350B LED60S/940 PSD W60L60	Yes	1%

Order Code	Full Product Name	Dimmable	Maximum dim level
912401483366	CR350B LED40S/940 PSU W30L120	No	Not applicable
912401483372	CR350B LED60S/940 PSU W30L120	No	Not applicable
912401483375	CR350B LED60S/940 PSD W30L120	Yes	1%




Polar Wide Diagrams



Polar Normal (separate) - null - 912401483360

Polar Normal (separate) - null - 912401483366

Polar Normal (separate) - null - 912401483372



Polar Normal (separate) - null - 912401483354

Polar Normal (separate) - null - 912401483375

Polar Normal (separate) - null - 912401483363

