



# Philips Cleanroom: when light has to be hygienic, excellent quality and high definition

## Cleanroom CR350B

When operating a facility where the highest levels of hygiene are required, the demands placed on light are also very high. It must comply with strict standards; it must be easy to clean, dust-free, sealed and waterproof – all while offering exceptional optical performance. Philips Cleanroom CR350B luminaires are designed specifically for facilities where hygiene is critical, such as hospitals, laboratories, surgical and examination rooms, as well as applications in the pharmaceutical industry. These energy-efficient, durable cleanroom lighting solutions deliver excellent quality of light that complies with the strictest norms, as well as legislation that requires special IP65, easy-to-clean, dust-free luminaires. Thanks to excellent quality of light and color rendering, these Philips cleanroom luminaires also reduce eye strain. This can make all the difference in industries such as cleanroom production, graphics and textile manufacturing where high lumen and low glare light are so important.

### Benefits

- Excellent quality of light
- Complies with cleanroom norms and legislation
- High reliability, low maintenance

# Cleanroom CR350B

## Features

- Fully IP65 and ENEC compliant
- Excellent color rendering CRI >90
- Lumen output up to 6000 lm
- Low glare UGR <19
- Surface-mounted bracket and safety cable available as an accessory

## Application

- Surgical and examination rooms
- Laboratories and pharmaceutical facilities
- Cleanroom production areas

## Versions





Photo



Photo

## Dimensional drawing



Cleanroom CR350B

Product details



Photo



Photo



Photo



Photo



Photo



Photo

Cleanroom CR350B

General Information	
Driver included	Yes
Light source replaceable	No
Number of gear units	1 unit
Service tag	Yes
Light Technical	
Beam angle of light source	120 degree(s)
Correlated Color Temperature (Nom)	4000 K
Optic type	Wide beam
Operating and Electrical	
Protection class IEC	Safety class I
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	No
Mechanical and Housing	
Housing Color	White
Mech. impact protection code	IK07
Ingress protection code	IP65
Approval and Application	
Ambient temperature range	-20 to +35 °C
CE mark	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	-
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

Light Technical

Order Code	Full Product Name	Color rendering	Luminous Efficacy (rated)	
		index (CRI)	(Nom)	Luminous Flux
912401483354	CR350B LED40S/940 PSU W60L60	>90	98 lm/W	4,000 lm
912401483355	CR350B LED40S/840 PSD W60L60	>80	108 lm/W	4,000 lm
912401483360	CR350B LED60S/940 PSU W60L60	>90	100 lm/W	6,000 lm
912401483366	CR350B LED40S/940 PSU W30L120	>90	98 lm/W	4,000 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
912401483354	CR350B LED40S/940 PSU W60L60	41 W
912401483355	CR350B LED40S/840 PSD W60L60	37 W

Order Code	Full Product Name	Power Consumption
912401483360	CR350B LED60S/940 PSU W60L60	60 W
912401483366	CR350B LED40S/940 PSU W30L120	41 W

Controls and Dimming

Order Code	Full Product Name	Dimmable	Maximum dim level
912401483354	CR350B LED40S/940 PSU W60L60	No	Not applicable
912401483355	CR350B LED40S/840 PSD W60L60	Yes	1%




Order Code	Full Product Name	Dimmable	Maximum dim level
912401483360	CR350B LED60S/940 PSU W60L60	No	Not applicable
912401483366	CR350B LED40S/940 PSU W30L120	No	Not applicable

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
912401483354	CR350B LED40S/940 PSU W60L60	(0.39, 0.38) SDCM <3
912401483355	CR350B LED40S/840 PSD W60L60	(0.38, 0.38) SDCM <3

Order Code	Full Product Name	Initial chromaticity
912401483360	CR350B LED60S/940 PSU W60L60	(0.39, 0.38) SDCM <3
912401483366	CR350B LED40S/940 PSU W30L120	(0.39, 0.38) SDCM <3


Polar Wide Diagrams



Polar Normal (separate) - null - 912401483355

Polar Normal (separate) - null - 912401483360

Polar Normal (separate) - null - 912401483366



Polar Normal (separate) - null - 912401483354

