



Simple, robust magnetic ballast

HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

The HID Basic Semi-Parallel ballast is an impregnated (HID standard) electromagnetic copper/iron ballast for use with an external ignitor for HID lamps.

Benefits

- Limited volume of ballast coil; also lightweight
- Simple installation and cabling

Features


- Orthocyclic winding process
- Ballasts equipped with screw terminal blocks as standard
- Earthing-while-mounting facility (HID Standard ballasts)
- Low watt losses

Application

- For use with SON and HPI (PLUS) lamps in road, public, area and industry lighting
- For use with MHN/CDM lamps in shop, lobby and city beautification applications
- HID-Basic ballasts should be restricted to built-in situations where relative humidity is limited.



HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

Versions



GPPR BCSONE 0001

Dimensional drawing



Operating and Electrical

Order Code	Full Product Name	Input Frequency	Input Voltage	Line Frequency
913710102016	BSN 150L 301I	60 Hz	220 V	60 Hz
913710102116	BSN 250L 301I	50 Hz	230 V	50 Hz
913710102850	BSN 250L 302I	50 Hz	230 V	50 Hz
913710103750	BSN 100L 300I	50 Hz	220 V	50 Hz

Product	D1	C1	A1	A2	B1
BSN 100L 300I	6.2 mm	51.5 mm	122.0 mm	107 mm	57.1 mm
BSN 100L 300I TS	6.2 mm	51.5 mm	122.0 mm	107 mm	57.1 mm
BSN 150L 300I TS	6.2 mm	64.5 mm	125.0 mm	110 mm	75.5 mm
BSN 150L 301I	6.3 mm	64.5 mm	150.0 mm	104.0 mm	72.5 mm
BSN 250L 300I TS	6.2 mm	64.5 mm	150.0 mm	135 mm	75.5 mm
BSN 250L 301I	6.3 mm	64.5 mm	150.0 mm	135.0 mm	72.5 mm
BSN 250L 302I	6.3 mm	64.5 mm	150.0 mm	129.0 mm	72.5 mm
BSN 400L 300I TS	6.2 mm	82 mm	165.0 mm	150 mm	96.5 mm
BSN 600L 300I TS.	6.2 mm	82 mm	175 mm	160 mm	96.5 mm
BSN 70L 300I	6.2 mm	51.5 mm	117.0 mm	102 mm	57.1 mm
BSN 70L 300I TS	6.2 mm	51.5 mm	117.0 mm	110 mm	57.1 mm
BSN 70L 301I	6.3 mm	51.5 mm	110.0 mm	89 mm	60.0 mm

Product	D1	C1	A1	A2	B1
BSNE 150L 300I TS	6.3 mm	64.5 mm	120.0 mm	99.0 mm	75.0 mm
BSNE 250L 300I TS	6.3 mm	64.5 mm	165.0 mm	144 mm	75.0 mm
BSNE 400L 300I TS	6.3 mm	82 mm	165.0 mm	144 mm	96.0 mm

HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

Order Code	Full Product Name	Input Frequency	Input Voltage	Line Frequency
913710109142	BSN 150L 300I TS	50 Hz	220 V	50 Hz
913710109342	BSN 250L 300I TS	50 Hz	220 V	50 Hz
913710109542	BSN 400L 300I TS	50 Hz	220 V	50 Hz
913713206016	BSN 70L 301I	60 Hz	220 V	60 Hz

Order Code	Full Product Name	Input Frequency	Input Voltage	Line Frequency
913713019359	BSNE 150L 300I TS	50 Hz	220 V	50 Hz
913713019459	BSNE 250L 300I TS	50 Hz	220 V	50 Hz
913713019559	BSNE 400L 300I TS	50 Hz	220 V	50 Hz

